



















NUMBER	PART NAME	MATERIAL	COLOR	QUANTITY
TABLE 2	12P 0.64 YESC KAIZEN UNSEALED FEMALE CONNECTOR HOUSING	PBT-GF	SEE TABLE 2	1
583	12P 0.64 YESC KAIZEN UNSEALED FEMALE CONNECTOR FRONT HOLDER	PBT-GF	NATURAL	1
TABLE 2	12P 0.64 YESC KAIZEN UNSEALED FEMALE CONNECTOR HOUSING	PBT-GF	SEE TABLE 2	1
583	12P 0.64 YESC KAIZEN UNSEALED FEMALE CONNECTOR FRONT HOLDER	PBT-GF	NATURAL	1
01-50	0.64 KAIZEN UNSEALED CONNECTOR CPA	PA66-GF	RED	1

EMBLEM PART NUMBER	HOUSING PART NUMBER	KEYWAY	 CPA	COLOR	 MASS (g)	YAZAKI INLINE MATING PART NUMBER
9052-30	7183-9046-30	A	N	BLACK	(4.52)	TBD
5491-30	7183-9046-30	A	Y	BLACK	(4.83)	TBD
9053-40	7183-9047-40	B	N	LIGHT GRAY	(4.52)	TBD
9054-80	7183-9048-80	C	N	BROWN	(4.52)	TBD
9055-60	7183-9049-60	D	N	GREEN	(4.52)	TBD
9056-90	7183-9050-90	E	N	BLUE	(4.52)	TBD
3-9057	7183-9051	F	N	NATURAL	(4.52)	TBD



- NOTES:**
1. PARTS MUST BE PURCHASED FROM YAZAKI.
 2. PARTS MUST BE FREE OF FLASH AND IMPERFECTIONS THAT AFFECT FUNCTION.
 3. APPLICABLE TERMINAL: SEE 7116-4618-02:R DRAWING (YESC KAIZEN 0.64).
MAX WIRE OD: 1.90mm.
 4. PART DESIGNED TO MEET USCAR INTERFACE: 064-U-012-2-A03.
 5. MATING PART NUMBER: SEE TABLE 2.
 6. PART SATISFIES USCAR-2, REV.4, MAY 2004, (T2M1/S1/MF3) WITH THE FOLLOWING EXCEPTIONS:
 - A. SECTION 5.4.2 LOCK DEFLECTION FORCE= 7.71N-70.00N.
 - B. SECTION 5.4.2 CONNECTOR DISENGAGE FORCE (LOCK DISABLED) = 86.90N MAX.
 7. PART TO COMPLY WITH YPES-31-038 REQUIREMENTS.
 8. THIS DIMENSION SHOWS THE PRE-SET POSITION OF THE TPA.
 9. THIS DIMENSION SHOWS THE PRE-SET POSITION OF THE CPA.
 10. HANDLING MANUAL NUMBER: YPES-15-711.
 11. THIS DRAWING IS TO BE USED FOR INTERNAL YAZAKI PSW SUBMISSION.



A	5-24-2017	ADDED NEW VIEWS, UPDATED NOTES	C17-A573	A.P.
-	10-14-2011	NEW	C11-A867	M.R.
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE											
	10MAX	50MAX	100MAX	250MAX	250OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.2	±0.3	±0.5	±2.5	±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4					±3°	0.1
(C)	±0.3	±0.5	±0.8	±1.4	±2					±3°	0.15
SPECIFIED										MASS SEE TABLE 2 (g)	

CUSTOMER							MATL. SPEC.		SEE TABLE 1		TREAT. & FIN.		N/A	
CUSTOMER PART NO.				CUSTOMER DWG NO.			NAME 12P 0.64 YESC KAIZEN UNSEALED							
OFFICE YNA				TRIAL PART NO.										
VENDOR							FEMALE CONNECTOR SUB-ASSEMBLY							
VENDOR NO.														
DWG TYPE R		DWG SOURCE 7283-9052-30/M/2		DWG DATE 10-14-2011		UNIT mm	SCL 5/1	ANGLE 3	PART NO. CH. CODE 7283-9052-30 ETC.					
APPROVED		CHECKED		CHECKED		DESIGN DESMOND ONG 05-12-2005		DRAWN ALISON PANEK 06-09-17		DWG NO. 7283-9052-30:R		SET DWG NO. N/A		
YAZAKI CORPORATION														

