







3	YAZAKI SUBASSY NO.	NO.	YAZAKI PART NUMBER	4	PART NAME	5	MATERIAL	COLOR	QTY
		3	7137-1298-50		PACKING (M)		SILICONE RUBBER	RED	1
	7286-1657-30	2	7158-6832-70		FRONT HOLDER (M)		PBI-GF15	YELLOW	1
		1	7185-1657-30		TOP HOUSING (M)		PBI-GF15	BLACK	1

NOTES:

1. MATERIAL: SEE TABLE;
2. COLOR: SEE TABLE;
3. APPLICABLE TERMINALS: TERMINAL No. 211CL251160 AND 211CL252160;
4. APPLICABLE SEALS: SEE TABLE;
5. THIS DIMENSION SHOWS THE PRESET POSITION OF FRONT HOLDER ON THE SUBASSEMBLY;
6. MATING PART ACCORDING DRAWING: 19201EV10NT1;
7. FOR GENERAL GEOMETRICAL TOLERANCE SEE TABLE (ECCENT=ECCENTRICITY);
8. HANDLING MANUAL: TBD;
9. PRODUCT STANDARD: TBD;
10. THE MATERIALS USED IN THIS PRODUCT SHOULD BE IN CONFORMITY WITH REQUIREMENTS OF EU ELY 2000/53/EC DIRECTIVE AND ASSOCIATED DOCUMENTS AND "CONTROL STANDARD FOR CHEMICAL SUBSTANCE (Y65-L21-010)".
11. PRINTED COPIES ARE UNCONTROLLED. THEY ARE POTENTIALLY OUT-OF-DATE AND INVALID. DATABASE IS MASTER.



ISOMETRIC VIEW
(SCALE 1:1)

SECTION A-A

Δ	08/10/30	CHANGED FORM AND MAT	Y08-0196	V.M.
Δ	08/01/23	CHANGED FORM	E08-0538	V.M.
Δ	01/01/04	NEW	E07-0504	V.M.

LET	DATE	REVISION RECORD	NO.	CHKD
			1	

GENERAL TOLERANCE

SPECIFIED	10MAX	50MAX	100MAX	250MAX	2500V	ANGLE	ECCENT	
	A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1
	B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1
	C	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15
MASS								

CUSTOMER PART NO.	CUSTOMER DWG NO.	MAT. SPEC.	SEE NOTES	TREAT. & FIN.	ISSUE MARK
OFFICE YEL-K	TRIAL PART NO.	NAME 1.5 SICMA3 SYSTEM CONNECTOR			
VENDOR NO.		10P (M) SUBASSY			
DWG. TYPE	DWG. SOURCE	DWG. DATE	UNIT	SCL	ANGLE
N	NEW	07/01/05	mm	2/1	3
APPROVED	CHECKED	DESIGN	DRAWN	PART NO. 7286-1657-30	
STERN LEN R. RESMAN V. VAKHOTIC R. JORIC T. REBIC				CH. CODE	DWG NO. 7286-1657-30:R
18/08/2008					07/01/07108/11/26
YAZAKI CORPORATION					SET DWG NO.