



1

2



3

STD LIB-SW2016

SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	PART NAME	MATERIAL	COLOR	QTY.
7298-1853-10	①	7198-1853-10	HS 025 2P SEALED HOUSING FEMALE	PBT	DARK GLAY	1
	②	7137-3186-80	HS 025 2P SEALED PACKING	SILICONE RUBBER	BROWN	1



ISOMETRIC



SEC. A-A

注記

1. かん合相手品番 : 7282-2090-30 ETC.
2. 適用端子品番 : 7116-4415-02, 7116-4416-02, 7116-4417-02
3. 適用ゴム栓品番 : 7158-3165-90, 7158-3166-60, 7158-3167-80
7158-3168-80
4. 適用防水栓品番 : 7158-3169-40

NOTES

1. MATING PART NO. : 7282-2090-30 ETC.
2. APPLICABLE TERMINAL NO. : 7116-4415-02, 7116-4416-02, 7116-4417-02
3. APPLICABLE WIRE SEAL PART NO. : 7158-3165-90, 7158-3166-60, 7158-3167-80
7158-3168-80
4. APPLICABLE SEALING PLUG PART NO. : 7158-3169-40

GENERAL TOLERANCE											
	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75					±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±2.5	±3°	0.1
©	±0.3	±0.5	±0.8	±1.4	±2					±3°	0.15

ISSUE MARK

								CUSTOMER	MATL. SPEC.					SEE TABLE		TREAT. & FIN.					
								CUSTOMER PART NO.													
								CUSTOMER DWG NO.													
	2018/07/17		NEW			C18-P220		Y. M		OFFICE			TRIAL PART NO. or PRODUCT NO.					NAME		HS 025 2P SEALED HOUSING	
LET	DATE		REVISION RECORD			NO.		CHKD		VENDOR											
GENERAL TOLERANCE								VENDOR NO.										SUB ASSEMBLY FEMALE			
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE		DWG DATE	UNIT	SCL	ANGLE	PART NO.	7298-1853-10					
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.5°	0.1	R	NEW		2018/07/17	mm	2:1	3	CH. CODE						
B	±0.2	±0.3	±0.55	±0.95	±1.4	±1.0°	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		DWG NO.	7298-1853-10:R		SET DWG NO.				
C	±0.3	±0.5	±0.8	±1.4	±2	±1.5°	0.15	S. KODAMA		N. KOBAYASHI		H. ANMA		Y. MAEDA							
SPECIFIED						MASS		2018/07/17		2018/07/17		2018/07/17		2018/07/02		2018/07/17					
						(3.2) g															
																		YAZAKI Corporation			