







1	2	3	4	5	6	7																																																																																																		
(5/1)				SUB-ASSEMBLY PART NUMBER		KEYWAY	NO.	PART NUMBER	PART NAME			MATERIAL	COLOR	QUANTITY																																																																																										
				7298-6354-30		A	①	7198-6354-30	8P HYBRID (6Px1.2mm + 2PxMINI COAX) UNSEALED FEMALE HOUSING	PBT-GF15	BLACK	1																																																																																												
							②	7172-1886	8P HYBRID (6Px1.2mm + 2PxMINI COAX) UNSEALED FEMALE ISL	PBT-GF15	NATURAL	1																																																																																												
							③	7172-1336-50	SMALL 1.2mm SYSTEM UNSEALED CPA	PBT-GF15	RED	1																																																																																												
 <p>7198-6354-30 KEYWAY A</p> <p>EXPLDED VIEW (2/1)</p>				 <p>FRONT ISOMETRIC VIEW (2/1)</p>		 <p>REAR ISOMETRIC VIEW (2/1)</p>																																																																																																		
 <p>(24.40)</p> <p>(22.35)</p> <p>(18.65)</p> <p>(20.50)</p> <p>(16.45)</p> <p>(5.43)</p> <p>(4.15)</p> <p>(12.70)</p> <p>(7.62)</p> <p>(2.54)</p> <p>(1.05~2.50) (SEE NOTE 8)</p>		 <p>(1.025~2.175) (SEE NOTE 7)</p> <p>(5.00)</p> <p>(18.65)</p> <p>SECTION A-A</p>		 <p>CAVITY 1 CAVITY 6</p> <p>CAVITY 7 CAVITY 8</p> <p>>PBT-GF15<</p>		<p>RECOMMENDED PASS-THROUGH HOLE DIMENSION (1mm CLEARANCE ALL AROUND) (2/1)</p> <p>NOTES:</p> <ol style="list-style-type: none"> PARTS MUST BE PURCHASED FROM YAZAKI. PARTS MUST BE FREE OF FLASH AND IMPERFECTIONS THAT AFFECT FUNCTION. APPLICABLE TERMINAL: SEE 7196-1367-02-R DRAWING (1.2mm YCO) OR 13543112 DRAWING (APTV 1.2mm OCS) OR S1208153 DRAWING (SUMITOMO 1.2mm) MAX WIRE OD: 1.90mm SEE AMK12A-1025 DRAWING (ROSENBERGER HFM) MAX WIRE OD: 2.90mm MATING PART NUMBER: 7297-6353-30 PART SATISFIES GMW3191, MARCH 2019, (T2/V1/S1/MF3) PART TO COMPLY WITH YPES-31-038 REQUIREMENTS. THIS DIMENSION SHOWS THE PRE-SET POSITION OF THE ISL. THIS DIMENSION SHOWS THE PRE-SET POSITION OF THE CPA. THIS DRAWING IS TO BE USED FOR INTERNAL YAZAKI PSW SUBMISSION. HANDLING MANUAL NUMBER: YPES-15-2037 																																																																																																		
<p>11-24-2021</p> <p>NEW</p> <p>C21-A847</p> <p>F.R.</p>		<p>REVISION RECORD</p> <p>NO.</p> <p>CHKD</p>		<p>GENERAL TOLERANCE</p> <table border="1"> <thead> <tr> <th></th> <th>10MAX</th> <th>50MAX</th> <th>100MAX</th> <th>250MAX</th> <th>250OVR</th> <th>R5 MAX</th> <th>R10 MAX</th> <th>R20 MAX</th> <th>R20 OVR</th> <th>ANGLE</th> <th>ECENT</th> <th>DWG TYPE</th> <th>DWG SOURCE</th> <th>DWG DATE</th> <th>UNIT</th> <th>SCL</th> <th>ANGLE</th> <th>PART NO.</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>± 0.15</td> <td>± 0.20</td> <td>± 0.30</td> <td>± 0.50</td> <td>± 0.75</td> <td></td> <td>± 0.20</td> <td>± 0.30</td> <td>± 0.50</td> <td>± 2.50</td> <td>$\pm 3^\circ$</td> <td>0.1</td> <td>R</td> <td>7298-6354-30.M</td> <td>11-24-2021</td> <td>mm</td> <td>5/1</td> <td>3</td> <td>7298-6354-30</td> </tr> <tr> <td>B</td> <td>± 0.20</td> <td>± 0.30</td> <td>± 0.55</td> <td>± 0.95</td> <td>± 1.40</td> <td></td> <td>± 0.20</td> <td>± 0.30</td> <td>± 0.50</td> <td>± 2.50</td> <td>$\pm 3^\circ$</td> <td>0.1</td> <td>APPROVED</td> <td>CHECKED</td> <td>CHECKED</td> <td>DESIGN</td> <td>DRAWN</td> <td>7298-6354-30:R</td> </tr> <tr> <td>C</td> <td>± 0.30</td> <td>± 0.50</td> <td>± 0.80</td> <td>± 1.40</td> <td>± 2.00</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>$\pm 3^\circ$</td> <td>0.15</td> <td></td> <td></td> <td></td> <td>DALE</td> <td>FERNANDA</td> <td></td> </tr> <tr> <td></td> <td colspan="11">SPECIFIED</td><td>MASS</td><td>(4.40) g</td><td></td><td></td><td>06-11-2021</td><td>03-18-2022</td><td></td> <td>YAZAKI CORPORATION</td> </tr> </tbody> </table>			10MAX	50MAX	100MAX	250MAX	250OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.	A	± 0.15	± 0.20	± 0.30	± 0.50	± 0.75		± 0.20	± 0.30	± 0.50	± 2.50	$\pm 3^\circ$	0.1	R	7298-6354-30.M	11-24-2021	mm	5/1	3	7298-6354-30	B	± 0.20	± 0.30	± 0.55	± 0.95	± 1.40		± 0.20	± 0.30	± 0.50	± 2.50	$\pm 3^\circ$	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	7298-6354-30:R	C	± 0.30	± 0.50	± 0.80	± 1.40	± 2.00						$\pm 3^\circ$	0.15				DALE	FERNANDA			SPECIFIED											MASS	(4.40) g			06-11-2021	03-18-2022		YAZAKI CORPORATION	<p>ISSUE MARK</p>	
	10MAX	50MAX	100MAX	250MAX	250OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.																																																																																						
A	± 0.15	± 0.20	± 0.30	± 0.50	± 0.75		± 0.20	± 0.30	± 0.50	± 2.50	$\pm 3^\circ$	0.1	R	7298-6354-30.M	11-24-2021	mm	5/1	3	7298-6354-30																																																																																					
B	± 0.20	± 0.30	± 0.55	± 0.95	± 1.40		± 0.20	± 0.30	± 0.50	± 2.50	$\pm 3^\circ$	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	7298-6354-30:R																																																																																						
C	± 0.30	± 0.50	± 0.80	± 1.40	± 2.00						$\pm 3^\circ$	0.15				DALE	FERNANDA																																																																																							
	SPECIFIED											MASS	(4.40) g			06-11-2021	03-18-2022		YAZAKI CORPORATION																																																																																					