



LTCC SURFACE MOUNT

High Pass Filter

HFCW-6010+

Mini-Circuits

50Ω

6.4 to 20 GHz

THE BIG DEAL


- Insertion Loss, Typ. 0.9 dB
- Good Rejection, Typ. 44 dB
- 0603 Surface Mount Footprint
- Power Handling: 2.5 Watts



Generic photo used for illustration purposes only

APPLICATIONS

- Test & Measurements
- Military Applications
- Telecommunications and Broadband Wireless Systems

FUNCTIONAL DIAGRAM**PRODUCT OVERVIEW**

Mini-Circuits' HFCW-6010+ is a miniature low temperature co-fired ceramic (LTCC) high pass filter with a 6.4 to 20 GHz passband supporting a variety of applications. This model provides 0.9 dB typical insertion loss over a wide band due to its rugged monolithic construction. Housed in an 0603 ceramic form factor which is ideal for dense signal chain PCB layouts where it complements MMIC size and performance. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well suited for environmental extremes of high humidity and temperature.

KEY FEATURES

Features	Advantages
Wide Passband, 13.6 GHz	This filter has a very wide passband from 6.4 to 20 GHz.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Small Size, 0603	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Rugged Power Handling, 2.5 Watts	Handles up to 2.5 Watts in a small 0603 package.

REV. A
ECO-026396
HFCW-6010+
EDU3855
URJ
250731

Mini-Circuits®www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 1 OF 5



LTCC SURFACE MOUNT

High Pass Filter

HFCW-6010+

50Ω

6.4 to 20 GHz

ELECTRICAL SPECIFICATIONS^{1,2,3} AT +25°C

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	F3-F4	6.4 - 7.7	—	2.0	—	dB
		F4-F5	7.7 - 14	—	0.9	1.4	
		F5-F6	14 - 20	—	2.0	—	
Stopband	Return Loss	F3-F6	6.4 - 20	—	9	—	dB
		DC-F1	DC - 3.5	39	44	—	dB
	F1-F2	3.5 - 4.9	20	34	—	—	
Freq. Cut-Off ⁴		Fc	6.01		2.8	—	dB

1. Tested in Evaluation Board P/N TB-HFCW-6010+.

2. Bi-directional, RF1 and RF2 can be interchanged.

3. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.


4. Typical variation ± 5%.

ABSOLUTE MAXIMUM RATINGS⁵

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power ⁶	2.5 W @ +25°C

5. Permanent damage may occur if any of these limits are exceeded.

6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 0.7 W at +125°C.

TYPICAL FREQUENCY RESPONSE AT +25°C**Mini-Circuits®**

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 2 OF 5



LTCC SURFACE MOUNT






High Pass Filter

HFCW-6010+

50Ω

6.4 to 20 GHz

TYPICAL PERFORMANCE GRAPHS





FUNCTIONAL DIAGRAM





Figure 1. HFCW-6010+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1 ²	1	Connects to RF Input Port
RF2 ²	3	Connects to RF Output Port
GROUND	2,4,5,6	Connects to Ground on PCB, (See drawing PL-703)

SUGGESTED PCB LAYOUT (PL-703)





NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4350B) WITH DIELECTRIC THICKNESS .0200±.0015. COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRAC WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)
DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

Figure 2. PL-703 Suggested PCB Layout

CASE STYLE DRAWING



A rectangular box containing a diagonal hatching pattern, used to indicate the area of metallization.

Weight: .005 grams.
Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

PRODUCT MARKING*: S

*Marking may contain other features or characters for internal lot control.



LTCC SURFACE MOUNT

High Pass Filter

HFCW-6010+

50Ω

6.4 to 20 GHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD.**CLICK HERE**

Performance Data and Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	JC0603C Lead Finish: Tin over Nickel Plating
RoHS Status	Compliant
Tape and Reel	F114
Suggested Layout for PCB Design	PL-703
Evaluation Board	TB-HFCW-6010+
	Gerber File
Environmental Rating	ENV06

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Mini-Circuits®www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 5 OF 5