



Mini-Circuits®

CERAMIC

# Low Pass Filter

50Ω DC<sup>1</sup> to 3000 MHz


LFCN-3000+

## FEATURES

- Excellent power handling, 10 W
- Small size
- 7 sections
- Temperature stable
- LTCC construction
- Protected by U.S. Patent 6,943,646

## APPLICATIONS

- Harmonic rejection
- VHF/UHF transmitters/receivers
- Lab use



Generic photo used for illustration purposes only

CASE STYLE: FV1206

### +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## ELECTRICAL SPECIFICATIONS<sup>1,2</sup> AT +25°C

| Parameter | F#             | Frequency (MHz) | Min.       | Typ. | Max. | Units |
|-----------|----------------|-----------------|------------|------|------|-------|
| Passband  | Insertion Loss | DC-F1           | DC-3000    | —    | 1.2  | dB    |
|           | Freq. Cut-Off  | F2              | 3600       | 3.0  | —    | dB    |
|           | VSWR           | DC-F1           | DC-3000    | 1.2  | —    | :1    |
| Stop Band | Rejection Loss | F3              | 4550       | 20   | —    | dB    |
|           |                | F4-F5           | 4780-7500  | —    | 30   |       |
|           |                | F6              | 10000      | —    | 20   |       |
|           | VSWR           | F3-F6           | 4550-10000 | —    | 20   | :1    |

1. In Applications where DC isolation to ground is required, coupling capacitors are recommended to avoid DC leakage. Alternatively, if DC pass IN-OUT is required, Mini-Circuits' "D" suffix version of this model will support DC IN-OUT, and provide >100 MOhm isolation to ground.


2. Measured on Mini-Circuits Characterization Test Board TB-270.

## ABSOLUTE MAXIMUM RATINGS


| Parameter                   | Ratings            |
|-----------------------------|--------------------|
| Operating temperature       | -55°C to +100°C    |
| Storage temperature         | -55°C to +100°C    |
| RF Power Input <sup>3</sup> | 10 W max. at +25°C |

3. Passband rating, derate linearly to 3.5 W at +100°C ambient.  
Permanent damage may occur if any of these limits are exceeded.

## TYPICAL FREQUENCY RESPONSE



## FUNCTIONAL SCHEMATIC





Mini-Circuits®

CERAMIC

## Low Pass Filter

LFCN-3000+


50Ω DC<sup>1</sup> to 3000 MHz

## PIN CONNECTIONS

|        |     |
|--------|-----|
| RF IN  | 1   |
| RF OUT | 3   |
| GROUND | 2,4 |

PRODUCT MARKING: R6

DEMO BOARD MCL P/N: TB-270  
SUGGESTED PCB LAYOUT (PL-137)




**NOTES:** 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH THICKNESS .020" ± .0015".  
COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.


2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## OUTLINE DRAWING



## PCB Land Pattern



## OUTLINE DIMENSIONS (Inches mm)

| A    | B    | C    | D    | E    | F    | G    |       |
|------|------|------|------|------|------|------|-------|
| .126 | .063 | .037 | .020 | .032 | .009 | .169 |       |
| 3.20 | 1.60 | 0.94 | 0.51 | 0.81 | 0.23 | 4.29 |       |
| H    | J    | K    | L    | M    | N    | P    | wt    |
| .087 | .024 | .122 | .024 | .087 | .012 | .071 | grams |
| 2.21 | 0.61 | 3.10 | 0.61 | 2.21 | 0.30 | 1.80 | .020  |

## TAPE &amp; REEL INFORMATION: F71



CERAMIC

# Low Pass Filter


LFCN-3000+

Mini-Circuits

50Ω DC<sup>1</sup> to 3000 MHz

## TYPICAL PERFORMANCE DATA AT +25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|-----------------|---------------------|-----------|
| 50              | 0.03                | 1.01      |
| 1000            | 0.29                | 1.23      |
| 1500            | 0.40                | 1.34      |
| 3000            | 0.77                | 1.15      |
| 3600            | 2.96                | 3.08      |
| 4480            | 25.24               | 25.19     |
| 4780            | 40.44               | 29.96     |
| 5000            | 46.26               | 27.59     |
| 6500            | 36.73               | 19.98     |
| 10000           | 21.68               | 18.70     |
| 11000           | 19.41               | 13.70     |
| 13000           | 13.67               | 12.99     |
| 15000           | 14.56               | 11.61     |
| 17000           | 16.94               | 4.41      |
| 20000           | 24.85               | 4.88      |



### NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

