



Mini-Circuits

ULTRA HIGH DYNAMIC RANGE

Monolithic Amplifier

LHA-13LN+

50Ω

1 MHz to 1 GHz

THE BIG DEAL

- Ultra-High IP3, +38.3 dBm Typ.
- Gain, 22.4 dB Typ. at 0.5 GHz
- Low Supply Voltage, +3 V to +5 V
- Excellent Noise Figure, 1.1 dB Typ.



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Base Station Infrastructure
- CATV
- Cellular

PRODUCT OVERVIEW

LHA-13LN+ (RoHS compliant) is an advanced wideband amplifier fabricated using E-pHEMT technology and offers extremely high dynamic range over a broad frequency range, along with low noise figure. In addition, the LHA-13LN+ has good input and output return loss over a broad frequency range. LHA-13LN+ is enclosed in a 3x3 mm 12-lead QFN-style package and has very good thermal performance.

KEY FEATURES

Feature	Advantages
Broadband: 1 MHz to 1 GHz	Covers primary wireless communications bands: VHF, UHF, and Cellular.
Extremely High IP3 +36.1 dBm Typical at 1 MHz +38.3 dBm Typical at 0.5 GHz	The LHA-13LN+ matches industry leading IP3 performance relative to device size and power consumption. The combination of the design and E-pHEMT structure provides enhanced linearity over a broad frequency range, as shown by the IP3 being approximately 13-17 dB above the P1dB point. This feature makes this amplifier ideal for use in: <ul style="list-style-type: none"> • Driver amplifiers for complex waveform upconverter paths • Drivers in linearized transmit systems • Secondary amplifiers in ultra-high dynamic range receivers
Low Noise Figure, 1.1 dB at 0.5 GHz	Low system noise figure performance along with high OIP3 provides high dynamic range.
Low Supply Voltage	Enables operation in applications with low DC power consumption limits.

REV. B
ECO-026525
LHA-13LN+
MCL NY
250811

Mini-Circuitswww.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 1 OF 4



ULTRA HIGH DYNAMIC RANGE

Monolithic Amplifier

LHA-13LN+

Mini-Circuits

50Ω 1 MHz to 1 GHz

ELECTRICAL SPECIFICATIONS¹ AT +25°C, 50Ω, UNLESS NOTED OTHERWISE

Parameter	Condition (MHz)	V _{DD} = +5 V ¹			V _{DD} = +3 V ¹	Units
		Min.	Typ.	Max.	Typ.	
Frequency Range		1	22.1	24.6	1000	1-1000
Gain	1			27.1	23.7	MHz
	20		24.0		23.2	
	250		22.8		22.0	
	500	20.2	22.4	24.6	21.5	
	1000		20.1		18.7	
Input Return Loss	1		11		10	dB
	20		15		15	
	250		18		18	
	500		18		15	
	1000		11		9	
Output Return Loss	1		12		12	dB
	20		20		22	
	250		18		20	
	500		25		22	
	1000		11		9	
Reverse Isolation	500		26		25.6	dB
Output Power @ 1 dB Compression	1		+20.8		+14.6	dBm
	20		+22.0		+15.8	
	250		+24.2		+19.3	
	500		+23.9		+18.9	
	1000		+23.3		+17.6	
Output IP3 ²	1		+36.1		+29.6	dBm
	20		+38.9		+32.5	
	250		+40.0		+33.6	
	500		+38.3		+32.3	
	1000	+36	+36.4		+28.5	
Noise Figure	1		3.1		3.0	dB
	20		1.1		1.0	
	250		0.9		1.0	
	500		1.1		1.0	
	1000		1.2		1.2	
Device Operating Voltage			+5.0		+3.0	V
Device Operating Current			143	162	73	mA
Device Current Variation vs. Temperature ³			-30.7		24.2	µA/°C
Device Current Variation vs. Voltage			0.0355		0.0354	mA/mV
Thermal Resistance, Junction-to-Ground Lead Junction-to-Ground Lead at +85°C Stage Temperature			23.3		23.3	°C/W

1. Measured on Mini-Circuits Characterization test board TB-1063-13LN+. See Characterization Test Circuit (Fig. 1).

2. Tested at P_{OUT} = 0 dBm/tone.

3. (Current at +105°C - Current at -45°C)/+150°C

ABSOLUTE MAXIMUM RATINGS⁴

Parameter	Ratings
Operating Temperature (Ground Lead)	-40°C to +105°C
Storage Temperature	-65°C to +150°C
Power Dissipation	3.3 W ⁵
Input Power (CW)	+21 dBm (5 minutes max.) ⁶ +10 dBm (continuous) for 1-10 MHz +11 dBm (continuous) for 10-1000 MHz
DC Voltage on Pad 7	+10 V

4. Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.

5. Up to +85°C, derate linearly to 2.5 W at +95°C.

6. Up to +85°C, derate linearly to +18 dBm at +95°C.

Mini-Circuits



ULTRA HIGH DYNAMIC RANGE

Monolithic Amplifier



LHA-13LN+

Mini-Circuits

50Ω

1 MHz to 1 GHz

SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF-IN	3	RF Input
RF-OUT and DC-IN	7	RF Output and DC Bias
GND	Paddle	Connections to ground
NC	1-2, 4-6, 8-12	No connection, grounded externally

CHARACTERIZATION TEST / RECOMMENDED APPLICATION CIRCUIT





Fig 1. Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-1063-13LN+) Gain, Return Loss, Output Power at 1 dB Compression (P1dB), Output IP3 (OIP3) and Noise Figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return Loss: $P_{IN} = -25$ dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

Components	Size	Value	Manufacturer	P/N
C1	0402	1.5 pF	Murata	GRM1555C1H1R5CA01
C2	0603	2.2 uF		GRM188R61C225KE15
C3	0402	0.1 uF		GRM155R71C104KA88
C4	0603	2.2uF		GRM188R61C225KE15
C5	0402	1000 pF		GRM1555C1H102JA01
C6	0805	10 uF		GRM21BR61C106KE15
L1	1210	15 uH		LQH32DN150K53L
L2	0603	5.1 nH	Coilcraft	0603CS-5N1XJL
R1	0402	1500 Ohms	Koa	RK73H1ELTP1501F

PRODUCT MARKING



Marking may contain other features or characters for internal lot control.

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 3 OF 4



Mini-Circuits

ULTRA HIGH DYNAMIC RANGE

Monolithic Amplifier

LHA-13LN+

50Ω

1 MHz to 1 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. [CLICK HERE](#)

Performance Data	Data Table Swept Graphs
Case Style	DQ1225 Plastic package, exposed paddle Lead Finish: Matte-Tin
Tape & Reel Standard Quantities Available on Reel	F66 7" Reels with 20, 50, 100, 200, 500, 1000, 2000 or 3000 devices
Suggested Layout for PCB Design	PL-594
Evaluation Board	TB-1063-13LN+
Environmental Ratings	ENV08T9

ESD RATING

Human Body Model (HBM): Class 1B (Pass 500 V) in accordance with ANSI/ESD STM 5.1 - 2001

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

 **Mini-Circuits**

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 4 OF 4