



SURFACE MOUNT RF Transformer

50Ω 500 to 2500 MHz

TC4-25+

TC4-25X+
Upgraded Version*

Mini-Circuits

- *Addition of Top Hat® Feature Benefits
- Allows Faster Pick-and-Place
- Enables Visual Identification Marking

FEATURES

- Wideband, 500 to 2500 MHz
- Balanced Transmission Line with Secondary Center Tap
- Good Return Loss
- Plastic Base with Leads
- Aqueous Washable



Generic photo used for illustration purposes only
CASE STYLE: AT224-1A

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- PCS
- Cellular

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Condition	Min.	Typ.	Max.	Unit
Impedance Ratio (Secondary/Primary)			4		Ohm
Frequency Range		500		2500	MHz
Insertion Loss ¹	500-2500			3.0	
	700-1500			2.0	
	750-1200			1.0	dB


1. Insertion Loss is referenced to mid-band loss, 0.2 dB typ.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
RF Power	0.25 W
DC Current	30 mA

Permanent damage may occur if any of these limits are exceeded.

CONFIG. H




REV. D
ECO-027808
TC4-25+
MCL NY
251203

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 1 OF 3



SURFACE MOUNT



RF Transformer

TC4-25+

50Ω 500 to 2500 MHz

PIN CONNECTIONS

PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	3
SECONDARY	1
SECONDARY CT	2


PRODUCT MARKING: N/A**DEMO BOARD MCL P/N:** TB-TC4-25+**OUTLINE DRAWING****PCB Land Pattern**

Suggested Layout,
Tolerance to be within $\pm .002$ in

OUTLINE DIMENSIONS (Inch mm)

A	B	C	D	E	F
.150 3.81	.150 3.81	.160 4.06	.050 1.27	.040 1.02	.025 0.64
G	H	J	K		wt
.028 0.71	.065 1.65	.190 4.83	.030 0.76		grams 0.15

TAPE & REEL INFORMATION: F17**Mini-Circuits®**



SURFACE MOUNT

RF Transformer


TC4-25+

Mini-Circuits

50Ω 500 to 2500 MHz

TYPICAL PERFORMANCE DATA

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)
500	1.07	8.37
1000	0.37	22.67
1500	0.59	13.79
1600	0.64	12.90
1800	0.74	11.65
2000	0.84	10.75
2200	0.96	10.03
2400	1.08	9.35
2500	1.14	8.96
2800	1.38	7.82
3000	1.59	7.06



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Mini-Circuits®