



GENERAL TOLERANCE						
10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
±0.5	±0.8	±1.2	±1.8	±2.6	±5°	0.15


	YAZAKI PART NO.	A/B PART NO.	a	b	c	d	e	f	g	MASS	WIRE SIZE(sq)
①	7009-2280-02	△7A09-2280-02	4.0	2.0	3.7	R0.7	3.1	R0.7	13.5	1.6	0.5~1.0
②	7009-2281-02		4.0	2.5	7.2	R2.0	5.4	R1.0	13.5	1.8	1.05~2.0
③	7009-2282-02	△7A09-2282-02	4.0	2.5	8.4	R2.4	7.4	R1.4	13.5	2.2	2.05~3.0
④	7009-2283-02	△7A09-2283-02	5.5	4.0	9.5	R2.8	8.1	R1.6	16.5	2.6	3.05~5.0
⑤	7009-2284-02		5.5	4.0	11.3	R3.5	9.5	R2.0	16.5	2.8	5.05~8.0





SEC. D-D



SEC. C-C



SEC. B-B



SEC. E-E



SEC. A-A

NOTES

- 1) APPLICABLE WIRE SIZE : SEE TABLE
- 2) MATING PART NO. : 7009-2285-02, 7009-2286-02,
7009-2287-02, 7009-2288-02, 7009-2289-02

注 記

- 1) 適応電線サイズ : 表記
- 2) 嵌合相手品番: 7009-2285-02, 7009-2286-02,
7009-2287-02, 7009-2288-02,
7009-2289-02

3	14.06.17	ADDED PART NO. & RENEW	C14-3823	G. S
2	07.04.25	ADDED PART NO.	C07-3777	E. T
1	05.03.29	CORRECTED ERROR	C05-3391	A. F
0	03.01.16	CHANGED FORM & RELEASE & RENEW	C03-3058	F. P
	02.10.21	NEW	T02-3891	H. G
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE						
10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°
C	±0.3	±0.5	±0.8	±1.4	±2	±30°
SPECIFIED	SEE TABLE				MASS	SEE TABLE g

CUSTOMER						MATL. C2680R				TREAT. TIN PLATING					
CUSTOMER PART NO.						CUSTOMER DWG NO.				SPEC. t=0.8					
OFFICE						TRIAL PART NO.				NAME					
VENDOR						X30109-3369 ETC.				EARTH TERMINAL(R)					
VENDOR NO.															
DWG TYPE		DWG SOURCE		DWG DATE		UNIT		SCL		ANGLE		PART NO.		7009-2280-02 ETC.	
R		NEW		03.01.16		mm		5/1		3		CH. CODE			
APPROVED		CHECKED		CHECKED		DESIGN		DRAWN				DWG NO.		7009-2280-02:R	
寺田		関野		山本		H. GOTO		G. SABATER						SET DWG NO.	
						02. 10. 21		14. 06. 17						YAZAKI CORPORATION	