





10MAX	50MAX	ANGLE	ECCENT
±0.5	±0.8	±5°	0.3

YAZAKI PART NO.	A	B	C	ØD	E	T	F	△G	△J	△K	△M	REMARKS
7010-3014	7	7	16	3.3	2.4	0.6	20.9	4	(4.2)	4.2	(4.6)	
7010-3015	8	8	17	4.4	3.4	0.8	22.7	4	(5.7)	4.6	(4.6)	
7010-3016	10	△9	18	5.4	4.4	0.8	24.7	4	(5.7)	4.6	(4.6)	
7010-3017	12	10	19	△6.4	5.3	0.8	26.8	4	(5.7)	4.6	(4.6)	
7010-3017-02	12	10	19	△6.4	5.3	0.8	△26.8	4	(5.7)	4.6	(4.6)	TIN PLATING
7010-3016-02	10	△9	18	5.4	4.4	0.8	24.7	4	(5.7)	4.6	(4.6)	TIN PLATING
7010-3015-02	8	8	17	4.4	3.4	0.8	22.7	4	(5.7)	4.6	(4.6)	TIN PLATING



注記
1) 適用電線サイズはAV0.5~1.25とする。

△ NOTE
1) APPLICABLE WIRE SIZE: AV 0.5~1.25

10.07.26	ADDED TOLERANCE ETC. & RENEW	C10-0148	K.M
08.01.07	CORRECTION	C08-1A05	T.S
89.06.22	品番追加	C89-0683	牛山
87.04.06	×ツキ追加	C87-0321	石崎
80.06.05	寸法追記	C80-0287	新岡
79.11.08	寸法の誤記訂正	C79-0662	新岡
78.10.30	品番追記	C78-0575	新岡
76.10.06	提出用として作成		H.T
DATE	REVISION RECORD	NO.	CHKD

10MAX	50MAX	100MAX	250MAX	500V	ANGLE	ECCENT	CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG. NO.	MATL. △	BRASS	TREAT. SEE TABLE	ISSUE MARK
±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1	R			△	JIS H 3100		
±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1	APPROVED	CHECKED	DESIGN	3	DRAWN		
±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15	T. SUZUKI	H. SATO			K. MORISHITA		
SPECIFIED							△ SEE TABLE	MASS	9				