






RUBBER PART GENERAL TOLERANCE			
PART DIM.	1	2	3
0 TO 3	±0.2	±0.3	±0.4
3 TO 6	±0.2	±0.4	±0.5
6 TO 10	±0.3	±0.5	±0.6
10 TO 18	±0.3	±0.6	±0.8
18 TO 30	±0.4	±0.8	±1.0
30 TO 50	±0.5	±1.0	±1.5
50 TO 80	±0.6	±1.2	±2.0
80 TO 120	±0.7	±1.4	±2.5
120 TO 180	±0.8	±1.6	±3.0
180 TO 250	±1.0	±2.0	±4.0
250 TO 315	±1.2	±2.5	±5.0
315 TO 400	±1.5	±3.0	±6.0
400 TO 500	±1.8	±3.5	±7.0
500 OVER	±0.4 *	±0.8 *	±1.5 *

NOTES

- 1) MUST BE FREE OF FLASH AND IMPERFECTIONS THAT AFFECT FUNCTION.
- 2) APPLICABLE PANEL : HOLE DIA=φ 20.00, THICKNESS=0.80.

注 記

- 1) 機能上有害な「リ、キリツ等無き事。
- 2) 嵌合の「スル」穴径 φ20.00, 板厚 0.80

LETI	DATE	92.06.09	REVISION RECORD	NEW	C92-3492	K.F	CHKD
1							

GENERAL TOLERANCE			
10MAX	50MAX	100MAX	250MAX
A ±0.15	±0.2	±0.3	±0.5
B ±0.2	±0.3	±0.5	±0.75
C ±0.3	±0.5	±0.8	±1.4
CLASS-3	±0.5	±0.8	±1.4
SPECIFIED	±0.5	±0.8	±1.4
SEE RUBBER PART GENERAL TOLERANCE	±0.5	±0.8	±1.4

CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG NO.	MATL. SPEC.	TREAT. & FIN.	ISSUE MARK
OFFICE					
VENDOR NO.					
DWG TYPE	NEW	DWG SOURCE	NEW	DWG DATE	92.06.09
APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	3
7.0/20.0	K. Amano	K. Amano	FUJITA	K. FUJITA	3
92.06.10	92.06.10	92.06.10	87.01.12	92.06.09	3
YAZAKI CORPORATION					5