


YAZAKI PART NO.	W ₁	H ₁	W ₂	H ₂	APPLICABLE WIRE SIZE
7114-2924-02	2.4	(2.8)	6.2	(5.6)	CAVUS, CAVS, AVS 0.3~0.5
7114-2925-02	3.1	(3.1)	6.2	(5.6)	CAVUS, CAVS, AVS 0.85~1.25
7114-2926-02	4.1	(5.2)	8.1	(7.1)	AVS 2~3, AVSS 2





注 記


1. 炭合線端子品番: 7116-2924-02
 7116-2925-02
 7116-2926-02
 7116-2941-02
 7116-2942-02
 7116-2943-02

NOTE

1. MATING FEMALE TERMINAL NO.: 7116-2924-02
 7116-2925-02
 7116-2926-02
 7116-2941-02
 7116-2942-02
 7116-2943-02



SEC. A-A



SEC. B-B

										CUSTOMER					MATL. COPPER ALLOY (t=0.4) TREAT. & FIN.				
										CUSTOMER PART NO.					CUSTOMER DWG NO.				
96.07.11 NEW C96-M328 H. K										OFFICE					TRIAL PART NO.				
LET DATE REVISION RECORD NO. CHKD										VENDOR					VENDOR NO.				
GENERAL TOLERANCE																			
										DWG TYPE					DWG SOURCE				
										DWG DATE					UNIT				
										SCL					ANGLE				
A ±0.15 ±0.2 ±0.3 ±0.5 ±0.75 ±30' 0.1										R					NEW				
B ±0.2 ±0.3 ±0.55 ±0.95 ±1.4 ±30' 0.1										APPROVED					CHECKED				
C ±0.3 ±0.5 ±0.8 ±1.4 ±2 ±30' 0.15										CHECKED					DESIGN				
SPECIFIED										MASS					DRAWN				
										神田					辻				
										櫻					H. YOSHIDA				
										KARAMATSU									
										96.11.18					96.11.13				
										96.11.11					96.11.11				
										96.06.24					96.07.11				
															YAZAKI CORPORATION				