




TABLE 1

YAZAKI SUB ASSEMBLY PART NO.	NO.	YAZAKI PART NO.	MATERIAL	COLOR	QTY.
7282-3013-10 ETC.	①	SEE TABLE 2	PBT	SEE TABLE 2	1
	②	7157-4358	PBT	NATURAL	1

TABLE 2

YAZAKI SUB ASSEMBLY PART NO.	YAZAKI PART NO.	COLOR
△ 7282-3013, [A]	7182-3013	NATURAL
7282-3013-10, [A]	7182-3013-10	DARK GRAY
7282-3013-30, [A]	7182-3013-30	BLACK
7282-3013-40, [A]	7182-3013-40	LIGHT GRAY
△ 7282-3013-50, [A]	7182-3013-50	ORANGE
△ 7282-3013-60, [A]	7182-3013-60	GREEN
△ 7282-3013-80, [A]	7182-3013-80	BROWN
△ 7282-3013-90, [A]	7182-3013-90	BLUE



- NOTES
- MATING PART NO.: 7283-3013-10 ETC.
 - APPLICABLE TERMINAL NO.: 7114-6045 ETC.
 - APPLICABLE SEAL RUBBER NO.: 7157-3854 ETC.

- 注記
- 嵌合相手品番: 7283-3013-10 ETC.
 - 適用端子品番: 7114-6045 ETC.
 - 適用ゴム品番: 7157-3854 ETC.

△ 96.12.21	ADDED PART NO. & CHANGED FORM. [A]	C96-N209	M. T	CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG NO.	MATL. SPEC.	SEE TABLE 1	TREAT. & FIN.	ISSUE MARK				
90.06.27	NEW	C90-L741	H. W	OFFICE	TRIAL PART NO.		NAME	312 1P SEALED CONNECTOR						
LET DATE	REVISION RECORD	NO.	CHKD	VENDOR			HOUSING MALE SUB ASSEMBLY							
GENERAL TOLERANCE														
10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.	7282-3013-10 ETC.
A ±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW	90.06.27	mm	2/1	3	CH. CODE	7282-3013-10:R
B ±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED		DESIGN			DWG NO.	7282-3013-10:R
③ ±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15		CHECKED		YAMAMOTO	AKIMOTO		SET DWG NO.	
SPECIFIED														
MASS														
96.12.27														
96.12.25														
89.08.02														
96.12.21														
1														
2														
3														