




TABLE 1



SEC. A-A



SEC. B-B

SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	MATERIAL	COLOR	QTY.
7283-1054 ETC.	①	SEE TABLE 2	△ PBT	SEE TABLE 2	1
	②	7157-4344	△ PBT	NATURAL	1

△ TABLE 2

SUB ASSEMBLY PART NO. AND CH. CODE	PART NO. AND CH. CODE	COLOR
7283-1054. 回	7183-1054	NATURAL
7283-1054-10. 回	7183-1054-10	DARK GRAY
7283-1054-30. 回	7183-1054-30	BLACK
7283-1054-40. 回	7183-1054-40	LIGHT GRAY
7283-1054-50. 回	7183-1054-50	ORANGE
7283-1054-60. 回	7183-1054-60	GREEN
7283-1054-90. 回	7183-1054-90	BLUE

注 記

- 嵌合相手品番: 7282-1054 ETC.
- 適用端子品番: 090 II 7116-4020 ETC.
187 7116-4030 ETC.

NOTES

- MATING PART NO.: 7282-1054 ETC.
- APPLICABLE TERMINAL NO.: 090 II 7116-4020 ETC.
187 7116-4030 ETC.

△ 99.03.05	ELIMINATED COLOR NO. & CHANGED MATERIAL. 回	C99-L420	T. M	CUSTOMER				MATL. SPEC.	SEE TABLE 1	TREAT. & FIN.				
△ 96.07.01	CHANGED FORM & CHANGED MATERIAL. 回	C96-M102	A. Y	CUSTOMER PART NO.				NAME 090 II 4P+187 1P HYBRID						
90.11.10	NEW	C90-M209	M. H	OFFICE				CONNECTOR SUB ASSEMBLY FEMALE						
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR				PART NO. 7283-1054 ETC.					
GENERAL TOLERANCE				VENDOR NO.				DWG NO. 7283-1054:R						
10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO. CH. CODE	
A ±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW	90.11.10	mm	2/1	3	7283-1054 ETC.	
B ±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		DWG NO. 7283-1054:R	
(C) ±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	加藤	山梨	三輪	Y. OHTA	KANAZAWA	杉山	SET DWG NO.	
SPECIFIED				MASS	g		99.03.22	99.03.18	99.03.16	89.02.28	99.03.05	YAZAKI CORPORATION		