


4



3

2

1



.003  
See Notes 2 & 3.



## NOTES:

1. Unless otherwise noted, all dimensions are in inches.
2. Foil Material: .002 thick 1145 aluminum
3. Interface Material: .0005 thick phase-change thermal compound, both sides.  
Maximum shipping & storage temperature – 40°C  
Reflow temperature – 60°C  
Maximum recommended service temperature – 200°C
4. Thermal impedance: .030 °C–in<sup>2</sup>/W (.194 °C–cm<sup>2</sup>/W) @ 20psi
5. Thermal washers shall be packaged in quantities of 10 with oversize separators between them.
6. Used with 10–pin PSIP packages (Apex designator: DN).
7. Power Devices part no. AL–102–070–APX
8. Supplier is to label each plastic box with the Apex part number.

TOLERANCES - UNLESS  
OTHERWISE SPECIFIED

.XX = ±.01 [.254]  
.XXX = ±.005 [.127]  
ANG. = ±5°



TITLE:

THERMAL WASHER, P-SIP

SUBJECT:

MECHANICAL DRAWING

ENGINEER:

D-M

DRAWN BY:

R.MOR

DATE:

13242

SH.

OF

1 1

MODEL:

TW06

FILENAME:

TW06

REV:

F

DATE:

03JUN13

4

3

2

1