



Wiremold
Exterior Box Cover Assembly, 2 NEMA 5-20R Locking Receptacles, Brown (COVER ONLY)
Part No. XB814C520BN



The brown Outdoor Ground Box cover assembly is prewired on a single circuit with (2) 20A weather resistant duplex receptacles. **CAUTION:** All ground box electrical circuits must be protected by a Ground Fault Circuit Interrupter upstream from the ground box. **NOTE:** Cover must be closed while in use. Use only molded plug and cord assemblies that are rated for outdoor use. **NOTE:** Maximum length of plug allowed at end of cord is 3" (76mm).

Features & Benefits

- cUL Coming Soon
- UL listed to UL50E Type 6P (NEMA 6P) and IP68 requirements while in use
- ADA compliant
- Outdoor-rated construction
- Keeps receptacles and connections dry even when submerged

Specifications

General Info

Product Line	Wiremold	Color	Brown
UPC Number	786776187199	Country Of Origin	China
Material	Plastic	Number of Receptacles	1
Construction	Assembled	Features	ADA Compliant
Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit	Standard	UL Listed Outdoor In-Ground Boxes: File E486738 Guide QCNL.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Ground Box Cover
Installed Devices	Duplex Receptacle		

Dimensions

Product Width US	7.375 in	Product Weight US	9.0 lb
Product Height US	19.625 in	Product Length US	14.0 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E486738	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Is Pre-Wired	Yes	Service Capacity	Single
--------------	-----	------------------	--------

Number of Gangs	1	Amperage	20 A
-----------------	---	----------	------

Enclosure Type	Type 6P	Load Capacity	5000 lb
----------------	---------	---------------	---------

NEMA Configuration Code	5-20R
-------------------------	-------
