

QSiC™ 1200V SiC Half-Bridge Module

Features

- 62mm standard footprint
- High speed switching SiC MOSFETs
- Reliable body diode
- All parts tested to above 1350V
- Kelvin reference for stable operation
- AlN Isolated baseplate

Benefits

- Low switching losses
- Low junction to case thermal resistance
- Very rugged and easy mounting
- Direct mounting to heatsink (isolated package)
- Low thermal impedance

Applications

- Photovoltaic and Wind Inverter
- EV/Battery charger
- Energy storage system
- High voltage DC to DC converter
- Induction Heating
- SMPS and UPS

Package



Part #	Package	Marking
GCMX003A120S3B1-N	S3	GCMX003A120S3B1-N



Absolute Maximum Ratings, at $T_J=25^\circ\text{C}$, unless otherwise specified

Characteristics	Symbol	Conditions	Values	Unit
Drain-Source Voltage	V_{rated}	$V_{\text{GS}}=0\text{V}$, $I_D=1\mu\text{A}$	1200	V
Continuous Drain Current	I_{DS}	$T_C=25^\circ\text{C}$, $V_{\text{GS}}=20\text{V}$, $T_J=175^\circ\text{C}$	625	A
		$T_C=65^\circ\text{C}$, $V_{\text{GS}}=20\text{V}$, $T_J=175^\circ\text{C}$	542	
Body Diode Drain Current	I_{SD}	$T_C=25^\circ\text{C}$, $V_{\text{GS}}=-5\text{V}$, $T_J=175^\circ\text{C}$	523	
Pulsed Drain Current	$I_{\text{DS,pulse}}$	$T_C=25^\circ\text{C}$, $V_{\text{GS}}=20\text{V}$	1050	
Gate Source Voltage	V_{GSmax}		-10/25	V
	V_{GSop}	Recommended operational	-5/20	
Power Dissipation	P_{tot}	$T_C=25^\circ\text{C}$, $T_J=175^\circ\text{C}$	2113	W
Junction Temperature	T_J	Continuous	-40...175	°C
Case & Storage Temperature	T_C , T_{storage}	Continuous	-40...150	°C

Static Electrical Characteristics, at $T_J=25^\circ\text{C}$, unless otherwise specified

Characteristics	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{\text{GS}}=0\text{V}, I_{\text{D}}=1\text{mA}$	1200	-	-	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{\text{DS}}=1200\text{V}, V_{\text{GS}}=0\text{V}$	-	0.6	6	μA
		$V_{\text{DS}}=1200\text{V}, V_{\text{GS}}=0\text{V}, T_J=150^\circ\text{C}$	-	6	600	
Gate-Source Leakage Current	$I_{\text{GSS+}}$	$V_{\text{GS}}=20\text{V}, V_{\text{DS}}=0\text{V}$	-	60	1000	nA
		$V_{\text{GS}}=-5\text{V}, V_{\text{DS}}=0\text{V}$	-	-60	-1000	
Gate Threshold Voltage	$V_{\text{GS}(\text{th})}$	$V_{\text{GS}}=V_{\text{DS}}, I_{\text{D}}=120\text{mA}$	1.8	3.0	4	V
		$V_{\text{GS}}=V_{\text{DS}}, I_{\text{D}}=120\text{mA}, T_J=150^\circ\text{C}$	-	2.0	-	
Drain-Source On-Resistance	R_{DSon}^*	$V_{\text{GS}}=20\text{V}, I_{\text{D}}=300\text{A}$	-	3.0	5.5	$\text{m}\Omega$
		$V_{\text{GS}}=20\text{V}, I_{\text{D}}=150\text{A}$	-	2.9	-	
		$V_{\text{GS}}=20\text{V}, I_{\text{D}}=300\text{A}, T_J=150^\circ\text{C}$	-	4.6	-	
Transconductance	g_{fs}	$V_{\text{DS}}=20\text{V}, I_{\text{D}}=300\text{A}$	-	125.5	-	S
		$V_{\text{DS}}=20\text{V}, I_{\text{D}}=300\text{A}, T_J=150^\circ\text{C}$	-	136.2	-	
Internal Gate Resistance	$R_{\text{G(int)}}$	$f=1\text{MHz}, V_{\text{AC}}=25\text{mV}, \text{D-S Short, including internal 0.9 ohm series gate resistor}^{**}$	-	1.04	-	Ω

* R_{DSon} including package resistance

**Internal series gate resistor limits maximum switching frequency defined by Figure 31

AC Electrical Characteristics, at $T_J=25^\circ\text{C}$, unless otherwise specified

Characteristics	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Input Capacitance	C_{ISS}	$V_{\text{GS}}=0\text{V}$ $V_{\text{DS}}=800\text{V}$ $f=200\text{kHz}$ $V_{\text{AC}}=25\text{mV}$	-	41.4	-	nF
Output Capacitance	C_{OSS}		-	1.69	-	
Reverse Transfer Capacitance	C_{RSS}		-	0.07	-	
Coss Stored Energy	E_{OSS}^{***}		-	660	-	μJ
Turn-On Switching Energy	E_{ON}	$T_J=25^\circ\text{C}$	$V_{\text{DD}}=600\text{V}, I_{\text{DS}}=300\text{A}, R_{\text{G(ext)}}=1\Omega, V_{\text{GS}}=-5/+20\text{V}, L=62\mu\text{H}$	-	3.74	mJ
		$T_J=125^\circ\text{C}$		-	4.41	
		$T_J=150^\circ\text{C}$		-	4.78	
Turn-Off Switching Energy	E_{OFF}	$T_J=25^\circ\text{C}$	$V_{\text{DD}}=600\text{V}, I_{\text{DS}}=300\text{A}, R_{\text{G(ext)}}=1\Omega, V_{\text{GS}}=-5/+20\text{V}, L=62\mu\text{H}$	-	2.40	mJ
		$T_J=125^\circ\text{C}$		-	2.37	
		$T_J=150^\circ\text{C}$		-	2.37	
Turn-On Delay Time	$t_{\text{D(on)}}$	$V_{\text{DD}}=600\text{V}, I_{\text{DS}}=300\text{A}, R_{\text{G(ext)}}=1\Omega, V_{\text{GS}}=-5/+20\text{V}, L=62\mu\text{H}$	-	79	-	ns
Rise Time	t_{R}		-	21	-	
Turn-Off Delay Time	$t_{\text{D(off)}}$		-	138	-	
Fall Time	t_{F}		-	28	-	
Total Gate Charge	Q_{G}	$V_{\text{DD}}=800\text{V}, I_{\text{DS}}=300\text{A}$ $V_{\text{GS}}=-5/20\text{V}$	-	1408	-	nC
Gate to Source Charge	Q_{GS}		-	487	-	
Gate to Drain Charge	Q_{GD}		-	200	-	

*** E_{OSS} is calculated from C_{OSS} curve

Freewheeling Diode Characteristics, at $T_J=25^\circ\text{C}$, unless otherwise specified

Characteristics	Symbol	Conditions	Values			Unit	
			min.	typ.	max.		
Diode Forward Voltage	V_{SD}	$V_{GS}=-5\text{V}$, $I_S=300\text{A}$	-	4.0	-	V	
		$V_{GS}=-5\text{V}$, $I_S=300\text{A}$, $T_J=150^\circ\text{C}$	-	3.6	-		
Reverse Recovery Time	t_{RR}	$T_J=25^\circ\text{C}$	$I_S=300\text{A}$, $V_R=600\text{V}$, $V_{GS}=-5\text{V}$, $dI/dt=18.9\text{A/ns}$	-	24	-	ns
Reverse Recovery Charge	Q_{RR}		-	3423	-	nC	
Peak Reverse Recovery Current	I_{RRM}		-	245	-	A	
Reverse Recovery Energy	E_{RR}	$T_J=25^\circ\text{C}$	$I_S=300\text{A}$, $V_R=600\text{V}$, $V_{GS}=-5\text{V}/20\text{V}$, $R_{G(ext)}=1\Omega$	-	1.59	-	mJ
		$T_J=125^\circ\text{C}$	-	3.23	-		
		$T_J=150^\circ\text{C}$	-	3.84	-		

Thermal and Package Characteristics, at $T_J=25^\circ\text{C}$, unless otherwise specified

Characteristics	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Thermal resistance, junction-case	R_{thJC}		-	0.060	0.071	°C/W
Mounting torque	M_d	M6-1.0 screws	-	-	5.0	N-m
Terminal connection torque	M_{dt}		-	-	5.0	N-m
Package weight	W_t		-	310	-	g
Isolation voltage	V_{ISOL}	$I_{ISOL} < 1\text{mA}, 50/60\text{ Hz, 1 min}$	4000	-	-	V

NTC Characteristics, at $T_J=25^\circ\text{C}$, unless otherwise specified

Characteristics	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Rated resistance	R_{NTC}	$T_{NTC} = 25^\circ\text{C}$	-	5.0	-	kΩ
Resistance tolerance	$\Delta R/R$		-5	-	5	%
Beta Value ($T_2 = 50^\circ\text{C}$)	$\beta_{25/50}$		-	3380	-	k
Beta Value ($T_2 = 80^\circ\text{C}$)	$\beta_{25/80}$		-	3440	-	k
Power dissipation	P_{MAX}	$T_{NTC} = 25^\circ\text{C}$	-	-	50	mW

Typical Performance




Figure 1. Output Characteristics for Various Temperatures



Figure 2. Output Characteristics $T_J = 150^\circ C$ 

Figure 3. On-Resistance vs. Drain Current For Various Temperatures




Figure 4. Normalized On-Resistance vs. Temperature





Figure 5: On-Resistance vs. Temperature For Various Gate Voltages

Figure 6: Threshold Voltage vs. Temperature





Figure 7: Transfer Characteristic for Various Junction Temperatures

Figure 8: 3rd Quadrant Characteristics at $V_{GS} = 20\text{ V}$




Figure 9. Body Diode Characteristics at
 $V_{GS} = 0V$




Figure 10. Body Diode Characteristics at
 $V_{GS} = -5V$




Figure 11. Output Capacitor Stored Energy




Figure 12. Capacitance vs. Drain-Source Voltage




Figure 13. Continuous Drain Current Derating vs. Case Temperature




Figure 14. Maximum Power Dissipation Derating vs. Case Temperature




Figure 15. Transient Thermal impedance (Junction to Case)




Figure 16. Safe Operating Area




Figure 17. Gate Charge Characteristics




Figure 18. Nominal NTC Resistance vs. Temperature




Figure 19. Clamped Inductive Switching Energy vs. Drain Current (600V)




Figure 20. Clamped Inductive Switching Energy vs. Drain Current (800V)




Figure 21. Clamped Inductive Switching Energy vs. Temperature




Figure 22. Reverse Recovery Energy vs. Temperature




Figure 23. Clamped Inductive Switching Energy vs. $R_{G(ext)}$




Figure 24. Reserve Recovery Energy vs. $R_{G(ext)}$




Figure 25. Switching Times vs. Drain Current




Figure 26. dv/dt and di/dt vs. Source Current




Figure 27. Switching Times vs. Temperature




Figure 28. dv/dt and di/dt vs. Temperature

QSiC™ 1200V SiC Half-Bridge Module

GCMX003A120S3B1-N




Figure 29. Switching Times vs. $R_{G(\text{ext})}$




Figure 30. dv/dt and di/dt vs. $R_{G(\text{ext})}$




Figure 31. Frequency vs Minimum $R_{G(\text{ext})}$




Figure 32. Reverse Recovery Definitions




Figure 33. Turn-on Transient Definitions






Figure 34. Turn-off Transient Definitions

Pinout and Circuit Diagram



Package Dimensions (mm)



Revision History		
Date	Revision	Notes
1/12/2024	0.1	Preliminary release
5/25/2024	1.0	Initial release
5/29/2024	1.1	Updated thermals
11/14/2024	1.2	Updated thermals, switching loss, typos

Notes

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented March, 2013. RoHS Declarations for this product can be obtained from the Product Documentation sections of www.SemiQ.com.

REACH Compliance

REACH substances of high concern (SVHC) information is available for this product. Since the European Chemicals Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact our office at SemiQ Headquarters in Lake Forest, California to insure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

SemiQ Inc., reserves the right to make changes to the product specifications and data in this document without notice. SemiQ products are sold pursuant to SemiQ's terms and conditions of sale in place at the time of order acknowledgement.

This product has not been designed or tested for use in, and is not intended for use in, applications implanted into the human body nor in applications in which failure of the product could lead to death, personal injury or property damage, including but not limited to equipment used in the operation of nuclear facilities, life-support machines, cardiac defibrillators or similar emergency medical equipment, aircraft navigation or communication or control systems, or air traffic control.

SemiQ makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SemiQ assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using SemiQ products.

To obtain additional technical information or to place an order for this product, please contact us. The information in this datasheet is provided by SemiQ. SemiQ reserves the right to make changes, corrections, modifications, and improvements of datasheet without notice.