

MISSION-CRITICAL
INTERCONNECT
SOLUTIONS



AEROSPACE-GRADE

Rectangular Connector Backshells and Accessories

for D-Subminiature, M83513 Micro-D, Series 28 HiPer-D,
Series 79 Micro-Crimp, M83733, DPX, ARINC 600 and more

JUNE 2024

AEROSPACE - GRADE
RECTANGULAR
CONNECTOR
BACKSHELLS AND
ACCESSORIES



Comprehensive range of material and plating classes available. See individual how-to-order pages for recommended finish codes.



Glenair Accessory Material and Finish Code Performance

Code	Material	Finish	Specification	Salt Spray Hours	Temperature Range (°C)	Conductive Yes/No	RoHS Yes/No
C	Aluminum	Anodize, Black	AMS-A-8625	500	-65 to +200	No	Yes
JF	Aluminum	Gold Chromate over Cad over Nickel	AMS-QQ-P-416	1000	-65 to +200	Yes	No
G2	Aluminum	Anodize, Hardcoat, Undyed	AMS-A-8625	500	-65 to +200	No	Yes
M	Aluminum	Electroless Nickel	AMS-C-26074	96	-65 to +200	Yes	Yes
MA	Aluminum	Electroless Nickel, Matte Finish	AMS-C-26074	96	-65 to +200	Yes	Yes
ME	Aluminum	Electroless Nickel, Heavy	AMS-C-26074	96	-65 to +200	Yes	Yes
MN	Aluminum	Mega-Nickel	AMS-C-26074	1000	-65 to +200	Yes	Yes
MT	Aluminum	Nickel-PTFE	AMS2524	500	-65 to +175	Yes	Yes
NF	Aluminum	Cadmium, Olive Drab Chromate	AMS-QQ-P-416	1000	-65 to +175	Yes	No
TZ	Aluminum	Tin-Zinc	AMS2434	1000	-65 to +175	Yes	Yes
XB	Composite	Unplated, Black Color	N/A	2000	-65 to +200	No	Yes
XM	Composite	Electroless Nickel	AMS-C-26074	2000	-65 to +200	Yes	Yes
XMT	Composite	Nickel-PTFE	AMS2524	2000	-65 to +175	Yes	Yes
XW	Composite	Cadmium, Olive Drab Chromate	AMS-QQ-P-416	1000	-65 to +175	Yes	No
Z1	Stainless Steel	Passivated	AMS-QQ-P-35	1000	-65 to +200	Yes	Yes
ZL	Stainless Steel	Electrodeposited Nickel	AMS-QQ-N-290	500	-65 to +200	Yes	Yes
ZM	Stainless Steel	Electroless Nickel	AMS-C-26074	1000	-65 to +200	Yes	Yes
ZMT	Stainless Steel	Nickel-PTFE	AMS2524	1000	-65 to +175	Yes	Yes
ZR	Aluminum	Zinc-Nickel, Black Chromate	AMS2417	1000	-65 to +175	Yes	Yes
ZU	Stainless Steel	Cadmium, Black Chromate	AMS-QQ-P-416	1000	-65 to +175	Yes	No

For new design applications, Glenair lists recommended material and plating codes on the how-to-order pages for each connector backshell series. Additional material and plating types, however, are available. Glenair can support every required material and plating type necessary to ensure compatibility with customer connectors, shielding, and hardware. Consult this connector accessory material and finish master table and/or the factory for non-standard, legacy, or unusual plating requirements.

Go to 3dparts.glenair.com for 3D part models in all popular CAD formats for the complete range of Glenair backshells and connector accessories.

GLENAIR
3D Parts
Models



3dparts.glenair.com

Table of Contents

Band Straps and Tools		Band-Master ATS® Shield Termination System Glenair signature band strap technology and tools optimized for use with all band-porch-equipped rectangular backshells.	Selection Guide Page Intro-1
D-Subminiature M24308 • HiPer-D		MIL-DTL-24308 and Series 28 HiPer-D D-Subminiature connector backshells, screwlocks, protective covers, shorting caps, and panel gaskets.	Selection Guide Page A-1
Micro-D M83513		MIL-DTL-83513 and Glenair Signature Micro-D connector backshells, dust caps, protective covers, jackpost hardware, and panel gaskets.	Selection Guide Page B-1
Micro-Crimp Series 79		Glenair Signature Series 79 Micro-Crimp connector backshells, dust caps, protective covers, and mounting hardware.	Selection Guide Page C-1
ARINC 600 BKA • M83527		MIL-DTL-83527, BKA, and ARINC 600 connector backshells (Sizes 1, 2, and 3).	Selection Guide Page D-1
Modular Rectangular EPXB • BACC65 • SIM • EN4165		EPXB, BACC65, EN4165, and SIM modular rectangular connector backshells.	Selection Guide Page E-1
AS81659 DPX		SAE AS81659 and DPX connector backshells and strain reliefs.	Selection Guide Page F-1
M83733 DPKA • DPKB		MIL-DTL-83733 and DPKA / DPKB connector backshells.	Selection Guide Page G-1

Band Straps and Tools

Band-Master ATS®



For more information on the Band-Master ATS EMI shield termination system, including instruction manuals and calibration details:

<https://www.glenair.com/bandmaster/>




Hand Tool for Band Installation

Glenair Band-Master ATS tools are equipped with a built-in counter to ensure required recalibration is performed in accordance with military and commercial aerospace requirements.



High Volume Pneumatic Tool

Terminate cable braid shield to adapter with stainless steel **Band-Master ATS®** bands. Install band with hand tool or bench-mounted pneumatic tool. Bands are available in three widths: **Standard** (.24 inch), **Micro** (.12 inch) and **Nano** (.075 inch). **Slim Standard** and **Micro Slim** bands have reduced thickness for weight reduction. Hardened steel **Micro-Max** bands have 60% more tensile strength than standard Micro bands. Available pre-coiled, bands are 304 series stainless steel, passivated.



Band Part Numbers

Size	A Length in mm		Fits up to Dia. in mm		B Width in mm		C Thickness in mm		Part Number Pre-coiled	Hand Tool Part Number
Standard	9	228	1.00	25.4	.24	6.1	.02	0.5	601-006	601-100
	14	355	1.80	45.7	.24	6.1	.02	0.5	601-041	
	18	457	2.50	63.5	.24	6.1	.02	0.5	601-050	
Slim Standard	9	228	.94	23.9	.24	6.1	.01	0.3	601-571	601-109
	14	355	1.80	45.7	.24	6.1	.01	0.3	601-573	
Micro	5	127	.50	12.7	.12	3.0	.015	0.4	601-025	601-101
	8	203	.88	22.4	.12	3.0	.015	0.4	601-061	
	14	356	1.88	47.7	.12	3.0	.015	0.4	601-065	
Micro Slim	8	203	.88	22.4	.12	3.0	.01	0.3	601-601	601-122
	14	356	1.88	47.7	.12	3.0	.01	0.3	601-603	
Micro-Max	8	203	.88	22.4	.12	3.0	.015	0.4	601-701	601-129
	14	356	1.88	47.7	.12	3.0	.015	0.4	601-703	
Nano	6	152	.60	15.2	.075	1.9	.009	0.9	601-501	601-108
	9	229	.94	23.9	.075	1.9	.009	0.9	601-505	
	14	356	1.80	45.7	.075	1.9	.009	0.9	601-509	

Pneumatic Banding Tool Part Numbers

Standard	Standard pneumatic banding tool with counter	601-106
Slim Standard	Slim Standard pneumatic banding tool with counter	601-110
Micro	Micro pneumatic banding tool with counter	601-107
Micro Slim	Micro Slim pneumatic banding tool with counter	601-123
Micro-Max	Micro-Max pneumatic banding tool with counter	601-130
Nano	Nano pneumatic banding tool with counter	601-118

Band Straps and Tools

Hand Banding Tools and Straps

Standard Banding Tool 601-100



Band-Master ATS® Standard Tool Designed for .240" width clamping bands in a tension range from 100 to 180 lbs. Calibrate at 150 lbs. $\pm$ 5 lbs. for most shield terminations.

Slim Standard Banding Tool 601-109



Band-Master ATS® Slim Standard Tool For use with slim standard pre-coiled .240" wide clamping bands. Tension range is approximately 30 to 80 lbs. Calibrate at 100 lbs. $\pm$ 3 lbs of linear pull.

Micro Banding Tool 601-101



Band-Master ATS® Micro Tool Designed for Micro .120" width clamping bands in a tension range from 50 to 85 lbs. Calibrate at 80 lbs $\pm$ 5 lbs. for most shield terminations.

Micro Slim Banding Tool 601-122



Band-Master ATS® Micro Slim Tool Designed for Micro Slim .120" width clamping bands in a tension range from 60 to 90 lbs. Calibrate at 82 lbs $\pm$ 3 lbs. for most terminations.

Nano Banding Tool 601-108



Band-Master ATS® Nano Tool Designed for us with Nano .075" width clamping bands in a tension range from 25 to 90 lbs. Calibrate at 50 lbs. $\pm$ 3 lbs. for most shield terminations.

Band-Master ATS® High-Tension Micro-Max Banding Tool



The 601-129 Band-Master ATS® Micro-Max with Counter for use with high-tension, low-resistivity Micro-Max Bands

Designed for use with high-tension Micro-Max .120" width clamping bands. Micro-Max is designed for shield termination requirements to a higher tension range from 100-180 lbs. resulting in lower-resistivity shield termination. Calibrate at 132 $\pm$ 3 lbs. for most shield terminations. Tool and Band should never be lubricated.

M24308 TYPE
FOR INDUSTRY-
STANDARD AND
GLENAIR SERIES 28
HIPER-D




Precision-machined
D-Sub backshells improve
shielding and environmental
performance of
MIL-DTL-24308 connectors



This catalog section includes
backshells for both standard M24308
connectors and Glenair Series 28
HiPer-D

Industry-standard M24308 D-Sub connectors are notoriously poor performers in terms of resistance to electromagnetic interference, environmental leakage, and overall mechanical durability. Glenair series backshells for D-Sub connectors are designed to markedly improve the performance of stamped-and-formed D-Subs through the use of fully-shrouded backshell enclosures, robust environmental seals, and durable machined or injection-molded construction. Also in this section, Glenair Series 28 HiPer-D connector backshells are built to advanced-performance standards in accordance with the performance benchmarks of this better-than-QPL D-Sub interconnect.


Glenair Signature Series M24308 Backshells



All Series 55 EMI backshells meet or exceed the shielding requirements of MIL-STD-461 (TEMPEST) as well as FCC Part 15 Subpart J on RS 232, RS 449 and similar installations.

D-Subminiature Accessories Selection Guide

Dust Caps & Covers



Protective Cover
289-003, -004, -019
Page A-4



Protective Cover,
Panel Mounting
500-008
Page A-5



Rubber Cover
780-518
Page A-7



Conductive Plastic
Dust Cap
289-052
Page A-8

Potting Shells



Potting Shell
557-666
Page A-9



HiPer-D Potting Shell
289-181
Page A-10

Shorting Caps



Shrouded Split
550-200
Page A-11



Solid Shorting Cap
557-493
Page A-13



HiPer-D Shorting Cap
289-064
Page A-14


Screwlocks



Female Screwlock
289-015
Page A-15



HiPer-D Female
Screwlock
289-016
Page A-15




Rear Panel Mount
Female Screwlock
559-001
Page A-15



Jackscrew
289-062
Page A-16


Replacement Screwlocks



Screwlocks for Type 1
Shrouded Backshells
687-092, -345
Page A-17



Screwlocks for Type 2 Solid
Backshells with .25" Flange
687-172, -236, -418, -626
Page A-19




Screwlocks for Type 3 Solid
Backshells with .035" Flange
687-316
Page A-21

Panel Gasket



EMI Panel Gasket
559-002
Page A-22

Dummy Stowage



Dummy Stowage Plugs
and Receptacles
500-024, 500-068
Page A-23

D-Subminiature Backshell Selection Guide

Type 1 Shrouded Backshells

- Rugged split body
- Shrouded design protects connector and enhances EMI performance
- Four shielding styles: banding, braid trap, cone-and-ring, TAG ring
- Connector is captivated between the two halves of the backshell



EMI Cone-and-Ring
550-004
Page A-24



EMI Braid Trap
550-005
Page A-26



EMI Panel Mount
550-009
Page A-28



EMI Banding
550-039
Page A-30



EMI TAG Ring®
550-041
Page A-32



Saddle Clamp
550-100
Page A-34



Qwik-Ty®
550-102
Page A-36



EMI Composite Banding
557-186
Page A-38

Type 2 Solid Backshells

- One piece machined aluminum body
- Lightweight
- Two shielding styles: banding, cone-and-ring
- Backshell attaches to connector with SST clips



EMI Banding
557-071
Page A-43



EMI Cone-and-Ring
557-110
Page A-45



EMI Elliptical Micro Band
557-246
Page A-47



Low Profile EMI Banding
557-316
Page A-49



Low Profile EMI Micro Band
557-432
Page A-51



Straight Clamp
557-467
Page A-53



EMI TAG Ring®
557-553
Page A-54

D-Subminiature Backshell Selection Guide

Type 3

Lightweight
EMI Backshells

- One piece machined aluminum body
- Thin-wall construction



EMI Banding
557-107
Page A-56



EMI Micro Band
557-281
Page A-58



45° & 90° EMI Banding
557-319
Page A-60



45° & 90° EMI Micro Band
557-561
Page A-62

Split Lip
Backshell

- Two piece machined aluminum body
- Round and elliptical banding platform



EMI Banding
557-609
Page A-42

Composite
Qwik-Snap
Backshell


- Two piece
- Elliptical banding platform




EMI Banding
557-538
Page A-40

HiPer-D
EMI
Backshells

- One piece machined aluminum body
- For standard D-Sub and HiPer-D connectors



EMI Banding
289-008
Page A-68




EMI Cone-and-Ring
289-085
Page A-70

HiPer-D
Piggyback
Backshells

- HiPer-D only, not for standard D-Sub connectors
- EMI Banding



Split EMI Banding
289-005
Page A-64



Panel Mount EMI
Banding
289-007
Page A-66




60° EMI Banding
289-087
Page A-71

D-Subminiature

289-003, 289-004, 289-019


Protective Cover



289-003, 289-004, 289-019

This accessory fits D-Subminiature M24308 and Series 28 HiPer-D connectors.

Protective cover fits Glenair Series 28 HiPer-D connectors and MIL-DTL-24308 connectors. Socket connector cover fits over connector shell and has fluorosilicone gasket. Pin connector cover fits inside connector shell. Socket connector cover has optional ground springs for EMI protection. Attach to panel with optional lanyard. Aluminum or stainless steel. Stainless steel screwlocks. Socket cover has nickel-plated copper alloy ground springs and fluorosilicone gasket.



Shell Size	A		B		C	
	±.015 (0.38)		±.015 (0.38)		in	mm
1	1.213	30.8	.494	12.6	.984	25.0
2	1.541	39.1	.494	12.6	1.312	33.3
3	2.088	53.0	.494	12.6	1.852	47.0
4	2.729	69.3	.494	12.6	2.500	63.5
5	2.635	66.9	.605	15.4	2.406	61.1
6	2.729	69.3	.668	17.0	2.500	63.5

PART NUMBER

Sample PN → **289-003 ME 3 S F 4 -06**

Base P/N	289-003	Cover, Pin Connector
	289-004	Cover, Socket Connector, with Ground Springs
	289-019	Cover, Socket Connector, No Ground Springs
Shell Size	1 2 3 4 5 6	
Material / Finish	TZ	Tin-Zinc
	MN	Mega-Nickel
	ME	Aluminum/Electroless Nickel
	NF	Aluminum/Olive Drab Cadmium
	MT	Aluminum/Nickel-PTFE
	ZR	Aluminum/Black Zinc-Nickel
Screwlocks	ZI	SST/Passivated
	N	No Screwlocks (.120 (3.0) dia. thru-holes)
	S	Socket Head Male Screwlocks
	P	Female Screwlocks (fixed, non-rotating)
Attachment Type	N	No Attachment
	F	Wire Rope, Black Nylon Jacket
	H	Wire Rope, Black FEP Jacket
Attachment Length	Omit for Attachment Type N Length in One Inch Increments (Example: "5" for five inches)	
Attachment Diameter	Omit for Attachment Type N	
	Code	Screw Size Ring ID
	Omit	#4 .126 (3.2)
	-06	#6 .145 (3.7)
	-08	#8 .187 (4.7)
	-10	#10 .197 (5.0)





TABLE 1
SCREWLOCK OPTIONS

S
4-40 SST Socket Head Male Screwlocks and Retainers



P
4-40 SST Female Screwlocks, Nuts, and Lockwashers




TABLE 2
ATTACHMENT TYPE

F
Wire Rope, Black Nylon Jacket
6/6 nylon over stainless steel rope, .034 (0.9) diameter, good flexibility, good abrasion resistance, -55 to +100 °C

H
Wire Rope, Black FEP Jacket
Black FEP jacket over SST rope, good flexibility, good abrasion resistance, .034" diameter, -65 to +200 °C

D-Subminiature

500-008

Protective Cover, Panel Mount



500-008

This accessory fits D-Subminiature M24308 and Series 28 HiPer-D connectors.

Metal cover for panel-mounted connectors. 500-008 aluminum cover fits M24308 D-Subminiature and Series 28 HiPer-D connectors. Variable height cover completely shrouds connector and seats against panel. Optional EMI panel gasket. Supplied with standard 4 inch (102mm) attachment. Cover has silicone gasket to protect connector face. Cover is supplied with 4-40 male screwlocks to mate with M24308/26 female screwlocks on panel connector. Also available with female screwlocks for use with cable mounted connectors. Aluminum body, passivated SST screwlocks, and silicone gasket.

TABLE 1
SCREWLOCK OPTIONS

No Designator Fillister Hd Male	A Socket Hd Male	H Hex Head Male
J Female	K Slotted Knurled	

PART NUMBER

Sample PN→ 500-008 M 3 R3 G A T 01 -4

Base P/N 500-008


Finish
TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size 1 2 3 4 5 6

Omit for front mounted connector.
Omit for Female Screwlocks (Code J).

Rear Panel Mounted Connector

Cover Height		Panel	Cover
	Code	Thickness	Height
	<i>Omit</i>	N/A	.344 (8.7)
	R1	.031 (0.8)	.187 (4.8)
	R2	.047 (1.2)	.171 (4.3)
	R3	.062 (1.6)	.156 (4.0)
	R4	.093 (2.4)	.125 (3.2)
	R5	.104 (2.6)	.114 (2.9)
	R6	.125 (3.2)	.093 (2.4)
	R7	.156 (4.0)	.062 (1.6)
R8	.138 (3.5)	.080 (2.0)	




EMI Panel Gasket G Gasket Included Omit if not required

Screwlocks (Table 1)
Omit Fillister Head Male Screwlocks
A Socket Head Male Screwlocks
H Hex Head Male Screwlocks
J Female Screwlocks (fixed, non-rotating)
K Knurled Slotted Head

Protective cover is supplied with standard 4 inch attachment:
SST wire rope with blue nylon jacket (Type F) and .182" diameter ring. Use the attachment codes below to modify or delete the attachment.

Attachment Type (Table 2)
Omit for standard attachment
L No Attachment
See Table 2 for Attachment Types

Omit for standard attachment. Omit for Attachment Type SK.
Attachment Diameter
Code Ring Diameter
01 .140 (3.6)
02 .182 (4.6)
04 .197 (5.0)
06 .125 (3.2)



Attachment Length Omit for standard attachment.
Length in One Inch Increments (Example: -5 for five inch length)


D-Subminiature

500-008

Protective Cover, Panel Mount

Height Code	Panel Thickness		Height	
	in	mm	in	mm
Omit	N/A	N/A	.344	8.7
R1	.031	0.8	.187	4.8
R2	.047	1.2	.171	4.3
R3	.062	1.6	.156	3.4
R4	.093	2.4	.125	3.2
R5	.104	2.6	.114	2.9
R6	.125	3.2	.093	2.4
R7	.156	4.0	.062	1.6
R8	.138	3.4	.080	2.0

COVER IS SUPPLIED WITH 4 INCH (61.0) SST WIRE ROPE WITH BLUE NYLON JACKET AND .182 (4.6) DIAMETER RING.


TABLE 2
ATTACHMENT TYPE
D**SST Bead Chain**

.125 (3.2) diameter, size 6, -65 to +200 °C

E**Wire Rope, Clear FEP Jacket**

Clear FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C

F**Wire Rope, Blue Nylon Jacket**

6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C

G**Black Nylon Rope**

Very flexible, good abrasion and fuel resistance, .062 (1.6) diameter, -55 to +100 °C

S**Sash Chain**#8 sash chain, stainless steel. Length tolerance is $\pm$ one link .280 (71)**SK****Nylon Rope with Slip Knot**

Very flexible, good abrasion and fuel resistance, .094 (2.4) diameter. Length includes .5" (13mm) dia. loop, -55 to +100 °C

T**SST Wire Rope, No Jacket**

Good flexibility, good abrasion resistance, .047 (1.2) diameter, passivated, -65 to +200 °C


U**SST Wire Rope, Black Polyurethane**

Black polyurethane coating, very flexible, excellent abrasion resistance, .080" (2mm) diameter, -55 to +125 °C


EMI PANEL GASKET

Install gasket on front side of panel. When cover is fastened to panel connector, the front edge of the cover seats onto gasket for aperture-free EMI protection.


OPTIONAL EMI GASKET



COVER SEATS ONTO EMI PANEL GASKET

**EMI PANEL GASKET**

MATL: METLASTIC (ALUMINUM MESH EMBEDDED IN SILICONE) .020 (0.5) THICK



Shell Size	Gasket Part No.	A		B		C	
		in	mm	in	mm	in	mm
1	559-002-1	.740	18.8	1.500	38.1	.980	24.9
2	559-002-2	.740	18.8	1.810	46.0	1.310	33.3
3	559-002-3	.740	18.8	2.380	60.5	1.850	47.0
4	559-002-4	.740	18.8	3.010	76.5	2.500	63.5
5	559-002-5	.850	21.6	2.920	74.2	2.410	61.2
6	559-002-6	.925	23.5	3.010	76.5	2.500	63.5

Shell Size	A Max		B Max		C	D ± .005 (0.13)		E		
	in	mm	in	mm		in	mm	in	mm	
1	1.39	35.3	.51	13.0	1.23	31.2	.984	25.0	.41	10.4
2	1.72	43.7	.51	13.0	1.56	39.6	1.312	33.3	.41	10.4
3	2.26	57.4	.51	13.0	2.10	53.3	1.852	47.0	.41	10.4
4	2.90	73.7	.51	13.0	2.74	69.6	2.500	63.5	.41	10.4
5	2.81	71.4	.62	15.7	2.65	67.3	2.406	61.1	.52	13.2
6	2.90	73.7	.68	17.3	2.74	69.6	2.500	63.5	.58	14.7

D-Subminiature

780-518


Protective Cover, Rubber



780-518

This accessory fits D-Subminiature M24308 and Series 28 HiPer-D connectors

Neoprene or silicone. 780-518 rubber cover fits M24308 D-Subminiature and Series 28 HiPer-D connectors. Cover protects connector from damage and contamination. Three material choices: black neoprene, carbon-filled conductive black neoprene, or red silicone. Attach cover with nylon rope. Attachment choices include cable tie, slip knot or stainless steel ring. **Not rated for water immersion.**



PART NUMBER

Sample PN→

780-518 -25S G 4 -06 C

Base P/N 780-518


Size -09P -15P -25P -37P -50P -104P
-09S -15S -25S -37S -50S -104S

Attachment *Omit for none*
G Nylon Rope

Attachment Length Length in One Inch Increments
(Example: 4 for four inch lanyard)

Attachment Fitting	Code	Fitting Type	Ring Dia.
	-00	No Fitting	N/A
	-04	Ring	.197 (5.0)
	-06	Ring	.125 (3.2)
	-07	Ring	.218 (5.5)
	-09	Ring	.156 (4.0)
	-WS	Cable Tie	N/A
	-SK	Slip Knot	N/A

RING ID



Material *Omit* Black Neoprene
C Conductive Black Neoprene (10⁵ Ω/square min.)
S Red Silicone

Size	A		B		C		D	
	in	mm	in	mm	in	mm	in	mm
09S	.61	15.5	.28	7.1	.22	5.6	.82	20.8
09P	.65	16.5	.33	8.4	.23	5.8	.82	20.8
15S	.94	23.9	.28	7.1	.24	6.1	1.26	32.0
15P	.97	24.6	.33	8.4	.24	6.1	1.26	32.0
25S	1.48	37.6	.28	7.1	.25	6.4	1.76	44.7
25P	1.50	38.1	.33	8.4	.25	6.4	1.78	45.2
37S	2.12	53.8	.28	7.1	.23	5.8	2.37	60.2
37P	2.15	54.6	.33	8.4	.23	5.8	2.37	60.2
50S	2.03	51.6	.39	9.9	.24	6.1	2.28	57.9
50P	2.05	52.0	.45	11.4	.23	5.8	2.28	57.9
104S	2.23	56.7	.47	11.9	.25	6.4		61.2
104P	2.26	57.4	.50	12.7	.23	5.8	2.41	61.2

ATTACHMENT FITTING

SK SLIP KNOT



Nylon Rope, Kynar Friction Sleeve

WS CABLE TIE



6/6 nylon cable tie with screw and locknut.
1.77 (45.0) max. wire bundle dia. -40 to +85 °C.

RING TERMINAL



Screw Size	Ring Code	Ring I.D. ± .010 (0.25) in mm	
#4	-06	.125	3.2
#6	-09	.156	4.0
#8	-04	.197	5.0
#10	-07	.218	5.5

D-Subminiature

289-052
Conductive Dust Cap




289-052

This accessory fits D-Subminiature M24308 connectors and Series 28 HiPer-D connectors.

		PART NUMBER			
Size	Part No.	A		B	
		in	mm	in	mm
1P (E-9P)	289-052-1-P	.86	21.8	.51	13.0
1S (E-9S)	289-052-1-S	.79	20.1	.45	11.4
2P (A-15P)	289-052-2-P	1.19	30.2	.51	13.0
2S (A-15S)	289-052-2-S	1.10	27.9	.45	11.4
3P (B-25P)	289-052-3-P	1.70	43.2	.52	13.0
3S (B-25S)	289-052-3-S	1.66	42.2	.46	11.7
4P (C-37P)	289-052-4-P	2.37	60.2	.52	13.0
4S (C-37S)	289-052-4-S	2.29	58.2	.45	11.4
5P (D-50P)	289-052-5-P	2.27	57.7	.62	15.8
5S (D-50S)	289-052-5-S	2.21	56.1	.56	14.2
6P (F-104P)	289-052-6-P	2.40	61.0	.69	17.5
6S (F-104S)	289-052-6-S	2.33	59.2	.63	16.0

Conductive dust caps fit HiPer-D® and M24308-type D-Subminiature connectors. These caps provide electrostatic discharge protection to sensitive equipment. These caps meet the static decay requirement of MIL-PRF-81705E. Surface resistivity is less than 1 x 10⁵ ohms/square. Integral lip allows easy removal. Conductive polyethylene copolymer.



D-Subminiature



557-666

Potting Shell



557-666

This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Aluminum potting shell fits M24308-type D-Subminiature connectors. Available in five standard finishes. Fill with potting compound to encapsulate connector terminals and to provide wire strain relief. One piece aluminum shell with passivated stainless steel screwlocks and clips.

Shell Size	A Max		B		C	
	in	mm	in	mm	±.005 (0.13)	in
1	1.203	30.6	.500	12.7	.984	25.0
2	1.531	38.9	.500	12.7	1.312	33.3
3	2.078	52.8	.500	12.7	1.852	47.0
4	2.718	69.0	.500	12.7	2.500	63.5
5	2.625	66.7	.609	15.5	2.406	61.1

PART NUMBER

Sample PN → **557-666** **M** **3** **A**

Base P/N **557-666**

Finish

- TZ** Tin-Zinc
- MN** Mega-Nickel
- JF** Cadmium, Yel. Chromate
- M** Electroless Nickel
- NF** Olive Drab Cadmium
- MT** Nickel-PTFE
- ZR** Black Zinc-Nickel

Shell Size **1 2 3 4 5**

Screwlocks (Table 1)

- Omit** .128 (3.3) diameter thru holes
- A** Socket Head Male Screwlocks
- C** Fillister Head Slotted Male Screwlocks






TABLE 1
SCREWLOCK OPTIONS

A


4-40 Socket Head Male Screwlocks with Clips



Part Number **687-316M**
Order 2 per backshell

C

4-40 Fillister Head Male Screwlocks with Clips



Part Number **687-316**
Order 2 per backshell

D-Subminiature

289-181

Potting Shell, HiPer-D



289-181

This accessory fits HiPer-D connectors with backshell groove: 280-018P, 280-019S, 280-046P, 280-047S. Not compatible with standard D-Sub connectors.

HiPer-D Potting Shell. Low profile two piece potting shell fits HiPer-D® connectors with backshell groove (280-018P, 280-019S, 280-046P, 280-047S). Available in five standard finishes. Fill cavity with potting compound to provide wire strain relief. Aluminum with passivated stainless steel screwlocks and clips.

PART NUMBER


Sample PN→ 289-181 2 NF

Base P/N 289-181

Shell Size 1 2 3 4 5 6

Finish
TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Height
Omit .75 (19.1) Height
4 1.00 (25.4) Height
6 1.50 (38.1) Height



* HEIGHT ACCORDING TO P/N

Shell Size	A Max		B Max		C		D	
	in	mm	in	mm	in	mm	in	mm
1	.894	22.7	.550	14.0	.65	16.5	.38	9.7
2	1.218	30.9	.550	14.0	.88	22.4	.38	9.7
3	1.760	44.7	.550	14.0	1.50	38.1	.38	9.7
4	2.408	61.2	.550	14.0	2.13	54.1	.38	9.7
5	2.297	58.3	.654	16.6	1.90	48.3	.50	12.7
6	2.422	61.5	.716	18.2	2.13	54.1	.55	14.0

D-Subminiature

550-200

Shorting Cap Backshell, Shrouded




550-200

This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Split, shrouded. 550-200 shorting cap fits M24308 D-Subminiature connectors. Two piece backshell has overlapping lip for EMI shielding. Install optional EMI gasket on mating connector panel. Connector is captivated between backshell halves. Eleven shroud lengths to accommodate mating connector mounting dimensions. #4-40 screwlocks are included. Aluminum with stainless steel screws and washers.

TABLE 1
SCREWLOCK OPTIONS



PART NUMBER

Sample PN → **550-200 NF 4 R3 K 0 U 6 -06**

Base P/N		550-200
Finish	TZ	Tin-Zinc
	MN	Mega-Nickel
	JF	Cadmium, Yel. Chromate
	M	Electroless Nickel
	NF	Olive Drab Cadmium
	MT	Nickel-PTFE
	ZR	Black Zinc-Nickel
Shell Size		1 2 3 4 5 6
Shroud Length	Mating Connector Rear Panel Mounting	
	Panel	
	Code	Thickness E
	R1	.031 (0.8) .247 (6.3)
	R2	.047 (1.2) .231 (5.9)
	R3	.062 (1.6) .216 (5.5)
	R4	.093 (2.4) .185 (4.7)
	R5	.104 (2.6) .174 (4.4)
	R6	.125 (3.2) .153 (3.9)
	R7	.156 (4.0) .125 (3.2)
	R8	.135 (3.4) .140 (3.6)
	R9	.188 (4.8) .094 (2.4)
	CC	Cable-to-Cable .174 (4.4)
F0	Front Panel Mtng. .343 (8.7)	
Screwlocks (Table 1)	A	Male, Socket Head
	B	Male, Fillister Head
	E	Male, Extended Slotted
	H	Male, Hex Head, Drilled
	K	Male, Slotted, Knurled
	P	Female Hex Post, Fixed
EMI Panel Gasket	0	No Gasket
	1	Gasket Included (install on mating connector)
Attachment Type (Table 2)		Omit if not required. See Table 2 for attachment types.
Attachment Length		Omit if not required. Length in One Inch Increments
Attachment Ring (Table 3)		Omit if not required See Table 3 for attachment ring options.



D-Subminiature

550-200

Shorting Cap Backshell, Shrouded

TABLE 2
ATTACHMENT TYPE
D**SST Bead Chain**

.125 (3.2) diameter, size 6, -65 to +200 °C

F**Wire Rope, Blue Nylon Jacket**

6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C

G**Black Nylon Rope**

Very flexible, good abrasion and fuel resistance, .094 (2.4) diameter, -55 to +100 °C

H**Wire Rope, Clear FEP Jacket**

Clear FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C

S**Sash Chain**

#8 sash chain, stainless steel. Length tolerance is ± one link .280 (71)

T**SST Wire Rope, No Jacket**

Good flexibility, good abrasion resistance, .047 (1.2) diameter, passivated, -65 to +200 °C

U**SST Wire Rope, Black Polyurethane**


Black polyurethane coating, very flexible, excellent abrasion resistance, .080" (2mm) diameter, -55 to +125 °C

Shroud Length	Mating Connector Panel		E	F					
	Thickness	Shroud Length		Size 1, 2		Size 3, 4, 5		Size 6	
in	mm	in	mm	in	mm	in	mm	in	mm
CC	N/A	N/A	.174	4.4	1.451	36.9	1.671	42.4	46.2
F0	N/A	N/A	.343	8.7	1.625	41.3	1.844	46.8	50.8
R1	.031	0.8	.247	6.3	1.525	38.7	1.745	44.3	48.0
R2	.047	1.2	.231	5.9	1.509	38.3	1.728	43.9	47.6
R3	.062	1.6	.216	5.5	1.500	38.1	1.720	43.7	47.2
R4	.093	2.4	.185	4.7	1.470	37.3	1.690	42.9	46.5
R5	.104	2.6	.174	4.4	1.451	36.9	1.671	42.4	46.2
R6	.125	3.2	.153	3.9	1.430	36.3	1.650	41.9	45.7
R7	.156	4.0	.125	3.2	1.400	35.6	1.620	41.1	44.9
R8	.135	3.4	.140	3.6	1.417	36.0	1.637	41.6	45.8
R9	.188	4.8	.094	2.4	1.368	34.7	1.590	40.6	44.2

Shell Size	A Max		B Max		C		D	
	in	mm	in	mm	in	mm	± .005 (0.13)	mm
1	1.393	35.4	.624	15.8	.312	7.9	.984	25.0
2	1.706	43.3	.624	15.8	.312	7.9	1.312	33.3
3	2.265	57.5	.624	15.8	.312	7.9	1.852	47.0
4	2.900	73.7	.624	15.8	.312	7.9	2.500	63.5
5	2.800	71.1	.750	19.1	.375	9.5	2.406	61.1
6	2.900	73.7	.844	21.4	.422	10.7	2.500	63.5

TABLE 3
ATTACHMENT RING

EYELET




Code	Eyelet I.D.
06	.125 (3.2)
01	.140 (3.6)
02	.182 (4.6)
04	.197 (5.0)

SPLIT RING






Code	Ring I.D.
50	.425 (10.8)
52	.485 (12.3)
54	.640 (16.3)
56	.750 (19.1)
58	.890 (22.6)
60	1.015 (25.8)
64	1.130 (28.7)
68	1.350 (34.3)



EMI PANEL GASKET

Install gasket on front side of mating connector panel. Gasket is die cut from .020" thick metalastic (aluminum mesh and silicone) material. When backshell is fastened to panel connector, the front edge of the shroud seats onto gasket for aperture-free EMI protection.




Shell Size	Gasket Part No.	A		B		C	
		in	mm	in	mm	in	mm
1	559-002-1	.740	18.8	1.500	38.1	.980	24.9
2	559-002-2	.740	18.8	1.810	46.0	1.310	33.3
3	559-002-3	.740	18.8	2.380	60.5	1.850	47.0
4	559-002-4	.740	18.8	3.010	76.5	2.500	63.5
5	559-002-5	.850	21.6	2.920	74.2	2.410	61.2
6	559-002-6	.925	23.5	3.010	76.5	2.500	63.5

D-Subminiature

289-064

Shorting Cap Backshell, HiPer-D



289-064

This accessory fits HiPer-D connectors with backshell groove: 280-018P, 280-019S, 280-046P, 280-047S. Not compatible with standard D-Sub connectors.

HiPer-D Shorting Cap. Low profile two piece adapter fits HiPer-D® connectors with backshell groove (280-018P, 280-019S, 280-046P, 280-047S). Available in five standard finishes. Optional lanyard for attaching cap. Aluminum with passivated stainless steel screwlocks and clips.

ATTACHMENT TYPE

F

Wire Rope, Black Nylon Jacket
6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C

H

Wire Rope, Black FEP Jacket
Black FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C

Shell Size	A Max		B Max	
	in	mm	in	mm
1	.894	22.7	.550	14.0
2	1.218	30.9	.550	14.0
3	1.760	44.7	.550	14.0
4	2.408	61.2	.550	14.0
5	2.297	58.3	.654	16.6
6	2.422	61.5	.716	18.2

PART NUMBER

Sample PN→ 289-064 3 JF H 4



Base P/N 289-064

Shell Size 1 2 3 4 5 6

Finish
TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Attachment Type
Omit No Attachment
F Wire Rope, Black Nylon Jacket
H Wire Rope, Black FEP Jacket


Attachment Length
Omit No Attachment
Length in One Inch Increments (Example: "5" for five inch length)



D-Subminiature

289-015, 289-016, 559-001



Female Screwlock, Panel Mounting

289-015 FEMALE SCREWLOCK KIT, FRONT OR REAR MOUNTING, .50 (12.7) OAL

Attach D-Subminiature connectors to panel with 289-015 female screwlock kit. Kit contains (2) posts, (2) lockwashers and (2) nuts. 300 Series stainless steel.
Order (1) kit per connector.

PART NUMBER



Panel Thickness		Part No.	A	
in	mm		in	mm
(None)	(None)	289-015-A	.250	6.4
.031	0.8	289-015-B	.219	5.6
.047	1.2	289-015-C	.203	5.2
.062	1.6	289-015-D	.188	4.8

**289-016 FEMALE SCREWLOCK, HIPER-D, .40 (10.2) OAL**

Attach connector to panel with shortened 289-016 female screwlock. For use with HiPer-D connectors with tapped 4-40 mounting holes. Install with threadlocking compound. Kit contains (2) posts. 300 Series stainless steel, passivated.
Order (1) kit per connector.

PART NUMBER




Panel Thickness		Part No.	A	
in	mm		in	mm
(None)	(None)	289-016-A	.250	6.4
.031	0.8	289-016-B	.219	5.6
.047	1.2	289-016-C	.203	5.2
.062	1.6	289-016-D	.188	4.8

**559-001 FEMALE SCREWLOCK KIT, REAR MOUNTING**

For rear panel mounting. Attach D-Subminiature connectors to panel with 559-001 female screwlock kit. Kit contains (2) posts, (8) flat washers, (2) lockwashers and (2) nuts. 300 Series stainless steel.
Order (1) kit per connector.

PART NUMBER

Material/ Finish	Part No.
Steel/ Yellow Chromate over Cadmium	559-001
Stainless Steel/ Passivated	559-001-49



Panel Thickness		A		ø B		No. of Washers
in	mm	in	mm	in	mm	
.031	0.8	No Counterbore		—		4
.047	1.2	No Counterbore		—		4
.062	1.6	.020	0.51	.171	4.3	3
.093	2.4	.051	1.30	.171	4.3	2
.104	2.6	.062	1.6	.171	4.3	1
.125	3.2	.083	2.1	.171	4.3	1
.156	4.0	.114	2.9	.171	4.3	2
.140	3.5	.098	2.5	.171	4.3	2
.188	4.8	.146	3.7	.219	5.6	2

D-Subminiature




289-062


Jackscrew, HiPer-D

- For Connector without Backshell
- Fits Series 28 HiPer-D and M24308
- Includes Retention Clip

289-062 JACKSCREW FOR HIPER-D CONNECTOR WITHOUT BACKSHELL




Socket Head Jackscrew



Hex Head Jackscrew



Slot Head Jackscrew




Long Jackscrew

Jackscrew fits Series 28 HiPer-D and M24308 D-Subminiature connectors. Available in two lengths and three styles: socket head, hex head and knurled slot head. For connector without backshell. Kit includes (2) jackscrews and (2) clips. 300 Series stainless steel. *Order (1) kit per connector.*


PART NUMBER

Length	Head Style	Part No.
Short 1	Socket Head	289-062Z1S1
	Hex Head	289-062Z1H1
	Knurled Slot Hd.	289-062Z1F1
Long 2	Socket Head	289-062Z1S2
	Hex Head	289-062Z1H2
	Knurled Slot Hd.	289-062Z1F2


HEX HEAD



SOCKET HEAD




RETENTION CLIP



*the '2' length Long jackscrew does not work with backshells 289T005, 289S005, 289T008, and 289S008. Order '1' length Short jackscrew for these backshells.


KNURLED SLOT HEAD



D-Subminiature



687-092, 687-345

Replacement Screwlocks for Type 1 Shrouded Backshells

687-092A SOCKET HEAD MALE SCREWLOCK FOR TYPE 1 BACKSHELLS



Replacement male screwlock for Type 1 split shrouded Series 550 backshells. 300 Series stainless steel. Includes nylon washer.

- Order (2) per backshell
- Fits Top Entry and Side Entry backshells

PART NUMBER**687-092A****687-092B FILLISTER HEAD MALE SCREWLOCK FOR TYPE 1 BACKSHELLS**

Replacement male screwlock for Type 1 split shrouded Series 550 backshells. 300 Series stainless steel. Includes nylon washer.

- Order (2) per backshell
- Fits Top Entry and Side Entry backshells



PART NUMBER**687-092B****687-092E EXTENDED KNURLED SLOT HEAD MALE SCREWLOCK FOR TYPE 1 BACKSHELLS**

Replacement male screwlock for Type 1 split shrouded Series 550 backshells. 300 Series stainless steel. Includes nylon washer.

- Order (2) per backshell
- Fits Top Entry and Side Entry backshells


PART NUMBER

Shell Size	Part No.	A	
		in	mm
1	687-092E1	1.03	26.2
2	687-092E2	1.03	26.2
3-6	687-092E	1.53	38.9

**687-092H HEX HEAD SLOTTED DRILLED MALE SCREWLOCK FOR TYPE 1 BACKSHELLS**

Replacement male screwlock for Type 1 split shrouded Series 550 backshells. 300 Series stainless steel. Hex head is cross-drilled for safety wire.

- Order (2) per backshell
- Fits Top Entry and Side Entry backshells


PART NUMBER**687-092H**

D-Subminiature

687-092, 687-345

Replacement Screwlocks for Type 1 Shrouded Backshells

687-092K KNURLED SLOTTED MALE SCREWLOCK FOR TYPE 1 BACKSHELLS




Replacement male screwlock for Type 1 split shrouded Series 550 backshells. 300 Series stainless steel. Head is cross-drilled for safety wire.


- Order (2) per backshell
- Fits Top Entry and Side Entry backshells

PART NUMBER

687-092K



687-092P FEMALE SCREWLOCK FOR TYPE 1 BACKSHELLS




Replacement female screwlock for Type 1 split shrouded Series 550 backshells. 300 Series stainless steel. Fixed, non-rotating.


- Order (2) per backshell
- Fits Top Entry and Side Entry backshells

PART NUMBER

687-092P



687-345 MALE SCREWLOCK FOR TYPE 1 END ENTRY BACKSHELLS





Replacement male screwlock for End Entry Type 1 split shrouded Series 550 backshells. 300 Series stainless steel. Hex head or knurled slot head. Includes nylon washer and heatshrink tube.

- Order (2) per backshell
- Fits End Entry backshells

PART NUMBER


Head Style	Shell Size	Part No.	A	
			in	mm
Slot	1-2	687-345-03	1.87	47.5
	3-6	687-345-04	2.16	54.9
Hex	1-2	687-345-03H	1.87	47.5
	3-6	687-345-04H	2.16	54.9



D-Subminiature



687-172, 687-236

Replacement Screwlocks for Type 2 Solid Backshells (.25" Flange)

687-172 SOCKET HEAD MALE JACKSCREW WITH "E" RING



Replacement socket head male jackscrew for Type 2 solid Series 557 backshells with .25 (6.4) flange. Included "E" ring retains connector and screw to backshell. 300 Series stainless steel.

- Order (2) per backshell
- Fits Type 2 solid backshells with .25 (6.4) flange

PART NUMBER**687-172****687-236, 687-236S** SOCKET HEAD MALE SCREWLOCK WITH CLIP



Replacement socket head male screwlock for Type 2 solid Series 557 backshells with .25 (6.4) flange. Available with safety wire hole. Includes clip. 300 Series stainless steel.

- Order (2) per backshell
- Fits Type 2 solid backshells with .25 (6.4) flange

PART NUMBERSocket Head **687-236**Socket Head w/ Safety Wire Hole **687-236S****687-236B** SLOTTED FILLISTER HEAD MALE SCREWLOCK WITH CLIP


Replacement fillister head male screwlock for Type 2 solid Series 557 backshells with .25 (6.4) flange. Includes clip. 300 Series stainless steel.

- Order (2) per backshell
- Fits Type 2 solid backshells with .25 (6.4) flange

PART NUMBER**687-236B****687-236H** HEX HEAD MALE SCREWLOCK WITH CLIP

Replacement hex head male screwlock for Type 2 solid Series 557 backshells with .25 (6.4) flange. Includes clip. 300 Series stainless steel.

- Order (2) per backshell
- Fits Type 2 solid backshells with .25 (6.4) flange


PART NUMBER**687-236H**

D-Subminiature

687-236X, 687-418, 687-626

Replacement Screwlocks for Type 2 Solid Backshells (.25" Flange)

687-236X CROSS RECESS HEAD MALE SCREWLOCK WITH CLIP




Replacement cross recess head male screwlock for Type 2 solid Series 557 backshells with .25 (6.4) flange. 300 Series stainless steel.


- Order (2) screws per backshell
- Fits Type 2 solid backshells with .25 (6.4) flange

PART NUMBER

687-236X



687-418 FEMALE SCREWLOCK




Replacement female screwlock for Type 2 solid Series 557 backshells with .25 (6.4) flange. Includes slotted nut and lockwasher.


- Order (2) screws per backshell
- Fits Type 2 solid backshells with .25 (6.4) flange

PART NUMBER

687-418F



687-626 EXTENDED SLOT HEAD MALE SCREWLOCK WITH CLIP




Replacement socket head male screwlock for Type 2 solid Series 557 backshells with .25 (6.4) flange. 300 Series stainless steel.

- Order (2) per backshell
- Fits Type 2 solid backshells with .25 (6.4) flange
- Not for End Entry backshells

PART NUMBER

Shell Size	Part No.	Length	
		in	mm
1-2	687-626-1E	.75	19.1
3-6	687-626-2E	1.00	25.4




D-Subminiature

687-316

Replacement Screwlocks for Type 3 Solid Backshells (.035" Flange)

687-316 FILLISTER HEAD MALE SCREWLOCK WITH CLIP




Replacement slotted fillister head male screwlock for Type 3 solid Series 557 ultra-lightweight backshells with .035 (0.9) flange. 300 Series stainless steel. Includes clip.


- Order (2) per backshell
- Fits Type 3 solid backshells with .035 (0.9) flange

PART NUMBER

687-316



687-316M SOCKET HEAD MALE SCREWLOCK WITH CLIP




Replacement socket head male screwlock for Type 3 solid Series 557 ultra-lightweight backshells with .035 (0.9) flange. 300 Series stainless steel. Includes clip.


- Order (2) per backshell
- Fits Type 3 solid backshells with .035 (0.9) flange

PART NUMBER

687-316M



687-316H HEX HEAD MALE SCREWLOCK




Replacement slotted hex head male screwlock for Type 3 solid Series 557 ultra-lightweight backshells with .035 (0.9) flange. 300 Series stainless steel. Includes clip.


- Order (2) per backshell
- Fits Type 3 solid backshells with .035 (0.9) flange

PART NUMBER

687-316H



687-316E1 EXTENDED LENGTH SLOTTED MALE SCREWLOCK WITH CLIP




Replacement slotted fillister head male screwlock for Type 3 solid Series 557 ultra-lightweight backshells with .035 (0.9) flange. 300 Series stainless steel. Includes clip.

- Order (2) per backshell
- Fits Type 3 solid backshells with .035 (0.9) flange

PART NUMBER


687-316E1



D-Subminiature

559-002
EMI Panel Gasket



559-002 EMI PANEL GASKET FOR TYPE 1 SHROUDED BACKSHELLS



Gasket attaches to panel-mounted D-Subminiature connector. Use with shrouded Type 1 backshell. Backshell shroud seats onto gasket for EMI protection. Woven aluminum wire embedded in silicone.

■ For Series 550 Type 1 split backshells

PART NUMBER							
Shell Size	Gasket Part No.	A in	A mm	B in	B mm	C in	C mm
1	559-002-01	.740	18.8	1.500	38.1	.980	24.9
2	559-002-02	.740	18.8	1.810	46.0	1.312	33.3
3	559-002-03	.740	18.8	2.380	60.5	1.852	47.0
4	559-002-04	.740	18.8	3.010	76.5	2.500	63.5
5	559-002-05	.850	21.6	2.920	74.2	2.406	61.1
6	559-002-06	.925	23.5	3.010	76.4	2.500	63.5




Install gasket onto panel with M24308/26 female screwlocks. When backshell is fastened to panel connector, the front edge of the shroud seats onto gasket for aperture-free EMI protection.

D-Subminiature


500-024, 500-068

Dummy Stowage Plugs and Receptacles

Use dummy stowage accessory to secure and protect unused D-Subminiature connectors. Aluminum with silicone rubber gasket.

**500-024**

Dummy Plug for Stowing D-Sub Pin
(Receptacle) Connectors

**500-068**

Dummy Receptacle for Stowing D-Sub
Socket (Plug) Connectors


PART NUMBER

Sample PN → **500-024 M 4**


Base P/N **500-024** Dummy Stowage Plug
500-068 Dummy Stowage Receptacle

Finish **TZ** Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size **1 2 3 4 5 6**

500-024 DUMMY STOWAGE PLUG

Shell Size	C									
	A		B Max		± .005 (0.13)		D Max		E	
	in	mm	in	mm	in	mm	in	mm	in	mm
1	1.213	30.8	.648	16.5	.984	25.0	.316	8.0	.494	12.5
2	1.541	39.1	.976	24.8	1.312	33.3	.316	8.0	.494	12.5
3	2.088	53.0	1.516	38.5	1.852	47.0	.316	8.0	.494	12.5
4	2.729	69.3	2.164	55.0	2.500	63.5	.316	8.0	.494	12.5
5	2.635	66.9	2.069	52.6	2.406	61.1	.428	10.9	.605	15.4
6	2.729	69.3	2.194	55.7	2.500	63.5	.490	12.4	.668	17.0

500-068 DUMMY STOWAGE RECEPTACLE

Shell Size	C									
	A		B Max		± .005 (0.13)		D Max		E	
	in	mm	in	mm	in	mm	in	mm	in	mm
1	1.213	30.8	.661	16.8	.984	25.0	.324	8.2	.494	12.5
2	1.541	39.1	.989	25.1	1.312	33.3	.324	8.2	.494	12.5
3	2.088	53.0	1.529	38.8	1.852	47.0	.324	8.2	.494	12.5
4	2.729	69.3	2.177	55.3	2.500	63.5	.324	8.2	.494	12.5
5	2.635	66.9	2.074	52.7	2.406	61.1	.436	11.1	.605	15.4
6	2.729	69.3	2.207	56.1	2.500	63.5	.498	12.6	.668	17.0

D-Subminiature




550-004

Shrouded Backshell, EMI

- Split EMI Backshell
- Cone-and-Ring Shield Termination
- Saddle Clamp Strain Relief

**T** Top Entry**S** Side Entry**E** End Entry


CONE-AND-RING



550-004

This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Split, Cone-and-Ring shield termination. 550-004 diecast aluminum backshell fits M24308 D-Subminiature connectors. EMI protected with ground ring for terminating cable shield. Backshell fully shrouds the connector. Eleven shroud lengths. Choose shroud length based on mating connector mounting style. Optional EMI panel gasket installs onto mating connector. When mated, the backshell shroud seats onto the gasket for low-resistance grounding and EMI protection.

TABLE 1
SCREWLOCK OPTIONS


PART NUMBER

Sample PN → **550T004** **M** **3** **R3** **A** **0** **F** **04**

Base P/N	550T004 T Top Entry
	550E004 E End Entry
	550S004 S Side Entry

Finish	TZ Tin-Zinc
	MN Mega-Nickel
	JF Cadmium, Yel. Chromate
	M Electroless Nickel
	NF Olive Drab Cadmium
	MT Nickel-PTFE
ZR Black Zinc-Nickel	

Shell Size	1 2 3 4 5 6
------------	--------------------

Shroud Length	Mating Connector Rear Panel Mounting	
	Code	Panel Thickness E
	R1	.031 (0.8) .247 (6.3)
	R2	.047 (1.2) .231 (5.9)
	R3	.062 (1.6) .216 (5.5)
	R4	.093 (2.4) .185 (4.7)
	R5	.104 (2.6) .174 (4.4)
	R6	.125 (3.2) .153 (3.9)
	R7	.156 (4.0) .125 (3.2)
	R8	.135 (3.4) .140 (3.6)
	R9	.188 (4.8) .094 (2.4)
	CC	Cable-to-Cable .174 (4.4)
	F0	Front Panel Mount .343 (8.7)




Screwlocks (Table 1)	Code	Type	Profiles
	A	Male, Socket Head	S T
	B	Male, Fillister Head	S T
	E	Male, Extended Slotted	S T
	H	Male, Hex Head, Drilled	S T
	J	Male, Slotted, Knurled	E
	K	Male, Slotted, Knurled	S T
	P	Female Hex Post, Fixed	S T

EMI Panel Gasket	0 No Gasket
	1 Gasket Included <i>(install on mating connector)</i>

Strain Relief	F Saddle Clamp
---------------	-----------------------

Entry Size	Entry Size	Cable Range		Shell Size
		Min	Max	
	02	.125 (3.2)	.250 (6.4)	1-6
	03	.250 (6.4)	.375 (9.5)	1-6
	04	.312 (7.9)	.500 (12.7)	1-6
	05	.437 (11.1)	.625 (15.9)	1-6
	06	.562 (14.3)	.750 (19.1)	1-6
	07	.687 (17.4)	.875 (22.2)	6
08	.812 (20.6)	1.000 (25.4)	6	




D-Subminiature

550-004

Shrouded Backshell, EMI

- Split EMI Backshell
- Cone-and-Ring Shield Termination
- Saddle Clamp Strain Relief



Shell Size	A Max		B Max		C	mm	D		P		R		Max Entry Size
	in	mm	in	mm			± .005 (0.13)	in	mm	in	mm		
1	1.393	35.4	.624	15.8	.312	7.9	.984	25.0	.730	18.5	.719	18.3	06
2	1.706	43.3	.624	15.8	.312	7.9	1.312	33.3	1.050	26.7	.719	18.3	06
3	2.265	57.5	.624	15.8	.312	7.9	1.852	47.0	1.594	40.5	.938	23.8	06
4	2.900	73.7	.624	15.8	.312	7.9	2.500	63.5	2.240	56.9	.938	23.8	06
5	2.800	71.1	.750	19.1	.375	9.5	2.406	61.1	2.140	54.4	.938	23.8	06
6	2.900	73.7	.844	21.4	.422	10.7	2.500	63.5	2.240	56.9	1.094	27.8	08



Shroud Length	Mating Connector Panel		E		F						G			
	Thickness		Shroud Length		Size 1, 2		± .031 (0.8) Size 3, 4, 5		Size 6		± .031 (0.8) Size 1, 2		Size 3-6	
					in	mm	in	mm	in	mm	in	mm	in	mm
CC	N/A	N/A	.174	4.4	1.451	36.9	1.671	42.4	1.820	46.2	1.583	40.2	1.831	46.7
F0	N/A	N/A	.343	8.7	1.625	41.3	1.844	46.8	2.000	50.8	1.750	44.5	2.000	50.8
R1	.031	0.8	.247	6.3	1.525	38.7	1.745	44.3	1.890	48.0	1.656	42.1	1.904	48.4
R2	.047	1.2	.231	5.9	1.509	38.3	1.728	43.9	1.875	47.6	1.640	41.7	1.888	48.0
R3	.062	1.6	.216	5.5	1.500	38.1	1.720	43.7	1.860	47.2	1.625	41.3	1.873	47.6
R4	.093	2.4	.185	4.7	1.470	37.3	1.690	42.9	1.829	46.5	1.594	40.5	1.842	46.8
R5	.104	2.6	.174	4.4	1.451	36.9	1.671	42.4	1.820	46.2	1.583	40.2	1.831	46.5
R6	.125	3.2	.153	3.9	1.430	36.3	1.650	41.9	1.798	45.7	1.563	39.7	1.811	46.0
R7	.156	4.0	.125	3.2	1.400	35.6	1.620	41.1	1.767	44.9	1.531	38.9	1.781	45.2
R8	.135	3.4	.140	3.6	1.417	36.0	1.637	41.6	1.805	45.8	1.550	39.4	1.798	45.7
R9	.188	4.8	.094	2.4	1.368	34.7	1.590	40.6	1.740	44.2	1.500	38.1	1.750	44.5

Entry Size	H Max		Cable Range				Shell I.D. Min.			
	in	mm	in	mm	in	mm	in	mm	in	mm
02	.968	24.6	.125	3.2	.250	6.4	.375	9.5	.375	9.5
03	1.046	26.6	.250	6.4	.375	9.5	.475	12.1	.475	12.1
04	1.156	29.4	.312	7.9	.500	12.7	.475	12.1	.475	12.1
05	1.218	30.9	.437	11.1	.625	15.9	.475	12.1	.475	12.1
06	1.343	34.1	.562	14.3	.750	19.1	.575	14.6	.575	14.6
07	1.468	37.3	.687	17.4	.875	22.2	1.000	25.4	1.000	25.4
08	1.593	40.5	.812	20.6	1.000	25.4				


Shell Size	Shell I.D. mm.			
	Top Entry		End Entry	
	in	mm	in	mm
1	.250	6.4	.375	9.5
2	.375	9.5	.375	9.5
3	.475	12.1	.475	12.1
4	.475	12.1	.475	12.1
5	.575	14.6	.575	14.6
6	1.000	25.4	1.000	25.4

EMI PANEL GASKET

Install gasket on front side of mating connector panel. When backshell is fastened to panel connector, the front edge of the shroud seats onto gasket for aperture-free EMI protection.



EMI PANEL GASKET
.020 (0.5) THICK
MATL: ALUMINUM
MESH EMBEDDED IN
SILICONE



Shell Size	Gasket Part No.	A		B		C	
		in	mm	in	mm	in	mm
1	559-002-1	.740	18.8	1.500	38.1	.980	24.9
2	559-002-2	.740	18.8	1.810	46.0	1.312	33.3
3	559-002-3	.740	18.8	2.380	60.5	1.852	47.0
4	559-002-4	.740	18.8	3.010	76.5	2.500	63.5
5	559-002-5	.850	21.6	2.920	74.2	2.406	61.1
6	559-002-6	.925	23.5	3.010	76.4	2.500	63.5



D-Subminiature

550-005

Shrouded Backshell, Braid Trap

- Split EMI Backshell
- Braid Trap Shield Termination
- Saddle Clamp Strain Relief




550-005

This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Braid trap shield termination. 550-005 diecast aluminum backshell fits M24308 D-Subminiature connectors. EMI protected. Tapered candelabra thread captivates shield braid. Backshell has groove for heatshrink boot (P/N 770-007). Backshell fully shrouds the connector. Eleven shroud lengths. Choose shroud length based on mating connector mounting style. Optional metalastic EMI panel gasket installs onto mating connector. When fully mated, the backshell shroud seats onto the gasket for low-resistance grounding and EMI protection. Aluminum alloy, stainless steel hardware.

TABLE 1 SCREWLOCK OPTIONS



PART NUMBER

Sample PN → 550T005 M 3 R3 A 0 F 04

Base P/N	550T005	T	Top Entry			
	550E005	E	End Entry			
	550S005	S	Side Entry			
Finish	TZ	Tin-Zinc				
	MN	Mega-Nickel				
	JF	Cadmium, Yel. Chromate				
	M	Electroless Nickel				
	NF	Olive Drab Cadmium				
	MT	Nickel-PTFE				
	ZR	Black Zinc-Nickel				
Shell Size	1	2	3	4	5	6
Shroud Length	Mating Connector Rear Panel Mounting					
	Code	Panel Thickness	E			
	R1	.031 (0.8)	.247 (6.3)			
	R2	.047 (1.2)	.231 (5.9)			
	R3	.062 (1.6)	.216 (5.5)			
	R4	.093 (2.4)	.185 (4.7)			
	R5	.104 (2.6)	.174 (4.4)			
	R6	.125 (3.2)	.153 (3.9)			
	R7	.156 (4.0)	.125 (3.2)			
	R8	.135 (3.4)	.140 (3.6)			
	R9	.188 (4.8)	.094 (2.4)			
	CC	Cable-to-Cable	.174 (4.4)			
	F0	Front Panel Mount	.343 (8.7)			
Screwlocks (Table 1)	Code	Type	Profiles			
	A	Male, Socket Head	S T			
	B	Male, Fillister Head	S T			
	E	Male, Extended Slotted	S T			
	H	Male, Hex Head, Drilled	S T			
	J	Male, Slotted, Knurled	E			
	K	Male, Slotted, Knurled	S T			
	P	Female Hex Post, Fixed	S T			
EMI Panel Gasket	0	No Gasket				
	1	Gasket Included (install on mating connector)				
Strain Relief	E	Saddle Clamp				
	G	Gland Nut				
Entry Size	Entry Size	Cable Range		Shell Size		
		Min	Max			
	02	.125 (3.2)	.250 (6.4)	1-6		
	03	.250 (6.4)	.375 (9.5)	1-6		
	04	.312 (7.9)	.500 (12.7)	1-6		
	05	.437 (11.1)	.625 (15.9)	1-6		
	06	.562 (14.3)	.750 (19.1)	1-6		
	07	.687 (17.4)	.875 (22.2)	6		
	08	.812 (20.6)	1.000 (25.4)	6		



D-SUBMINIATURE ACCESSORIES


D-Subminiature



550-005

Shrouded Backshell, Braid Trap

- Split EMI Backshell
- Braid Trap Shield Termination
- Saddle Clamp Strain Relief



Shell Size	A Max		B Max		C		D		P		R		Max Entry Size
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	
1	1.393	35.4	.624	15.8	.312	7.9	.984	25.0	.730	18.5	.719	18.3	06
2	1.706	43.3	.624	15.8	.312	7.9	1.312	33.3	1.050	26.7	.719	18.3	06
3	2.265	57.5	.624	15.8	.312	7.9	1.852	47.0	1.594	40.5	.938	23.8	06
4	2.900	73.7	.624	15.8	.312	7.9	2.500	63.5	2.240	56.9	.938	23.8	06
5	2.800	71.1	.750	19.1	.375	9.5	2.406	61.1	2.140	54.4	.938	23.8	06
6	2.900	73.7	.844	21.4	.422	10.7	2.500	63.5	2.240	56.9	1.094	27.8	08


Shroud Length	Mating Connector Panel Thickness		E Shroud Length		F						G			
					Size 1, 2		±.031 (0.8) Size 3, 4, 5		Size 6		±.031 (0.8) Size 1, 2		Size 3-6	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm		
CC	N/A	N/A	.174	4.4	1.451	36.9	1.671	42.4	1.820	46.2	1.583	40.2	1.831	46.5
F0	N/A	N/A	.343	8.7	1.625	41.3	1.844	46.8	2.000	50.8	1.750	44.5	2.000	50.8
R1	.031	0.8	.247	6.3	1.525	38.7	1.745	44.3	1.890	48.0	1.656	42.1	1.904	48.4
R2	.047	1.2	.231	5.9	1.509	38.3	1.728	43.9	1.875	47.6	1.640	41.7	1.888	48.0
R3	.062	1.6	.216	5.5	1.500	38.1	1.720	43.7	1.860	47.2	1.625	41.3	1.873	47.6
R4	.093	2.4	.185	4.7	1.470	37.3	1.690	42.9	1.829	46.5	1.594	40.5	1.842	46.8
R5	.104	2.6	.174	4.4	1.451	36.9	1.671	42.4	1.820	46.2	1.583	40.2	1.831	46.5
R6	.125	3.2	.153	3.9	1.430	36.3	1.650	41.9	1.798	45.7	1.563	39.7	1.811	46.0
R7	.156	4.0	.125	3.2	1.400	35.6	1.620	41.1	1.767	44.9	1.531	38.9	1.781	45.2
R8	.135	3.4	.140	3.6	1.417	36.0	1.637	41.6	1.805	45.8	1.550	39.4	1.798	45.7
R9	.188	4.8	.094	2.4	1.368	34.7	1.590	40.4	1.740	44.2	1.500	38.1	1.750	44.5

Entry Size	H Max		Cable Range			
			Min		Max	
	in	mm	in	mm	in	mm
02	.968	24.6	.125	3.2	.250	6.4
03	1.046	26.6	.250	6.4	.375	9.5
04	1.156	29.4	.312	7.9	.500	12.7
05	1.218	30.9	.437	11.1	.625	15.9
06	1.343	34.1	.562	14.3	.750	19.1
07	1.468	37.3	.687	17.4	.875	22.2
08	1.593	40.5	.812	20.6	1.000	25.4

Shell Size	Top Entry		End Entry	
	in	mm	in	mm
1	.250	6.4	.375	9.5
2	.375	9.5	.375	9.5
3	.475	12.1	.475	12.1
4	.475	12.1	.475	12.1
5	.575	14.6	.575	14.6
6	1.000	25.4		


BRAID TRAP

TAPERED CANDELABRA THREAD




EMI PANEL GASKET

Install gasket on front side of mating connector panel. When backshell is fastened to panel connector, the front edge of the shroud seats onto gasket for aperture-free EMI protection.



EMI PANEL GASKET
.020 (0.5) THICK
MATL: ALUMINUM
MESH EMBEDDED IN
SILICONE



Shell Size	Gasket Part No.	A		B		C	
		in	mm	in	mm	in	mm
1	559-002-1	.740	18.8	1.500	38.1	.980	24.9
2	559-002-2	.740	18.8	1.810	46.0	1.312	33.3
3	559-002-3	.740	18.8	2.380	60.5	1.852	47.0
4	559-002-4	.740	18.8	3.010	76.5	2.500	63.5
5	559-002-5	.850	21.6	2.920	74.2	2.406	61.1
6	559-002-6	.925	23.5	3.010	76.4	2.500	63.5

D-Subminiature


550-009

Shrouded Backshell, Rear Panel Mount


- Rear Panel Mount
- Cone-and-Ring Shield Termination
- Saddle Clamp Strain Relief



T Top Entry




S Side Entry



E End Entry

REAR PANEL MOUNTING




FOR REAR-MOUNTED CONNECTORS ONLY
BACKSHELL ATTACHES TO INSIDE OF PANEL
WITH FEMALE SCREWLOCKS (INCLUDED).

550-009

This accessory fits D-Subminiature
M24308 connectors.
Not compatible with Series 28 HiPer-D

For rear panel mounted connectors, Cone-and-Ring shield termination. 550-009 diecast aluminum backshell fits rear panel mounted M24308 D-Subminiature connectors. EMI protected. Cable shield attaches to backshell with ground ring. For panel thicknesses up to 3/16 inch (4.8mm). Optional metalastic EMI panel gasket. Connector fits into groove between backshell halves. #4-40 female screwlocks are included. Aluminum with stainless steel screws and washers.

CONE-AND-RING
SHIELD TERMINATION



Fold braid over grounding ring. Tighten
clamp onto backshell to captivate braid.

PART NUMBER

Sample PN→ 550T009 M 3 R3 L 0

Base P/N	Base Part No.	Profile				
	550T009	T	Top Entry			
	550E009	E	End Entry			
	550S009	S	Side Entry			
Finish	TZ	Tin-Zinc				
	MN	Mega-Nickel				
	JF	Cadmium, Yel. Chromate				
	M	Electroless Nickel				
	NF	Olive Drab Cadmium				
	MT	Nickel-PTFE				
Shell Size	ZR	Black Zinc-Nickel				
	1	2	3	4	5	6
Panel Thickness	Code	Panel Thickness				
	R1	.031 (0.8)				
	R2	.047 (1.2)				
	R3	.062 (1.6)				
	R4	.093 (2.4)				
	R5	.104 (2.6)				
	R6	.125 (3.2)				
	R7	.156 (4.0)				
	R8	.135 (3.4)				
	R9	.188 (4.8)				
Strain Relief	F	Saddle Clamp				
	G	Gland Nut				
EMI Gasket	0	No Gasket				
	1	Gasket Included (install on mating connector)				


D-Subminiature



550-009

Shrouded Backshell, Rear Panel Mount

- Rear Panel Mount
- Cone-and-Ring Shield Termination
- Saddle Clamp Strain Relief




Shell Size	A Max		B Max		C	±.005 (0.13)	D		E		F Max		G		H Max	
	in	mm	in	mm			in	mm	in	mm	in	mm	in	mm	in	mm
1	1.393	35.4	.624	15.8	.312	7.9	.984	25.0	1.320	33.5	1.046	26.6	1.460	37.1	.843	21.4
2	1.706	43.3	.624	15.8	.312	7.9	1.312	33.3	1.320	33.5	1.046	26.6	1.460	37.1	.843	21.4
3	2.265	57.5	.624	15.8	.312	7.9	1.852	47.0	1.540	39.1	1.156	29.4	1.710	43.4	.968	24.6
4	2.900	73.7	.624	15.8	.312	7.9	2.500	63.5	1.540	39.1	1.156	29.4	1.710	43.4	.968	24.6
5	2.800	71.1	.750	19.1	.375	9.5	2.406	61.1	1.540	39.1	1.218	30.9	1.710	43.4	1.109	28.2
6	2.900	73.7	.844	21.4	.422	10.7	2.500	63.5	1.690	42.9	1.594	40.5	1.710	43.4	1.468	37.3


Shell Size	Cable Range							
	Profile S, T				Profile E			
	Min	Max	Min	Max	Min	Max	Min	Max
1	.125	3.2	.250	6.4	.250	6.4	.375	9.5
2	.250	6.4	.375	9.5	.250	6.4	.375	9.5
3	.312	7.9	.475	12.1	.312	7.9	.475	12.1
4	.312	7.9	.475	12.1	.312	7.9	.475	12.1
5	.437	11.1	.575	14.6	.437	11.1	.575	14.6
6	.812	20.6	1.000	25.4	.812	20.6	1.000	25.4

EMI PANEL GASKET

Install gasket on front side of panel. When the mating backshell is fastened to the panel connector, the front edge of the backshell seats onto the gasket for aperture-free EMI protection.




EMI PANEL GASKET
.020 (0.5) THICK
MATL: ALUMINUM
MESH EMBEDDED IN
SILICONE



Shell Size	Gasket Part No.	A		B		C	
		in	mm	in	mm	in	mm
1	559-002-1	.740	18.8	1.500	38.1	.980	24.9
2	559-002-2	.740	18.8	1.810	46.0	1.312	33.3
3	559-002-3	.740	18.8	2.380	60.5	1.852	47.0
4	559-002-4	.740	18.8	3.010	76.5	2.500	63.5
5	559-002-5	.850	21.6	2.920	74.2	2.406	61.1
6	559-002-6	.925	23.5	3.010	76.4	2.500	63.5

PANEL COUNTERBORE DIMENSIONS

Panel Thk. Code	Panel Thickness		A Counterbore Depth		B Counterbore Diameter		No. of Washers
	in	mm	in	mm	in	mm	
R1	.031	0.8	.000	0.00	.000	0.00	4
R2	.047	1.2	.000	0.00	.000	0.00	4
R3	.062	1.6	.020	0.51	.199	5.05	3
R4	.093	2.4	.051	1.30	.199	5.05	2
R5	.104	2.6	.061	1.55	.199	5.05	1
R6	.125	3.2	.082	2.08	.199	5.05	1
R7	.156	4.0	.097	2.46	.199	5.05	2
R8	.135	3.4	.098	2.49	.199	5.05	2
R9	.188	4.8	.146	3.71	.219	5.56	2



D-Subminiature



550-039

Shrouded Backshell, EMI Banding

- Split EMI Backshell
- Banding Shield Termination
- .24" (6.1mm) Band




550-039

This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Band platform, shrouded. 550-039 diecast aluminum backshell fits M24308 D-Subminiature connectors. EMI protected. Cable shield attaches to backshell with optional band strap. Install optional metalastic EMI gasket on mating connector panel. Connector is captivated between backshell halves. Eleven shroud lengths to accommodate mating connector mounting dimensions. #4-40 screwlocks are included. Aluminum with stainless steel screws and washers.


TABLE 1
SCREWLOCK OPTIONS



PART NUMBER

Sample PN → **550T039 M 3 R3 A 0 -03 B**

Base P/N	550T039	T	Top Entry		
	550E039	E	End Entry		
	550S039	S	Side Entry		
Finish	TZ		Tin-Zinc		
	MN		Mega-Nickel		
	JF		Cadmium, Yel. Chromate		
	M		Electroless Nickel		
	NF		Olive Drab Cadmium		
	MT		Nickel-PTFE		
	ZR		Black Zinc-Nickel		
Shell Size	1 2 3 4 5 6				
Shroud Length	Mating Connector Rear Panel Mounting				
	Code	Panel Thickness	E		
	R1	.031 (0.8)	.247 (6.3)		
	R2	.047 (1.2)	.231 (5.9)		
	R3	.062 (1.6)	.216 (5.5)		
	R4	.093 (2.4)	.185 (4.7)		
	R5	.104 (2.6)	.174 (4.4)		
	R6	.125 (3.2)	.153 (3.9)		
	R7	.156 (4.0)	.125 (3.2)		
	R8	.135 (3.4)	.140 (3.6)		
	R9	.188 (4.8)	.094 (2.4)		
	CC	Cable-to-Cable	.185 (4.7)		
	F0	Front Panel Mount	.343 (8.7)		
Screwlocks (Table 1)	Code	Type	Profiles		
	A	Male, Socket Head	S T		
	B	Male, Fillister Head	S T		
	E	Male, Extended Slotted	S T		
	H	Male, Hex Head, Drilled	S T		
	J	Male, Slotted, Knurled	E		
	K	Male, Slotted, Knurled	S T		
	P	Female Hex Post, Fixed	S T		
EMI Panel Gasket	0	No Gasket			
	1	Gasket Included (install on mating connector)			
Entry Size	Entry Size	H Entry Dia.	Shell Size		
			S	T	E
	-01	.125 (3.2)	1-6	1-6	1-6
	-02	.250 (6.4)	1-6	1-6	1-6
	-03	.312 (7.9)	1-6	1-6	1-6
	-04	.395 (10.0)	1-6	1-6	1-6
	-05	.438 (11.1)	1-6	1-6	1-6
	-06	.500 (12.7)	4-6	4-6	4-6
	-07	.562 (14.3)	4-6	4-6	4-6
	-08	.624 (15.8)	4-6	4-6	6
	-09	.688 (17.5)	6	6	6
	-10	.750 (19.1)	6	6	6
	-11	.812 (20.6)	6	6	6
	-12	.875 (22.2)	6	6	6
	-13	.937 (23.8)	6	6	6
	-14	1.000 (25.4)	6	6	6
Band	Omit	No Band			
	B	Standard Band Included			
	J	Slim Standard Band Included			




D-Subminiature



550-039

Shrouded Backshell, EMI Banding

- Split EMI Backshell
- Banding Shield Termination
- .24" (6.1mm) Band



Shell Size	A Max		B Max		C		D ± .005 (0.13)		P		R		Max Entry Size
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	
1	1.393	35.4	.624	15.8	.312	7.9	.984	25.0	.730	18.5	.719	18.3	05
2	1.706	43.3	.624	15.8	.312	7.9	1.312	33.3	1.050	26.7	.719	18.3	05
3	2.265	57.5	.624	15.8	.312	7.9	1.852	47.0	1.594	40.5	.938	23.8	05
4	2.900	73.7	.624	15.8	.312	7.9	2.500	63.5	2.240	56.9	.938	23.8	08
5	2.800	71.1	.750	19.1	.375	9.5	2.406	61.1	2.140	54.4	.938	23.8	08
6	2.900	73.7	.844	21.4	.422	10.7	2.500	63.5	2.240	56.9	1.094	27.8	14




▲ .07 is Max Entry Size for End Entry Shell Size 4.

37 IS Max Entry Size for End Entry Shell Size 4.														
Shroud Length	Mating Connector Panel Thickness		E Shroud Length		F						G			
	in	mm	in	mm	Size 1, 2		Size 3, 4, 5		Size 6		Size 1, 2		Size 3-6	
					in	mm	in	mm	in	mm	in	mm	in	mm
CC	N/A	N/A	.185	4.7	1.467	37.3	1.686	42.8	1.842	46.8	1.592	40.4	1.842	46.8
F0	N/A	N/A	.343	8.7	1.625	41.3	1.844	46.8	2.000	50.8	1.750	44.5	2.000	50.8
R1	.031	0.8	.247	6.3	1.529	38.8	1.748	44.4	1.904	48.4	1.654	42.0	1.904	48.4
R2	.047	1.2	.231	5.9	1.513	38.4	1.732	44.0	1.888	48.0	1.638	41.6	1.888	48.0
R3	.062	1.6	.216	5.5	1.498	38.0	1.717	43.6	1.873	47.6	1.623	41.2	1.873	47.6
R4	.093	2.4	.185	4.7	1.467	37.3	1.686	42.8	1.842	46.8	1.592	40.4	1.842	46.8
R5	.104	2.6	.174	4.4	1.456	37.0	1.675	42.5	1.831	46.5	1.581	40.2	1.831	46.5
R6	.125	3.2	.153	3.9	1.435	36.4	1.654	42.0	1.810	46.0	1.560	39.6	1.810	46.0
R7	.156	4.0	.125	3.2	1.407	35.7	1.626	41.3	1.782	45.3	1.532	38.9	1.782	45.3
R8	.135	3.4	.140	3.6	1.422	36.1	1.641	41.7	1.797	45.7	1.547	39.3	1.797	45.7
R9	.188	4.8	.094	2.4	1.376	34.9	1.595	40.5	1.751	44.5	1.501	38.1	1.751	44.5

Entry Size	ø H		ø J		ø K	
	in	mm	in	mm	in	mm
01	.125	3.2	.250	6.4	.312	7.9
02	.250	6.4	.375	9.5	.438	11.1
03	.312	7.9	.438	11.1	.500	12.7
04	.395	10.0	.500	12.7	.562	14.3
05	.438	11.1	.562	14.3	.625	15.9
06	.500	12.7	.625	15.9	.688	17.5
07	.562	14.3	.688	17.5	.750	19.1
08	.624	15.8	.750	19.1	.812	20.6
09	.688	17.5	.812	20.6	.875	22.2
10	.750	19.1	.875	22.2	.937	23.8
11	.812	20.6	.937	23.8	1.000	25.4
12	.875	22.2	1.000	25.4	1.125	28.6
13	.937	23.8	1.062	27.0	1.187	30.1
14	1.000	25.4	1.125	28.6	1.250	31.8

EMI PANEL GASKET

Install gasket on front side of mating connector panel. Gasket is die cut from .020" thick metalastic (aluminum mesh and silicone) material. When backshell is fastened to panel connector, the front edge of the shroud seats onto gasket for aperture-free EMI protection.



Shell Size	Gasket Part No.	A		B		C	
		in	mm	in	mm	in	mm
1	559-002-1	.740	18.8	1.500	38.1	.980	24.9
2	559-002-2	.740	18.8	1.810	46.0	1.310	33.3
3	559-002-3	.740	18.8	2.380	60.5	1.850	47.0
4	559-002-4	.740	18.8	3.010	76.5	2.500	63.5
5	559-002-5	.850	21.6	2.920	74.2	2.410	61.2
6	559-002-6	.925	23.5	3.010	76.5	2.500	63.5

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110


D-Subminiature



550-041

Shrouded Backshell, TAG Ring®


- Split EMI Backshell
- TAG Ring® Shield Termination
- Saddle Clamp Strain Relief

**T** Top Entry**S** Side Entry**E** End Entry

550-041

This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

TAG Ring® for terminating individual shields, shrouded. 550-041 diecast aluminum backshell fits M24308 D-Subminiature connectors. EMI protected. TAG ring has slots for terminating wire shields. Install optional metalastic EMI gasket on mating connector panel. Available with saddle clamp strain relief or gland nut. Eleven shroud lengths to accommodate mating connector mounting dimensions. #4-40 screwlocks are included. Aluminum with stainless steel hardware.

TABLE 1
SCREWLOCK OPTIONS


PART NUMBER

Sample PN→

550T041

M

3

R3

A

0

L

T

Base P/N	550T041 T Top Entry 550E041 E End Entry 550S041 S Side Entry
Finish	TZ Tin-Zinc MN Mega-Nickel JF Cadmium, Yel. Chromate M Electroless Nickel NF Olive Drab Cadmium MT Nickel-PTFE ZR Black Zinc-Nickel
Shell Size	1 2 3 4 5 6
Shroud Length	Mating Connector Rear Panel Mounting
	Code Panel Thickness E R1 .031 (0.8) .247 (6.3) R2 .047 (1.2) .231 (5.9) R3 .062 (1.6) .216 (5.5) R4 .093 (2.4) .185 (4.7) R5 .104 (2.6) .174 (4.4) R6 .125 (3.2) .153 (3.9) R7 .156 (4.0) .125 (3.2) R8 .135 (3.4) .140 (3.6) R9 .188 (4.8) .094 (2.4) CC Cable-to-Cable .174 (4.4) F0 Front Panel Mount .343 (8.7)
Screwlocks (Table 1)	Code Type Profiles A Male, Socket Head ST B Male, Fillister Head ST E Male, Extended Slotted ST H Male, Hex Head, Drilled ST J Male, Slotted, Knurled E K Male, Slotted, Knurled ST P Female Hex Post, Fixed ST
EMI Panel Gasket	0 No Gasket 1 Gasket Included (install on mating connector)
Strain Relief	L Saddle Clamp G Gland Nut
Shrink Boot	Omit No Shrink Boot T Shrink Boot Included




D-Subminiature



550-041

Shrouded Backshell, TAG Ring®

- Split EMI Backshell
- TAG Ring® Shield Termination
- Saddle Clamp Strain Relief




Shell Size	A Max		B Max		C		± .005 (0.13)		P		R	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
1	1.393	35.4	.624	15.8	.312	7.9	.984	25.0	.730	18.5	.719	18.3
2	1.706	43.3	.624	15.8	.312	7.9	1.312	33.3	1.050	26.7	.719	18.3
3	2.265	57.5	.624	15.8	.312	7.9	1.852	47.0	1.594	40.5	.938	23.8
4	2.900	73.7	.624	15.8	.312	7.9	2.500	63.5	2.240	56.9	.938	23.8
5	2.800	71.1	.750	19.1	.375	9.5	2.406	61.1	2.140	54.4	.938	23.8
6	2.900	73.7	.844	21.4	.422	10.7	2.500	63.5	2.240	56.9	1.094	27.8

Shell Size	Ø H Max Cable Dia.		Ø J Max Gland Nut		Ø K Max		L Max. Saddle Clamp	
	in	mm	in	mm	in	mm	in	mm
1	.250	6.4	.545	13.8	.650	16.5	.968	24.6
2	.375	9.5	.670	17.0	.774	19.7	1.046	26.6
3	.475	12.1	.795	20.2	.963	24.5	1.156	29.4
4	.475	12.1	.795	20.2	.963	24.5	1.156	29.4
5	.575	14.6	.920	23.4	1.042	26.5	1.218	30.9
6	1.000	25.4	1.295	32.9	1.420	36.1	1.593	40.5

Shroud Length	Mating Connector Panel Thickness		E Shroud Length		F						G			
					Size 1, 2		Size 3, 4, 5		Size 6		Size 1, 2		Size 3-5	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
CC	N/A	N/A	.174	4.4	1.451	36.9	1.671	42.4	1.827	46.2	1.583	40.2	1.831	46.5
F0	N/A	N/A	.343	8.7	1.625	41.3	1.844	46.8	2.000	50.8	1.750	44.5	2.000	50.8
R1	.031	0.8	.247	6.3	1.525	38.7	1.745	44.3	1.890	48.0	1.656	42.1	1.904	48.4
R2	.047	1.2	.231	5.9	1.509	38.3	1.728	43.9	1.875	47.6	1.640	41.7	1.888	48.0
R3	.062	1.6	.216	5.5	1.500	38.1	1.720	43.7	1.860	47.2	1.625	41.3	1.873	47.6
R4	.093	2.4	.185	4.7	1.470	37.3	1.690	42.9	1.829	46.5	1.594	40.5	1.842	46.8
R5	.104	2.6	.174	4.4	1.451	36.9	1.671	42.4	1.820	46.2	1.583	40.2	1.831	46.5
R6	.125	3.2	.153	3.9	1.430	36.3	1.650	41.9	1.798	45.7	1.563	39.7	1.811	46.0
R7	.156	4.0	.125	3.2	1.400	35.6	1.620	41.1	1.767	44.9	1.531	38.9	1.781	45.2
R8	.135	3.4	.140	3.6	1.417	36.0	1.637	41.6	1.805	45.8	1.550	39.4	1.798	45.7
R9	.188	4.8	.094	2.4	1.368	34.7	1.590	40.4	1.740	44.2	1.500	38.1	1.750	44.5

EMI PANEL GASKET

Install gasket on front side of mating connector panel. Gasket material is .020" thick metalastic (aluminum mesh and silicone). When backshell is fastened to panel connector, the front edge of the shroud seats onto gasket for aperture-free EMI protection.



Shell Size	Gasket Part No.	A		B		C	
		in	mm	in	mm	in	mm
1	559-002-1	.740	18.8	1.500	38.1	.980	24.9
2	559-002-2	.740	18.8	1.810	46.0	1.310	33.3
3	559-002-3	.740	18.8	2.380	60.5	1.850	47.0
4	559-002-4	.740	18.8	3.010	76.5	2.500	63.5
5	559-002-5	.850	21.6	2.920	74.2	2.410	61.2
6	559-002-6	.925	23.5	3.010	76.5	2.500	63.5

SHRINK BOOT

Optional heatshrink boot provides cable strain relief. Lipped boot fits .135 (3.4) wide boot groove. Type 1 high-performance semi-rigid elastomer resists fuels and oils and withstands temperature extremes. Operating temperature range -75 to +150 °C.

Shell Size	Shrink Boot P/N
1	770-001S103
2	770-001S104
3	770-001S105
4	770-001S105
5	770-001S106
6	770-001S107



D-Subminiature


550-100

Shrouded Backshell, Saddle Clamp


- Split Backshell
- For Unshielded Cable
- Saddle Clamp Strain Relief



T Top Entry



S Side Entry




E End Entry

550-100

This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Saddle clamp, shrouded. 550-100 diecast aluminum backshell fits M24308 D-Subminiature connectors. Type L saddle clamp strain relief. Eleven shroud lengths to accommodate mating connector mounting dimensions. #4-40 screwlocks are included. Aluminum with stainless steel hardware.

TABLE 1
SCREWLOCK OPTIONS



PART NUMBER

Sample PN→

550T100

M

3

R3

A

Base P/N 550T100 T Top Entry
550E100 E End Entry (Shell Size 1-5)
550S100 S Side Entry

Finish TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size 1 2 3 4 5 6

Shroud Length

Mating Connector Rear Panel Mounting

Code	Panel Thickness	E
R1	.031 (0.8)	.247 (6.3)
R2	.047 (1.2)	.231 (5.9)
R3	.062 (1.6)	.216 (5.5)
R4	.093 (2.4)	.185 (4.7)
R5	.104 (2.6)	.174 (4.4)
R6	.125 (3.2)	.153 (3.9)
R7	.156 (4.0)	.125 (3.2)
R8	.138 (3.5)	.140 (3.6)
R9	.188 (4.8)	.094 (2.4)
CC	Cable-to-Cable	.170-.172 (4.3-4.4)
F0	Front Panel Mount	.340-.344 (8.6-8.7)



Screwlocks (Table 1)	Code	Type	Profiles
	A	Male, Socket Head	ST
	B	Male, Fillister Head	ST
	E	Male, Extended Slotted	ST
	H	Male, Hex Head, Drilled	ST
	J	Male, Slotted, Knurled	E
	K	Male, Slotted, Knurled	ST
	P	Female Hex Post, Fixed	ST

D-Subminiature




550-100


Shrouded Backshell, Saddle Clamp

- Split Backshell
- For Unshielded Cable
- Saddle Clamp Strain Relief


550T100 TOP ENTRY



550E100 END ENTRY



550S100 SIDE ENTRY



Shell Size	A Max		B Max		C		D ± .005 (0.13)		H Max		Cable Range							
											Profile S, T		Profile E		Profile E		Profile E	
	in	mm	in	mm	in	mm	in	mm	in	mm	Min	Max	Min	Max	Min	Max	Min	Max
1	1.393	35.4	.624	15.8	.312	7.9	.984	25.0	1.046	26.6	.125	3.2	.250	6.4	.250	6.4	.375	9.5
2	1.691	43.3	.624	15.8	.312	7.9	1.312	33.3	1.046	26.6	.250	6.4	.375	9.5	.250	6.4	.375	9.5
3	2.250	57.5	.624	15.8	.312	7.9	1.852	47.0	1.156	29.4	.312	7.9	.475	12.1	.312	7.9	.475	12.1
4	2.879	73.7	.624	15.8	.312	7.9	2.500	63.5	1.156	29.4	.312	7.9	.475	12.1	.312	7.9	.475	12.1
5	2.785	71.1	.750	19.1	.375	9.5	2.406	61.1	1.218	30.9	.437	11.1	.575	14.6	.437	11.1	.575	14.6
6	2.875	73.7	.844	21.4	.422	10.7	2.500	63.5	1.594	40.5	.812	20.6	1.000	25.4	N/A	N/A	N/A	N/A

Shroud Length	Mating Connector Panel Thickness		E		F						G			
					Size 1, 2		Size 3, 4, 5		Size 6		Size 1, 2		Size 3, 4, 5	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
CC	N/A	N/A	.170-.172	4.3-4.4	1.455	36.9	1.673	42.4	1.844	46.2	1.583	40.2	1.831	46.5
F0	N/A	N/A	.343-.344	8.7	1.625	41.3	1.844	46.8	2.000	50.8	1.750	44.5	2.000	50.8
R1	.031	0.8	.247	6.3	1.525	38.7	1.745	44.3	1.890	48.0	1.656	42.1	1.904	48.4
R2	.047	1.2	.231	5.9	1.509	38.3	1.728	43.9	1.875	47.6	1.640	41.7	1.888	48.0
R3	.062	1.6	.216	5.5	1.500	38.1	1.720	43.7	1.860	47.2	1.625	41.3	1.873	47.6
R4	.093	2.4	.185	4.7	1.470	37.3	1.690	42.9	1.829	46.5	1.594	40.5	1.842	46.8
R5	.104	2.6	.174	4.4	1.451	36.9	1.671	42.4	1.820	46.2	1.583	40.2	1.831	46.5
R6	.125	3.2	.153	3.9	1.430	36.3	1.650	41.9	1.798	45.7	1.563	39.7	1.811	46.0
R7	.156	4.0	.125	3.2	1.400	35.6	1.620	41.1	1.767	44.9	1.531	38.9	1.781	45.2
R8	.138	3.4	.140	3.6	1.417	36.0	1.637	41.6	1.805	45.8	1.550	39.4	1.798	45.7
R9	.188	4.8	.094	2.4	1.368	34.7	1.590	40.6	1.740	44.2	1.500	38.1	1.750	44.5

D-Subminiature



550-102

Shrouded Backshell, Qwik-Ty®

- Split Backshell
- For Unshielded Cable
- Qwik-Ty® Strain Relief



550-102

This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Qwik-Ty strain relief, split, shrouded. 550-102 diecast aluminum backshell fits M24308 D-Subminiature connectors. Attach cable tie to Qwik-Ty arm for strain relief. Connector is captivated between backshell halves. Eleven shroud lengths to accommodate mating connector mounting dimensions. #4-40 screwlocks are included. Aluminum with stainless steel screws and washers.

PART NUMBER

Sample PN→

550T102

M

2

R4

H

Base P/N	Base Part No.	Profile	Shell Sizes
	550T102	T Top Entry	1-6
	550E102	E End Entry	1-5
	550S102	S Side Entry	1-5
Finish	TZ	Tin-Zinc	
	MN	Mega-Nickel	
	JF	Cadmium, Yel. Chromate	
	M	Electroless Nickel	
	NF	Olive Drab Cadmium	
	MT	Nickel-PTFE	
	ZR	Black Zinc-Nickel	
Shell Size	1 2 3 4 5 6		
Shroud Length	Mating Connector Rear Panel Mounting		
	Code	Panel Thickness	E
	R1	.031 (0.8)	.247 (6.3)
	R2	.047 (1.2)	.231 (5.9)
	R3	.062 (1.6)	.216 (5.5)
	R4	.093 (2.4)	.185 (4.7)
	R5	.104 (2.6)	.174 (4.4)
	R6	.125 (3.2)	.153 (3.9)
	R7	.156 (4.0)	.125 (3.2)
	R8	.138 (3.5)	.140 (3.6)
	R9	.188 (4.8)	.094 (2.4)
	CC	Cable-to-Cable	.170-.172 (4.3-4.4)
	F0	Front Panel Mount	.340-.344 (8.6-8.7)
Screwlocks (Table 1)	Code	Type	Profiles
	A	Male, Socket Head	S T
	B	Male, Fillister Head	S T
	E	Male, Extended Slotted	S T
	H	Male, Hex Head, Drilled	S T
	J	Male, Slotted, Knurled	E
	K	Male, Slotted, Knurled	S T
	P	Female Hex Post, Fixed	S T



TABLE 1 SCREWLOCK OPTIONS

A	B	H	E	J K	P
Socket Head	Fillister Head	Hex Head	Extended Slotted	Slotted Knurled	Female Post


D-Subminiature



550-102

Shrouded Backshell, Qwik-Ty®

- Split Backshell
- For Unshielded Cable
- Qwik-Ty® Strain Relief



Shell Size	A Max		B Max		C		D		H Entry		J		K Max		R Ref	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
1	1.393	35.4	.624	15.8	.312	7.9	.984	25.0	.437	11.1	-	-	1.080	27.4	.719	18.3
2	1.706	43.3	.624	15.8	.312	7.9	1.312	33.3	.500	12.7	-	-	1.250	31.8	.719	18.3
3	2.265	57.5	.624	15.8	.312	7.9	1.852	47.0	.500	12.7	.200	5.1	1.520	38.6	.938	23.8
4	2.900	73.7	.624	15.8	.312	7.9	2.500	63.5	.500	12.7	.600	15.2	1.840	46.7	.938	23.8
5	2.800	71.1	.750	19.1	.375	9.5	2.406	61.1	.600	15.2	.500	12.7	1.790	45.5	.938	23.8
6	2.900	73.7	.844	21.4	.422	10.7	2.500	63.5	1.020	25.9	-	-	1.840	46.7	1.094	27.8

Shroud Length	Mating Connector Panel Thickness		E		F					
	in	mm	in	mm	Size 1, 2		Size 3, 4, 5		Size 6	
CC	N/A	N/A	.174	4.4	1.455	36.9	1.673	42.4	1.844	46.2
F0	N/A	N/A	.343	8.7	1.625	41.3	1.844	46.8	2.000	50.8
R1	.031	0.8	.247	6.3	1.509	38.7	1.728	44.3	1.875	48.0
R2	.047	1.2	.231	5.9	1.509	38.3	1.728	43.9	1.875	47.6
R3	.062	1.6	.216	5.5	1.500	38.1	1.720	43.7	1.860	47.2
R4	.093	2.4	.185	4.7	1.470	37.3	1.690	42.9	1.829	46.5
R5	.104	2.6	.174	4.4	1.451	36.9	1.671	42.4	1.820	46.2
R6	.125	3.2	.153	3.9	1.430	36.3	1.650	41.9	1.798	45.7
R7	.156	4.0	.125	3.2	1.400	35.6	1.620	41.1	1.767	44.9
R8	.138	3.4	.140	3.6	1.417	36.0	1.637	41.6	1.785	45.8
R9	.188	4.8	.094	2.4	1.368	34.7	1.590	40.6	1.740	44.2

D-Subminiature

557-186

Shrouded Backshell, Composite Banding

- Split EMI Backshell
- Banding Shield Termination
- Composite Thermoplastic





557-186

This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Corrosion-free lightweight composite.
557-186 composite thermoplastic backshell fits M24308 D-Subminiature connectors. EMI protected. Cable shield attaches to backshell with optional band strap. Install optional EMI gasket on mating connector panel. Connector is captivated between backshell halves. Eleven shroud lengths to accommodate mating connector mounting dimensions. #4-40 screwlocks are included. Thermoplastic with stainless steel screws and washers.

TABLE 1
SCREWLOCK OPTIONS



PART NUMBER										
Sample PN→		557T186	XM	3	R3	A	0	-04	S	K
Base P/N	557T186	T	Top Entry							
	557E186	E	End Entry							
	557S186	S	Side Entry							
Finish	XM	Electroless Nickel								
	XW	Olive Drab Cadmium								
	XMT	Nickel-PTFE								
Shell Size	1 2 3 4 5 6									
Shroud Length	Mating Connector Rear Panel Mounting									
	Code	Panel Thickness	E							
	R1	.031 (0.8)	.247 (6.3)							
	R2	.047 (1.2)	.231 (5.9)							
	R3	.062 (1.6)	.216 (5.5)							
	R4	.093 (2.4)	.185 (4.7)							
	R5	.104 (2.6)	.174 (4.4)							
	R6	.125 (3.2)	.153 (3.9)							
	R7	.156 (4.0)	.125 (3.2)							
	R8	.135 (3.4)	.140 (3.6)							
	R9	.188 (4.8)	.094 (2.4)							
	CC	Cable-to-Cable	.174 (4.4)							
	F0	Front Panel Mtng.	.343 (8.7)							
	Screwlocks (Table 1)	Profiles								
A		Male, Socket Head	S T							
B		Male, Fillister Head	S T							
E		Male, Extended Slotted	S T							
H		Male, Hex Head, Drilled	S T							
J		Male, Slotted, Knurled	E							
K		Male, Slotted, Knurled	S T							
P		Female Hex Post, Fixed	S T							
EMI Panel Gasket	0	No Gasket								
	1	Gasket Included (install on mating connector)								
Entry Size	Entry Size	ø H	Shell Size							
			S	T	E					
	-01	.125 (3.2)	1-5	1-6	1-6					
	-02	.250 (6.4)	1-5	1-6	1-6					
	-03	.312 (7.9)	1-5	1-6	1-6					
	-04	.395 (10.0)	1-5	1-6	1-6					
	-05	.438 (11.1)	2-5	1-6	1-6					
	-06	.500 (12.7)	5-5	5-6	5-6					
	-07	.562 (14.3)	5	5-6	5-6					
	-08	.625 (15.9)	-	6	6					
	-09	.750 (19.1)	-	6	6					
	-10	.875 (22.2)	-	6	6					
-11	1.000 (25.4)	-	6	6						
Slot	Omit	No Slot								
	S	Slot (in banding area)								
Band	Omit	No Band								
	B	Standard Band Included								
	J	Slim Standard Band Included								


D-Subminiature



557-186

Shrouded Backshell, Composite Banding

- Split EMI Backshell
- Banding Shield Termination
- Composite Thermoplastic



Shell Size	A Max		B Max		C		D		Max Entry Size		
	in	mm	in	mm	in	mm	±.005 (0.13)	mm	S	T	E
1	1.393	35.4	.624	15.8	.312	7.9	.984	25.0	04	05	05
2	1.706	43.3	.624	15.8	.312	7.9	1.312	33.3	05	05	05
3	2.265	57.5	.624	15.8	.312	7.9	1.852	47.0	05	05	05
4	2.900	73.7	.624	15.8	.312	7.9	2.500	63.5	05	05	05
5	2.800	71.1	.750	19.1	.375	9.5	2.406	61.1	07	07	07
6	2.900	73.7	.844	21.4	.422	10.7	2.500	63.5	-	11	11




Shroud Length	Mating Connector Panel Thickness		E* Shroud Length	F*				G*			
				Size 1, 2	Size 3, 4, 5	Size 6	±.031 (0.8)	Size 1, 2	Size 3-6	±.031 (0.8)	
in	mm	mm	in	in	mm	in	mm	in	mm	in	mm
CC	N/A	N/A	.185	4.7	1.455	37.3	1.673	42.8	1.829	46.8	1.592
F0	N/A	N/A	.343	8.7	1.625	41.3	1.844	46.8	2.000	50.8	1.750
R1	.031	0.8	.247	6.3	1.525	38.7	1.745	44.3	1.904	48.4	1.656
R2	.047	1.2	.231	5.9	1.509	38.3	1.728	43.9	1.888	48.0	1.640
R3	.062	1.6	.216	5.5	1.500	38.1	1.720	43.7	1.873	47.6	1.625
R4	.093	2.4	.185	4.7	1.470	37.3	1.690	42.9	1.842	46.8	1.594
R5	.104	2.6	.174	4.4	1.451	36.9	1.671	42.4	1.831	46.5	1.585
R6	.125	3.2	.153	3.9	1.430	36.3	1.650	41.9	1.811	46.0	1.563
R7	.156	4.0	.125	3.2	1.400	35.6	1.620	41.1	1.781	45.2	1.532
R8	.135	3.4	.140	3.6	1.422	36.1	1.641	41.7	1.797	45.7	1.547
R9	.188	4.8	.094	2.4	1.376	34.9	1.595	40.5	1.751	44.5	1.501

*+.030/- .000 for CC only

Entry Size	ø H		ø J		ø K		X	
	in	mm	in	mm	in	mm	in	mm
01	.125	3.2	.250	6.4	.312	7.9	N/A	N/A
02	.250	6.4	.375	9.5	.438	11.1	.062	1.6
03	.312	7.9	.438	11.1	.500	12.7	.094	2.4
04	.395	10.0	.500	12.7	.562	14.3	.156	4.0
05	.438	11.1	.562	14.3	.625	15.9	.188	4.8
06	.500	12.7	.625	15.9	.688	17.5	.219	5.6
07	.562	14.3	.688	17.5	.750	19.1	.250	6.4
08	.625	15.9	.750	19.1	.812	20.6	.250	6.4
09	.750	19.1	.875	22.2	.937	23.8	.312	7.9
10	.875	22.2	1.000	25.4	1.062	27.0	.375	9.5
11	1.000	25.4	1.125	28.6	1.188	30.2	.375	9.5

EMI PANEL GASKET

Install gasket on front side of mating connector panel. Gasket material: metalastic (aluminum mesh and silicone). When backshell is fastened to panel connector, the front edge of the shroud seats onto gasket for aperture-free EMI protection.



Shell Size	Gasket Part No.	A		B		C	
		in	mm	in	mm	in	mm
1	559-002-1	.740	18.8	1.500	38.1	.980	24.9
2	559-002-2	.740	18.8	1.810	46.0	1.310	33.3
3	559-002-3	.740	18.8	2.380	60.5	1.850	47.0
4	559-002-4	.740	18.8	3.010	76.5	2.500	63.5
5	559-002-5	.850	21.6	2.920	74.2	2.410	61.2
6	559-002-6	.925	23.5	3.010	76.5	2.500	63.5

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

D-Subminiature

557-538

Shrouded Backshell, Banding, Composite Snap-Together

- Split EMI Backshell
- Banding Shield Termination
- Lightweight Composite




557-538


This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Lightweight composite, snap-together.
557-538 composite thermoplastic backshell fits M24308 D-Subminiature connectors. Two-piece snap-together backshell offers simple, fast assembly. Banding platform has Qwik-Ty strain relief arm and optional slots for individual wire shields. Backshell fully shrouds the connector. Eleven shroud lengths: Choose shroud length based on mating connector mounting style. Cable shield attaches to backshell with optional band strap. Connector is captivated between backshell halves. #4-40 screwlocks are included. Thermoplastic with stainless steel screws and washers.

TABLE 1
HARDWARE OPTIONS



PART NUMBER									
Sample PN→		557T538	XM	314	R3	B	S	K	
Base P/N		557T538							
Finish	XM	Electroless Nickel							
	XMT	Nickel-PTFE							
Shell Size	Size Code	Shell Size							
	114	1 (DE)							
	214	2 (DA)							
	314	3 (DB)							
	414	4 (DC)							
	517	5 (DD)							
Shroud Length	Mating Connector Rear Panel Mounting								
	Code	Panel Thickness	L						
	R1	.031 (0.8)	.247 (6.3)						
	R2	.047 (1.2)	.231 (5.9)						
	R3	.062 (1.6)	.216 (5.5)						
	R4	.093 (2.4)	.185 (4.7)						
	R5	.104 (2.6)	.174 (4.4)						
	R6	.125 (3.2)	.153 (3.9)						
	R7	.156 (4.0)	.125 (3.2)						
	R8	.135 (3.4)	.140 (3.6)						
	R9	.188 (4.8)	.094 (2.4)						
	CC	Cable-to-Cable	.174 (4.4)						
	F0	Front Panel Mtng.	.343 (8.7)						
	Screwlocks (Table 1)	B	Male, Fillister Head						
E		Male, Extended Slotted							
K		Male, Socket Head, Knurled							
Slot	Omit	No Slot							
	S	Slot (in Banding Area)							
Band	Omit	No Band							
	K	Standard Band Included							
	J	Slim Standard Band Included							




D-Subminiature



557-538

Shrouded Backshell, Banding, Snap-Together

- Split EMI Backshell
- Banding Shield Termination
- Lightweight Composite



Shroud Length	Mating Connector Panel Thickness		L Shroud Length	
	in	mm	in	mm
CC	N/A	N/A	.174	4.4
F0	N/A	N/A	.343	8.7
R1	.031	0.8	.247	6.3
R2	.047	1.2	.231	5.9
R3	.062	1.6	.216	5.5
R4	.093	2.4	.185	4.7
R5	.104	2.6	.174	4.4
R6	.125	3.2	.153	3.9
R7	.156	4.0	.125	3.2
R8	.135	3.4	.140	3.6
R9	.188	4.8	.094	2.4

Shell Size	A Max		B		C Min		D Min		E ±.005 (0.13)		H		J		K	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
1	.625	15.9	1.395	35.4	.510	13.0	1.229	31.2	.984	25.0	.436	11.1	.436	11.1	.436	11.1
2	.625	15.9	1.723	43.8	.510	13.0	1.557	39.5	1.312	33.3	.436	11.1	.759	19.3	.759	19.3
3	.625	15.9	2.270	57.7	.510	13.0	2.104	53.4	1.852	47.0	.436	11.1	.875	22.2	1.125	28.6
4	.625	15.9	2.911	73.9	.510	13.0	2.745	69.7	2.500	63.5	.436	11.1	1.100	27.9	1.773	45.0
5	.750	19.1	2.817	71.6	.620	15.7	2.651	67.3	2.406	61.1	.547	13.9	1.100	27.9	1.679	42.6

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

557-609

Split Lip Backshell, EMI Banding



- Round or Elliptical Entry
- 1-3 Entries
- Split Backshell



557-609

*This accessory fits D-Subminiature
M24308 connectors.
Not compatible with Series 28 HiPer-D*

Two piece banding, round or elliptical entry. 557-609 backshell fits M24308 D-Subminiature connectors. EMI protected. Cable shield attaches to backshell with optional band strap. Connector is captivated between backshell halves. #4-40 socket head screwlocks are included. Aluminum with stainless steel screws and washers.



PART NUMBER

Sample PN→

557T609

M

4

R

S

K

Base P/N **557T609**

Material/ Finish	TZ	Tin-Zinc
	MN	Mega-Nickel
	JF	Cadmium, Yel. Chromate
	M	Electroless Nickel
	NF	Olive Drab Cadmium
	MT	Nickel-PTFE
	ZR	Black Zinc-Nickel

Shell Size **1 2 3 4 5 6**


Code	Shell Size
R1 1 Round Entry	1-6
R2 2 Round Entries	3-6
R3 3 Round Entries	4-6
E1 1 Elliptical Entry	2-6
RIE1 1 Round and 1 Elliptical	3-6

Slots	<i>Omit</i>	No Slot
	S	Slot (<i>in banding area</i>)


	Omit	No Band
Band	B	Standard Band Included
	I	Slim Standard Band Included




ENTRY	R1	R2	R3
ROUND ENTRY			



ENTRY E1
1 ELLIPTICAL ENTRY



ENTRY R1E1
1 ELLIPTICAL AND 1
BOUND ENTRY



Shell Size	A		B		$\pm .005 (0.13)$		D		E Max		F Max		G Max		H		K Max	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
1	1.213	30.8	.630	16.0	.984	25.0	.728	18.5	1.300	33.0	.315	8.0	N/A	N/A	2.308	58.6	N/A	N/A
2	1.535	39.0	.630	16.0	1.312	33.3	1.059	26.9	1.300	33.0	.315	8.0	N/A	N/A	2.308	58.6	.661	16.8
3	2.087	53.0	.630	16.0	1.852	47.0	1.598	40.6	1.520	38.6	.315	8.0	.575	14.6	2.528	64.2	1.200	30.5
4	2.728	69.3	.630	16.0	2.500	63.5	2.248	57.1	1.520	38.6	.315	8.0	1.225	31.1	2.528	64.2	1.850	47.0
5	2.638	67.0	.750	19.1	2.406	61.1	2.192	55.7	1.520	38.6	.433	11.0	1.051	26.7	2.528	64.2	1.794	45.6
6	2.728	69.3	.787	20.0	2.500	63.5	2.248	57.1	1.520	38.6	.470	11.9	1.070	27.2	2.528	64.2	1.850	47.0

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.

Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

D-Subminiature



557-071

EMI Banding Backshell

- Solid EMI Backshell, .25" Flange
- Banding Shield Termination
- Qwik-Ty® Strain Relief

**T** Top Entry**S** Side Entry**B** 45° Entry**E** End Entry

557-071


This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

One piece, banding, .25 (6.4) flange.
557-071 lightweight aluminum backshell fits M24308 D-Subminiature connectors. Supplied with #4-40 male screwlocks. Terminate cable braid to backshell with banding strap. Optional slot for individual shield pigtails. Optional Qwik-Ty arm for attaching cable tie (not supplied). Aluminum with stainless steel screwlocks and clips.


TABLE 1
SCREWLOCK OPTIONS

No Designator

4-40 Socket Head Male
Jackscrews with "E"
Rings



4-40 Socket Head Male
Screwlocks with Clips



PART NUMBER

Sample PN → **557T071** **M** **3** **31** **S** **C** **T** **K**

Base P/N
557B071 **B** 45° Entry
557E071 **E** End Entry
557S071 **S** Side Entry
557T071 **T** Top Entry

Finish
TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size **1 2 3 4 5 6**

Entry Size

Entry Size	Entry Dia.	Shell Size
16	.175 (4.4)	1-6
23	.250 (6.4)	1-6
30	.312 (7.9)	1-6
31	.375 (9.5)	1-6
32	.430 (10.9)	1-6
33	.550 (14.0)	5-6



Slot
Omit No Slot
S Slot (in banding area)



Screwlocks
 (Table 1)
Omit Socket Head Jackscrews with "E" Rings
C Socket Head Screwlocks with Clips

Qwik-Ty
Omit No Qwik-Ty Strain Relief Arm
T Qwik-Ty Arm Included

Band
Omit No Band
B Standard Band Included
J Slim Standard Band Included

D-Subminiature

**557-071**


EMI Banding Backshell

- Solid EMI Backshell, .25" Flange
- Banding Shield Termination
- Qwik-Ty® Strain Relief

SCREWLOCK OPTIONS

No Designator


4-40 Socket Head Male Jackscrews with "E" Rings



Part Number **687-172**
Order 2 per backshell



4-40 Socket Head Male Screwlocks with Clips




Part Number **687-236**
Order 2 per backshell

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110



Shell Size	A Max		B		D ± .005 (0.13)		E		J		Max Entry Size
	in	mm	in	mm	in	mm	in	mm	in	mm	
1	1.25	31.8	.53	13.5	.984	25.0	1.25	31.8	1.68	42.7	32
2	1.58	40.1	.53	13.5	1.312	33.3	1.25	31.8	1.68	42.7	32
3	2.13	54.1	.53	13.5	1.852	47.0	1.25	31.8	1.68	42.7	32
4	2.77	70.4	.53	13.5	2.500	63.5	1.25	31.8	1.68	42.7	32
5	2.68	68.1	.66	16.8	2.406	61.1	1.38	35.1	1.81	46.0	33
6	2.77	70.4	.73	18.5	2.500	63.5	1.47	37.3	1.97	50.0	33

Entry Size	ø F		ø G		ø H		K		L	
	in	mm	in	mm	in	mm	in	mm	in	mm
16	.175	4.4	.300	7.6	.422	10.7	.08	2.0	.19	4.8
23	.250	6.4	.375	9.5	.497	12.6	.08	2.0	.22	5.6
30	.312	7.9	.437	11.1	.560	14.2	.08	2.0	.25	6.4
31	.375	9.5	.500	12.7	.622	15.8	.08	2.0	.28	7.1
32	.430	10.9	.555	14.1	.677	17.2	.08	2.0	.31	7.9
33	.550	14.0	.675	17.1	.797	20.2	.08	2.0	.38	9.7



D-Subminiature



557-110

EMI Backshell

- Solid EMI Backshell, .25" Flange
- Cone-and-Ring Shield Termination
- Saddle Clamp Strain Relief

**T** Top Entry**S** Side Entry**E** End EntryCONE-AND-RING
SHIELD TERMINATION

Fold braid over grounding ring. Tighten clamp onto backshell to captivate braid.

557-110


This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

One piece, Cone-and-ring shield termination, saddle clamp, .25 (6.4) flange.


557-110 aluminum backshell fits M24308 D-Subminiature connectors. Grounding ring shield termination. Three screwlock options: male socket head, male extended length, or fixed female hex posts. Aluminum with stainless steel screws and clips.

TABLE 1
SCREWLOCK OPTIONS**C**


4-40 Socket Head Male
Screwlocks With Clips

**F**

4-40 Female
Screwlocks (fixed, non-
rotating)

**E**

4-40 Extended Length
Slotted Male Screwlocks
With Clips



PART NUMBER

Sample PN → **557T110** **M** **3** **F** **03** **C**

Base P/N **557E110** **E** End Entry
557S110 **S** Side Entry
557T110 **T** Top Entry

Finish

TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size **1 2 3 4 5 6**Strain Relief **F** Saddle Clamp

Entry Size

Entry Size	Cable Range		Shell Size
	Min	Max	
02	.125 (3.2)	.250 (6.4)	1-6
03	.250 (6.4)	.375 (9.5)	1-6
04	.312 (7.9)	.500 (12.7)	1-6
05	.375 (9.5)	.625 (15.9)	6


Screwlocks
(Table 1)

Omit #4-40 Tapped Holes
C Socket Head Male Screwlocks
E Extended Slotted Male Screwlock (Profiles **S** **T** only)
P Female Screwlocks (fixed)

D-Subminiature

557-110
EMI Backshell

- Solid EMI Backshell, .25" Flange
- Cone-and-Ring Shield Termination
- Saddle Clamp Strain Relief




Shell Size	A Max		B		C		D		E		F		G		Max Entry Size
	in	mm	in	mm	in	mm	± .005 (0.13)	in	mm	in	mm	in	mm		
1	1.25	31.8	.53	13.5	.75	19.1	.984	25.0	1.88	47.8	.43	10.9	.90	22.9	04
2	1.58	40.1	.53	13.5	.75	19.1	1.312	33.3	1.88	47.8	.43	10.9	.90	22.9	04
3	2.13	54.1	.53	13.5	1.00	25.4	1.852	47.0	1.88	47.8	.43	10.9	2.00	50.8	04
4	2.77	70.4	.53	13.5	1.00	25.4	2.500	63.5	1.88	47.8	.43	10.9	2.00	50.8	04
5	2.68	68.1	.66	16.8	1.25	31.8	2.406	61.1	2.13	54.1	.56	14.2	2.00	50.8	04
6	2.77	70.4	.73	18.5	1.25	31.8	2.500	63.5	2.22	56.4	.63	16.0	2.00	50.8	05

Entry Size	H Max		Ferrule I.D. (REF)		Cable Range Min		Max	
	in	mm	in	mm	in	mm	in	mm
02	.968	24.6	.125	3.2	.125	3.2	.250	6.4
03	1.046	26.6	.250	6.4	.250	6.4	.375	9.5
04	1.156	29.4	.375	9.5	.312	7.9	.500	12.7
05	1.218	30.9	.500	12.7	.375	9.5	.625	15.9

SCREWLOCK OPTIONS

C


4-40 Socket Head Male Screwlocks With Clips



Part Number **687-236**
Order 2 per backshell

P


4-40 Female Screwlocks with Nut and Lockwasher



Part Number **687-418F**
Order 2 per backshell

E

4-40 Extended Length Slotted Male Screwlocks With Clips



Shell Size	G Length		Part Number
	in	mm	
1, 2	.90	22.9	687-236-3
3-6	2.00	50.8	687-236-2
			Order 2 per backshell

D-Subminiature



557-246

Elliptical Micro Band Backshell

- Solid EMI Backshell, .25" Flange
- Micro Band Shield Termination
- Qwik-Ty Strain Relief



557-246


This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

One piece, elliptical Micro band, .25 (6.4) flange. 557-246 aluminum backshell fits M24308 D-Subminiature connectors. Terminate cable braid to backshell with .12 wide (3.0) Micro band. Optional slot for routing individual pigtail shields. Optional Qwik-Ty strain relief arm. Aluminum with stainless steel screws and clips.

TABLE 1
SCREWLOCK OPTIONS


No Designator

4-40 Socket Head Male
Screwlocks With Clips




P

4-40 Female
Screwlocks (fixed, non-
rotating)



E

4-40 Extended Length
Slotted Male Screwlocks
With Clips



PART NUMBER

Sample PN→ 557T246 M 3 08 S T K

Base P/N 557T246 Top Entry

Finish

- TZ Tin-Zinc
- MN Mega-Nickel
- JF Cadmium, Yel. Chromate
- M Electroless Nickel
- NF Olive Drab Cadmium
- MT Nickel-PTFE
- ZR Black Zinc-Nickel


Shell Size 1 2 3 4 5 6

Screwlocks
(Table 1)

- Omit Socket Head Screwlocks
- E Extended Slotted Male Screwlock
- P Female Screwlocks (fixed)

Entry Size

Entry Size	F	Shell Size
04	.500 (12.7)	1-6
05	.625 (15.9)	1-6
06	.750 (19.1)	2-6
07	.875 (22.2)	2-6
08	1.000 (25.4)	2-6
09	1.125 (28.6)	3-6
10	1.250 (31.8)	3-6
11	1.375 (34.9)	3-6
12	1.500 (38.1)	3-6
13	1.625 (41.3)	4-6
14	1.750 (44.5)	4-6
15	1.875 (47.6)	4-6
16	2.000 (50.8)	4-6



Slot

- Omit No Slot
- S Slot (in banding area)



Qwik-Ty

- Omit No Qwik-Ty Strain Relief Arm
- T Qwik-Ty Arm Included



Band

- Omit No Band
- K Micro Band Included
- J Micro Slim Band Included
- L Micro-Max Band Included

D-SUBMINIATURE ACCESSORIES


D-Subminiature



557-246

Elliptical Micro Band Backshell

- Solid EMI Backshell, .25" Flange
- Micro Band Shield Termination
- Qwik-Ty Strain Relief



Shell Size	A Max		B		D ±.005 (0.13)		E		Max Entry Size
	in	mm	in	mm	in	mm	in	mm	
1	1.25	31.8	.53	13.5	.984	25.0	.375	9.5	05
2	1.58	40.1	.53	13.5	1.312	33.3	.375	9.5	08
3	2.13	54.1	.53	13.5	1.852	47.0	.375	9.5	12
4	2.77	70.4	.53	13.5	2.500	63.5	.375	9.5	16
5	2.68	68.1	.66	16.8	2.406	61.1	.484	12.3	16
6	2.77	70.4	.73	18.5	2.500	63.5	.554	14.1	16

Entry Size	F		H		Shell Size
	in	mm	in	mm	
04	.500	12.7	.19	4.8	1-6
05	.625	15.9	.19	4.8	1-6
06	.750	19.1	.22	5.6	2-6
07	.875	22.2	.22	5.6	2-6
08	1.000	25.4	.22	5.6	2-6
09	1.125	28.6	.22	5.6	3-6
10	1.250	31.8	.22	5.6	3-6
11	1.375	34.9	.25	6.4	3-6
12	1.500	38.1	.25	6.4	3-6
13	1.625	41.3	.25	6.4	4-6
14	1.750	44.5	.25	6.4	4-6
15	1.875	47.6	.25	6.4	4-6
16	2.000	50.8	.25	6.4	4-6

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.




Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-130

SCREWLOCK OPTIONS

No Designator


4-40 Socket Head Male Jackscrews with Clips



Part Number **687-236**
Order 2 per backshell


P

4-40 Female Screwlocks with Nut, Lockwasher and (2) Spacer Washers



E

4-40 Extended Length Slotted Male Screwlocks with Clips



D-Subminiature



557-316

Low Profile Banding Backshell

- Solid EMI Backshell, .25" Flange
- Banding Shield Termination
- Qwik-Ty® Strain Relief

**T** Top Entry**S** Side Entry**B** 45° Entry**E** End Entry


557-316

This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D


One piece, reduced height, .25 (6.4) flange. 557-316 aluminum backshell fits M24308 D-Subminiature connectors. Top entry version has reduced can height for limited clearance equipment. Terminate cable braid to backshell with .24" (6.1) wide banding strap. Optional slot for routing individual pigtail shields. Optional Qwik-Ty strain relief arm. Aluminum with stainless steel screws and clips.

TABLE 2
SCREWLOCK OPTIONS
A

4-40 Socket Head Male
Screwlocks with Clips

**H**

Thru-Holes (Screwlocks
not included)




PART NUMBER

Sample PN → **557T316 M 3 32 S T K A**

Base P/N	557B316	B 45° Entry	
	557E316	E End Entry	
	557S316	S Side Entry	
	557T316	T Top Entry	
Finish	TZ	Tin-Zinc	
	MN	Mega-Nickel	
	JF	Cadmium, Yel. Chromate	
	M	Electroless Nickel	
	NF	Olive Drab Cadmium	
	MT	Nickel-PTFE	
	ZR	Black Zinc-Nickel	
Shell Size	1 2 3 4 5 6		
Entry Size	See Table 1		
Slot	Omit	No Slot	
	S	Slot (in banding area)	
Qwik-Ty	Omit	No Qwik-Ty Strain Relief Arm	
	T	Qwik-Ty Arm Included	
Band	Omit	No Band	
	K	Standard Band Included	
	J	Slim Standard Band Included	
Screwlocks (Table 1)	Omit	#4-40 Tapped Holes	
	A	Socket Head Male Screwlocks	
	H	Thru-Holes (order screwlocks separately)	

TABLE 1 ENTRY SIZE

Entry Size	T B Top and 45° Entry								E S End and Side Entry			
	Shell Sizes 1-4				Shell Sizes 5-6				Shell Sizes 1-6			
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
16	.188	4.8	—	—	1-4	.188	4.8	—	.188	4.8	—	—
23	.250	6.4	—	—	1-4	.250	6.4	—	.250	6.4	—	—
30	.312	7.9	—	—	1-4	.312	7.9	—	.312	7.9	—	—
31	.375	9.5	—	—	1-4	.375	9.5	—	.375	9.5	—	—
32	.438	11.1	—	—	1-4	.438	11.1	—	.438	11.1	—	—
33	.562	14.3	.723	18.4	2-4	.562	14.3	—	.562	14.3	—	—
34	.650	16.5	.967	24.6	2-4	.460	11.7	1.380	.650	16.5	—	—
35	.562	14.3	1.250	31.8	3-4	.460	11.7	1.500	—	—	—	—
36	—	—	—	—	—	—	—	—	.650	16.5	.967	24.9





D-Subminiature

557-316

Low Profile Banding Backshell

- Solid EMI Backshell, .25" Flange
- Banding Shield Termination
- Qwik-Ty® Strain Relief




Shell Size	A Max		B		C		D		E Max		F Max		G Max		H	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
1	1.250	31.8	.520	13.2	.984	25.0	.440	11.2	.695	17.7	1.413	35.9	1.035	26.3	.856	21.7
2	1.580	40.1	.520	13.2	1.312	33.3	.440	11.2	.945	24.0	1.413	35.9	1.035	26.3	1.186	30.1
3	2.130	54.1	.520	13.2	1.852	47.0	.440	11.2	.945	24.0	1.595	40.5	1.035	26.3	1.727	43.9
4	2.770	70.4	.520	13.2	2.500	63.5	.440	11.2	.945	24.0	1.595	40.5	1.035	26.3	2.383	60.5
5	2.680	68.1	.629	16.0	2.406	61.1	.549	13.9	1.135	28.8	1.595	40.5	1.125	28.6	2.287	58.1
6	2.770	70.4	.690	17.5	2.500	63.5	.610	15.5	1.265	32.1	1.595	40.5	1.185	30.1	2.405	61.1

SCREWLOCKS

A


4-40 Socket Head Male Screwlocks with "C" Clips




Part Number 687-236
Order 2 per backshell

SLOT OPTION

Entry Size	in	mm
16	.19	4.8
23	.22	5.6
30	.25	6.4
31	.28	7.1
32	.31	7.9
33	.38	9.7
34	.44	11.2
35	.45	11.4



QWIK-TY OPTION



BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

D-Subminiature

557-432

Low Profile Micro Band Backshell

- Solid EMI Backshell, .25" Flange
- Micro Band Shield Termination
- Qwik-Ty® Strain Relief

**T** Top Entry**B** 45° Entry

557-432


This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

One piece, reduced can height, Micro band shield termination. 557-432 aluminum backshell fits M24308 D-Subminiature connectors. Low profile backshell has reduced can height for limited clearance equipment. Terminate cable braid to backshell with .12 wide (3.0) Micro band. Optional slot for routing individual pigtail shields. Qwik-Ty strain relief arm. Aluminum with stainless steel screws and clips.


TABLE 1 SCREWLOCK OPTIONS

C


4-40 Socket Head Male
Screwlocks with "C"
Clips

**P**

4-40 Female
Screwlocks (fixed, non-
rotating)

**E**

4-40 Extended Length
Slotted Male Screwlocks
with "C" clips



PART NUMBER

		557T432	M	3	32	C	K
Base P/N	557B432 B 45° Entry 557T432 T Top Entry						
Finish	TZ Tin-Zinc MN Mega-Nickel JF Cadmium, Yel. Chromate M Electroless Nickel NF Olive Drab Cadmium MT Nickel-PTFE ZR Black Zinc-Nickel						
Shell Size	1 2 3 4 5 6						
Entry Size	Entry Size	Entry Dia.	Shell Size				
	16	.188 (4.8)	1-6				
	23	.250 (6.4)	1-6				
	30	.312 (7.9)	1-6				
	31	.375 (9.5)	1-6				
	32	.438 (11.1)	1-6				
	33	.562 (14.3)	6				
Screwlocks (Table 1)	Omit Thru-Holes (screwlocks not included)						
	C Socket Head Male Screwlocks						
	E Extended Male Screwlocks (T top entry only)						
	P Female Screwlocks (fixed, non-rotating)						
Band	Omit No Band						
	K Micro Band Included						
	J Micro Slim Band Included						
	L Micro-Max Band Included						

BAND OPTIONS

Terminate braid to backshell with band strap and banding tool. Pre-coiled bands are passivated SST. Micro Slim bands: reduced thickness for weight reduction. Micro-Max bands: high-tension for lower-resistivity termination.


Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-130

D-Subminiature

557-432

Low Profile Micro Band Backshell

- Solid EMI Backshell, .25" Flange
- Micro Band Shield Termination
- Qwik-Ty® Strain Relief




Shell Size	A Max		B		C Max		D		Max Entry Size
	in	mm	in	mm	in	mm	±.005 (0.13)	in	
1	1.250	31.8	.53	13.5	.75	19.1	.984	25.0	32
2	1.580	40.1	.53	13.5	.75	19.1	1.312	33.3	32
3	2.130	54.1	.53	13.5	.93	23.6	1.852	47.0	32
4	2.770	70.4	.53	13.5	.93	23.6	2.500	63.5	32
5	2.680	68.1	.66	16.8	.93	23.6	2.406	61.1	32
6	2.770	70.4	.73	18.5	.93	23.6	2.500	63.5	33

Entry Size	in	ø H	mm	in	ø J	mm
16	.299	.76	.188	4.8		
23	.361	9.2	.250	6.4		
30	.423	10.7	.312	7.9		
31	.486	12.3	.375	9.5		
32	.548	13.9	.438	11.1		
33	.673	17.1	.562	14.3		

SCREWLOCK OPTIONS

C


4-40 Socket Head Male Screwlocks with Clips



Part Number **687-236**
Order 2 per backshell

P


4-40 Female Screwlocks with Nut and Lockwasher



Part Number **687-178P**
Order 2 per backshell

E

4-40 Extended Length Slotted Male Screwlocks with Clips



Shell Size	Length		Part Number
	in	mm	
1, 2	.75	19.1	687-626-1E
3, 4, 5, 6	1.00	25.4	687-626-2E

Order 2 per backshell

D-Subminiature



557-467

Straight Clamp Backshell

- Solid Backshell, .25" Flange
- Straight Clamp Strain Relief
- For Unshielded Cable



557-467


This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Straight clamp. 557-467 aluminum backshell fits M24308 D-Subminiature connectors. Use with unshielded wire bundles. Flat bars with silicone pads provide strain relief. Aluminum with stainless steel screws and clips.


TABLE 1
SCREWLOCK OPTIONS

B


4-40 Fillister Head Male Screwlocks with Clips

**C**

4-40 Socket Head Male Screwlocks with Clips

**E**

4-40 Extended Length Slotted Male Screwlocks with Clips



PART NUMBER

Sample PN → **557T467 M -2 C**Base P/N **557T467**


Finish

TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size **-1 -2 -3 -4 -5 -6**

Screwlocks
(Table 1)

B Fillister Head Male Screwlocks
C Socket Head Male Screwlocks
E Extended Slotted Male Screwlocks



Shell Size	A ±.005 (0.13)		B		C		D		E		F Min		G Min		H (open)	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
1	.984	25.0	1.250	31.8	.75	19.1	1.06	26.9	.53	13.5	.50	12.7	.350	8.9	.188	4.8
2	1.312	33.3	1.580	40.1	.75	19.1	1.06	26.9	.53	13.5	.50	12.7	.562	14.3	.188	4.8
3	1.852	47.0	2.100	53.3	.75	19.1	1.06	26.9	.53	13.5	.50	12.7	1.000	25.4	.188	4.8
4	2.500	63.5	2.750	69.9	1.00	25.4	1.31	33.3	.53	13.5	.68	17.3	1.625	41.3	.188	4.8
5	2.406	61.1	2.680	68.1	1.00	25.4	1.31	33.3	.66	16.8	.68	17.3	1.500	38.1	.250	6.4
6	2.500	63.5	2.740	69.6	1.00	25.4	1.31	33.3	.71	18.5	.68	17.3	1.625	41.3	.250	6.4

D-Subminiature

557-553
TAG Ring® Backshell


- Solid Backshell, .25" Flange
- TAG Ring® Shield Termination
- Saddle Clamp Strain Relief




T Top Entry



S Side Entry



E End Entry



557-553


This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

TAG Ring shield termination. 557-553 backshell fits M24308 D-Subminiature connectors. TAG ring has slots for individual wire shields. Gold-plated copper alloy spring and PTFE friction washer. Backshell body is aluminum, screws and clips are stainless steel.

TABLE 1
SCREWLOCK OPTIONS


C

4-40 Socket Head Male
Screwlocks with Clips



E

4-40 Extended
Length Slotted Male
Screwlocks with Clips



PART NUMBER

Sample PN→

557T553

M

3

F

03

C

Base P/N
557E553 **E** End Entry
557S553 **S** Side Entry
557T553 **T** Top Entry

Finish
TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size 1 2 3 4 5 6

Strain Relief
F Saddle Clamp, Short
G Nut
L Saddle Clamp, Long



Entry Size	Cable Range		Shell Size
	Min	Max	
02	.125 (3.2)	.250 (6.4)	1-6
03	.250 (6.4)	.375 (9.5)	1-6
04	.250 (6.4)	.438 (11.1)	1-6
05	.375 (9.5)	.625 (15.9)	6

Screwlocks
(Table 1)
Omit #4-40 Tapped Holes
C Socket Head Male Screwlocks
E Extended Slotted Male Screwlock (Profiles **S** **T** only)
X .125 (3.2) Thru-Holes (screwlocks not included)



D-Subminiature



557-553

TAG Ring® Backshell

- Solid Backshell, .25" Flange
- TAG Ring® Shield Termination
- Saddle Clamp Strain Relief




Shell Size	A Max		B		C ± .005 (0.13)		D		E		F		G		Max Entry Size
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	
1	1.25	31.8	.53	13.5	.984	25.0	.43	10.9	1.88	47.8	.75	19.1	.90	22.9	04
2	1.58	40.1	.53	13.5	1.312	33.3	.43	10.9	1.88	47.8	.75	19.1	.90	22.9	04
3	2.13	54.1	.53	13.5	1.852	47.0	.43	10.9	1.88	47.8	1.00	25.4	2.00	50.8	04
4	2.77	70.4	.53	13.5	2.500	63.5	.43	10.9	1.88	47.8	1.00	25.4	2.00	50.8	04
5	2.68	68.1	.66	16.8	2.406	61.1	.56	14.2	2.13	54.1	1.25	31.8	2.00	50.8	04
6	2.77	70.4	.73	18.5	2.500	63.5	.63	16.0	2.22	56.4	1.25	31.8	2.00	50.8	05

Entry Size	H Entry		J Max		K Max		Cable Range			
							Min		Max	
	in	mm	in	mm	in	mm	in	mm	in	mm
02	.25	6.4	.55	14.0	.97	24.63	.125	3.2	.250	6.4
03	.37	9.4	.67	17.0	1.05	26.7	.250	6.4	.375	9.5
04	.50	12.7	.80	20.3	1.16	29.5	.250	6.4	.438	11.1
05	.62	15.7	.92	23.4	1.22	31.0	.375	9.5	.625	15.9


SCREWLOCK OPTIONS



4-40 Socket Head Male Screwlocks with Clips

Part Number **687-236**
Order 2 per backshell

4-40 Extended Length Slotted Male Screwlocks with Clips



Shell Size	G Length	Part Number
in	mm	
1, 2	.90 22.9	687-236-3
3, 4, 5	2.00 50.8	687-236-2

Order 2 per backshell

D-Subminiature



557-107

Banding Backshell, Lightweight

- Solid Backshell, .035" Flange
- Banding Shield Termination
- Lightweight Trapezoidal



557-107

This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Lightweight, one piece, EMI banding.
557-107 backshell fits M24308 D-Subminiature connectors. Backshell body is aluminum, screws and clips are stainless steel.

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

PART NUMBER

Sample PN → **557-107 M 3 -05 A B S**

Base P/N **557-107**


Finish

TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size **1 2 3 4 5 6**

Entry Size

Entry Size	Entry Dia.	Shell Size
-01	.125 (3.2)	1-6
-02	.187 (4.7)	1-6
-03	.265 (6.7)	1-6
-04	.312 (7.9)	1-6
-05	.390 (9.9)	1-6
-06	.415 (10.5)	1-6
-07	.500 (12.7)	5-6
-08	.525 (13.3)	5-6
-09	.595 (15.1)	6

Screwlocks
(Table 1)

Omit Thru-Holes (screwlocks not included)
A Socket Head Male Screwlocks
C Fillister Head Male Screwlocks
E Extended Slotted Male Screwlocks

Band

Omit No Band
B Standard Band Included
J Slim Standard Band Included


Slot

Omit No Slot
S Slot in Banding Area


TABLE 1 SCREWLOCK OPTIONS

A


4-40 Socket Head Male
Screwlocks with Clips

**C**

4-40 Fillister Hd. Male Screwlocks
with Clips

**E**

4-40 Extended Male Screwlocks
with Clips




D-Subminiature



557-107

Banding Backshell, Lightweight

- Solid Backshell, .035" Flange
- Banding Shield Termination
- Lightweight Trapezoidal




Shell Size	A Max		B		C ±.008 (0.20)		D		E		Max Entry Size
	in	mm	in	mm	in	mm	in	mm	in	mm	
1	1.203	30.6	.500	12.7	.984	25.0	1.190	30.2	.440	11.2	06
2	1.531	38.9	.500	12.7	1.312	33.3	1.270	32.3	.440	11.2	06
3	2.078	52.8	.500	12.7	1.852	47.0	1.550	39.4	.500	12.7	06
4	2.718	69.0	.500	12.7	2.500	63.5	1.690	42.9	.500	12.7	06
5	2.625	66.7	.609	15.5	2.406	61.1	1.670	42.4	.440	11.2	08
6	2.718	69.0	.668	17.0	2.500	63.5	1.690	42.9	.500	12.7	09

Entry Size	ø F		ø G		H	
	in	mm	in	mm	in	mm
01	.125	3.2	.205	5.2	.090	2.3
02	.187	4.7	.267	6.8	.190	4.8
03	.265	6.7	.360	9.1	.220	5.6
04	.312	7.9	.392	10.0	.250	6.4
05	.390	9.9	.485	12.3	.280	7.1
06	.415	10.5	.510	13.0	.310	7.9
07	.500	12.7	.580	14.7	.310	7.9
08	.525	13.3	.620	15.7	.380	9.7
09	.595	15.1	.690	17.5	.380	9.7

SCREWLOCK OPTIONS

A


4-40 Socket Head Male Screwlocks with Clips



Part Number **687-316M**
Order 2 per backshell

C


4-40 Fillister Head Male Screwlocks with Clips



Part Number **687-316**
Order 2 per backshell

E

4-40 Extended Length Slotted Male Screwlocks with Clips



Part Number **687-316E1**
Order 2 per backshell

D-Subminiature



557-281

Banding Backshell, Micro Band

- Solid Backshell, .035" Flange
- Micro Band Shield Termination
- Lightweight Trapezoidal



557-281


This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Lightweight, one piece, Micro band. 557-281 trapezoidal backshell fits M24308 D-Subminiature connectors. Terminate cable shield to backshell with .12" wide Micro band. 13 entry sizes from ½ inch to 2 inches. Available in 8 heights ranging from ½ inch to 1 ⅝ inch. Backshell body is aluminum, screwlocks are stainless steel.

TABLE 1
SCREWLOCK OPTIONS


C

4-40 Socket Head Male
Screwlocks with Clips



P

4-40 Female
Screwlocks



PART NUMBER

Sample PN→

557-281 M 3 06 A S C J

Base P/N 557-281

Finish

TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size 1 2 3 4 5 6


Entry Size

Entry Size	H	Shell Size
04	.500 (12.7)	1-6
05	.625 (15.9)	1-6
06	.750 (19.1)	2-6
07	.875 (22.2)	2-6
08	1.000 (25.4)	2-6
09	1.125 (28.6)	3-6
10	1.250 (31.8)	3-6
11	1.375 (34.9)	3-6
12	1.500 (38.1)	3-6
13	1.625 (41.3)	4-6
14	1.750 (44.5)	4-6
15	1.875 (47.6)	4-6
16	2.000 (50.8)	4-6



Height Code

Code	J
A	.50 (12.7)
B	.62 (15.8)
C	.75 (19.1)
D	.87 (22.1)
E	1.00 (25.4)
F	1.12 (28.5)
G	1.25 (31.8)
H	1.38 (35.1)



Qwik-Ty

Omit No Qwik-Ty Arm
S Qwik-Ty Arm Included

Screwlocks
(Table 1)

Omit Thru-Holes (screwlocks not included)
C Socket Head Male Screwlocks
P Female Screwlocks (fixed, non-rotating)

Band

Omit No Band
B Micro Band Included
J Micro Slim Band Included
L Micro-Max Band Included


D-Subminiature



557-281

Banding Backshell, Micro Band

- Solid Backshell, .035" Flange
- Micro Band Shield Termination
- Lightweight Trapezoidal



Shell Size	A		B		C ± .005 (0.13)		D		E		G ± .030 (0.8)		Max Entry Size
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	
1	1.203	30.6	.500	12.7	.984	25.0	.375	9.5	.467	11.7	.839	21.3	05
2	1.531	38.9	.500	12.7	1.312	33.3	.375	9.5	.467	11.7	1.178	29.9	08
3	2.078	52.8	.500	12.7	1.852	47.0	.375	9.5	.467	11.7	1.706	43.3	12
4	2.718	69.0	.500	12.7	2.500	63.5	.375	9.5	.467	11.7	2.364	60.0	16
5	2.625	66.7	.609	15.5	2.406	61.1	.484	12.3	.579	14.7	2.291	58.2	16
6	2.780	70.6	.670	17.0	2.500	63.5	.554	14.1	.621	15.8	2.421	61.5	16


Entry Size	H in	H mm	Shell Size
04	.500	12.7	1-6
05	.625	15.9	1-6
06	.750	19.1	2-6
07	.875	22.2	2-6
08	1.000	25.4	2-6
09	1.125	28.6	3-6
10	1.250	31.8	3-6
11	1.375	34.9	3-6
12	1.500	38.1	3-6
13	1.625	41.3	4-6
14	1.750	44.5	4-6
15	1.875	47.6	4-6
16	2.000	50.8	4-6

Height Code	J	
	in	mm
A	.50	12.7
B	.62	15.8
C	.75	19.1
D	.87	22.1
E	1.00	25.4
F	1.12	28.5
G	1.25	31.8
H	1.38	35.1

SCREWLOCK OPTIONS

C


4-40 Socket Head Male Screwlocks with Clips



Part Number **687-316M**
Order 2 per backshell

P

4-40 Female Screwlocks (fixed, non-rotating)



Part Number **687-180P**
Order 2 per backshell

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.



Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-130

D-Subminiature

557-319

Banding Backshell, 45° & End Entry

- Solid Backshell, .035" Flange
- Banding Shield Termination
- Lightweight



B 45° Entry



E End Entry

557-319


This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Lightweight, one piece. 557-319 backshell fits M24308 D-Subminiature connectors. Terminate cable shield to backshell with .12" wide Micro band. Available in 45° or end entry. Attach cable tie to optional Qwik-Ty strain relief arm. Backshell body is aluminum, screwlocks are stainless steel.

TABLE 1
SCREWLOCK OPTIONS


A

4-40 Socket Head Male
Screwlocks with Clips




C

4-40 Fillister Hd. Male
Screwlocks with Clips



P

4-40 Female
Screwlocks



PART NUMBER

Sample PN→

557B319

M

2

04

C

B


-T

Base P/N **557B319** **B** 45° Entry
557E319 **E** End Entry

Finish **TZ** Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size **1 2 3 4 5 6**


Entry Size	Entry Size		Shell Size
		E	
01	.125 (3.2)		1-6
02	.187 (4.7)		1-6
03	.265 (6.7)		1-6
04	.312 (7.9)		1-6
05	.390 (9.9)		1-6
06	.415 (10.5)		1-6
07	.500 (12.7)		5-6
08	.525 (13.3)		5-6
09	.570 (14.5)		6



Screwlocks (Table 1) **Omit** Thru-Holes (screwlocks not included)
A Socket Head Male Screwlocks
C Fillister Head Male Screwlocks
P Female Screwlocks (fixed, non-rotating)

Band **Omit** No Band
B Micro Band Included
J Micro Slim Band Included
L Micro-Max Band Included

Qwik-Ty **Omit** No Qwik-Ty Strain Relief Arm
-T Qwik-Ty Arm Included




D-Subminiature



557-319

Banding Backshell, 45° & End Entry

- Solid Backshell, .035" Flange
- Banding Shield Termination
- Lightweight



Shell Size	A		B		C		D		Max Entry Size	Entry Size	ø E		ø F	
	in	mm	in	mm	± .005 (0.13)	mm	± .015 (0.38)	mm			in	mm	in	mm
1	1.203	30.6	.520	13.2	.984	25.0	1.000	25.4	06	01	.125	3.2	.205	5.2
2	1.531	38.9	.520	13.2	1.312	33.3	1.125	28.6	06	02	.187	4.7	.267	6.8
3	2.078	52.8	.520	13.2	1.852	47.0	1.188	30.2	06	03	.265	6.7	.360	9.1
4	2.718	69.0	.520	13.2	2.500	63.5	1.188	30.2	06	04	.312	7.9	.392	10.0
5	2.625	66.7	.629	16.0	2.406	61.1	1.312	33.3	08	05	.390	9.9	.485	12.3
6	2.718	69.0	.690	17.5	2.500	63.5	1.312	33.3	09	06	.415	10.5	.510	13.0
										07	.500	12.7	.580	14.7
										08	.525	13.3	.620	15.7
										09	.570	14.5	.665	16.9

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.




Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-130

SCREWLOCK OPTIONS

A


4-40 Socket Head Male Screwlocks with Clips



Part Number **687-316M**
Order 2 per backshell

C


4-40 Fillister Head Male Screwlocks with Clips



Part Number **687-316**
Order 2 per backshell

P

4-40 Female Screwlocks (fixed, non-rotating)



Part Number **687-180P**
Order 2 per backshell

D-Subminiature

557-561

Banding Backshell, Micro Band, 45° & End Entry

- Solid Backshell, .035" Flange
- Micro Band Shield Termination
- Lightweight



B 45° Entry



E End Entry

557-561


This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

Lightweight, one piece, Micro band. 557-561 backshell fits M24308 D-Subminiature connectors. Terminate cable shield to backshell with .12" wide Micro band strap. Available in 45° or end entry. Backshell body is aluminum, screwlocks are stainless steel.

TABLE 1
SCREWLOCK OPTIONS


A

4-40 Socket Head Male
Screwlocks with Clips




C

4-40 Fillister Hd. Male
Screwlocks with Clips



P

4-40 Female
Screwlocks



PART NUMBER


Sample PN→ **557B561** **M** **2** **04** **C** **B**

Base P/N **557B561** **B** 45° Entry
557E561 **E** End Entry

Finish **TZ** Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
M Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size **1 2 3 4 5 6**

Entry Size	E	Shell Size
01	.125 (3.2)	1-6
02	.187 (4.7)	1-6
03	.265 (6.7)	1-6
04	.312 (7.9)	1-6
05	.390 (9.9)	1-6
06	.415 (10.5)	1-6
07	.500 (12.7)	5-6
08	.525 (13.3)	5-6
09	.570 (14.5)	6



Screwlocks (Table 1) **Omit** Thru-Holes (screwlocks not included)
A Socket Head Male Screwlocks
C Fillister Head Male Screwlocks
P Female Screwlocks (fixed, non-rotating)

Band **Omit** No Band
B Micro Band Included
J Micro Slim Band Included
L Micro-Max Band Included


D-Subminiature



557-561

Banding Backshell, Micro Band, 45° & End Entry

- Solid Backshell, .035" Flange
- Micro Band Shield Termination
- Lightweight



Shell Size	A		B		C		D		Max Entry Size	Entry Size	ø E		ø F	
	in	mm	in	mm	± .005 (0.13)	in	mm	± .015 (0.38)			in	mm	in	mm
1	1.203	30.6	.520	13.2	.984	25.0	1.000	25.4	06	01	.125	3.2	.205	5.2
2	1.531	38.9	.520	13.2	1.312	33.3	1.125	28.6	06	02	.187	4.7	.267	6.8
3	2.078	52.8	.520	13.2	1.852	47.0	1.188	30.2	06	03	.265	6.7	.360	9.1
4	2.718	69.0	.520	13.2	2.500	63.5	1.188	30.2	06	04	.312	7.9	.392	10.0
5	2.625	66.7	.629	16.0	2.406	61.1	1.312	33.3	08	05	.390	9.9	.485	12.3
6	2.718	69.0	.690	17.5	2.500	63.5	1.312	33.3	09	06	.415	10.5	.510	13.0
										07	.500	12.7	.580	14.7
										08	.525	13.3	.620	15.7
										09	.570	14.5	.665	16.9

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.




Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

SCREWLOCK OPTIONS

A


4-40 Socket Head Male Screwlocks with Clips



Part Number **687-316M**
Order 2 per backshell

C


4-40 Fillister Head Male Screwlocks with Clips



Part Number **687-316**
Order 2 per backshell

P

4-40 Female Screwlocks (fixed, non-rotating)



Part Number **687-180P**
Order 2 per backshell




D-Subminiature


289-005

Banding Backshell, HiPer-D

- Split EMI Backshell
- Banding Shield Termination
- For Series 28 HiPer-D with Groove



T Top Entry




S Side Entry

Lightweight, low profile space-saving two piece backshell fits HiPer-D® connectors with backshell groove (280-018P, 280-019S, 280-046P, 280-047S). Terminate cable shield with optional clamping band. Elliptical cable entry provides room for large wire bundles. Non-environmental. Aluminum alloy, passivated stainless steel hardware.

289-005

This accessory fits HiPer-D connectors with backshell groove.


TABLE 1
ENTRY SIZE



Shell Size	Entry Size	C in	C mm	D in	D mm
1	A	.143	3.6	.143	3.6
	B	.195	5.0	.195	5.0
	C	.242	6.2	.242	6.2
	D	.438	11.1	.375	9.5
	E	.638	16.2	.375	9.5
2	A	.188	4.8	.188	4.8
	B	.256	6.5	.256	6.5
	C	.480	12.2	.375	9.5
	D	.688	17.5	.375	9.5
	E	.969	24.6	.375	9.5
3	A	.245	6.2	.245	6.2
	B	.550	14.0	.375	9.5
	C	.780	19.8	.375	9.5
	D	1.125	28.6	.375	9.5
	E	1.484	37.7	.375	9.5
4	A	.291	7.4	.291	7.4
	B	.800	20.3	.375	9.5
	C	1.260	32.0	.375	9.5
	D	1.813	46.1	.375	9.5
	E	2.155	54.7	.375	9.5
5	A	.326	8.3	.326	8.3
	B	.770	19.6	.485	12.3
	C	1.250	31.8	.485	12.3
	D	1.750	44.5	.485	12.3
	E	2.031	51.6	.485	12.3
6	A	.376	9.6	.376	9.6
	B	.863	21.9	.550	14.0
	C	1.323	33.6	.550	14.0
	D	1.875	47.6	.550	14.0
	E	2.165	55.0	.550	14.0

PART NUMBER

Sample PN→ 289T005 ME 3 A T S K

Base P/N	289T005 T Top Entry 289S005 S Side Entry
Finish	TZ Tin-Zinc MN Mega-Nickel JF Cadmium, Yel. Chromate ME Electroless Nickel NF Olive Drab Cadmium MT Nickel-PTFE ZR Black Zinc-Nickel
Shell Size	1 2 3 4 5 6
Entry Size	A B C D E See Table 1
Qwik-Ty	N No Qwik-Ty Strain Relief Arm T Qwik-Ty Arm Included 
Slots	N No Slots S Slots in Banding Area 
Band	N No Band K Standard Band Included J Slim Standard Band Included
Entry Direction	Applies to 289S005 Side Entry Omit for 289T005 Top Entry 1 Direction 1 2 Direction 2 

D-Subminiature




289-005


Banding Backshell, HiPer-D

- Split EMI Backshell
- Banding Shield Termination
- For Series 28 HiPer-D with Groove

289T005 TOP ENTRY





*SEE TABLE 1 FOR C AND D DIM.



Shell Size	A Max		B Max	
	in	mm	in	mm
1	.894	22.7	.550	14.0
2	1.218	30.9	.550	14.0
3	1.760	44.7	.550	14.0
4	2.408	61.2	.550	14.0
5	2.297	58.3	.654	16.6
6	2.422	61.5	.716	18.2

289S005 SIDE ENTRY



*SEE TABLE 1 FOR C AND D DIM.

Shell Size	A Max		B Max	
	in	mm	in	mm
1	.894	22.7	.550	14.0
2	1.218	30.9	.550	14.0
3	1.760	44.7	.550	14.0
4	2.408	61.2	.550	14.0
5	2.297	58.3	.654	16.6
6	2.422	61.5	.716	18.2

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110




D-Subminiature

289-007

Panel Mount Banding Backshell, HiPer-D


- EMI Backshell
- Banding Shield Termination
- For Panel Mount Series 28 HiPer-D



T Top Entry



B 45° Entry




S Side Entry

Lightweight banding adapter fits HiPer-D® panel mount connectors with threaded accessory mounting holes (280-020, 280-021, 280-048, 280-049). Environmentally protected with gasket. Terminate cable shield with optional Band-Master® ATS clamping band. Elliptical cable entry provides room for large wire bundles. Compatible with Glenair Series 77 lipped heat-shrink boots. Aluminum alloy, stainless steel screws and washers, fluorosilicone gasket.

289-007

This accessory fits HiPer-D panel mount connectors:
280-020, 280-021, 280-048, 280-049

TABLE 1
ENTRY SIZE



Shell Size	Entry Size	C		D	
		in	mm	in	mm
1	A	.143	3.6	.143	3.6
	B	.195	5.0	.195	5.0
	C	.242	6.2	.242	6.2
	D	.438	11.1	.375	9.5
	E	.625	15.9	.375	9.5
2	A	.188	4.8	.188	4.8
	B	.256	6.5	.256	6.5
	C	.480	12.2	.375	9.5
	D	.688	17.5	.375	9.5
	E	.938	23.8	.375	9.5
3	A	.245	6.2	.245	6.2
	B	.550	14.0	.375	9.5
	C	.780	19.8	.375	9.5
	D	1.125	28.6	.375	9.5
	E	1.438	36.5	.375	9.5
4	A	.291	7.4	.291	7.4
	B	.800	20.3	.375	9.5
	C	1.260	32.0	.375	9.5
	D	1.813	46.1	.375	9.5
	E	2.125	54.0	.375	9.5
5	A	.326	8.3	.326	8.3
	B	.770	19.6	.485	12.3
	C	1.250	31.8	.485	12.3
	D	1.750	44.5	.485	12.3
	E	2.00	50.8	.485	12.3
6	A	.376	9.6	.376	9.6
	B	.863	21.9	.550	14.0
	C	1.323	33.6	.550	14.0
	D	1.875	47.6	.550	14.0
	E	2.125	54.0	.550	14.0

PART NUMBER

Sample PN→ 289T007 ME 4 D T S K

Base P/N
289T007 T Top Entry
289S007 S Side Entry
289B007 B 45° Entry

Finish
TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
ME Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel


Shell Size 1 2 3 4 5 6

Entry Size A B C D E See Table 1

Qwik-Ty
N No Qwik-Ty Strain Relief Arm
T Qwik-Ty Arm Included



Slots
N No Slots
S Slots in Banding Area



Band
N No Band
K Standard Band Included
J Slim Standard Band Included

Entry Direction
Applies to 289S005 Side Entry
Omit for 289T005 Top Entry
1 Direction 1
2 Direction 2



D-Subminiature





289-007

Panel Mount Banding Backshell, HiPer-D



- EMI Backshell
- Banding Shield Termination
- For Panel Mount Series 28 HiPer-D

289T007 TOP ENTRY





Shell Size	A Max		B Max	
	in	mm	in	mm
1	1.244	31.6	.526	13.4
2	1.572	39.9	.526	13.4
3	2.112	53.6	.526	13.4
4	2.760	70.1	.526	13.4
5	2.666	67.7	.628	16.0
6	2.760	70.1	.690	17.5

289S007 SIDE ENTRY



Shell Size	A Max		B Max	
	in	mm	in	mm
1	1.244	31.6	.526	13.4
2	1.572	39.9	.526	13.4
3	2.112	53.6	.526	13.4
4	2.760	70.1	.526	13.4
5	2.666	67.7	.628	16.0
6	2.760	70.1	.690	17.5

289B007 45° ENTRY



Shell Size	A Max		B Max	
	in	mm	in	mm
1	1.244	31.6	.526	13.4
2	1.572	39.9	.526	13.4
3	2.112	53.6	.526	13.4
4	2.760	70.1	.526	13.4
5	2.666	67.7	.628	16.0
6	2.760	70.1	.690	17.5

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110




D-Subminiature

289-008

Banding Backshell, HiPer-D

- Solid Backshell
- Banding Shield Termination
- Environmental



T Top Entry




S Side Entry

Lightweight, one piece, banding. 289-008 backshell fits M24308 D-Subminiature and Series 28 HiPer-D connectors. Internal gasket provides environmental protection when used with Series 28 connector and boot. Heatshrink boot groove accepts lipped Series 77 lipped boots. Terminate cable shield to backshell with .24" wide banding strap. Available in top or side entry. Aluminum with passivated stainless steel screwlocks and clips. Fluorosilicone gasket.

289-008

This accessory fits HiPer-D and D-Subminiature M24308 connectors.

TABLE 1
ENTRY SIZE



Shell Size	Entry Size	D in	D mm	E in	E mm
1	A	.143	3.6	.143	3.6
	B	.195	5.0	.195	5.0
	C	.242	6.2	.242	6.2
	D	.438	11.1	.375	9.5
	E	.638	16.2	.375	9.5
2	A	.188	4.8	.188	4.8
	B	.256	6.5	.256	6.5
	C	.480	12.2	.375	9.5
	D	.688	17.5	.375	9.5
	E	.969	24.6	.375	9.5
3	A	.245	6.2	.245	6.2
	B	.550	14.0	.375	9.5
	C	.780	19.8	.375	9.5
	D	1.125	28.6	.375	9.5
	E	1.484	37.7	.375	9.5
4	A	.291	7.4	.291	7.4
	B	.800	20.3	.375	9.5
	C	1.260	32.0	.375	9.5
	D	1.813	46.1	.375	9.5
	E	2.155	54.7	.375	9.5
5	A	.326	8.3	.326	8.3
	B	.770	19.6	.485	12.3
	C	1.250	31.8	.485	12.3
	D	1.750	44.5	.485	12.3
	E	2.031	51.6	.485	12.3
6	A	.376	9.6	.376	9.6
	B	.863	21.9	.550	14.0
	C	1.323	33.6	.550	14.0
	D	1.875	47.6	.550	14.0
	E	2.165	55.0	.550	14.0

PART NUMBER

Sample PN→ 289T008 ME 3 A -T S K

Base P/N 289T008 T Top Entry
289S008 S Side Entry

Finish TZ Tin-Zinc
MN Mega-Nickel
JF Cadmium, Yel. Chromate
ME Electroless Nickel
NF Olive Drab Cadmium
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size 1 2 3 4 5 6

Entry Size A B C D E See Table 1

Qwik-Ty N No Qwik-Ty Strain Relief Arm
T Qwik-Ty Arm Included

Slots N No Slots
S Slots in Banding Area

Band N No Band
K Standard Band Included
J Slim Standard Band Included

Entry Direction Applies to 289S008 Side Entry
Omit for 289T008 Top Entry

1 Direction 1
2 Direction 2



Screwlocks Omit Socket Head Male Screwlocks
T Extended Slot Head Male Screwlocks Entry Sizes ABCD only
W Socket Head Male Screwlocks with Safety Wire Holes
N Through Holes, No Screwlocks

D-Subminiature




289-008


Banding Backshell, HiPer-D

- Solid Backshell
- Banding Shield Termination
- Environmental

289T008 TOP ENTRY




289S008 SIDE ENTRY



SCREWLOCK OPTIONS

No Designator


4-40 Socket Head Male Jackscrews with Clips




Part Number **289-092**
Order 1 per backshell



4-40 Socket Head Male Jackscrews with Safety Wire Hole. Clips are included.



4-40 Extended Length Slotted Male Screwlocks With Clips



Part Number **289-068Z1**
Order 1 per backshell

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110


D-Subminiature



289-085

EMI Backshell, Solid

- Solid Backshell
- Cone-and-Ring Shield Termination
- Saddle Clamp Strain Relief




289-085

This accessory fits HiPer-D and D-Subminiature M24308 connectors.


EMI, one piece, saddle clamp. 289-085 backshell fits M24308 D-Subminiature and Series 28 HiPer-D connectors. Shielded backshell has grounding ring and saddle clamp strain relief. Connector flange is fully recessed into backshell. Aluminum with passivated stainless steel hardware.

CONE-AND-RING SHIELD TERMINATION




Shell Size	A Max		B Max		C		Max Entry Size
	in	mm	in	mm	in	mm	
1	1.395	35.4	.624	15.9	.984	25.0	04
2	1.706	43.3	.624	15.9	1.312	33.3	06
3	2.265	57.5	.624	15.9	1.852	47.0	08
4	2.900	73.7	.624	15.9	2.500	63.5	08
5	2.800	71.1	.750	19.1	2.406	61.1	08
6	2.900	73.7	.844	21.4	2.500	63.5	08

PART NUMBER						
Sample PN→		289T085	ME	3	F	05
Base P/N		289T085				
Finish	TZ	Tin-Zinc				
	MN	Mega-Nickel				
	JF	Cadmium, Yel. Chromate				
	ME	Electroless Nickel				
	NF	Olive Drab Cadmium				
	MT	Nickel-PTFE				
	ZR	Black Zinc-Nickel				
Shell Size		1 2 3 4 5 6				
Strain Relief		F Saddle Clamp				
Entry Size	Entry Size	Cable Range		Shell Size		
		Min	Max			
	02	.125 (3.2)	.250 (6.4)	1-6		
	03	.250 (6.4)	.375 (9.5)	1-6		
	04	.312 (7.9)	.500 (12.7)	1-6		
	05	.437 (11.1)	.625 (15.9)	2-6		
	06	.562 (14.3)	.750 (19.1)	2-6		
	07	.687 (17.4)	.875 (22.2)	6		
	08	.812 (20.6)	1.000 (25.4)	6		
Screwlocks	Omit Socket Head Male Screwlocks					
	P Female Screwlocks					




SCREWLOCK OPTIONS

No Designator: 4-40 Socket Head Male Jackscrews with Clips



Part Number **289-092**
Order 1 per backshell

P 4-40 Female Screwlocks




Part Number **289-015-A**
Order 1 per backshell

D-Subminiature


**289-087**

EMI Backshell, HiPer-D, Split Piggyback


- Split Backshell, HiPer-D
- Micro Band Shield Termination
- 60° Entry

**289-087**

This accessory fits HiPer-D connectors with backshell groove. 280-018P, 280-019S, 280-046P, 280-047S



CONFIGURATION VARIES BY SHELL SIZE. SIZES 1 AND 2 ARE NOT ANGLED.



DIRECTION 1 DIRECTION 2

Shell Size	A Max in	A Max mm	B Max in	B Max mm	Max Entry Size
1	.894	22.7	.550	14.0	10
2	1.218	30.9	.550	14.0	12
3	1.760	44.7	.550	14.0	16
4	2.408	61.2	.550	14.0	18
5	2.297	58.3	.654	16.6	18
6	2.422	61.5	.716	18.2	18

EMI, Micro band, lightweight, 60° entry, HiPer-D piggyback. Lightweight, low profile two piece backshell fits HiPer-D® connectors with backshell groove (280-018P, 280-019S, 280-046P, 280-047S). Terminate cable shield with optional .12" width Micro band. Compatible with Glenair Series 77 lipped heat-shrink boots. Non-environmental. Backshell has 60° cable entry angle and large diameter banding porch for large wire bundles. Aluminum with passivated stainless steel screws.

PART NUMBER

Sample PN → **289-087 MT 5 10 -1 K T**Base P/N **289-087**


Finish

- TZ** Tin-Zinc
- MN** Mega-Nickel
- JF** Cadmium, Yel. Chromate
- ME** Electroless Nickel
- NF** Olive Drab Cadmium
- MT** Nickel-PTFE
- ZR** Black Zinc-Nickel

Shell Size **1 2 3 4 5 6**

Entry Size

Entry Size	C Diameter	Shell Size
04	.250 (6.4)	1-6
05	.312 (7.9)	1-6
06	.375 (9.5)	1-6
07	.438 (11.1)	1-6
08	.500 (12.7)	1-6
10	.625 (15.9)	1-6
12	.750 (19.1)	2-6
14	.875 (22.2)	3-6
16	1.000 (25.4)	3-6
18	1.125 (28.6)	4-6



Entry Direction

-1 Direction 1
-2 Direction 2



Direction 1 Direction 2

Band

Omit No Band
K Micro Band Included
J Micro Slim Band Included
L Micro-Max Band Included

Shrink Boot

Omit No Heatshrink Boot
T Heatshrink Boot Included

Entry Size	C Max in	C Max mm	D Max in	D Max mm	Shell Size	Shrink Boot
04	.250	6.4	1.330	33.8	1-6	809S060-1H
05	.312	7.9	1.380	35.1	1-6	809S060-2H
06	.375	9.5	1.430	36.3	1-6	809S060-2H
07	.438	11.1	1.480	37.6	1-6	809S060-2H
08	.500	12.7	1.530	38.9	1-6	809S060-3H
10	.625	15.9	1.680	42.7	1-6	809S060-3H
12	.750	19.1	1.780	45.2	2-6	809S060-4H
14	.875	22.2	1.880	47.8	3-6	809S060-5H
16	1.000	25.4	1.980	50.3	3-6	809S060-5H
18	1.125	28.6	2.080	52.8	4-6	809S060-6H

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.

Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

AEROSPACE-GRADE
FOR QPL MIL-
DTL-83513 AND
GLENAIR SIGNATURE
MICRO-D CONNECTORS




**M83513 Micro-D connector
backshells and accessories—
the world's most complete
selection, all with available
same-day delivery**



Special-formula rubber covers for
silent, non-abrasive performance


The MIL-DTL-83513 is the go-to connector for high-performance commercial and military aerospace applications. From satellites to miniaturized avionic equipment, the Micro-D is recognized worldwide for its high-reliability, life-of-system durability, and SWaP. Glenair manufactures and supplies both the connectors as well as the complete range of EMI, environmental, and mechanical strain relief backshells required in the construction of high-reliability wire harnesses and cable assemblies. All our Micro-D connectors and backshells are manufactured in our US and UK facilities and are uniquely supplied with industry-leading availability, up to and including same-day shipment.

**Glenair Signature Series
M83513 Backshells**



Lightweight thin-
wall construction
Series 507
backshells

Solid-body strain
relief backshell
with Qwik-Ty cable
attachment



Micro-D

Micro-D Accessories Selection Guide

Dust Caps & Covers



Protective Cover
500-017
Page B-5



Protective Cover,
Low Profile
500-107
Page B-7




Protective Cover,
Panel Mount
500-037
Page B-9



Anti-Static Dust Cap
000-00-XX-162/3
Page B-10



Rubber Cover
780-555
Page B-11

MLDM
Dust Caps & Covers

Protective Cover,
MLDM
500-147 Page B-12



Anti-Static Dust Cap,
MLDM
Page B-10

MLDM COVERS

These accessories fit **MLDM** Series Low
Profile Micro-D connectors


Jackscrews & Screwlocks




Mil Spec
Jackscrews
Page B-14



Jackscrews and
Screwlocks
Page B-15




Jackpost Kits
Page B-16



Rear Panel Mount
Jackpost Kits
Page B-17



Rear Panel Mount
PCB Jackpost Kits
Page B-18

Backshell
Hardware

Backshell Hardware
Page B-19

Gaskets and
Seals

Interfacial Seals
Page B-20



EMI Panel Gasket
Page B-21

Potting Shell



Potting Shell
507-035
Page B-22

Shorting Cap



Shorting Cap
500-016
Page B-23

Micro-D Accessories Selection Guide

EMI Backshells

Round Entry


Solid

EMI Banding
500-010
Page B-25EMI Braid Sock
500-011
Page B-27Composite EMI Banding
507-088
Page B-29Dual Entry EMI Banding
507-142
Page B-31

EMI Backshells

Elliptical Entry

Solid

Elliptical EMI Banding
500-047
Page B-32Elliptical EMI Micro Band
507-175
Page B-33**CHECK WIRE BUNDLE SIZE**

The ratio of wire bundle size to backshell entry should not exceed 80%. See 80% Entry Fill Table on next page for recommended sizes for round entry banding backshells when used with Micro-D pre-wired pigtails. In some cases the largest available entry size is too small to meet 80% maximum fill, and an elliptical entry backshell is recommended.

Lightweight EMI Backshells

Elliptical Entry

Solid

Elliptical EMI Banding
507-296
Page B-3545° Elliptical EMI Banding
507-297
Page B-37**MLDM BACKSHELL**

This accessory fits **MLDM** Series Low Profile Micro-D connectors

Elliptical EMI Banding, MLDM
507-299
Page B-46

Split EMI Backshells

Round Entry

Elliptical Entry

EMI Banding, Round Entry
507-145
Page B-39EMI Banding, Elliptical Entry
507-178
Page B-40

Strain Relief Backshells

Qwik-Ty
500-012
Page B-42Straight Clamp
507-146
Page B-44Deep Straight Clamp
507-198
Page B-45

Micro-D Backshell Entry Fill Percentage



ENTRY FILL PERCENTAGE

Entry fill percentage (the ratio of the wire bundle area to the backshell entry area) should not exceed 80% to help assure system performance and safety.

Round entry banding backshells are not large enough to meet this best practice requirement, depending on the number of wires and the wire size. Elliptical backshells should be used instead.

Use the **80% Entry Fill Table** to determine the minimum backshell entry size code for standard Micro-D wire types and sizes.

Use the **Entry Fill Calculator** for custom wire bundles and/or elliptical backshells.



Elliptical banding backshells are recommended if the wire bundle area is greater than 80% of the backshell entry.


80% ENTRY FILL
FOR ROUND ENTRY BACKSHELLS

This table shows recommended entry size codes for standard Micro-D pigtail wiring harnesses used with round entry banding backshells. If no entry size is shown (*), an elliptical backshell is recommended.

No. of Wires	Wire Type	Entry Size Code @80% Max Fill		
		24 AWG	26 AWG	28 AWG
9	M22759/11	06	06	05
	M22759/33	06	05	04
15	M22759/11	08	07	06
	M22759/33	07	06	05
21	M22759/11	09	08	07
	M22759/33	08	07	06
25	M22759/11	10	09	08
	M22759/33	09	08	07
31	M22759/11	11	10	09
	M22759/33	10	09	07
37	M22759/11	12	11	10
	M22759/33	10	09	08
51	M22759/11	*	12	11
	M22759/33	12	11	09
67	M22759/11	*	*	12
	M22759/33	*	12	10
69	M22759/11	*	*	*
	M22759/33	*	12	11
100	M22759/11	*	*	*
	M22759/33	*	*	*
130	M22759/11	*	*	*
	M22759/33	*	*	*

ENTRY SIZE
FOR ROUND ENTRY BACKSHELLS

ENTRY DIAMETER

MICRO-D BANDING
BACKSHELL WITH ROUND
ENTRY

Entry Size Code	Entry Diameter Min.		Cross-Sectional Area	
	in	mm	sq in	sq mm
04	.110	2.8	.010	6.2
05	.141	3.6	.016	10.1
06	.173	4.4	.024	15.3
07	.204	5.2	.033	21.2
08	.235	6.0	.044	28.1
09	.266	6.8	.056	36.1
10	.297	7.5	.070	45.0
11	.329	8.4	.086	55.2
12	.360	9.1	.102	66.1

ENTRY FILL CALCULATOR

Step	Example
1 Calculate Wire Cross-Sectional Area Wire Cross-Sectional Area = (Wire Diameter) ² * .79 * (No. of Wires) (Repeat for each wire size and add together)	51 wires @ .045 inch diameter .79 * .045 * .045 * 51 = .082 sq. in.
2 Calculate Backshell Cross-Sectional Area Round Entry Cross-Sectional Area = (Entry Diameter) ² * .79 Elliptical Entry Area = .79 * a * b	Round Entry Size 12, .360 diameter .79 * .360 * .360 = .103 sq. in. Elliptical Entry Size 03 (507-175) .79 * .644 * .290 = .148 sq. in.
3 Entry Fill Ratio = $\frac{\text{1 Wire Cross-Sectional Area}}{\text{2 Backshell Entry Cross-Sectional Area}}$	Round Entry $\frac{.082}{.103} = .80$ or 80% Elliptical Entry $\frac{.082}{.148} = .55$ or 55%

NOTES


- When round entry banding backshells are used with solder cup Micro-D connectors, the transition angle from the outer pins to the entry port becomes severe and can increase damage susceptibility. Elliptical entry backshells minimize the transition angle and can reduce damage susceptibility.
- For additional protection against wire abrasion, wrap wire bundle with polyimide tape in areas that may come into contact with interior angles.

Micro-D

Band-Master ATS®
Shield Termination Bands and Tools

Band-Master ATS®

Terminate cable braid shield to adapter with stainless steel **Band-Master ATS®** bands. Install band with hand tool or bench-mounted pneumatic tool. Bands are available in *Standard* (.24 inch) and *Micro* (.12 inch) widths. *Slim Standard* and *Micro Slim* bands have reduced thickness for weight reduction. Hardened steel *Micro-Max* bands have 60% more tensile strength than standard Micro bands. Available pre-coiled, bands are 304 series stainless steel, passivated.



For more information on the Band-Master ATS EMI shield termination system, including instruction manuals and calibration details:

<https://www.glenair.com/bandmaster/>


Band and Band Tool Part Numbers

Size		A Length in mm	Fits up to Dia. in mm	B Width in mm	C Thickness in mm	Part Number Pre-coiled	Hand Tool Part Number
Standard		9 228	1.00 25.4	.24 6.1	.02 0.5	601-006	601-100
		14 355	1.80 45.7	.24 6.1	.02 0.5	601-041	
		18 457	2.50 63.5	.24 6.1	.02 0.5	601-050	
Slim Standard		9 228	.94 23.9	.24 6.1	.01 0.3	601-571	601-109
		14 355	1.80 45.7	.24 6.1	.01 0.3	601-573	
Micro		5 127	.50 12.7	.12 3.0	.015 0.4	601-025	601-101
		8 203	.88 22.4	.12 3.0	.015 0.4	601-061	
		14 356	1.88 47.7	.12 3.0	.015 0.4	601-065	
Micro Slim		8 203	.88 22.4	.12 3.0	.01 0.3	601-601	601-122
		14 356	1.88 47.7	.12 3.0	.01 0.3	601-603	
Micro-Max		8 203	.88 22.4	.12 3.0	.015 0.4	601-701	601-129
		14 356	1.88 47.7	.12 3.0	.015 0.4	601-703	

Micro-D

500-017
Protective Cover

- Fits MWDM and M83513 Class M
- Silicone Gasket
- Top, Side and 45° Entry



500-017

This accessory fits MIL-DTL-83513 Class M and MWDM Micro-D connectors

500-017 protective cover fits M83513 Class M and MWDM Micro-D connectors. Rubber gasket provides dust and moisture protection. Available with lanyard for panel or cable attachment. Aluminum with stainless steel screws and washers, silicone gasket.


TABLE 1
ATTACHMENT TYPE

F	 Wire Rope, Blue Nylon Jacket 6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C
G	 Black Nylon Rope Very flexible, good abrasion and fuel resistance, .062 (1.6) diameter, -55 to +100 °C
H	 Wire Rope, Clear FEP Jacket Clear FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C
SK	 Nylon Rope with Slip Knot Very flexible, good abrasion and fuel resistance, .094 (2.4) diameter. Length includes .5" (13mm) dia. loop, -55 to +100 °C
T	 SST Wire Rope, No Jacket Good flexibility, good abrasion resistance, .047 (1.2) diameter, passivated, -65 to +200 °C

PART NUMBER

Sample PN→ 500-017 NF 37 F F 6 -06



Base P/N	500-017
Finish	TZ Tin-Zinc JF Cadmium w/ Yellow Chromate M Electroless Nickel MT Nickel-PTFE ZR Black Zinc-Nickel Z2 Gold NF CAD/O. D. Over Electroless Nickel (1000 Hour Salt Spray)
Shell Size	09 15 21 25 31 37 51 51-2 67 69 75 100 130
Jackscrews	F Female Threads MB Fillister Head Male Jackscrews MH Socket Head Male Jackscrews
Attachment Type (Table 1)	N No Attachment F SST Wire Rope, Nylon Jacket G Nylon Rope H SST Wire Rope, FEP Jacket SK Nylon Rope with Slip Knot T SST Wire Rope, No Jacket
Attachment Length	Omit If No Attachment Length in One Inch Increments
Dash Number	Omit If No Attachment Omit for Attachment Type SK Ring Inside Code Diameter -06 .125 (3.2) -01 .140 (3.6) -02 .182 (4.6) -04 .197 (5.0)



Micro-D

500-017
Protective Cover

- Fits MWDM and M83513 Class M
- Silicone Gasket
- Top, Side and 45° Entry



Size	A Max.		B Max		C		D Max		E Max		F Thd UNC-2
	in	mm	in	mm	in	mm	in	mm	in	mm	
09	.453	11.5	.930	23.6	.565	14.4	.380	9.7	.795	20.2	2-56
15	.453	11.5	1.080	27.4	.715	18.2	.380	9.7	.945	24.0	2-56
21	.453	11.5	1.230	31.2	.865	22.0	.380	9.7	1.095	27.8	2-56
25	.453	11.5	1.330	33.8	.965	24.5	.380	9.7	1.195	30.4	2-56
31	.453	11.5	1.480	37.6	1.115	28.3	.380	9.7	1.345	34.2	2-56
37	.453	11.5	1.630	41.4	1.265	32.1	.380	9.7	1.495	38.0	2-56
51	.496	12.6	1.580	40.1	1.215	30.9	.420	10.7	1.445	36.7	2-56
51-2	.453	11.5	1.980	50.3	1.615	41.0	.380	9.7	1.845	46.9	2-56
67	.453	11.5	2.380	60.5	2.015	51.2	.380	9.7	2.245	57.0	2-56
69	.496	12.6	1.880	47.8	1.515	38.5	.420	10.7	1.745	44.3	2-56
75	.496	12.6	2.220	56.4	1.705	43.3	.420	10.7	2.085	53.0	4-40
100	.539	13.7	2.315	58.8	1.800	45.7	.470	11.9	2.180	55.4	4-40
130	.539	13.7	2.675	67.9	2.160	54.6	.470	11.9	2.540	64.5	4-40

Micro-D

500-107

Protective Cover, Low Profile

■ For MWDM and M83513 Micro-D



500-107

This accessory fits MIL-DTL-83513 Class M and MWDM Micro-D connectors

500-107 protective cover fits M83513 Class M and MWDM metal shell Micro-D connectors. Plug connector cover fits over connector shell and has fluorosilicone gasket. Receptacle connector cover fits inside connector shell. Aluminum or stainless steel. Stainless steel hardware.

TABLE 1
HARDWARE OPTIONS





TABLE 2
ATTACHMENT TYPE




PART NUMBER

Sample PN → 500-107 M 51 R L F 5 -06

Base P/N		500-107										
Material / Finish	TZ	Tin-Zinc										
	JF	Alum / Cadmium w/ Yel. Chromate										
	M	Alum / Electroless Nickel										
	MT	Alum / Nickel-PTFE										
	ZR	Alum / Black Zinc-Nickel										
	Z1	SST / Passivated										
	Z2	Alum / Gold										
Shell Size		09	15	21	25	31	37	51	51-2			
		67	69	75	100	130						
Plug/ Receptacle	P	Cover for Plug Connector										
	R	Cover for Receptacle Connector										
Hardware (Table 1)	B	No Hardware (Thru-Holes)										
	P	Female Jackposts										
	L	Socket Head Jackscrews										
	S	Slot Head Jackscrews										
Attachment Type (Table 2)	NB	No Attachment (Boss Deleted)										
	F	SST Wire Rope, Nylon Jacket										
	G	Nylon Rope										
	H	SST Wire Rope, FEP Jacket										
	T	SST Wire Rope, No Jacket										
Attachment Length		Omit If No Attachment Length in One Inch Increments ("5" = Five Inches)										
Attachment Ring Dia.		Omit If No Attachment Ring Dia.										
	-06	.125 (3.2)										
	-01	.140 (3.6)										
	-02	.182 (4.6)										
	-04	.197 (5.0)										

RING ID





Micro-D

500-107

Protective Cover, Low Profile

■ For MWDM and M83513 Micro-D



Layout	A Max		B ± .003		C Max		D Max		E Max		F Thd
	in	mm	in	mm	in	mm	in	mm	in	mm	
09R	.785	19.9	.565	14.4	.333	8.5	.184	4.7	.308	7.8	2-56
09P	.785	19.9	.565	14.4	.400	10.2	.250	6.4	.308	7.8	2-56
15R	.935	23.7	.715	18.2	.483	12.3	.184	4.7	.308	7.8	2-56
15P	.935	23.7	.715	18.2	.551	14.0	.250	6.4	.308	7.8	2-56
21R	1.085	27.6	.865	22.0	.633	16.1	.184	4.7	.308	7.8	2-56
21P	1.085	27.6	.865	22.0	.701	17.8	.250	6.4	.308	7.8	2-56
25R	1.185	30.1	.965	24.5	.733	18.6	.184	4.7	.308	7.8	2-56
25P	1.185	30.1	.965	24.5	.801	20.3	.250	6.4	.308	7.8	2-56
31R	1.335	33.9	1.115	28.3	.883	22.4	.184	4.7	.308	7.8	2-56
31P	1.335	33.9	1.115	28.3	.951	24.2	.250	6.4	.308	7.8	2-56
37R	1.485	37.7	1.265	32.1	1.033	26.2	.184	4.7	.308	7.8	2-56
37P	1.485	37.7	1.265	32.1	1.101	28.0	.250	6.4	.308	7.8	2-56
51R	1.435	36.4	1.215	30.9	.983	25.0	.228	5.8	.351	8.9	2-56
51P	1.435	36.4	1.215	30.9	1.051	26.7	.296	7.5	.351	8.9	2-56
51-2R	1.835	46.6	1.615	41.0	1.384	35.2	.184	4.7	.308	7.8	2-56
51-2P	1.835	46.6	1.615	41.0	1.450	36.8	.250	6.4	.308	7.8	2-56
67R	2.235	56.8	2.015	51.2	1.784	45.3	.184	4.7	.310	7.9	2-56
67P	2.235	56.8	2.015	51.2	1.850	47.0	.250	6.4	.310	7.9	2-56
69R	1.735	44.1	1.515	38.5	1.284	32.6	.228	5.8	.351	8.9	2-56
69P	1.735	44.1	1.515	38.5	1.350	34.3	.296	7.5	.351	8.9	2-56
75R	2.080	52.8	1.705	43.3	1.384	35.2	.228	5.8	.351	8.9	4-40
75P	2.080	52.8	1.705	43.3	1.450	36.8	.296	7.5	.351	8.9	4-40
100R	2.170	55.1	1.800	45.7	1.383	35.1	.270	6.9	.394	10.0	4-40
100P	2.170	55.1	1.800	45.7	1.451	36.9	.333	8.5	.394	10.0	4-40
130R	2.520	64.0	2.150	54.6	1.735	44.1	.270	6.9	.394	10.0	4-40
130P	2.520	64.0	2.150	54.6	1.795	45.6	.333	8.5	.394	10.0	4-40

Micro-D

500-037

Protective Cover, Rear Panel Mount



500-037

This accessory fits rear-panel mounted MIL-DTL-83513 Class M Micro-D and MWDM connectors


For rear panel mounted connectors. 500-037 protective cover fits M83513 Class M and MWDM Micro-D connectors. Rubber gasket provides dust and moisture protection. Available with lanyard for panel attachment. Aluminum with stainless steel jackscrews, silicone gasket.

TABLE 2
ATTACHMENT TYPE

F SST Wire Rope, Nylon Jacket
-55 to +100 °C

H SST Wire Rope, FEP Jacket
-65 to +200 °C

T Wire Rope, No Jacket
-65 to +200 °C



PART NUMBER

Sample PN → **500-037 M 21 R3 B F -06 -5**


Base P/N **500-037**

Finish
TZ Tin-Zinc
JF Cadmium w/ Yellow Chromate
M Electroless Nickel
MT Nickel-PTFE
ZR Black Zinc-Nickel
Z2 Gold

Shell Size
09 15 21 25 31 37 51 51-2
67 69 75 100 130

Panel Thickness

Panel Code	Thickness	F
R1	.031 (0.8)	.126 (3.2)
R2	.047 (1.2)	.110 (2.8)
R3	.062 (1.6)	.095 (2.4)
R4	.093 (2.4)	.064 (1.6)
R5	.125 (3.2)	.032 (.8)




Jackscrews
B Fillister Head Male Jackscrews
H Socket Head Male Jackscrews

Attachment Type
N No Attachment
F SST Wire Rope, Nylon Jacket
H SST Wire Rope, FEP Jacket
T SST Wire Rope, No Jacket

Attachment Dia.

Code	Ring I.D.
-06	.125 (3.2)
-01	.140 (3.6)
-02	.182 (4.6)
-04	.197 (5.0)



Attachment Length Omit for standard 4 inch (102mm) length
 Length in Inches (Ex: **-2** = 2 inches)

Size	A Max		B Max		C		D Max		E Max		H Thd
	in	mm	in	mm	in	mm	in	mm	in	mm	UNC-2A
09	.328	8.3	.805	20.4	.565	14.4	.453	11.5	.930	23.6	2-56
15	.328	8.3	.955	24.3	.715	18.2	.453	11.5	1.080	27.4	2-56
21	.328	8.3	1.105	28.1	.865	22.0	.453	11.5	1.230	31.2	2-56
25	.328	8.3	1.205	30.6	.965	24.5	.453	11.5	1.330	33.8	2-56
31	.328	8.3	1.355	34.4	1.115	28.3	.453	11.5	1.480	37.6	2-56
37	.328	8.3	1.505	38.2	1.265	32.1	.453	11.5	1.630	41.4	2-56
51	.371	9.4	1.455	37.0	1.215	30.9	.496	12.6	1.580	40.1	2-56
51-2	.328	8.3	1.855	47.1	1.615	41.0	.453	11.5	1.980	50.3	2-56
67	.328	8.3	2.255	57.3	2.015	51.2	.453	11.5	2.380	60.5	2-56
69	.371	9.4	1.755	44.6	1.515	38.5	.496	12.6	1.880	47.8	2-56
75	.371	9.4	2.100	53.3	1.705	43.3	.496	12.6	2.225	56.5	4-40
100	.414	10.5	2.190	55.6	1.800	45.7	.539	13.7	2.315	58.8	4-40
130	.414	10.5	2.550	64.8	2.160	54.6	.539	13.7	2.675	67.9	4-40

Anti-Static Dust Caps

For M83513 and Micro-D Connectors




Anti-static dust caps fit Micro-D and MIL-DTL-83513 connectors. These caps provide electrostatic protection to sensitive equipment. These caps meet the static decay requirement of MIL-PRF-81705. Surface resistivity is greater than 1×10^5 ohms/square and less than 1×10^{12} ohms/square. Black LDPE.


DUST CAPS FOR M83513 CLASS M AND MWDM MICRO-D

Size	Part No.	A		B	
		in	mm	in	mm
9P	000-01-09-162	.524	13.3	.393	10.0
9S	000-01-09-163	.563	14.3	.428	10.9
15P	000-01-15-162	.647	16.4	.393	10.0
15S	000-01-15-163	.713	18.1	.428	10.9
21P	000-01-21-162	.824	20.9	.393	10.0
21S	000-01-21-163	.863	21.9	.428	10.9
25P	000-01-25-162	.924	23.5	.393	10.0
25S	000-01-25-163	.963	24.5	.428	10.9
31P	000-01-31-162	1.074	27.3	.393	10.0
31S	000-01-31-163	1.113	28.3	.428	10.9
37P	000-01-37-162	1.224	31.1	.393	10.0
37S	000-01-37-163	1.263	32.1	.428	10.9
51P	000-01-51-162	1.174	29.8	.436	11.1
51S	000-01-51-163	1.213	30.8	.470	11.9
51-2P	000-01-51-172	1.574	40.0	.393	10.0
51-2S	000-01-51-173	1.612	40.9	.428	10.9
67P	000-01-67-162	1.974	50.1	.393	10.0
67S	000-01-67-163	2.013	51.1	.428	10.9
69P	000-01-69-162	1.474	37.4	.436	11.1
69S	000-01-69-163	1.512	38.4	.470	11.9
75P	000-01-75-162	1.574	40.0	.436	11.1
75S	000-01-75-163	1.612	40.9	.470	11.9
100P	000-01-00-162	1.574	40.0	.479	12.2
100S	000-01-00-163	1.615	41.0	.516	13.1
130P	000-01-30-162	1.947	49.5	.476	12.1
130S	000-01-30-163	1.975	50.2	.504	12.8

SIZE 09 THRU 75




PLUG CONNECTOR COVER
000-01-XX-162 & -172




RECEPTACLE CONNECTOR COVER
000-01-XX-163 & -173

SIZE 100




SIZE 130




DUST CAPS FOR M83513 CLASS P AND MLDM LOW PROFILE MICRO-D

Size	Part No.	A		B	
		in	mm	in	mm
9P	000-01-09-164	.491	12.5	.349	8.9
9S	000-01-09-165	.565	14.4	.392	10.0
15P	000-01-15-164	.639	16.2	.349	8.9
15S	000-01-15-165	.715	18.2	.392	10.0
21P	000-01-21-164	.789	20.0	.349	8.9
21S	000-01-21-165	.865	22.0	.392	10.0
25P	000-01-25-164	.889	22.6	.349	8.9
25S	000-01-25-165	.965	24.5	.392	10.0
31P	000-01-31-164	1.039	26.4	.349	8.9
31S	000-01-31-165	1.115	28.3	.392	10.0
37P	000-01-37-164	1.189	30.2	.349	8.9
37S	000-01-37-165	1.265	32.1	.392	10.0
51P	000-01-51-164	1.139	28.9	.390	9.9
51S	000-01-51-165	1.215	30.9	.435	11.0



PLUG CONNECTOR COVER
000-01-XX-164



RECEPTACLE CONNECTOR COVER
000-01-XX-165

Micro-D

780-555

Protective Cover, Rubber



780-555

This accessory fits MIL-DTL-83513 Class M and MWDM Micro-D connectors

Neoprene or silicone. 780-555 rubber cover fits metal shell Micro-D connectors. Cover protects connector from damage and contamination. Three material choices: black neoprene, carbon-filled conductive black neoprene, or red silicone. Nylon rope lanyard attaches cover to cable or panel. Attachment choices include cable tie, slip knot or stainless steel ring. **Not rated for water immersion.**

PART NUMBER

Sample PN →

780-555 -25S G 4 -06 C

Base P/N 780-555


Size -9P -9S -15P -15S -21P -21S -25P
-25S -31P -31S -37P -51P -51S
-51-2P -51-2S -69P -69S -100P -100S

Attachment *Omit* No Attachment
G Nylon Rope

Attachment Length Length in One Inch Increments
(Example: 4 = four inch lanyard)

Attachment Fitting	Code	Fitting Type	Ring I.D.
	-00	No Fitting	N/A
	-04	Ring	.197 (5.0)
	-06	Ring	.125 (3.2)
	-07	Ring	.218 (5.5)
	-09	Ring	.156 (4.0)
	-WS	Cable Tie	N/A
	-SK	Slip Knot	N/A

RING ID



Material *Omit* Black Neoprene
C Conductive Black Neoprene (10⁵ Ω/square min.)
S Red Silicone

ATTACHMENT FITTING

SK SLIP KNOT



Nylon Rope, Kynar Friction Sleeve

WS CABLE TIE




6/6 nylon cable tie with screw and locknut.
1.77 (45.0) max. wire bundle dia. -40 to +85 °C.

RING TERMINAL



Screw Size	Ring Code	Ring I.D. ± .010 (0.25) in mm
#4	-06	.125 3.2
#6	-09	.156 4.0
#8	-04	.197 5.0
#10	-07	.218 5.5




Layout	A		B		C		D	
	in	mm	in	mm	in	mm	in	mm
9P	.30	7.6	.15	3.8	.13	3.3	.69	17.5
9S	.37	9.4	.22	5.6	.13	3.3	.69	17.5
15P	.45	11.4	.15	3.8	.13	3.3	.84	21.3
15S	.52	13.2	.22	5.6	.13	3.3	.84	21.3
21P	.60	15.2	.15	3.8	.13	3.3	.99	25.1
21S	.67	17.0	.22	5.6	.13	3.3	.99	25.1
25P	.70	17.8	.15	3.8	.13	3.3	1.09	27.7
25S	.77	19.6	.22	5.6	.13	3.3	1.09	27.7
31P	.85	21.6	.15	3.8	.13	3.3	1.24	31.5
31S	.92	23.4	.22	5.6	.13	3.3	1.24	31.5
37P	1.00	25.4	.15	3.8	.13	3.3	1.39	35.3
37S	1.07	25.9	.22	5.6	.13	3.3	1.39	35.3
51-2P	1.35	34.3	.15	3.8	.13	3.3	1.74	44.2
51-2S	1.42	36.1	.22	5.6	.13	3.3	1.74	44.2
51P	.95	24.1	.19	4.8	.13	3.3	1.34	34.0
51S	1.02	25.9	.26	6.6	.13	3.3	1.34	34.0
69P	1.25	31.8	.19	4.8	.13	3.3	1.64	41.7
69S	1.32	33.5	.26	6.6	.13	3.3	1.64	41.7
100P	1.35	34.3	.24	6.1	.19	4.8	1.99	50.5
100S	1.41	35.8	.30	7.6	.19	4.8	1.99	50.5

Micro-D

500-147

Protective Cover, MLDM

■ For Low-Profile MLDM Micro-D



500-147

This accessory fits MLDM Low Profile Metal Shell Micro-D Connectors


500-147 protective cover fits low profile MLDM metal shell Micro-D connectors. Plug connector cover fits over connector shell and has fluorosilicone gasket. Receptacle connector cover fits inside connector shell. Aluminum or stainless steel with stainless steel hardware.

PART NUMBER

Sample PN→ 500-147 M 51 R M F 5 -06

Base P/N		500-147							
Material / Finish	TZ	Tin-Zinc							
	JF	Alum / Cadmium w/ Yel. Chromate							
	M	Alum / Electroless Nickel							
	MT	Alum / Nickel-PTFE							
	ZR	Alum / Black Zinc-Nickel							
	Z1	SST / Passivated							
	Z2	Alum / Gold							
Shell Size		09	15	21	25	31	37	51	51-2
Plug/ Receptacle	P	Cover for Plug Connector							
	R	Cover for Receptacle Connector							
Hardware (Table 1)	B	No Hardware (Thru-Holes)							
	P	Female Jackposts							
	L	Socket Head Jackscrews							
	S	Slot Head Jackscrews							
Attachment Type (Table 2)	N	No Attachment							
	F	SST Wire Rope, Nylon Jacket							
	G	Nylon Rope							
	H	SST Wire Rope, FEP Jacket							
	T	SST Wire Rope, No Jacket							
Attachment Length		Omit If No Attachment Length in One Inch Increments ("5" = Five Inches)							
Attachment Ring Dia.	Omit If No Attachment								
		Ring Dia.							
	-06	.125 (3.2)							
	-01	.140 (3.6)							
	-02	.182 (4.6)							
	-04	.197 (5.0)							

RING ID






TABLE 1
HARDWARE OPTIONS

P	L	S
Female Jackposts	Socket Head Jackscrews	Slotted Jackscrews

TABLE 2
ATTACHMENT TYPE



F		SST Wire Rope, Nylon Jacket -55 to +100 °C
G		Black Nylon Rope -55 to +100 °C
H		SST Wire Rope, FEP Jacket -65 to +200 °C
T		Wire Rope, No Jacket -65 to +200 °C

Micro-D

500-147

Protective Cover, MLDM

■ For Low-Profile MLDM Micro-D




Layout	A Max		B		C Max		D Max		E Max		F Thd
	in	mm	in	mm	in	mm	in	mm	in	mm	UNC-2
09R	.788	20.0	.565	14.4	.292	7.4	.134	3.4	.218	5.5	2-56
09P	.788	20.0	.565	14.4	.380	9.7	.218	5.5	.218	5.5	2-56
15R	.938	23.8	.715	18.2	.442	11.2	.134	3.4	.218	5.5	2-56
15P	.938	23.8	.715	18.2	.530	13.5	.218	5.5	.218	5.5	2-56
21R	1.088	27.6	.865	22.0	.592	15.0	.134	3.4	.218	5.5	2-56
21P	1.088	27.6	.865	22.0	.680	17.3	.218	5.5	.218	5.5	2-56
25R	1.188	30.2	.965	24.5	.692	17.6	.134	3.4	.218	5.5	2-56
25P	1.188	30.2	.965	24.5	.780	19.8	.218	5.5	.218	5.5	2-56
31R	1.338	34.0	1.115	28.3	.842	21.4	.134	3.4	.218	5.5	2-56
31P	1.338	34.0	1.115	28.3	.930	23.6	.218	5.5	.218	5.5	2-56
37R	1.488	37.8	1.265	32.1	.992	25.2	.134	3.4	.218	5.5	2-56
37P	1.488	37.8	1.265	32.1	1.080	27.4	.218	5.5	.218	5.5	2-56
51R	1.438	36.5	1.215	30.9	.942	23.9	.177	4.5	.260	6.6	2-56
51P	1.438	36.5	1.215	30.9	1.030	26.2	.260	6.6	.260	6.6	2-56
51-2R	1.838	46.7	1.615	41.0	1.340	34.0	.134	3.4	.218	5.5	2-56
51-2P	1.838	46.7	1.615	41.0	1.425	36.2	.218	5.5	.218	5.5	2-56

Micro-D

Mil-Spec Jackscrew Kits






For M83513 and Micro-D Connectors



Stainless steel Micro-D jackscrew kits conform to MIL-DTL-83513/05. Kit consists of (2) jackscrews and (2) retainer rings. Choose slotted head or socket head. Two thread sizes: 2-56 for size 9 to 69, 4-40 for sizes 79, 100 and 130. Place jackscrew through connector mounting hole, then slide e-ring into slot on jackscrew.

Material: 125 kpsi stainless steel, passivated

Application note: retainer ring does not meet the 2 μ magnetic permeability requirement of M83513 connectors.



M83513/05 MICRO-D JACKSCREW KITS



Figure	Type	Thread Size	Connector Size	Part Number	M83513 PIN	ϕA		B Max		C		D Max		E Thread
						in	mm	in	mm	in	mm	in	mm	UNC-2A
1	Slotted Low Profile	2-56	9-69	080-00-00-505	M83513/05-05	.125	3.2	.103	2.6	.083	2.1	.258	6.6	2-56
		4-40	75, 100, 130	080-00-00-515	M83513/05-15	.187	4.7	.098	2.5	.140	3.6	.292	7.4	4-40
2	Socket Head Low Profile	2-56	9-69	080-00-00-502	M83513/05-02	.125	3.2	.103	2.6	.083	2.1	.258	6.6	2-56
		4-40	75, 100, 130	080-00-00-512	M83513/05-12	.187	4.7	.098	2.5	.140	3.6	.292	7.4	4-40
3	Slotted Extended	2-56	9-69	080-00-00-506	M83513/05-06	.156	4.0	.610	15.5	.083	2.1	.258	6.6	2-56
		4-40	75, 100, 130	080-00-00-516	M83513/05-16	.200	5.1	.610	15.5	.140	3.6	.292	7.4	4-40
4	Socket Head Extended	2-56	9-69	080-00-00-503	M83513/05-03	.156	4.0	.610	15.5	.083	2.1	.258	6.6	2-56
		4-40	75, 100, 130	080-00-00-513	M83513/05-13	.200	5.1	.610	15.5	.140	3.6	.292	7.4	4-40

Micro-D

179-013, 179-162


Jackscrews and Screwlocks, Micro-D

- For Connector without Backshell
- Fits M83513 and MWDM Micro-D
- Includes Retention Clip



1

Fillister Head



2

Socket Head

Stainless steel screwlock and jackscrew kits fit Micro-D connectors without backshells. Screwlocks allow the connectors to be fully mated before the screws are tightened. Jackscrews must be tightened in order to mate connectors. Kit consists of (1) screw and (1) retainer clip, *order (2) kits per connector*. Jackscrew and clip are passivated stainless steel.

PART NUMBER


Figure	Style	Type	Thread Size	Connector Size	Part No.
1	Fillister Head	Screwlock	2-56	9-69	179-162-1S
			4-40	75-130	179-162-2S
		Jackscrew	2-56	9-69	179-013-1S
			4-40	75-130	179-013-2S
2	Socket Head	Screwlock	2-56	9-69	179-162-1H
			4-40	75-130	179-162-2H
		Jackscrew	2-56	9-69	179-013-1H
			4-40	75-130	179-013-2H

ASSEMBLY NOTE




CLIP

CLIP HAS CIRCULAR HOLE AND SQUARE HOLE.



SCREWLOCK


INSTALL CLIP ON CONNECTOR FLANGE WITH SQUARE HOLE. ON TOP. SCREW IS FLOATING.




JACKSCREW

INSTALL CLIP ON CONNECTOR FLANGE WITH SQUARE HOLE. ON THE BOTTOM. SCREW IS CAPTIVE.


179-013-1H




179-013-1S




179-013-2H




179-013-2S




179-162-1H




179-162-1S



179-162-2H




179-162-2S



Micro-D

Jackpost Kits
For Micro-D Connectors

- Mil Spec and Extended Length
- Fits M83513 and MWDM Micro-D



Stainless steel jackpost kits fit M83513 and MWDM Micro-D connectors. Two thread sizes: 2-56 for size 9 to 69, 4-40 for sizes 79, 100 and 130. Kit consists of (2) female posts, (2) hex nuts and (2) lockwashers. Passivated 300 series stainless steel.



JACKPOST KIT with (2) posts, (2) nuts and (2) lockwashers

A Thread Size	Micro-D Size	L Length in mm	Part No.	MIL Part Number	
2-56	9-69	.288 7.3	080-00-00-100	M83513/05-07	
		.500 12.7	500-069-2-1		
		.625 15.9	500-069-2-2		
		.750 19.1	500-069-2-3		
		.875 22.2	500-069-2-4		
		1.000 25.4	500-069-2-5		
4-40	75-130	.295 7.5	080-00-00-101	M83513/05-17	
		.500 12.7	500-069-4-1		
		.625 15.9	500-069-4-2		
		.750 19.1	500-069-4-3		
		.875 22.2	500-069-4-4		
		1.000 25.4	500-069-4-5		

177-504, 179-221

Jackpost Kit, Rear Panel Mount



- Rear Panel Mount
- Fits M83513 and MWDM Micro-D



Rear panel mount jackpost kits fit M83513 and MWDM Micro-D connectors. Two thread sizes: 2-56 for size 9 to 69, 4-40 for sizes 79, 100 and 130. Kit consists of (2) female posts, (2) hex nuts and (2) lockwashers. For panel thicknesses from $\frac{1}{32}$ to $\frac{1}{8}$ inch. Passivated 300 series stainless steel.


REAR PANEL MOUNT JACKPOST KIT with (2) posts, (2) nuts and (2) lockwashers

A Thread Size	Micro-D Size	Panel Thickness in mm	L Length (OAL) in mm	Part No.	K $\pm .003$ (0.08) in mm
2-56	9-69	$\frac{1}{32}$ 0.8	.475 12.1	177-504-2-2	.024 0.61
			.600 15.2	179-221-2-2-3	
		$\frac{3}{64}$ 1.2	.475 12.1	177-504-2-3	.041 1.04
			.600 15.2	179-221-2-3-3	
		$\frac{1}{16}$ 1.6	.475 12.1	177-504-2-4	.055 1.40
			.600 15.2	179-221-2-4-3	
		.080 2.0	.475 12.1	177-504-2-7	.073 1.85
			.600 15.2	179-221-2-7-3	
		$\frac{3}{32}$ 2.4	.475 12.1	177-504-2-5	.086 2.18
			.600 15.2	179-221-2-5-3	
		$\frac{1}{8}$ 3.2	.475 12.1	177-504-2-6	.118 3.00
			.600 15.2	179-221-2-6-3	
4-40	75-130	$\frac{1}{32}$ 0.8	.475 12.1	177-504-4-2	.024 0.61
			.600 15.2	179-221-4-2-3	
		$\frac{3}{64}$ 1.2	.475 12.1	177-504-4-3	.041 1.04
			.600 15.2	179-221-4-3-3	
		$\frac{1}{16}$ 1.6	.475 12.1	177-504-4-4	.055 1.40
			.600 15.2	179-221-4-4-3	
		.080 2.0	.475 12.1	177-504-4-7	.073 1.85
			.600 15.2	179-221-4-7-3	
		$\frac{3}{32}$ 2.4	.475 12.1	177-504-4-5	.086 2.18
			.600 15.2	179-221-4-5-3	
		$\frac{1}{8}$ 3.2	.475 12.1	177-504-4-6	.118 3.00
			.600 15.2	179-221-4-6-3	



RECOMMENDED PANEL CUTOUT FOR REAR PANEL MOUNT MICRO-D CONNECTORS


Shell Size	C $\pm .005$ (0.13) in mm	D $\pm .005$ (0.13) in mm	E $\pm .005$ (0.13) in mm	G in mm
09	.406 10.3	.565 14.4	.256 6.5	.125 3.2
15	.556 14.1	.715 18.2	.256 6.5	.125 3.2
21	.706 17.9	.865 22.0	.256 6.5	.125 3.2
25	.806 20.5	.965 24.5	.256 6.5	.125 3.2
31	.956 24.3	1.115 28.3	.256 6.5	.125 3.2
37	1.106 28.1	1.265 32.1	.256 6.5	.125 3.2
51	1.056 26.8	1.215 30.9	.300 7.6	.125 3.2
100	1.520 38.6	1.800 45.7	.406 10.3	.147 3.7



177-505

Jackpost Kit, Rear Panel Mount PCB

- For MWDM Types BS, BR and CBR
- Rear Panel Mount





Rear panel mount jackpost kit fits MWDM printed circuit board connectors types BS, BR and CBR. Two thread sizes: 2-56 for size 9 to 69, 4-40 for sizes 75, 100 and 130. For panel thicknesses from $\frac{1}{32}$ to $\frac{1}{8}$ inch. Passivated 300 series stainless steel.

Install with threadlocking compound.

Kit consists of (2) female posts.


REAR PANEL MOUNT PCB JACKPOST KIT with (2) posts

A Thread Size	Micro-D Size	Connector Type	Panel Thickness in mm	Part No.	F $\pm .003$ (0.08) in mm	H $\pm .015$ (0.4) in mm
2-56	9-69	BS, CBR	$\frac{1}{32}$ 0.8	177-505-A-2-2	.024 0.61	.365 9.3
			$\frac{3}{64}$ 1.2	177-505-A-2-3	.041 1.04	
			$\frac{1}{16}$ 1.6	177-505-A-2-4	.055 1.40	
			.080 2.0	177-505-A-2-7	.073 1.85	
			$\frac{3}{32}$ 2.4	177-505-A-2-5	.086 2.18	
	9-51	BR	$\frac{1}{8}$ 3.2	177-505-A-2-6	.118 3.00	.398 10.1
			$\frac{1}{32}$ 0.8	177-505-B-2-2	.024 0.61	
			$\frac{3}{64}$ 1.2	177-505-B-2-3	.041 1.04	
			$\frac{1}{16}$ 1.6	177-505-B-2-4	.055 1.40	
			.080 2.0	177-505-B-2-7	.073 1.85	
4-40	75-130	BR, CBR	$\frac{1}{32}$ 0.8	177-505-C-4-2	.024 0.61	.475 12.1
			$\frac{3}{64}$ 1.2	177-505-C-4-3	.041 1.04	
			$\frac{1}{16}$ 1.6	177-505-C-4-4	.055 1.40	
			.080 2.0	177-505-C-4-7	.073 1.85	
			$\frac{3}{32}$ 2.4	177-505-C-4-5	.086 2.18	
	100	BS	$\frac{1}{8}$ 3.2	177-505-C-4-6	.118 3.00	.360 9.1
			$\frac{1}{32}$ 0.8	177-505-D-4-2	.024 0.61	
			$\frac{3}{64}$ 1.2	177-505-D-4-3	.041 1.04	
			$\frac{1}{16}$ 1.6	177-505-D-4-4	.055 1.40	
			.080 2.0	177-505-D-4-7	.073 1.85	
			$\frac{3}{32}$ 2.4	177-505-D-4-5	.086 2.18	
			$\frac{1}{8}$ 3.2	177-505-D-4-6	.118 3.00	





RECOMMENDED PANEL CUTOUT FOR REAR PANEL MOUNT MICRO-D CONNECTORS

Shell Size	C $\pm .005$ (0.13) in mm	D $\pm .005$ (0.13) in mm	E $\pm .005$ (0.13) in mm	G in mm
09	.406 10.3	.565 14.4	.256 6.5	.125 3.2
15	.556 14.1	.715 18.2	.256 6.5	.125 3.2
21	.706 17.9	.865 22.0	.256 6.5	.125 3.2
25	.806 20.5	.965 24.5	.256 6.5	.125 3.2
31	.956 24.3	1.115 28.3	.256 6.5	.125 3.2
37	1.106 28.1	1.265 32.1	.256 6.5	.125 3.2
51	1.056 26.8	1.215 30.9	.300 7.6	.125 3.2
100	1.520 38.6	1.800 45.7	.406 10.3	.147 3.7




500-015, 687-152, 687-439, 687-695

Replacement Hardware for Micro-D Backshells with .175" Flange



Order (2) per backshell. Replacement screws and retainer clips fit Micro-D backshells with .175 (4.4) flange height. Two thread sizes: 2-56 for size 9 to 69, 4-40 for sizes 75, 100 and 130. Male screws are available in (3) styles: slotted fillister head, hex drive socket head, or extended length slotted. Stainless steel screws, washers, and retainer clips.

Clips, Screwlocks and Jackscrews



1 2 3 JACKSCREWS AND MALE SCREWLOCKS							
Figure	Style	Type	Thread Size	Connector Size	Kit with (1) Screw, (1) Clip	Screw Only	Length in mm
1	Fillister Head	Screwlock	2-56	9-69	687-152-01BF	687-152-01BFL	
			4-40	75, 100, 130	687-152-02BF	687-152-02BFL	
		Jackscrew	2-56	9-69	500-015-IS	500-015-ISL	
			4-40	75, 100, 130	500-015-2S	500-015-2SL	
2	Socket Head	Screwlock	2-56	9-69	500-015-1F	500-015-1FL	
			4-40	75, 100, 130	500-015-2F	500-015-2FL	
		Jackscrew	2-56	9-69	500-015-1H	500-015-1HL	
			4-40	75, 100, 130	500-015-2H	500-015-2HL	
3	Extended	Screwlock	2-56	9	687-439-09FC	687-439-09F	1.04 26.4
				15	687-439-15FC	687-439-15F	1.17 29.7
				21	687-439-21FC	687-439-21F	1.29 32.8
				25	687-439-25FC	687-439-25F	1.35 34.3
				31	687-439-31FC	687-439-31F	1.42 36.1
				37	687-439-37FC	687-439-37F	1.45 36.8
				51 to 69	687-439-51FC	687-439-51F	1.48 37.6
				75, 100, 130	687-439-100FC	687-439-100F	1.58 40.1
		Jackscrew	2-56	9	687-439-09	687-439-09J	1.04 26.4
				15	687-439-15	687-439-15J	1.17 29.7
				21	687-439-21	687-439-21J	1.29 32.8
				25	687-439-25	687-439-25J	1.35 34.3
				31	687-439-31	687-439-31J	1.42 36.1
				37	687-439-37	687-439-37J	1.45 36.8
				51 to 69	687-439-51	687-439-51J	1.48 37.6
				75, 100, 130	687-439-100	687-439-100J	1.58 40.1

4 FEMALE JACKPOST

Fig.	Type	Thread Size	Connector Size	Part Number	Ordering Note
4	Female Hex Post	2-56	9-69	687-695	Kit contains (1) female hex post, (1) nut and (1) flat washer. Order (2) per backshell.
		4-40	75, 100, 130	687-695-1	

687-695

687-695-1

5 RETAINER CLIP

Figure	Thread Size	Connector Size	Retainer Clip Part Number
5	2-56	9-69	500-015-1
	4-40	75, 100, 130	500-015-2


Part Number in A mm in B mm in øC mm

500-015-1 .172 4.4 .21 5.3 .090 2.3

500-015-2 .250 6.4 .32 8.1 .120 3.0

Micro-D

000-01-(XX)-132
Micro-D Interfacial Seal




000-01-(XX)-132

This accessory fits MWDM socket connectors.

Micro-D interfacial seals fit metal shell Micro-D socket connectors. These fluorosilicone seals are intended for replacement of worn or damaged seals.

PART NUMBER					
Size	Part No.	A		B	
		in	mm	in	mm
9S	000-01-09-132	.330	8.4	.180	4.6
15S	000-01-15-132	.480	12.2	.180	4.6
21S	000-01-21-132	.630	16.0	.180	4.6
25S	000-01-25-132	.730	18.5	.180	4.6
31S	000-01-31-132	.880	22.4	.180	4.6
37S	000-01-37-132	1.030	26.2	.180	4.6
51S	000-01-51-132	.976	24.8	.223	5.7
51-2S	000-01-15-143	1.380	35.0	.180	4.6
67S	000-01-67-132	1.780	45.2	.180	4.6
69S	000-01-69-132	1.276	32.4	.223	5.7
75S	000-01-75-132	1.376	35.0	.223	5.7
100S	000-01-00-132	1.386	35.2	.270	6.9
130S	000-01-30-132	1.736	44.1	.270	6.9





MICRO-D ACCESSORIES

Micro-D

179-135

EMI Gasket, Panel Mount

- For MWDM and M83513 Class M
- Conductive Fluorosilicone
- Rear Panel Mount



179-135

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors.

Rear mount, conductive. EMI panel gasket fits standard MWDM metal shell Micro-D connectors and M83513 Class M connectors. Gasket material is Chomerics CHO-Seal 1298 / MIL-DTL-83528 Type D. Install gasket between Micro-D flange and mounting panel for improved electrical bonding and environmental protection.

- Ag/Al filled fluorosilicone
- CHO-Seal 1298
- MIL-DTL-83528 Type D
- +200 °C
- ASTM E595 TML 0.12% CVCM 0.02%

PART NUMBER

Size	Part No.	A		B		C		D		E		F	
		in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
9	179-135-9-T	.78	19.8	.35	8.9	.565	14.4	.125	3.2	.41	10.4	.26	6.6
15	179-135-15-T	.93	23.6	.35	8.9	.715	18.2	.125	3.2	.56	14.2	.26	6.6
21	179-135-21-T	1.08	27.4	.35	8.9	.865	22.0	.125	3.2	.71	18.0	.26	6.6
25	179-135-25-T	1.18	30.0	.35	8.9	.965	24.5	.125	3.2	.81	20.6	.26	6.6
31	179-135-31-T	1.33	33.8	.35	8.9	1.115	28.3	.125	3.2	.96	24.4	.26	6.6
37	179-135-37-T	1.48	37.6	.35	8.9	1.265	32.1	.125	3.2	1.11	28.2	.26	6.6
51-2	179-135-51-2-T	1.83	46.5	.35	8.9	1.615	41.0	.125	3.2	1.46	37.1	.26	6.6
51	179-135-51-T	1.43	36.3	.44	11.2	1.215	30.9	.125	3.2	1.06	26.9	.31	7.9
69	179-135-69-T	1.73	43.9	.44	11.2	1.515	38.5	.125	3.2	1.36	34.5	.31	7.9
75	179-135-75-T	2.07	52.6	.44	11.2	1.705	43.3	.146	3.7	1.46	37.1	.31	7.9
100	179-135-100-T	2.16	54.9	.55	14.0	1.800	45.7	.146	3.7	1.46	37.1	.36	9.1

Micro-D

507-035
Potting Backshell

MICRO-D ACCESSORIES



507-035

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors

507-035 backshell fits MIL-DTL-83513 Class M and Glenair MWDM Micro-D connectors with metal shell. Fill backshell with potting compound to encapsulate solder joints and provide wire strain relief. Aluminum or stainless steel with passivated stainless steel screws and retainer clips.

TABLE 1
JACKSCREW OPTIONS

No Designator


Fillister Head Jackscrews

H

Socket Head Jackscrews

F

Female Jackposts




PART NUMBER					
Sample PN → 507-035 M 51 H 1					
Base P/N 507-035					
Material / Finish	TZ	Tin-Zinc			
	JF	Alum / Cadmium w/ Yellow Chromate			
	M	Alum / Electroless Nickel			
	MT	Alum / Nickel-PTFE			
	ZR	Alum / Black Zinc-Nickel			
	Z1	SST / Passivated			
Shell Size	09	15	21	25	31
	67	69	100	130	
Jackscrews (Table 1)	Omit	Fillister Head Male Jackscrews			
	H	Socket Head Male Jackscrews			
	F	Female Jackposts (fixed)			
Height	Omit	Standard Height .19 (4.8)			
	1	Extended Height .29 (7.4)			

Size	A Max.		B Max		C		D		E		F Ref		G Thd UNC-2A
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	
09	.850	21.6	.370	9.4	.565	14.4	.31	7.9	.26	6.6	.154	3.9	2-56
15	1.000	25.4	.370	9.4	.715	18.2	.48	12.2	.26	6.6	.154	3.9	2-56
21	1.150	29.2	.370	9.4	.865	22.0	.65	16.5	.26	6.6	.154	3.9	2-56
25	1.250	31.8	.370	9.4	.965	24.5	.75	19.1	.26	6.6	.154	3.9	2-56
31	1.400	35.6	.370	9.4	1.115	28.3	.88	22.4	.26	6.6	.154	3.9	2-56
37	1.550	39.4	.370	9.4	1.265	32.1	1.03	26.2	.26	6.6	.154	3.9	2-56
51	1.500	38.1	.410	10.4	1.215	30.9	.98	24.9	.30	7.6	.154	3.9	2-56
51-2	1.910	48.5	.370	9.4	1.615	41.0	1.38	35.1	.28	7.1	.154	3.9	2-56
67	2.310	58.7	.370	9.4	2.015	51.2	1.78	45.2	.26	6.6	.154	3.9	2-56
69	1.810	46.0	.410	10.4	1.515	38.5	1.28	32.5	.30	7.6	.154	3.9	2-56
100	2.235	56.8	.460	11.7	1.800	45.7	1.35	34.3	.36	9.1	.184	4.7	4-40
130	2.595	65.9	.460	11.7	2.150	54.6	1.71	43.4	.36	9.1	.184	4.7	4-40

Micro-D

500-016

Shorting Cap Backshell




500-016

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors.

500-016 shorting cap fits M83513 Class M and MWDM Micro-D connectors. Closed backshell is available with lanyard for panel or cable attachment. Aluminum with stainless steel screws and washers.

TABLE 2
ATTACHMENT TYPE

F	 Wire Rope, Nylon Jacket 6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C
G	 Black Nylon Rope Very flexible, good abrasion and fuel resistance, .062 (1.6) diameter, -55 to +100 °C
H	 Wire Rope, Clear FEP Jacket Clear FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C
S	 Wire Rope, Black Nylon Jacket 6/6 nylon over stainless steel rope, .034 (0.9) diameter, good flexibility, good abrasion resistance, -55 to +100 °C
T	 SST Wire Rope, No Jacket Good flexibility, good abrasion resistance, .047 (1.2) diameter, passivated, -65 to +200 °C

PART NUMBER

Sample PN → **500-016** **Z2** **51** **H** **F** **6** **-06**

Base P/N	500-016
Material / Finish	TZ Tin-Zinc JF Alum / Cadmium w/ Yel. Chromate M Alum / Electroless Nickel MT Alum / Nickel-PTFE ZR Alum / Black Zinc-Nickel Z2 Alum / Gold
Shell Size	09 15 21 25 31 37 51 51-2 67 69 100
Jackscrews (Table 1)	B Fillister Head Male E Extended Male F Female Jackpost H Socket Head Male
Attachment Type (Table 2)	N No Attachment See Table 2 for attachment types
Attachment Length	Omit If No Attachment Length in One Inch Increments
Attachment Fitting (Table 3)	Omit If No Attachment -00 No Fitting See Table 3 for attachment fittings

TABLE 1 JACKSCREW OPTIONS




B Fillister Head	H Socket Head	E Extended Slotted	F Female Post
			

TABLE 3 ATTACHMENT FITTING

Ring

Code	Ring I.D.
-06	.125 (3.2)
-01	.140 (3.6)
-02	.182 (4.6)
-04	.197 (5.0)

Slip/Crimp Sleeve

-SCS

Slip/Crimp Sleeve
For Attachment Type G Only
Sleeve is copper with black
chromate

Crimp Ferrule

-CF



Crimp Ferrule
*For Attachment Types G or
S Only*
Sleeve is copper with black
chromate

Micro-D

500-016

Shorting Cap Backshell

MICRO-D ACCESSORIES



Size	A Max.		B Max		C		D Max		E Ref		F Thd UNC-2
	in	mm	in	mm	in	mm	in	mm	in	mm	
09	.850	21.6	.370	9.4	.565	14.4	.350	8.9	.154	3.9	2-56
15	1.000	25.4	.370	9.4	.715	18.2	.470	11.9	.154	3.9	2-56
21	1.150	29.2	.370	9.4	.865	22.0	.590	15.0	.154	3.9	2-56
25	1.250	31.8	.370	9.4	.965	24.5	.650	16.5	.154	3.9	2-56
31	1.400	35.6	.370	9.4	1.115	28.3	.710	18.0	.154	3.9	2-56
37	1.550	39.4	.370	9.4	1.265	32.1	.750	19.1	.154	3.9	2-56
51	1.500	38.1	.410	10.4	1.215	30.9	.780	19.8	.154	3.9	2-56
51-2	1.910	48.5	.370	9.4	1.615	41.0	.780	19.8	.154	3.9	2-56
67	2.310	58.7	.370	9.4	2.015	51.2	.780	19.8	.154	3.9	2-56
69	1.810	46.0	.410	10.4	1.515	38.5	.780	19.8	.154	3.9	2-56
100	2.235	56.8	.460	11.7	1.800	45.7	.840	21.3	.184	4.7	4-40

Micro-D

500-010

EMI Banding Backshell


- Solid Backshell
- Band-Master ATS® Shield Termination
- Top, Side and 45° Entry

**T** Top Entry**S** Side Entry**E** 45° Entry**D** Dual 45°

500-010


This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors.

EMI, banding. 500-010 backshell fits MIL-DTL-83513 Class M and Glenair MWDM Micro-D connectors. Terminate cable shield to backshell with BandMaster ATS band strap. Available with screwlocks or jackscrews: screwlocks allow connectors to be fully mated prior to fastening screws, jackscrews must be tightened in order to mate connectors. Aluminum or stainless steel with passivated stainless steel screws and retainer clips.

TABLE 1
 SCREWLOCK OPTIONS


PART NUMBER


Sample PN → **500T010 M 37 H 07 S L**

Base P/N	500T010	T Top Entry								
	500S010	S Side Entry								
	500E010	E 45° Entry								
	500D010	D Dual 45° Entry								
Material / Finish	TZ	Tin-Zinc								
	JF	Alum / Cadmium w/ Yel. Chromate								
	M	Alum / Electroless Nickel								
	MT	Alum / Nickel-PTFE								
	ZR	Alum / Black Zinc-Nickel								
	Z1	SST / Passivated								
	Z2	Alum / Gold								
Shell Size	09	15	21	25	31	37	51	51-2		
	67	69	75	100	130					
Screwlocks (Table 1)	Male Screwlocks				Jackscrews					
	B	Fillister Head				BJ	Fillister Head			
	H	Socket Head				HJ	Socket Head			
	E*	Extended Slotted*				EJ*	Extended Slotted*			
	Female Post				* E and EJ options available on Profiles S T only					
	F	Female Jackpost								
Entry Size	Entry Size	P Diameter	T	S	E	D				
	04	.125 (3.2)	All	All	All	All				
	05	.156 (4.0)	All	All	All	All				
	06	.188 (4.8)	All	All	All	All				
	07	.219 (5.6)	All	All	All	15-up				
	08	.250 (6.4)	All	All	All	15-up				
	09	.281 (7.1)	All	All	31-up	31-up				
	10	.312 (7.9)	15-up	15-up	51, 69-up	51, 69-up				
	11	.344 (8.7)	100-up	15-up	100-up	100-up				
	12	.375 (9.5)	100-up	15-up	100-up	100-up				
	Qwik-Ty	Omit	No Qwik-Ty Strain Relief Arm							
		S	Qwik-Ty Arm Included							
Band	Omit	No Band				L	Micro Band Included			
	K	Standard Band Included				J	Micro Slim Band Included			
	P	Slim Standard Band Included				N	Micro-Max Band Included			

500-010

EMI Banding Backshell

- Solid Backshell
- Band-Master ATS® Shield Termination
- Top, Side and 45° Entry



Size	A Max.		B Max.		C		D Max.		E Max.		F Max.		G Max.		H Ref.		J Thd	K		L Max.		M Max.		N Max.	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	UNC-2A	in	mm	in	mm	in	mm	in	mm
09	.850	21.6	.370	9.4	.565	14.4	.780	19.8	.410	10.4	.350	8.9	.637	16.2	.154	3.9	2-56	.435	11.0	1.040	26.4	1.288	32.7	.968	24.6
15	1.000	25.4	.370	9.4	.715	18.2	.910	23.1	.580	14.7	.470	11.9	.673	17.1	.154	3.9	2-56	.440	11.2	1.170	29.7	1.288	32.7	.968	24.6
21	1.150	29.2	.370	9.4	.865	22.0	1.030	26.2	.740	18.8	.590	15.0	.707	18.0	.154	3.9	2-56	.458	11.6	1.290	32.8	1.288	32.7	.968	24.6
25	1.250	31.8	.370	9.4	.965	24.5	1.090	27.7	.850	21.6	.650	16.5	.748	19.0	.154	3.9	2-56	.483	12.3	1.350	34.3	1.090	27.7	.830	21.1
31	1.400	35.6	.370	9.4	1.115	28.3	1.150	29.2	.980	24.9	.710	18.0	.756	19.2	.154	3.9	2-56	.476	12.1	1.420	36.1	1.130	28.7	.890	22.6
37	1.550	39.4	.370	9.4	1.265	32.1	1.190	30.2	1.130	28.7	.750	19.1	.774	19.7	.154	3.9	2-56	.478	12.1	1.450	36.8	1.230	31.2	.955	24.3
51	1.500	38.1	.410	10.4	1.215	30.9	1.220	31.0	1.080	27.4	.780	19.8	.859	21.8	.154	3.9	2-56	.548	13.9	1.480	37.6	1.250	31.8	1.005	25.5
51-2	1.910	48.5	.370	9.4	1.615	41.0	1.220	31.0	1.510	38.4	.780	19.8	.859	21.8	.154	3.9	2-56	.548	13.9	1.480	37.6	1.250	31.8	1.005	25.5
67	2.310	58.7	.370	9.4	2.015	51.2	1.220	31.0	1.880	47.8	.780	19.8	.859	21.8	.154	3.9	2-56	.548	13.9	1.480	37.6	1.250	31.8	1.005	25.5
69	1.810	46.0	.410	10.4	1.515	38.5	1.220	31.0	1.380	35.1	.780	19.8	.859	21.8	.154	3.9	2-56	.548	13.9	1.480	37.6	1.250	31.8	1.005	25.5
75	2.140	54.4	.410	10.4	1.705	43.3	1.220	31.0	1.470	37.3	.780	19.8	.859	21.8	.184	4.7	4-40	.548	13.9	1.480	37.6	1.250	31.8	1.005	25.5
100	2.235	56.8	.460	11.7	1.800	45.7	1.280	32.5	1.470	37.3	.840	21.3	1.014	25.8	.184	4.7	4-40	.687	17.4	1.580	40.1	1.320	33.5	1.080	27.4
130	2.595	65.9	.460	11.7	2.160	54.6	1.280	32.5	1.830	46.5	.840	21.3	1.014	25.8	.184	4.7	4-40	.687	17.4	1.580	40.1	1.320	33.5	1.080	27.4

MAXIMUM ENTRY SIZE

Shell Size	Top T	Side S	45° E	Dual 45° D
09	09	09	08	06
15	10	12	08	08
21	10	12	08	08
25	10	12	08	08
31	10	12	09	09
37	10	12	09	09
51	10	12	10	10
51-2	10	12	09	09
67	10	12	09	09
69	10	12	10	10
75	10	12	10	10
100	12	12	12	12
130	12	12	12	12

SCREWLOCKS AND JACKSCREWS

CLIP
CLIP HAS CIRCULAR HOLE AND SQUARE HOLE.

SCREWLOCK
SQUARE HOLE IS ON THE TOP. SCREW IS FLOATING. MATE CONNECTORS FIRST, THEN FASTEN SCREWLOCKS.

JACKSCREW
SQUARE HOLE IS ON THE BOTTOM. SCREW IS CAPTIVE. TURN SCREWS TO JACK CONNECTORS TOGETHER.

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.


Band Type and Width	Hand Tool	Pneumatic
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

Micro-D

500-011

EMI Braidsock Backshell

- Solid Backshell with Braidsock
- EMI Shielded
- Top, Side and 45° Entry

**T** Top Entry**S** Side Entry**E** 45° Entry

500-011

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors


EMI, shield sock. 500-011 backshell fits MIL-DTL-83513 Class M and Glenair MWDM Micro-D connectors with metal shell. Supplied with tubular tinned copper braid. Aluminum or stainless steel with passivated stainless steel screws and retainer clips. Crimp ring is tin-plated copper.




- Soft-drawn tin-plated copper braid
- I.A.W. AA59569R36T
- EMI frequency effective to 1 GHz
- 150°C
- 90° Optical Coverage

TABLE 1
SCREWLOCK OPTIONS
B


Fillister Head

**H**

Socket Head

**F**

Female Post



PART NUMBER

Sample PN → **500T011 M 51 H 08 -12**


Base P/N
500T011 **T** Top Entry
500S011 **S** Side Entry
500E011 **E** 45° Entry

Material / Finish
TZ Tin-Zinc
JF Alum / Cadmium w/ Yel. Chromate
M Alum / Electroless Nickel
MT Alum / Nickel-PTFE
ZR Alum / Black Zinc-Nickel
Z1 SST / Passivated
Z2 Alum / Gold

Shell Size
09 15 21 25 31 37 51 51-2
67 69 100

Screwlocks
(Table 1)
B Fillister Head Male
H Socket Head Male
F Female Jackpost

Entry Size	L Diameter	Shell Size
04	.125 (3.2)	All
05	.156 (4.0)	All
06	.188 (4.8)	All
07	.219 (5.6)	All
08	.250 (6.4)	All
09	.281 (7.1)	15-up
10	.312 (7.9)	51-up
11	.344 (8.7)	100
12	.375 (9.5)	100



Braid Length **-12** Length in 1 inch increments. "**-12**" = 12 inches.




Micro-D

500-011

EMI Braidsock Backshell

- Solid Backshell with Braidsock
- EMI Shielded
- Top, Side and 45° Entry

MICRO-D ACCESSORIES



	A		B		C		D		E		F		G		H Ref		J Thd	K		M Max		Max Entry
Size	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	UNC-2	± in	(0.8) mm	in	mm	Size
09	.775	19.7	.36	9.1	.565	14.4	.32	8.1	.435	11.0	.607	15.4	.650	16.5	.154	3.9	2-56	.75	19.1	1.00	25.4	08
15	.925	23.5	.36	9.1	.715	18.2	.44	11.2	.440	11.2	.643	16.3	.700	17.8	.154	3.9	2-56	.88	22.4	1.03	26.2	08
21	1.075	27.3	.36	9.1	.865	22.0	.56	14.2	.458	11.6	.677	17.2	.735	18.7	.154	3.9	2-56	1.00	25.4	1.05	26.7	08
25	1.175	29.8	.36	9.1	.965	24.5	.62	15.7	.483	12.3	.718	18.2	.800	20.3	.154	3.9	2-56	1.06	26.9	1.09	27.7	08
31	1.325	33.7	.36	9.1	1.115	28.3	.68	17.3	.476	12.1	.726	18.4	.860	21.8	.154	3.9	2-56	1.12	28.4	1.13	28.7	09
37	1.475	37.5	.36	9.1	1.265	32.1	.72	18.3	.478	12.1	.744	18.9	.925	23.5	.154	3.9	2-56	1.16	29.5	1.16	29.5	09
51	1.425	36.2	.40	10.2	1.215	30.9	.75	19.1	.548	13.9	.829	21.1	.975	24.8	.154	3.9	2-56	1.19	30.2	1.19	30.2	10
51-2	1.835	46.6	.36	9.1	1.615	41.0	.75	19.1	.548	13.9	.829	21.1	.975	24.8	.154	3.9	2-56	1.19	30.2	1.19	30.2	10
67	2.230	56.6	.36	9.1	2.015	51.2	.75	19.1	.548	13.9	.829	21.1	.975	24.8	.154	3.9	2-56	1.19	30.2	1.19	30.2	10
69	1.730	43.9	.40	10.2	1.515	38.5	.75	19.1	.548	13.9	.829	21.1	.975	24.8	.154	3.9	2-56	1.19	30.2	1.19	30.2	10
100	2.160	54.9	.45	11.4	1.800	45.7	.81	20.6	.687	17.4	.984	25.0	1.050	26.7	.184	4.7	4-40	1.25	31.8	1.25	31.8	12

Entry		Ø L	
Size	Entry Dia.	in	mm
04	.125	3.2	
05	.156	4.0	
06	.188	4.8	
07	.219	5.6	
08	.250	6.4	
09	.281	7.1	
10	.312	7.9	
11	.344	8.7	
12	.375	9.5	


Micro-D




507-088

EMI Banding Backshell, Composite


- Lightweight Composite
- Micro Band Shield Termination
- Top, Side and 45° Entry



T Top Entry



S Side Entry




E 45° Entry

507-088

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors

EMI, lightweight composite. 507-088 backshell fits MIL-DTL-83513 Class M and Glenair MWDM Micro-D connectors. Terminate cable shield to backshell with BandMaster ATS Micro band strap. Available with screwlocks or jackscrews: screwlocks allow connectors to be fully mated prior to fastening screws, jackscrews must be tightened in order to mate connectors. Nickel-plated thermoplastic with passivated stainless steel screws and retainer clips.

TABLE 1 SCREWLOCK OPTIONS



PART NUMBER

Sample PN → 507T088 XM 51 HF 09 S K

Base P/N	507T088	T	Top Entry		
	507S088	S	Side Entry		
	507E088	E	45° Entry		
Finish	XM Electroless Nickel				
Shell Size	09 15 21 25 31 37 51 100				
Screwlocks (Table 1)	Male Screwlocks		Male Jackscrews		
	BF	Fillister Head	B	Fillister Head	
	HF	Socket Head	H	Socket Head	
	Female Post		E*	Extended Slotted*	
	F	Female Jackpost	* E option available on Profiles S T only		
Entry Size	Entry Size	K Diameter	Shell Size		
			T	S	E
	04	.125 (3.2)	All	All	All
	05	.156 (4.0)	All	All	All
	06	.188 (4.8)	All	All	All
	07	.219 (5.6)	All	All	All
	08	.250 (6.4)	All	All	All
	09	.281 (7.1)	31-100	All	31-100
	10	.312 (7.9)	51, 100	15-100	51, 100
	11	.344 (8.7)	100	15-100	100
	12	.375 (9.5)	100	15-100	100
Qwik-Ty	Omit	No Qwik-Ty Arm			
	S	Qwik-Ty Strain Relief Arm			
Band	Omit	No Band			
	K	Micro Band Included			
	J	Micro Slim Band Included			

ø K
ENTRY SIZE




Micro-D

507-088




EMI Banding Backshell, Composite

- Lightweight Composite
- Micro Band Shield Termination
- Top, Side and 45° Entry

MICRO-D ACCESSORIES




Entry Size	in	mm	in	mm
04	.125	3.2	.219	5.6
05	.156	4.0	.250	6.4
06	.188	4.8	.281	7.1
07	.219	5.6	.313	8.0
08	.250	6.4	.344	8.7
09	.281	7.1	.375	9.5
10	.312	7.9	.406	10.3
11	.344	8.7	.438	11.1
12	.375	9.5	.469	11.9



Size	A	B	C	D	E	F	G Thd	H	J Max	M Min
	in	mm	in	mm	in	mm	UNC-2	± .03(0.8)	in	mm
09	.775	19.7	.36	9.1	.565	14.4	.43	10.9	.650	16.5
15	.925	23.5	.36	9.1	.715	18.2	.44	11.2	.700	17.8
21	1.075	27.3	.36	9.1	.865	22.0	.56	14.2	.735	18.7
25	1.175	29.8	.36	9.1	.965	24.5	.62	15.7	.800	20.3
31	1.325	33.7	.36	9.1	1.115	28.3	.68	17.3	.860	21.8
37	1.475	37.5	.36	9.1	1.265	32.1	.72	18.3	.925	23.5
51	1.425	36.2	.40	10.2	1.215	30.9	.75	19.1	.975	24.8
100	2.160	54.9	.45	11.4	1.800	45.7	.81	20.6	1.050	26.7

SCREWLOCKS AND JACKSCREWS

CLIP
CLIP HAS CIRCULAR HOLE AND SQUARE HOLE.



SCREWLOCK
SQUARE HOLE IS ON THE TOP. SCREW IS FLOATING. MATE CONNECTORS FIRST, THEN FASTEN SCREWLOCKS.



JACKSCREW
SQUARE HOLE IS ON THE BOTTOM. SCREW IS CAPTIVE. TURN SCREWS TO JACK CONNECTORS TOGETHER.



BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123

Micro-D

507-142

EMI Banding Backshell, Dual Entry

- Solid Backshell
- Band-Master ATS® Shield Termination
- Two Band Platforms



507-142

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors

EMI, dual entry. 507-142 backshell fits MIL-DTL-83513 Class M and Glenair MWDM Micro-D connectors with metal shell. Two band platforms. Aluminum with passivated stainless steel screws and retainer clips.

PART NUMBER

Sample PN→

507-142

JF

31

B

P

Base P/N 507-142

Finish

TZ Tin-Zinc
JF Cadmium w/ Yellow Chromate
M Electroless Nickel
MT Nickel-PTFE
ZR Black Zinc-Nickel
Z2 Gold

Shell Size 21 25 31 37 51 51-2 69 100


Jackscrews
(Table 1)

B Fillister Head Male Jackscrews
F Female Jackposts (fixed)
H Socket Head Male Jackscrews

Band

Omit No Band
K Standard Bands Included
P Slim Standard Bands Included
M Micro Bands Included
J Micro Slim Bands Included
L Micro-Max Bands Included

TABLE 1 JACKSCREW OPTIONS



B

Fillister Head
Jackscrews

F

Female
Jackposts


H

Socket Head
Jackscrews

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.

Band Type and Width	Hand Tool	Pneumatic
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118



Size	A		B		C		D		E		F		G		H		J Thd
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	UNC-2
21	1.075	27.3	.34	8.6	1.00	25.4	.281	.71	.125	3.2	.56	14.2	.865	22.0	.438	11.1	2-56
25	1.175	29.8	.34	8.6	1.06	26.9	.344	.87	.188	4.8	.62	15.7	.965	24.5	.438	11.1	2-56
31	1.325	33.7	.34	8.6	1.12	28.4	.406	10.3	.250	6.4	.68	17.3	1.115	28.3	.438	11.1	2-56
37	1.475	37.5	.34	8.6	1.16	29.5	.500	12.7	.344	8.7	.72	18.3	1.265	32.1	.438	11.1	2-56
51	1.425	36.2	.38	9.7	1.19	30.2	.469	11.9	.312	7.9	.75	19.1	1.215	30.9	.438	11.1	2-56
51-2	1.835	46.6	.36	9.1	1.19	30.2	.469	11.9	.281	7.1	.75	19.1	1.615	41.0	.438	11.1	2-56
69	1.730	43.9	.40	10.2	1.19	30.2	.469	11.9	.312	7.9	.75	19.1	1.515	38.5	.438	11.1	2-56
100	2.160	54.9	.45	11.4	1.25	31.8	.688	17.5	.500	12.7	.81	20.6	1.800	45.7	.469	11.9	4-40

Micro-D



500-047

EMI Banding Backshell, Elliptical Entry


- Solid Backshell
- Band-Master ATS® Shield Termination
- Elliptical Entry



500-047

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors

EMI, elliptical entry. 500-047 backshell fits MIL-DTL-83513 Class M and Glenair MWDM Micro-D connectors with metal shell. Terminate cable shield to backshell with BandMaster ATS band strap. Available with screwlocks or jackscrews: screwlocks allow connectors to be fully mated prior to fastening screws, jackscrews must be tightened in order to mate connectors. Aluminum or stainless steel with passivated stainless steel screws and retainer clips.



PART NUMBER

Sample PN→

500-047

M

21

B

B

T

Base P/N 500-047

Material / Finish	TZ	Tin-Zinc
	JF	Alum / Cadmium w/ Yellow Chromate
	M	Alum / Electroless Nickel
	MT	Alum / Nickel-PTFE
	ZR	Alum / Black Zinc-Nickel
	ZI	SST / Passivated

Shell Size **09 15 21 25 31 37 51 51-2**
67 69 75 100 130


Screwlocks (Table 1)	B	Fillister Head Male Screwlocks
	E	Extended Slotted Male Screwlocks
	F	Female Screwlocks (fixed)
	H	Socket Head Male Screwlocks
	HJ	Socket Head Male Jackscrews

Band	Omit	No Band	M	Micro Band Included
	B	Standard Band Included	D	Micro Slim Band Included
	P	Slim Standard Band Included	L	Micro-Max Band Included

Qwik-Ty	Omit	No Qwik-Ty Strain Relief Arm
	T	Qwik-Ty Arm Included

Size	A		B		C		D		E		F		G		H		J Thd
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	UNC-2
09	.775	19.7	.34	8.6	.75	19.1	.312	7.9	.281	.71	.32	8.1	.565	14.4	.154	3.9	2-56
15	.925	23.5	.34	8.6	.88	22.4	.420	10.7	.281	.71	.44	11.2	.715	18.2	.154	3.9	2-56
21	1.075	27.3	.34	8.6	1.00	25.4	.590	15.0	.281	.71	.56	14.2	.865	22.0	.154	3.9	2-56
25	1.175	29.8	.34	8.6	1.06	26.9	.690	17.5	.281	.71	.62	15.7	.965	24.5	.154	3.9	2-56
31	1.325	33.7	.34	8.6	1.12	28.4	.820	20.8	.281	.71	.68	17.3	1.115	28.3	.154	3.9	2-56
37	1.475	37.5	.34	8.6	1.16	29.5	.970	24.6	.281	.71	.72	18.3	1.265	32.1	.154	3.9	2-56
51	1.425	36.2	.38	9.7	1.19	30.2	.920	23.4	.312	.79	.75	19.1	1.215	30.9	.154	3.9	2-56
51-2	1.835	46.6	.34	8.6	1.19	30.2	1.030	26.2	.281	.71	.75	19.1	1.615	41.0	.154	3.9	2-56
67	2.225	56.5	.34	8.6	1.19	30.2	1.720	43.7	.281	.71	.75	19.1	2.015	51.2	.154	3.9	2-56
69	1.730	43.9	.40	10.2	1.19	30.2	1.190	30.2	.312	.79	.75	19.1	1.515	38.5	.154	3.9	2-56
75	2.055	52.2	.40	10.2	1.19	30.2	1.195	30.4	.312	.79	.75	19.1	1.705	43.3	.184	4.7	4-40
100	2.160	54.9	.43	10.9	1.25	31.8	1.290	32.8	.360	.91	.81	20.6	1.800	45.7	.184	4.7	4-40
130	2.510	63.8	.43	10.9	1.50	38.1	1.650	41.9	.360	.91	1.06	26.9	2.150	54.6	.184	4.7	4-40

TABLE 1 SCREWLOCK OPTIONS



SCREWLOCKS AND JACKSCREWS

CLIP


Clip has circular hole and square hole.

JACKSCREW

Square hole is on the bottom. Screw is captive. Turn screws to mate connectors.

SCREWLOCK

Square hole is on the top. Screw is floating. Mate connectors first, then fasten screwlocks.



BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.

Band Type and Width	Hand Tool	Pneumatic
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118



Micro-D



507-175

EMI Banding Backshell, Elliptical Micro Band


- Elliptical Entry
- Micro Band Shield Termination
- Top, 45° and 90° Entry

**T** Top Entry**S** 90° Entry**E** 45° Entry


507-175

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors


EMI, variable elliptical entry. 507-175 backshell fits MIL-DTL-83513 Class M and Glenair MWDM Micro-D connectors. Elliptical entry accommodates large wire bundles. Optional Qwik-Ty strain relief arm. Terminate cable shield to backshell with BandMaster ATS .12" wide Micro band strap. Available with male or female screwlocks. Screwlocks allow connectors to be fully mated prior to fastening screws. Aluminum with passivated stainless steel screws and retainer clips.

TABLE 1 SCREWLOCK OPTIONS


No Designator
Fillister Head
Screwlocks



H
Socket Head
Screwlocks

**F**

Female Hex Post



**E**

Extended Screwlocks

PART NUMBER

Sample PN → **507T175 JF 100 07 H S J**

Base P/N	507T175	T Top Entry
	507S175	S 90° Entry
	507E175	E 45° Entry
Finish	TZ	Tin-Zinc
	JF	Cadmium w/ Yellow Chromate
	M	Electroless Nickel
	MT	Nickel-PTFE
	ZR	Black Zinc-Nickel
	Z2	Gold
Shell Size	09 15 21 25 31 37 51 51-2	
	67 69 75 100 130	
Entry Size	Entry Size	D
	01	.344 (8.7)
	02	.494 (12.5)
	03	.644 (16.4)
	04	.744 (18.9)
	05	.894 (22.7)
	06	.994 (25.2)
	07	1.044 (26.5)
	08	1.024 (26.0)
	09	1.625 (41.3)
Screwlocks (Table 1)	Omit	Fillister Head Male Screwlocks
	E	Extended Slotted Male Screwlocks
	F	Female Hex Post
	H	Socket Head Male Screwlocks
Qwik-Ty®	Omit	No Qwik-Ty Arm
	S	Qwik-Ty Arm Included
Band	Omit	No Band
	M	Micro Band Included
	J	Micro Slim Band Included
	L	Micro-Max Band Included





Micro-D



507-175

EMI Banding Backshell, Elliptical Micro Band

- Elliptical Entry
- Micro Band Shield Termination
- Top, 45° and 90° Entry



Entry Size	D		E		Shell Sizes
	± .010 (0.3)	in mm	± .010 (0.3)	in mm	
01	.344	8.7	.290	7.4	09 thru 130
02	.494	12.5	.290	7.4	15 thru 130
03	.644	16.4	.290	7.4	21 thru 130
04	.744	18.9	.304	7.7	25 thru 130
05	.894	22.7	.304	7.7	31 thru 130
06	.994	25.2	.304	7.7	37 thru 130
07	1.044	26.5	.304	7.7	37 thru 130
08	1.024	26.0	.384	9.8	75 thru 130
09	1.625	41.3	.360	9.1	130

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.



Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

Size	A Max.		B Max		C		F Max		G Max		H Max		J Max		K Max		L Thd UNC-2
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	
09	.850	21.6	.370	9.4	.565	14.4	.782	19.9	.970	24.6	.668	17.0	.673	17.1	.851	21.6	2-56
15	1.000	25.4	.370	9.4	.715	18.2	.832	21.1	.970	24.6	.668	17.0	.673	17.1	.876	22.3	2-56
21	1.150	29.2	.370	9.4	.865	22.0	.882	22.4	.970	24.6	.668	17.0	.673	17.1	.901	22.9	2-56
25	1.250	31.8	.370	9.4	.965	24.5	.932	23.7	.990	25.1	.678	17.2	.700	17.8	.943	24.0	2-56
31	1.400	35.6	.370	9.4	1.115	28.3	.972	24.7	.990	25.1	.678	17.2	.700	17.8	.963	24.5	2-56
37	1.550	39.4	.370	9.4	1.265	32.1	.972	24.7	.990	25.1	.678	17.2	.700	17.8	.983	25.0	2-56
51	1.500	38.1	.410	10.4	1.215	30.9	1.092	27.7	1.030	26.2	.698	17.7	.758	19.3	1.050	26.7	2-56
51-2	1.910	48.5	.370	9.4	1.615	41.0	1.092	27.7	1.030	26.2	.698	17.7	.758	19.3	1.050	26.7	2-56
67	2.310	58.7	.370	9.4	2.015	51.2	1.092	27.7	1.030	26.2	.698	17.7	.758	19.3	1.050	26.7	2-56
69	1.810	46.0	.410	10.4	1.515	38.5	1.092	27.7	1.030	26.2	.698	17.7	.758	19.3	1.050	26.7	2-56
75	2.140	54.4	.470	10.4	1.705	43.3	1.092	27.7	1.030	26.2	.698	17.7	.758	19.3	1.050	26.7	4-40
100	2.235	56.8	.460	11.7	1.800	45.7	1.157	29.4	1.090	27.7	.723	18.4	.824	20.9	1.130	28.7	4-40
130	2.585	65.9	.460	11.7	2.160	54.6	1.157	29.4	1.090	27.7	.723	18.4	.824	20.9	1.130	28.7	4-40


Micro-D




507-296

EMI Banding Backshell, Lightweight Micro Band

- Elliptical Top and 90° Entry
- Micro Band Shield Termination
- Lightweight



T Top Entry




S 90° Entry

507-296

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors

Lightweight, elliptical entry. 507-296 EMI banding backshell fits metal shell Micro-D connectors. Lightweight design features reduced flange height and reduced hardware weight. Jackscrews have e-rings to attach backshell to connector. Available with jackscrews or female jackposts. Aluminum or stainless steel. Stainless steel screws and e-rings.

TABLE 1
HARDWARE OPTIONS



PART NUMBER

Sample PN → 507T296 M 21 B E K

Base P/N	507T296 T Top Entry																																	
	507S296 S 90° Entry																																	
Material / Finish	TZ Tin-Zinc																																	
	JF Alum / Cadmium w/ Yel. Chromate																																	
	M Alum / Electroless Nickel																																	
	MT Alum / Nickel-PTFE																																	
	ZR Alum / Black Zinc-Nickel																																	
	Z1 SST / Passivated																																	
	Z2 Alum / Gold																																	
Shell Size	09 15 21 25 31 37 51 51-2																																	
	67 69 75 100 130																																	
Entry Size	<table><tr><th>Entry Size</th><th>G</th><th>Shell Size</th></tr><tr><td>A</td><td>.320 (8.1)</td><td>09 thru 130</td></tr><tr><td>B</td><td>.470 (11.9)</td><td>15 thru 130</td></tr><tr><td>C</td><td>.620 (15.7)</td><td>21 thru 130</td></tr><tr><td>D</td><td>.720 (18.3)</td><td>25 thru 130</td></tr><tr><td>E</td><td>.870 (22.1)</td><td>31 thru 130</td></tr><tr><td>F</td><td>.970 (24.6)</td><td>37 thru 130</td></tr><tr><td>G</td><td>1.020 (25.9)</td><td>37, 51-2 thru 130</td></tr><tr><td>H</td><td>1.270 (32.3)</td><td>51-2 thru 130</td></tr><tr><td>J</td><td>1.360 (34.5)</td><td>51-2, 67, 100, 130</td></tr><tr><td>K</td><td>1.770 (45.0)</td><td>67, 130</td></tr></table> 	Entry Size	G	Shell Size	A	.320 (8.1)	09 thru 130	B	.470 (11.9)	15 thru 130	C	.620 (15.7)	21 thru 130	D	.720 (18.3)	25 thru 130	E	.870 (22.1)	31 thru 130	F	.970 (24.6)	37 thru 130	G	1.020 (25.9)	37, 51-2 thru 130	H	1.270 (32.3)	51-2 thru 130	J	1.360 (34.5)	51-2, 67, 100, 130	K	1.770 (45.0)	67, 130
Entry Size	G	Shell Size																																
A	.320 (8.1)	09 thru 130																																
B	.470 (11.9)	15 thru 130																																
C	.620 (15.7)	21 thru 130																																
D	.720 (18.3)	25 thru 130																																
E	.870 (22.1)	31 thru 130																																
F	.970 (24.6)	37 thru 130																																
G	1.020 (25.9)	37, 51-2 thru 130																																
H	1.270 (32.3)	51-2 thru 130																																
J	1.360 (34.5)	51-2, 67, 100, 130																																
K	1.770 (45.0)	67, 130																																
Hardware	B Fillister Head Male Jackscrew																																	
(Table 1)	H Socket Head Male Jackscrew																																	
	E Extended Male Jackscrew*																																	
	F Female Jackpost																																	
	* Extended jackscrew is not to be used with top entry backshell at max entry size.																																	
Band	Omit No Band																																	
	L Micro Band Included																																	
	J Micro Slim Band Included																																	
	K Micro-Max Band Included																																	




Micro-D

507-296

EMI Banding Backshell, Lightweight Micro Band

- Elliptical Top and 90° Entry
- Micro Band Shield Termination
- Lightweight

MICRO-D ACCESSORIES



Size	A	B	C	D	E	F	Max Entry
	in mm	in mm	in mm	in mm	in mm	in mm	
09	.775 19.7	.340 8.6	.565 14.4	.520 13.2	.440 11.2	.250 6.4	A
15	.925 23.5	.340 8.6	.715 18.2	.520 13.2	.590 15.0	.250 6.4	B
21	1.075 27.3	.340 8.6	.865 22.0	.520 13.2	.740 18.8	.250 6.4	C
25	1.175 29.8	.340 8.6	.965 24.5	.520 13.2	.840 21.3	.250 6.4	D
31	1.325 33.7	.340 8.6	1.115 28.3	.520 13.2	.990 25.1	.250 6.4	E
37	1.475 37.5	.340 8.6	1.265 32.1	.520 13.2	1.140 29.0	.250 6.4	G
51	1.425 36.2	.380 9.7	1.215 30.9	.610 15.5	1.090 27.7	.290 7.4	F
51-2	1.825 46.4	.340 8.6	1.615 41.0	.520 13.2	1.490 37.8	.250 6.4	J
67	2.225 56.5	.340 8.6	2.015 51.2	.520 13.2	1.890 48.0	.250 6.4	K
69	1.725 43.8	.380 9.7	1.515 38.5	.610 15.5	1.390 35.3	.290 7.4	H
75	2.070 52.6	.380 9.7	1.705 43.3	.520 13.2	1.490 37.8	.290 7.4	H
100	2.160 54.9	.430 10.9	1.800 45.7	.630 16.0	1.522 38.7	.340 8.6	J
130	2.510 63.8	.430 10.9	2.150 54.6	.630 16.0	1.882 47.8	.340 8.6	K

Entry Size	G in	G mm	Available Shell Sizes
A	.320	8.1	09 thru 130
B	.470	11.9	15 thru 130
C	.620	15.7	21 thru 130
D	.720	18.3	25 thru 130
E	.870	22.1	31 thru 130
F	.970	24.6	37 thru 130
G	1.020	25.9	37, 51-2 thru 130
H	1.270	32.3	51-2 thru 130
J	1.360	34.5	51-2, 67, 100, 130
K	1.770	45.0	67, 130

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.




Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

507-297

EMI Banding Backshell, Lightweight 45°

- Elliptical 45° Entry
- Micro Band Shield Termination
- Lightweight



507-297

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors

Lightweight, elliptical entry. 507-297 EMI banding backshell fits metal shell Micro-D connectors. Lightweight design features reduced flange height and reduced hardware weight. Jackscrews have e-rings to attach backshell to connector. Available with jackscrews or female jackposts. Aluminum or stainless steel. Stainless steel screws and e-rings.

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.




Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118


PART NUMBER

		507E297		JF	37	E	H	K
Base P/N		507E297						
Material / Finish	TZ	Tin-Zinc						
	JF	Alum / Cadmium w/ Yel. Chromate						
	M	Alum / Electroless Nickel						
	MT	Alum / Nickel-PTFE						
	ZR	Alum / Black Zinc-Nickel						
	Z1	SST / Passivated						
	Z2	Alum / Gold						
Shell Size	09	15	21	25	31	37	51	51-2
	67	69	75	100	130			
Entry Size	Entry Size	H	Shell Size					
	A	.188 (4.8)	09 thru 130					
	B	.230 (5.8)	15 thru 130					
	C	.265 (6.7)	21 thru 130					
	D	.335 (8.5)	25 thru 130					
	E	.360 (9.1)	31 thru 130					
	F	.410 (10.4)	37 thru 130					
	G	.520 (13.2)	51 thru 130					
	H	.585 (14.9)	51-2 thru 130					
	J	.665 (16.9)	51-2 thru 130					
	K	.720 (18.3)	67, 100, 130					
	L	.760 (19.3)	67, 130					
Jackscrews (Table 1)	B	Fillister Head Male Jackscrew						
	F	Female Jackpost						
	H	Socket Head Male Jackscrew						
Band	Omit	No Band						
	L	Micro Band Included						
	J	Micro Slim Band Included						
	K	Micro-Max Band Included						


TABLE 1 JACKSCREW OPTIONS



B
Fillister Hd.
Jackscrew



F
Female Jackpost




**Socket Head
Jackscrew**

Micro-D

507-297

EMI Banding Backshell, Lightweight 45°

- Elliptical 45° Entry
- Micro Band Shield Termination
- Lightweight



Entry Size	in	H mm	Available Shell Sizes
A	ø .188	4.8	09 thru 130
B	ø .230	5.8	15 thru 130
C	.265	6.7	21 thru 130
D	.335	8.5	25 thru 130
E	.360	9.1	31 thru 130
F	.410	10.4	37 thru 130
G	.520	13.2	51 thru 130
H	.585	14.9	51-2 thru 130
J	.665	16.9	51-2 thru 130
K	.720	18.3	67, 100, 130
L	.760	19.3	67, 130

Shell Size	A		B		C		D		E		F		G		Max Entry
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	
09	.775	19.7	.340	8.6	.565	14.4	.500	12.7	.70	17.8	.440	11.2	-	-	A
15	.925	23.5	.340	8.6	.715	18.2	.560	14.2	.76	19.3	.590	15.0	-	-	B
21	1.075	27.3	.340	8.6	.865	22.0	.660	16.8	.86	21.8	.740	18.8	.250	6.4	C
25	1.175	29.8	.340	8.6	.965	24.5	.730	18.5	.93	23.6	.840	21.3	.250	6.4	D
31	1.325	33.7	.340	8.6	1.115	28.3	.810	20.6	1.01	25.7	.990	25.1	.250	6.4	E
37	1.475	37.5	.340	8.6	1.265	32.1	.890	22.6	1.09	27.7	1.140	29.0	.250	6.4	F
51	1.425	36.2	.380	9.7	1.215	30.9	.900	22.9	1.10	27.9	1.090	27.7	.290	7.4	G
51-2	1.825	46.4	.340	8.6	1.615	41.0	1.030	26.2	1.23	31.2	1.490	37.8	.250	6.4	J
67	2.225	56.5	.340	8.6	2.015	51.2	1.030	26.2	1.23	31.2	1.890	48.0	.250	6.4	L
69	1.725	43.8	.380	9.7	1.515	38.5	1.050	26.7	1.25	31.8	1.390	35.3	.290	7.4	J
75	2.070	52.6	.380	9.7	1.705	43.3	1.050	26.7	1.25	31.8	1.490	37.8	.290	7.4	J
100	2.160	54.9	.430	10.9	1.800	45.7	1.100	27.9	1.30	33.0	1.522	38.7	.340	8.6	K
130	2.510	63.8	.430	10.9	2.150	54.6	1.100	27.9	1.30	33.0	1.882	47.8	.340	8.6	L


Micro-D



507-145

EMI Banding Backshell, Split, Round Entry


- Split
- Round Entry
- Micro Band Shield Termination



507-145

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors

EMI, split, banding. 507-145 two piece backshell fits MIL-DTL-83513 Class M and Glenair MWDM Micro-D connectors with metal shell. Micro-D connector is captivated between backshell halves. Terminate cable shield to backshell with Micro band strap. Slide individual wire shields through optional slots on banding platform, or use slots for wire strain relief tie. Four screwlock styles are available: fillister head (standard), socket head, extended length (knurled, slotted), or fixed female hex jackposts. Aluminum with passivated stainless steel screws and washers.



BAND OPTIONS

Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

PART NUMBER

Sample PN→

507-145

M

21

H

K

S

Base P/N 507-145

Finish

TZ	Tin-Zinc
JF	Cadmium w/ Yellow Chromate
M	Electroless Nickel
MT	Nickel-PTFE
ZR	Black Zinc-Nickel
Z2	Gold

Shell Size

09 15 21 25 31 37 51 51-2 67 69 100

Screwlocks
(Table 1)

Omit	Fillister Head Male Screwlocks
E	Extended Knurled Slotted Screwlocks
F	Female Jackposts (fixed)
H	Socket Head Male Screwlocks

Band


Omit	No Band
K	Micro Band Included
J	Micro Slim Band Included
L	Micro-Max Band Included

Slots

Omit	No Slots
S	Slots included

	A		B		C		D		E		ø F		G	H		J			
Size	in	Max	mm	± .005 (0.1)	in	Max	mm	in	Max	mm	in	Max	mm	± .010 (0.3)	Thd	UNC-2	in	Max	mm
09	.915	23.2	.565	14.4	.450	11.4	.721	18.3	1.033	26.2	.160	4.1	2-56	.109	2.8	.554	14.1		
15	1.065	27.1	.715	18.2	.450	11.4	.783	19.9	1.096	27.8	.190	4.8	2-56	.125	3.2	.617	15.7		
21	1.215	30.9	.865	22.0	.450	11.4	.815	20.7	1.127	28.6	.220	5.6	2-56	.125	3.2	.649	16.5		
25	1.315	33.4	.965	24.5	.450	11.4	.877	22.3	1.190	30.2	.260	6.6	2-56	.156	4.0	.711	18.1		
31	1.465	37.2	1.115	28.3	.450	11.4	.908	23.1	1.221	31.0	.275	7.0	2-56	.156	4.0	.722	18.3		
37	1.615	41.0	1.265	32.1	.450	11.4	.971	24.7	1.283	32.6	.285	7.2	2-56	.156	4.0	.785	19.9		
51	1.565	39.8	1.215	30.9	.495	12.6	1.033	26.2	1.346	34.2	.350	8.9	2-56	.188	4.8	.867	22.0		
51-2	1.965	49.9	1.615	41.0	.450	11.4	1.033	26.2	1.346	34.2	.285	7.2	2-56	.188	4.8	.867	22.0		
67	2.365	60.1	2.015	51.2	.450	11.4	1.033	26.2	1.346	34.2	.350	8.9	2-56	.188	4.8	.867	22.0		
69	1.865	47.4	1.515	38.5	.495	12.6	1.033	26.2	1.346	34.2	.350	8.9	2-56	.188	4.8	.867	22.0		
100	2.305	58.5	1.800	45.7	.540	13.7	1.096	27.8	1.408	35.8	.490	12.4	4-40	.219	5.6	.930	23.6		

TABLE 1 SCREWLOCK OPTIONS



Micro-D



507-178

EMI Banding Backshell, Split, Elliptical Entry

- Split Elliptical
- Micro Band Shield Termination
- Top Entry




507-178

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors

EMI, split, banding, elliptical. 507-178 two piece backshell fits MIL-DTL-83513 Class M and Glenair MWDM Micro-D connectors with metal shell. Terminate cable shield to backshell with Micro band strap. Available with screwlocks or jackscrews: screwlocks allow connectors to be fully mated prior to fastening screws, jackscrews must be tightened in order to mate connectors. Aluminum with passivated stainless steel screws and washers.

TABLE 1

SCREWLOCK AND JACKSCREW OPTIONS



PART NUMBER

Sample PN→

507-178

M

21

05

K

HJ

T

Base P/N 507-178

Material / Finish	TZ	Tin-Zinc
	JF	Alum / Cadmium w/ Yel. Chromate
	M	Alum / Electroless Nickel
	MT	Alum / Nickel-PTFE
	ZR	Alum / Black Zinc-Nickel
	Z1	SST / Passivated
	Z2	Alum / Gold

Shell Size **09 15 21 25 31 37 51 51-2**
67 69 75 100 130

Entry Size	H	Shell Size
04	.250 (6.4)	09, 15, 21
05	.312 (7.9)	15, 21, 25, 31
06	.375 (9.5)	21, 25, 31, 37, 51
07	.437 (11.1)	25, 31, 37, 51
08	.500 (12.7)	25, 31, 37, 51
09	.562 (14.3)	31 to 130
10	.625 (15.9)	31 to 130
11	.688 (17.5)	37 to 130
12	.750 (19.1)	37 to 130
13	.812 (20.6)	37, 51-2 to 130
14	.875 (22.2)	51-2 to 130
15	.938 (23.8)	51-2 to 130
16	1.000 (25.4)	51-2 to 130

ENTRY SIZE




Band **Omit** No Band
K Micro Band Included
J Micro Slim Band Included
L Micro-Max Band Included

Screwlocks and Jackscrews (Table 1)	Omit	Male Screwlocks	Screwlocks float and allow the connectors to be mated before the screws are fastened.
	H	Slotted Male	
	E	Socket Head Male	
	E	Extended Slotted	Jackscrews must be fastened to mate connectors.
	J	Jackscrews	
	HJ	Slotted Male	
	EJ	Socket Head Male	Fixed Hex
	FF	Extended Slotted	
Qwik-Ty	Omit	Female Post	Fixed Hex
	T	Female Jackposts	

Qwik-Ty

Omit No Qwik-Ty
T Qwik-Ty Strain Relief Arm





507-178


EMI Banding Backshell, Split, Elliptical Entry

- Split Elliptical
- Micro Band Shield Termination
- Top Entry

SIZE 09

QWIK-TY
(OPTIONAL)

SIZES 15 THRU 130



Size	A Max		B ± .005 (0.1)		C Max		D ± .010 (0.3)		E ± .020 (0.5)		F		G Thd
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	UNC-2
15	1.065	27.1	.715	18.2	.450	11.4	.763	19.4	1.076	27.3	.190	4.8	2-56
21	1.215	30.9	.865	22.0	.450	11.4	.795	20.2	1.107	28.1	.220	5.6	2-56
25	1.315	33.4	.965	24.5	.450	11.4	.857	21.8	1.170	29.7	.260	6.6	2-56
31	1.465	37.2	1.115	28.3	.450	11.4	.888	22.6	1.201	30.5	.275	7.0	2-56
37	1.615	41.0	1.265	32.1	.450	11.4	.951	24.2	1.263	32.1	.285	7.2	2-56
51	1.565	39.8	1.215	30.9	.495	12.6	1.013	25.7	1.326	33.7	.350	8.9	2-56
51-2	1.965	49.9	1.615	41.0	.450	11.4	1.013	25.7	1.326	33.7	.350	8.9	2-56
67	2.365	60.1	2.015	51.2	.450	11.4	1.013	25.7	1.326	33.7	.350	8.9	2-56
69	1.865	47.4	1.515	38.5	.495	12.6	1.013	25.7	1.326	33.7	.350	8.9	2-56
75	2.210	56.13	1.705	43.3	.495	12.6	1.013	25.7	1.326	33.7	.350	8.9	4-40
100	2.305	58.5	1.800	45.7	.540	13.7	1.076	27.3	1.388	35.3	.490	12.4	4-40
130	2.665	67.7	2.160	54.6	.540	13.7	1.076	27.3	1.388	35.3	.490	12.4	4-40

Entry Size	H		Shell Size
	in	mm	
04	.250	6.4	09, 15, 21
05	.312	7.9	15, 21, 25, 31
06	.375	9.5	21, 25, 31, 37, 51
07	.437	11.1	25, 31, 37, 51
08	.500	12.7	25, 31, 37, 51
09	.562	14.3	31 to 130
10	.625	15.9	31 to 130
11	.688	17.5	37 to 130
12	.750	19.1	37 to 130
13	.812	20.6	37, 51-2 to 130
14	.875	22.2	51-2 to 130
15	.938	23.8	51-2 to 130
16	1.000	25.4	51-2 to 130

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.



Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

Micro-D

500-012

Qwik-Ty® Strain Relief Backshell


- Qwik-Ty Strain Relief
- For Unshielded Wire Bundles
- Top, Side and 45° Entry



T Top Entry



S Side Entry



E 45° Entry

500-012


This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors

Qwik-Ty. 500-012 backshell fits MIL-DTL-83513 Class M and Glenair MWDM Micro-D connectors. For unshielded wire bundles. Attach cable tie (not supplied) to Qwik-Ty strain relief arm. Aluminum or stainless steel with passivated stainless steel screws and retainer clips.

TABLE 1
JACKSCREW OPTIONS


B

Fillister Head




H

Socket Head




E

Extended Slotted



F

Female Post



PART NUMBER

Sample PN →

500T012

M

51

H

Base P/N **500T012** **T** Top Entry
500S012 **S** Side Entry
500E012 **E** 45° Entry

Material / Finish **TZ** Tin-Zinc
JF Alum / Cadmium w/ Yellow Chromate
M Alum / Electroless Nickel
MT Alum / Nickel-PTFE
ZR Alum / Black Zinc-Nickel
Z1 SST / Passivated
Z2 Alum / Gold

Shell Size **09 15 21 25 31 37 51 51-2 69 100**





Jack screws (Table 1) **B** Fillister Head Male
E Extended Male
F Female Jackpost
H Socket Head Male

Micro-D

500-012

Qwik-Ty® Strain Relief Backshell

- Qwik-Ty Strain Relief
- For Unshielded Wire Bundles
- Top, Side and 45° Entry



MICRO-D ACCESSORIES

	A		B		C		D		E		F		G		H		J		K		L		M		N			
Size	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	Ref	Thd	UNC-2	± .03 (0.8)	in	mm	in	mm	± .005 (0.1)	in	mm	in	mm
09	.775	19.7	.36	9.1	.565	14.4	.32	8.1	.435	11.0	.607	15.4	.650	16.5	.154	3.9	2-56		.70	17.8	.90	22.9	.156	4.0	1.04	26.4		
15	.925	23.5	.36	9.1	.715	18.2	.44	11.2	.440	11.2	.643	16.3	.700	17.8	.154	3.9	2-56		.82	20.8	.96	24.4	.188	4.8	1.17	29.7		
21	1.075	27.3	.36	9.1	.865	22.0	.56	14.2	.458	11.6	.677	17.2	.735	18.7	.154	3.9	2-56		.94	23.9	.99	25.1	.219	5.6	1.29	32.8		
25	1.175	29.8	.36	9.1	.965	24.5	.62	15.7	.483	12.3	.718	18.2	.800	20.3	.154	3.9	2-56		1.00	25.4	1.05	26.7	.250	6.4	1.35	34.3		
31	1.325	33.7	.36	9.1	1.115	28.3	.68	17.3	.476	12.1	.726	18.4	.860	21.8	.154	3.9	2-56		1.06	26.9	1.08	27.4	.265	6.7	1.42	36.1		
37	1.475	37.5	.36	9.1	1.265	32.1	.72	18.3	.478	12.1	.744	18.9	.925	23.5	.154	3.9	2-56		1.10	27.9	1.12	28.4	.281	7.1	1.45	36.8		
51	1.425	36.2	.40	10.2	1.215	30.9	.75	19.1	.548	13.9	.829	21.1	.975	24.8	.154	3.9	2-56		1.13	28.7	1.21	30.7	.312	7.9	1.48	37.6		
51-2	1.835	46.6	.36	9.1	1.615	41.0	.75	19.1	.548	13.9	.829	21.1	.975	24.8	.154	3.9	2-56		1.13	28.7	1.21	30.7	.312	7.9	1.48	37.6		
69	1.730	43.9	.40	10.2	1.515	38.5	.81	20.6	.548	13.9	.829	21.1	.975	24.8	.154	3.9	2-56		1.19	30.2	1.21	30.7	.344	8.7	1.48	37.6		
100	2.160	54.9	.45	11.4	1.800	45.7	.81	20.6	.687	17.4	.984	25.0	1.050	26.7	.184	4.7	4-40		1.19	30.2	1.28	32.5	.375	9.5	1.58	40.1		


Micro-D



507-146

Straight Clamp Backshell




- Solid Backshell
- Saddle Bar Strain Relief
- For Unshielded Cable



507-146

This accessory fits MWD and M83513 Class M metal shell Micro-D connectors

Straight clamp. 507-146 strain relief backshell fits metal shell Micro-D connectors. Use with unshielded wire bundles. Flat saddle bars with provide strain relief. Aluminum with stainless steel screws, washers, e-rings and clips.



PART NUMBER

		507-146		M		15		H	
Base P/N		507-146							
Finish	TZ	Tin-Zinc							
	JF	Cadmium w/ Yellow Chromate							
	M	Electroless Nickel							
	MT	Nickel-PTFE							
	ZR	Black Zinc-Nickel							
	Z2	Gold							
Shell Size	09	15	21	25	31	37	51	51-2	
	67	69	75	100					
Hardware (Table 1)	Jackscrews								
	Omit	Fillister Head Male				Jackscrews must be fastened to mate connectors. Jackscrews and connector are retained with e-rings. <i>Size 75 and 100 backshells have C clips instead of e-rings.</i>			
	H	Socket Head Male							
	E	Extended Slotted							
	Screwlocks								
	C	Fillister Head Male				Screwlocks float and allow the connectors to be mated before the screws are fastened. Screwlocks and connector are retained with C clips.			
	HC	Socket Head Male							
	EC	Extended Slotted							
	Female Post								
	F	Female Jackpost				Fixed, non-rotating			

Jackscrews must be fastened to mate connectors. Jackscrews and connector are retained with e-rings. Size 75 and 100 backshells have C clips instead of e-rings.

Screwlocks float and allow the connectors to be mated before the screws are fastened. Screwlocks and connector are retained with C clips.

Fixed, non-rotating

TABLE 1 HARDWARE OPTIONS


		No Designator		H		E		F		C		HC		EC	
		Fillister Head Jackscrews		Socket Head Jackscrews		Extended Jackscrews		Female Jackposts		Fillister Head Screwlocks		Socket Head Screwlocks		Extended Screwlocks	
Size		A	B	C	D	E	F	J	H	A	B	C	D	E	F
		Max.	± .005 (0.1)	Max	± .010 (0.3)	± .030 (0.8)	± .005 (0.1)	THD	± .005 (0.1)						
		in	mm	in	mm	in	mm	UNC-2	in	mm	in	mm	in	mm	in
09		.915	23.2	.565	14.4	.450	11.4	.530	13.5	.750	19.1	.160	4.1	2-56	.160
15		1.065	27.1	.715	18.2	.450	11.4	.580	14.7	.800	20.3	.190	4.8	2-56	.190
21		1.215	30.9	.865	22.0	.450	11.4	.630	16.0	.910	23.1	.220	5.6	2-56	.220
25		1.315	33.4	.965	24.5	.450	11.4	.680	17.3	.960	24.4	.260	6.6	2-56	.260
31		1.465	37.2	1.115	28.3	.450	11.4	.720	18.3	1.000	25.4	.275	7.0	2-56	.275
37		1.615	41.0	1.265	32.1	.450	11.4	.760	19.3	1.040	26.4	.285	7.2	2-56	.285
51		1.565	39.8	1.215	30.9	.495	12.6	.840	21.3	1.120	28.4	.350	8.9	2-56	.350
51-2		1.965	49.9	1.615	41.0	.450	11.4	.840	21.3	1.120	28.4	.500	12.7	2-56	.285
67		2.365	60.1	2.015	51.2	.450	11.4	.840	21.3	1.120	28.4	.500	12.7	2-56	.285
69		2.265	57.5	1.515	38.5	.495	12.6	.840	21.3	1.120	28.4	.500	12.7	2-56	.320
75		2.110	53.6	1.705	43.3	.495	12.6	.840	21.3	1.120	28.4	.530	13.5	4-40	.320
100		2.305	58.5	1.800	45.7	.540	13.7	.910	23.1	1.190	30.2	.530	13.5	4-40	.400

Micro-D

507-198

Deep Straight Clamp Backshell


- Solid Backshell
- Saddle Bar Strain Relief
- For Unshielded Cable



507-198

This accessory fits MWDM and M83513 Class M metal shell Micro-D connectors

Straight clamp. 507-198 strain relief backshell fits metal shell Micro-D connectors. Use with unshielded wire bundles. Flat saddle bars have silicone pads. Connector is retained with clips. Available with screwlocks, jackscrews or female jackposts. Aluminum with stainless steel screws and clips.



PART NUMBER

Sample PN→

507-198

MT

37

F

Base P/N 507-198

Finish

TZ Tin-Zinc
JF Cadmium w/ Yellow Chromate
M Electroless Nickel
MT Nickel-PTFE
ZR Black Zinc-Nickel
Z2 Gold

Shell Size

09 15 21 25 31 37 51 51-2
67 69 75 100 130


Hardware
(Table 1)

Omit Socket Head Male Screwlock
HJ Socket Head Male Jackscrew
F Female Hex Post


Jackscrews must be fastened to mate connectors. Screwlocks float and allow the connectors to be mated before the screws are fastened.

Size	A Max		B Max		C		DThd	E Max		F		G	
	in	mm	in	mm	in	mm	UNC-2	in	mm	in	mm	in	mm
09	.850	21.6	.840	21.3	.565	14.4	2-56	.420	10.7	.310	7.9	.310	7.9
15	1.000	25.4	.910	23.1	.715	18.2	2-56	.420	10.7	.310	7.9	.380	9.7
21	1.150	29.2	.970	24.6	.865	22.0	2-56	.420	10.7	.310	7.9	.440	11.2
25	1.250	31.8	1.030	26.2	.965	24.5	2-56	.420	10.7	.310	7.9	.500	12.7
31	1.400	35.6	1.080	27.4	1.115	28.3	2-56	.420	10.7	.310	7.9	.550	14.0
37	1.550	39.4	1.130	28.7	1.265	32.1	2-56	.420	10.7	.310	7.9	.600	15.2
51	1.500	38.1	1.080	27.4	1.215	30.9	2-56	.470	11.9	.360	9.1	.550	14.0
51-2	1.910	48.5	1.480	37.6	1.615	41.0	2-56	.420	10.7	.310	7.9	.950	24.1
67	2.310	58.7	1.880	47.8	2.015	51.2	2-56	.420	10.7	.310	7.9	1.350	34.3
69	1.810	46.0	1.380	35.1	1.515	38.5	2-56	.470	11.9	.360	9.1	.850	21.6
75	2.150	54.4	1.720	43.7	1.705	43.3	4-40	.470	11.9	.360	9.1	1.190	30.2
100	2.235	56.8	1.650	41.9	1.800	45.7	4-40	.510	13.0	.400	10.2	1.000	25.4
130	2.585	65.7	2.155	54.7	2.150	54.6	4-40	.510	13.0	.400	10.2	1.350	34.3


TABLE 1
SCREWLOCK AND JACKSCREW OPTIONS




No Designator
Socket Head Screwlocks




HJ
Socket Head Jackscrews




F
Female Hex Post



CLIP
CLIP HAS CIRCULAR HOLE AND SQUARE HOLE.



SCREWLOCK
SQUARE HOLE IS ON THE TOP. SCREW IS FLOATING. MATE CONNECTORS FIRST, THEN FASTEN SCREWLOCKS.




JACKSCREW
SQUARE HOLE IS ON THE BOTTOM. SCREW IS CAPTIVE. TURN SCREWS TO JACK CONNECTORS TOGETHER.

Micro-D

507-299

EMI Banding Backshell, MLDM


- For MLDM Connectors
- Micro Band Shield Termination
- Top, End and Side Entry



T Top Entry



S 90° Entry




E 45° Entry

507-299


This accessory fits MLDM metal shell and MWDL plastic shell Micro-D connectors

Lightweight, elliptical entry. 507-299 EMI banding backshell fits MLDM low-profile metal shell Micro-D connectors. Terminate cable shield to backshell with BandMaster ATS .12" wide Micro band strap. Available with male or female screwlocks. Screwlocks allow connectors to be fully mated prior to fastening screws. Aluminum with passivated stainless steel screws and retainer clips.


TABLE 1 SCREWLOCK OPTIONS




No Designator
Fillister Head



H
Socket Head



F
Female Hex Post



E
Extended

PART NUMBER

Sample PN→

507T299 JF 37 05 H J

Base P/N	Base Part No.	Profile
	507T299	T Top Entry
	507S299	S 90° Entry
	507E299	E 45° Entry

Finish	TZ	Tin-Zinc
	JF	Cadmium w/ Yellow Chromate
	M	Electroless Nickel
	MT	Nickel-PTFE
	ZR	Black Zinc-Nickel
	Z2	Gold

Shell Size 9 15 21 25 31 37 51 51-2

Entry Size	Entry Size	L	Shell Size
	01	.344 (8.7)	9 thru 51-2
	02	.494 (12.5)	15 thru 51-2
	03	.644 (16.4)	21 thru 51-2
	04	.744 (18.9)	25 thru 51-2
	05	.894 (22.7)	31 thru 51-2
	06	.994 (25.2)	37 thru 51-2
	07	1.044 (26.5)	37 and 51-2



ENTRY SIZE

Jackscrews (Table 1)	Omit	Fillister Head Male Screwlocks
	E	Extended Male Screwlocks
	F	Female Screwlocks
	H	Socket Head Male Screwlocks

Band	Omit	No Band
	M	Micro Band Included
	J	Micro Slim Band Included
	L	Micro-Max Band Included




Micro-D



507-299

EMI Banding Backshell, MLDM

- For MLDM Connectors
- Micro Band Shield Termination
- Top, End and Side Entry

T Top Entry**S** 90° Entry**E** 45° Entry

Shell Size	A		B		C		D		E		F		G		H		Max Entry
	in	Max mm	±.005 (0.13) in	mm	±.005 (0.13) in	mm	±.020 (0.5) in	mm	in	Max mm	in	Max mm	in	Max mm	in	Max mm	
9	.785	19.9	.565	14.4	.265	6.7	.762	19.4	.851	21.6	.673	17.1	.970	24.6	.668	17.0	01
15	.935	23.7	.715	18.2	.265	6.7	.812	20.6	.876	22.3	.673	17.1	.970	24.6	.668	17.0	02
21	1.085	27.6	.865	22.0	.265	6.7	.862	21.9	.901	22.9	.673	17.1	.970	24.6	.668	17.0	03
25	1.185	30.1	.965	24.5	.265	6.7	.912	23.2	.943	24.0	.700	17.8	.990	25.1	.678	17.2	04
31	1.335	33.9	1.115	28.3	.265	6.7	.952	24.2	.963	24.5	.700	17.8	.990	25.1	.678	17.2	05
37	1.485	37.7	1.265	32.1	.265	6.7	.952	24.2	.983	25.0	.700	17.8	.990	25.1	.678	17.2	07
51	1.435	36.4	1.215	30.9	.305	7.7	1.072	27.2	1.050	26.7	.758	19.3	1.030	26.2	.698	17.7	06
51-2	1.845	46.9	1.615	41.0	.265	6.7	1.072	27.2	1.050	26.7	.758	19.3	1.030	26.2	.698	17.7	07

Entry Size	L		Available Shell Sizes
	±.010 (0.3) in	mm	
01	.344	8.7	9 thru 51-2
02	.494	12.5	15 thru 51-2
03	.644	16.4	21 thru 51-2
04	.744	18.9	25 thru 51-2
05	.894	22.7	31 thru 51-2
06	.994	25.2	37 thru 51-2
07	1.044	26.5	37 and 51-2

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.



Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

ULTRA-LOW-
PROFILE
CRIMP-CONTACT
RECTANGULAR
SERIES




Series 79 micro miniature crimp-contact rectangular with advanced environmental and EMC performance



Series 79 is an advanced-performance, micro miniature crimp-contact rectangular connector for mission-critical mil-aero applications. The Series 79 is a high-density rectangular equivalent of the Glenair circular Mighty Mouse connector series. It is available with size #23 39029 crimp contacts set on .075" centers, as well as dozens of hybrid contact layouts supporting contact sizes up to #8. Special product line extensions include Series 791 (scoop-proof) and Series 792 (high-speed with common ground plane). Environmentally sealed and shrouded for EMC, the Series 79 meets the need for a higher-performing, precision-machined micro-sized rectangular with industry-standard crimp-and-poke contacts.

Glenair Signature
Series 79 Micro-Crimp Backshells



This precision-machined 799-164 non-environmental piggyback backshell fits Series 792 connectors. Backshell has internal fluorosilicone wire strain relief grommet optimized for axial alignment and support of twinax, quadax or octaxial Ethernet cables.

Series 79 Micro-Crimp® Accessories Selection Guide


Dust Caps & Covers



Anti-Static Dust Cap
Series 790
799-013
Page C-3



Anti-Static Dust Cap
Series 791
799-064, -065
Page C-4



Protective Cover
Series 790
799-018, -019
Page C-5




Protective Cover
Series 791
799-038, -039
Page C-7

Shorting Cap




Piggyback Shorting Cap
Series 790 & 791
799-067
Page C-9

Jackposts and Jackscrews



Jackpost
Rear Panel Mount
799-117, 799-176
Page C-10



Jackscrew
with Clip
799-172
Page C-12

Series 790 EMI Backshell




Elliptical Entry
Series 790
799-011
Page C-13

Series 790, 791, 792 Piggyback EMI Backshells



Piggyback EMI
Split Elliptical Entry
Series 790 & 791
799-015
Page C-15



Piggyback EMI
Panel Mount
Series 790 & 791
799-016
Page C-16



Piggyback EMI
Dual Port
Series 790 & 791
799-131
Page C-18




Piggyback EMI
Size #8 Contacts
Series 792
799-164
Page C-19

Series 79 Micro-Crimp®

Band-Master ATS®
Shield Termination Bands and Tools

Band-Master ATS®

Terminate cable braid shield to adapter with stainless steel **Band-Master ATS®** bands. Install band with hand tool or bench-mounted pneumatic tool. Bands are available in *Standard* (.24 inch) and *Micro* (.12 inch) widths. *Slim Standard* and *Micro Slim* bands have reduced thickness for weight reduction. Hardened steel *Micro-Max* bands have 60% more tensile strength than standard Micro bands. Available pre-coiled, bands are 304 series stainless steel, passivated.



For more information on the Band-Master ATS EMI shield termination system, including instruction manuals and calibration details:

<https://www.glenair.com/bandmaster/>

Band and Band Tool Part Numbers

Size		A Length in mm	Fits up to Dia. in mm	B Width in mm	C Thickness in mm	Part Number Pre-coiled	Hand Tool Part Number
Standard		9 228	1.00 25.4	.24 6.1	.02 0.5	601-006	601-100
		14 355	1.80 45.7	.24 6.1	.02 0.5	601-041	
		18 457	2.50 63.5	.24 6.1	.02 0.5	601-050	
Slim Standard		9 228	.94 23.9	.24 6.1	.01 0.3	601-571	601-109
		14 355	1.80 45.7	.24 6.1	.01 0.3	601-573	
Micro		5 127	.50 12.7	.12 3.0	.015 0.4	601-025	601-101
		8 203	.88 22.4	.12 3.0	.015 0.4	601-061	
		14 356	1.88 47.7	.12 3.0	.015 0.4	601-065	
Micro Slim		8 203	.88 22.4	.12 3.0	.01 0.3	601-601	601-122
		14 356	1.88 47.7	.12 3.0	.01 0.3	601-603	
Micro-Max		8 203	.88 22.4	.12 3.0	.015 0.4	601-701	601-129
		14 356	1.88 47.7	.12 3.0	.015 0.4	601-703	

Series 79 Micro-Crimp®



799-013

Dust Cap, Anti-Static, Series 790



799-013


This accessory fits Series 790 connectors.

Permanently anti-static. Non-sloughing.
Molded dust caps protect Series 790 connectors from contamination and static discharge.


- Black LDPE Material
- Static Decay per MIL-PRF-81705
- Surface Resistivity: 1E10 to 9.9E11 Ohm/SQ
- Static Decay: <2 sec @ 5kV to 50V, 12% RH

PART NUMBER						
Shell Size	Type	Part No.	A Max		C Max	
			in	mm	in	mm
A	Plug	799-013AP	.540	13.7	.436	11.1
	Recep	799-013AR	.587	14.9	.477	12.1
B	Plug	799-013BP	.690	17.5	.436	11.1
	Recep	799-013BR	.737	18.7	.477	12.1
C	Plug	799-013CP	.840	21.3	.436	11.1
	Recep	799-013CR	.887	22.5	.477	12.1
D	Plug	799-013DP	.940	23.9	.436	11.1
	Recep	799-013DR	.987	25.1	.477	12.1
E	Plug	799-013EP	1.090	27.7	.436	11.1
	Recep	799-013ER	1.137	28.9	.477	12.1
F	Plug	799-013FP	1.239	31.5	.436	11.1
	Recep	799-013FR	1.287	32.7	.477	12.1
G	Plug	799-013GP	1.213	30.8	.529	13.4
	Recep	799-013GR	1.260	32.0	.560	14.2
H	Plug	799-013HP	1.586	40.3	.552	14.0
	Recep	799-013HR	1.631	41.4	.587	14.9
J	Plug	799-013JP	1.595	40.5	.436	11.1
	Recep	799-013JR	1.642	41.7	.477	12.1
K	Plug	799-013KP	1.998	50.7	.436	11.1
	Recep	799-013KR	2.045	51.9	.477	12.1
L	Plug	799-013LP	1.823	46.3	.552	14.0
	Recep	799-013LR	1.867	47.4	.587	14.9
M	Plug	799-013MP	1.878	47.7	.612	15.5
	Recep	799-013MR	1.931	49.0	.647	16.4
N	Plug	799-013NP	2.265	57.5	.685	17.4
	Recep	799-013NR	2.335	59.3	.765	19.4

SHELL SIZE A-G, J, K



SHELL SIZE H, L, M, N



799-064, 799-065

Dust Cap, Anti-Static, Series 791



799-064, 799-065

This accessory fits Series 791 Scoop-Proof connectors.

Permanently anti-static. Non-sloughing.
Molded dust caps protect Series 790 connectors from contamination and static discharge.


- Black LDPE Material
- Static Decay per MIL-PRF-81705
- Surface Resistivity: 1E5 to 9.9E11 Ohm/SQ
- Static Decay: <2 sec @ 5kV to 50V, 12% RH

PART NUMBER

Shell Size	Type	Part No.	A Max in	A Max mm	C Max in	C Max mm
A	Plug	799-064A	.628	16.0	.524	13.3
	Recep	799-065A	.698	17.7	.594	15.1
B	Plug	799-064B	.778	19.8	.524	13.3
	Recep	799-065B	.848	21.5	.594	15.1
C	Plug	799-064C	.928	23.6	.524	13.3
	Recep	799-065C	.998	25.3	.594	15.1
D	Plug	799-064D	1.003	25.5	.524	13.3
	Recep	799-065D	1.073	27.3	.594	15.1
E	Plug	799-064E	1.153	29.3	.524	13.3
	Recep	799-065E	1.223	31.1	.594	15.1
F	Plug	799-064F	1.303	33.1	.524	13.3
	Recep	799-065F	1.373	34.9	.594	15.1
G	Plug	799-064G	1.265	32.1	.612	15.5
	Recep	799-065G	1.335	33.9	.682	17.3
H	Plug	799-064H	1.655	42.0	.630	16.0
	Recep	799-065H	1.725	43.8	.700	17.8
J	Plug	799-064J	1.678	42.6	.524	13.3
	Recep	799-065J	1.748	44.4	.594	15.1
K	Plug	799-064K	2.053	52.1	.524	13.3
	Recep	799-065K	2.123	53.9	.594	15.1
L	Plug	799-064L	1.891	48.0	.630	16.0
	Recep	799-065L	1.961	49.8	.700	17.8
M	Plug	799-064M	1.952	49.6	.714	18.1
	Recep	799-065M	2.022	51.4	.784	19.9


799-064

Anti-Static Dust Cap for Series 791 Plug Connector



799-065

Anti-Static Dust Cap for Series 791 Receptacle Connector



Series 79 Micro-Crimp®



799-018 and 799-019

Protective Cover, Series 790

- Fits Series 790 Connectors
- Environmental
- Conductive EMI Gasket



799-018, 799-019

This accessory fits Series 790 Micro-Crimp plug and receptacle connectors

Protective cover has conductive gasket for dust, moisture and EMI protection. Available with lanyard for panel or cable attachment. Aluminum with stainless steel screws and washers. Gasket is Cho-Seal 1287 Ag/Al-filled fluorosilicone.

TABLE 1
ATTACHMENT TYPE

F Wire Rope, Blue Nylon Jacket
6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C

G Black Nylon Rope
Very flexible, good abrasion and fuel resistance, .062 (1.6) diameter, -55 to +100 °C

H Wire Rope, Clear FEP Jacket
Clear FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C

SK Nylon Rope with Slip Knot
Very flexible, good abrasion and fuel resistance, .094 (2.4) diameter. Length includes .5" (13mm) dia. loop, -55 to +100 °C

T SST Wire Rope, No Jacket
Good flexibility, good abrasion resistance, .047 (1.2) diameter, passivated, -65 to +200 °C

PART NUMBER


Sample PN → **799-018** **M** **F** **MB** **F** **6** **-06**

Base P/N **799-018** Plug Cover
799-019 Receptacle Cover

Finish **TZ** Tin-Zinc
M Electroless Nickel
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size **A B C D E F G H J K L M**

Screwlocks



- Jackscrews Omitted

Attachment Type (Table 1)

N No Attachment
F SST Wire Rope, Nylon Jacket
G Nylon Rope
H SST Wire Rope, FEP Jacket
SK Nylon Rope with Slip Knot
T SST Wire Rope, No Jacket

Attachment Length *Omit If No Attachment*
Length in One Inch Increments

Attachment Ring



Omit If No Attachment
Omit for Attachment Type SK

EYELET		RING		SPLIT RING	
Code	Eyelet I.D.	Code	Ring I.D.	Code	Ring I.D.
-01	.125 (3.2)	-14	.385 (9.8)	-50	.425 (10.8)
-02	.140 (3.6)	-15	.445 (11.3)	-52	.485 (12.3)
-04	.182 (4.6)	-16	.570 (14.5)	-54	.640 (16.3)
-06	.197 (5.0)	-17	.635 (16.1)	-56	.750 (19.1)
		-18	.695 (17.7)	-58	.890 (22.6)
		-19	.885 (22.5)	-60	1.010 (25.7)
		-20	1.070 (27.2)	-64	1.125 (28.6)
				-68	1.345 (34.2)

Series 79 Micro-Crimp®

799-018 and 799-019
Protective Cover, Series 790

- Fits Series 790 Connectors
- Environmental
- Conductive EMI Gasket



Shell Size	A Max		B Max		C		D Thread	E	
	in	mm	in	mm	in	mm		in	mm
A	.308	7.8	.785	19.9	.565	14.4	2-56 UNC	.385	9.8
B	.308	7.8	.935	23.7	.715	18.2	2-56 UNC	.385	9.8
C	.308	7.8	1.085	27.6	.865	22.0	2-56 UNC	.385	9.8
D	.308	7.8	1.185	30.1	.965	24.5	2-56 UNC	.385	9.8
E	.308	7.8	1.335	33.9	1.115	28.3	2-56 UNC	.385	9.8
F	.308	7.8	1.485	37.7	1.265	32.1	2-56 UNC	.385	9.8
G	.395	10.0	1.435	36.4	1.215	30.9	2-56 UNC	.470	11.9
H	.410	10.4	2.170	55.1	1.800	45.7	4-40 UNC	.490	12.4
J	.308	7.8	1.845	46.9	1.615	41.0	2-56 UNC	.385	9.8
K	.308	7.8	2.240	56.9	2.015	51.2	2-56 UNC	.385	9.8
L	.410	10.4	2.406	61.1	2.036	51.7	4-40 UNC	.490	12.4
M	.470	11.9	2.570	65.3	2.200	55.9	6-32 UNC	.550	14.0


Series 79 Micro-Crimp®



799-038 and 799-039

Protective Cover, Series 791

- Fits Series 791 Connectors
- Environmental
- Conductive EMI Gasket



799-038, 799-039

This accessory fits Series 791 Scoop-Proof Micro-Crimp plug and receptacle connectors

Protective cover has conductive gasket for dust, moisture and EMI protection. Plug cover has internal copper alloy ground spring. Available with lanyard for panel or cable attachment. Aluminum with stainless steel screws and washers. Gasket is Cho-Seal 6503 Ni/Al-filled fluorosilicone.

TABLE 1
ATTACHMENT TYPE

F

Wire Rope, Blue Nylon Jacket
6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C

G

Black Nylon Rope
Very flexible, good abrasion and fuel resistance, .062 (1.6) diameter, -55 to +100 °C

H

Wire Rope, Clear FEP Jacket
Clear FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C

SK

Nylon Rope with Slip Knot
Very flexible, good abrasion and fuel resistance, .094 (2.4) diameter. Length includes .5" (13mm) dia. loop, -55 to +100 °C

T

SST Wire Rope, No Jacket
Good flexibility, good abrasion resistance, .047 (1.2) diameter, passivated, -65 to +200 °C

PART NUMBER

Sample PN → **799-038 M K L F 6 -01**


Base P/N **799-038** Receptacle Cover
799-039 Plug Cover

Finish
TZ Tin-Zinc
M Electroless Nickel
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size **A B C D E F G H J K L M**

Hardware

L Socket Head Male Jackscrews
P Female Hex Jackposts



L Socket Head Male **P** Female Post

Attachment Type (Table 1)

N No Attachment
F SST Wire Rope, Nylon Jacket
G Nylon Rope
H SST Wire Rope, FEP Jacket
SK Nylon Rope with Slip Knot
T SST Wire Rope, No Jacket

Attachment Length *Omit If No Attachment*
Length in One Inch Increments

Omit If No Attachment
Omit for Attachment Type SK

Attachment Ring

EYELET		RING		SPLIT RING	
Code	Eyelet I.D.	Code	Ring I.D.	Code	Ring I.D.
-01	.125 (3.2)	-14	.385 (9.8)	-50	.425 (10.8)
-02	.140 (3.6)	-15	.445 (11.3)	-52	.485 (12.3)
-04	.182 (4.6)	-16	.570 (14.5)	-54	.640 (16.3)
-06	.197 (5.0)	-17	.635 (16.1)	-56	.750 (19.1)
		-18	.695 (17.7)	-58	.890 (22.6)
		-19	.885 (22.5)	-60	1.010 (25.7)
		-20	1.070 (27.2)	-64	1.125 (28.6)
				-68	1.345 (34.2)


Series 79 Micro-Crimp®

799-038 and 799-039
Protective Cover, Series 791

- Fits Series 791 Connectors
- Environmental
- Conductive EMI Gasket

799-038


Protective Cover for Series 791 Receptacle Connector



JACKPOST TYPE P

799-039

Protective Cover for Series 791 Plug Connector



JACKPOST TYPE P

Shell Size	A	B	C Max	D Max	E Thread
	in	mm	in	mm	
A	1.005	25.5	.750	19.1	.525 13.3 .500 12.7 4-40 UNC
B	1.155	29.3	.900	22.9	.675 17.1 .500 12.7 4-40 UNC
C	1.305	33.1	1.050	26.7	.825 21.0 .500 12.7 4-40 UNC
D	1.380	35.1	1.125	28.6	.900 22.9 .500 12.7 4-40 UNC
E	1.530	38.9	1.275	32.4	1.050 26.7 .500 12.7 4-40 UNC
F	1.680	42.7	1.425	36.2	1.200 30.5 .500 12.7 4-40 UNC
G	1.643	41.7	1.388	35.3	1.162 29.5 .595 15.1 4-40 UNC
H	2.295	58.3	1.900	48.3	1.556 39.5 .615 15.6 6-32 UNC
J	2.055	52.2	1.800	45.7	1.575 40.0 .500 12.7 4-40 UNC
K	2.430	61.7	2.175	55.2	1.950 49.5 .500 12.7 4-40 UNC
L	2.531	64.3	2.136	54.3	1.792 45.5 .615 15.6 6-32 UNC
M	2.600	66.0	2.200	55.9	1.855 47.1 .710 18.0 8-32 UNC

Shell Size	A	B	C Max	D Max	E Thread
	in	mm	in	mm	
A	.975	24.8	.750	19.1	.445 11.3 .415 10.5 4-40 UNC
B	1.125	28.6	.900	22.9	.595 15.1 .415 10.5 4-40 UNC
C	1.275	32.4	1.050	26.7	.745 18.9 .415 10.5 4-40 UNC
D	1.350	34.3	1.125	28.6	.820 20.8 .415 10.5 4-40 UNC
E	1.500	38.1	1.275	32.4	.970 24.6 .415 10.5 4-40 UNC
F	1.650	41.9	1.425	36.2	1.120 28.4 .415 10.5 4-40 UNC
G	1.608	40.8	1.388	35.3	1.082 27.5 .500 12.7 4-40 UNC
H	2.275	57.8	1.900	48.3	1.472 37.4 .520 13.2 6-32 UNC
J	2.025	51.4	1.800	45.7	1.495 38.0 .415 10.5 4-40 UNC
K	2.400	61.0	2.175	55.2	1.865 47.4 .415 10.5 4-40 UNC
L	2.511	63.8	2.136	54.3	1.708 43.4 .520 13.2 6-32 UNC
M	2.515	63.9	2.200	55.9	1.769 44.9 .610 15.5 8-32 UNC

Series 79 Micro-Crimp®



799-067

Shorting Cap, Piggyback, Series 79



799-067


This accessory fits Series 790 and 791 connectors:
790-024, 790-025, 791-001, 791-003

Lightweight, split. 799-067 piggyback shorting cap fits Series 790 and 791 connectors with rear groove on shell. Aluminum or stainless steel with stainless steel screws. Non-environmental.

PART NUMBER

Sample PN → **799-067** **M** **H**Base P/N **799-067**

Finish
TZ Tin-Zinc
M Electroless Nickel
MT Nickel-PTFE
ZR Black Zinc-Nickel

Shell Size **A B C D E F G H J K L M**


Shell Size	A Max		B Max		C Max		D Max	
	in	mm	in	mm	in	mm	in	mm
A	.390	9.9	.485	12.3	.915	23.2	.390	9.9
B	.390	9.9	.635	16.1	.915	23.2	.540	13.7
C	.390	9.9	.785	19.9	.915	23.2	.690	17.5
D	.390	9.9	.885	22.5	.915	23.2	.790	20.1
E	.390	9.9	1.035	26.3	.915	23.2	.940	23.9
F	.390	9.9	1.185	30.1	.915	23.2	1.090	27.7
G	.470	11.9	1.145	29.1	.915	23.2	1.055	26.8
H	.500	12.7	1.525	38.7	1.165	29.6	1.440	36.6
J	.390	9.9	1.545	39.2	.915	23.2	1.450	36.8
K	.390	9.9	1.945	49.4	.915	23.2	1.840	46.7
L	.500	12.7	1.765	44.8	1.165	29.6	1.675	42.5
M	.560	14.2	1.830	46.5	1.300	33.0	1.740	44.2

Series 79 Micro-Crimp®



799-117, 799-176

Jackpost, Female Hex, Rear Panel Mount




799-117, 799-176

These jackposts fit Series 790, 791 and 792 rear panel mounted connectors:

790-024, 790-025, 791-001, 791-003, 792-001, 792-002

Rear panel mount jackpost kit accommodates panel thicknesses from 1/32 to 1/8 inch. Four thread sizes: 2-56, 4-40, 6-32 and 8-32. Kit consists of (2) female posts, (2) hex nuts and (2) lockwashers. Passivated 300 series stainless steel.




2-56	.156 (4.0)
4-40	.188 (4.8)
6-32	.250 (6.4)
8-32	.250 (6.4)

REAR PANEL MOUNT JACKPOST KIT


with (2) posts, (2) nuts and (2) lockwashers

X Thread Size	Shell Size	Panel Thickness in mm	Part Number	A ±.003 (0.08) in mm	Ø B in mm	Ø C in mm
2-56	Series 790 A-G, J, K	.032 0.8	799-117-A1	.027 .7	.120 3.0	N/A N/A
		.050 1.3	799-117-A2	.045 1.1	.120 3.0	N/A N/A
		.062 1.6	799-117-A3	.057 1.4	.120 3.0	N/A N/A
		.080 2.0	799-117-A4	.075 1.9	.120 3.0	N/A N/A
		.093 2.4	799-117-A5	.088 2.2	.120 3.0	N/A N/A
		.125 3.2	799-117-A6	.120 3.0	.120 3.0	N/A N/A
4-40	Series 790 H, L	.032 0.8	799-117-B1	.027 .7	.155 3.9	.140 3.6
		.050 1.3	799-117-B2	.045 1.1	.155 3.9	.140 3.6
		.062 1.6	799-117-B3	.057 1.4	.155 3.9	.140 3.6
	Series 791 A-G, J, K	.080 2.0	799-117-B4	.075 1.9	.155 3.9	.140 3.6
		.093 2.4	799-117-B5	.088 2.2	.155 3.9	.140 3.6
		.125 3.2	799-117-B6	.120 3.0	.155 3.9	.140 3.6
6-32	Series 790 M	.032 0.8	799-117-C1	.027 .7	.210 5.3	.163 4.1
		.050 1.3	799-117-C2	.045 1.1	.210 5.3	.163 4.1
		.062 1.6	799-117-C3	.057 1.4	.210 5.3	.163 4.1
	Series 791 H, L	.080 2.0	799-117-C4	.075 1.9	.210 5.3	.163 4.1
		.093 2.4	799-117-C5	.088 2.2	.210 5.3	.163 4.1
		.125 3.2	799-117-C6	.120 3.0	.210 5.3	.163 4.1
8-32	Series 791 M	.032 0.8	799-176-R1	.027 .7	.210 5.3	.190 4.8
		.050 1.3	799-176-R2	.045 1.1	.210 5.3	.190 4.8
		.062 1.6	799-176-R3	.057 1.4	.210 5.3	.190 4.8
	Series 792 A-F	.080 2.0	799-176-R4	.075 1.9	.210 5.3	.190 4.8
		.093 2.4	799-176-R5	.088 2.2	.210 5.3	.190 4.8
		.125 3.2	799-176-R6	.120 3.0	.210 5.3	.190 4.8



SERIES 792 PANEL CUTOUT

(SEE NEXT PAGE FOR 790 & 791)



Shell Size	A ±.002 (0.05) in mm	B Basic in mm	C ±.002 (0.05) in mm
A	.725 18.42	1.075 27.31	.623 15.82
B	1.100 27.94	1.450 36.83	.623 15.82
C	1.475 37.47	1.825 46.36	.623 15.82
D	1.850 46.99	2.200 55.88	.623 15.82
E	2.225 56.52	2.575 65.41	.623 15.82
F	2.225 56.52	2.575 65.41	.998 25.35


Series 79 Micro-Crimp®

799-117, 799-176


Jackpost, Female Hex, Rear Panel Mount

SERIES 790 PANEL CUTOUT


PANEL CUTOUT FOR SERIES 790
SHELL SIZES A-G, J, K



PANEL CUTOUT FOR SERIES 790
SHELL SIZES H AND L




PANEL CUTOUT FOR SERIES 790
SHELL SIZE M




Shell Size	A		B		C	
	±.002 (0.05)	in mm	±.002 (0.05)	in mm	in	mm
A	.406	10.31	.306	7.77	.565	14.35
B	.556	14.12	.306	7.77	.715	18.16
C	.706	17.93	.306	7.77	.865	21.97
D	.806	20.47	.306	7.77	.965	24.51
E	.956	24.28	.306	7.77	1.115	28.32
F	1.106	28.09	.306	7.77	1.265	32.13
G	1.084	27.53	.399	10.13	1.215	30.86
H	1.455	36.96	.419	10.64	1.800	45.72
J	1.461	37.11	.306	7.77	1.615	41.02
K	1.864	47.35	.306	7.77	2.015	51.18
L	1.691	42.95	.419	10.64	2.036	51.71
M	1.755	44.58	.479	12.17	2.200	55.88

SERIES 791 PANEL CUTOUT


PANEL CUTOUT FOR SERIES 791
SHELL SIZES A-G, J, K



PANEL CUTOUT FOR SERIES 791
SHELL SIZES H AND L



PANEL CUTOUT FOR SERIES 791
SHELL SIZE M





Shell Size	A		B		C		D	
	±.002 (0.05)	in mm	±.002 (0.05)	in mm	in	mm	in	mm
A	.505	12.83	.418	10.62	.750	19.50	.199	5.05
B	.655	16.64	.418	10.62	.900	22.86	.199	5.05
C	.805	20.45	.418	10.62	1.050	26.67	.199	5.05
D	.880	22.35	.418	10.62	1.125	28.58	.199	5.05
E	1.030	26.16	.418	10.62	1.275	32.39	.199	5.05
F	1.180	29.97	.418	10.62	1.425	36.20	.199	5.05
G	1.142	29.01	.506	12.85	1.388	35.25	.244	6.20
H	1.531	38.89	.521	13.23	1.900	48.26	.250	6.35
J	1.555	39.50	.418	10.62	1.800	45.72	.199	5.05
K	1.930	49.02	.418	10.62	2.175	55.25	.199	5.05
L	1.767	44.88	.521	13.23	2.136	54.26	.250	6.35
M	1.850	46.99	.623	15.82	2.200	55.88	.290	7.37

Series 79 Micro-Crimp®



799-172
Jackscrew, Series 79

- For Connector without Backshell
- Fits Series 790 and 791
- Includes Clip




799-172

This accessory fits Series 790 and 791 connectors:
790-024, 790-025, 791-001, 791-003

Stainless steel jackscrews fit Series 790 and 791 connectors. Kit consists of (2) screws and (2) retainer clip, **order (1) kit per connector**. Jackscrew and clip are passivated stainless steel.

JACKSCREW KIT with (2) jackscrews and (2) clips

A Thread UNC-2A	Shell Size		Part Number	B Hex		C		ø E		ø F		G		J		K	
	Series 790	Series 791		in	mm	in	mm	in	mm	in	mm	± .010 (0.2) in	mm	± .010 (0.2) in	mm	in	mm
2-56	A-G, J, K	—	799-172-1	5/64	2.0	.140	3.6	.083	2.1	.095	2.4	.210	5.3	.172	4.4	.072	1.8
4-40	H, L	A-G, J, K	799-172-2	3/32	2.4	.183	4.6	.109	2.8	.121	3.1	.325	8.3	.250	6.4	.091	2.3
6-32	M	H, L	799-172-3	7/64	2.8	.226	5.7	.135	3.4	.147	3.7	.350	8.9	.250	6.4	.112	2.8
8-32		M	799-172-4	9/64	3.6	.270	6.9	.161	4.1	.173	4.4	.375	9.5	.275	7.0	.141	3.6



Series 79 Micro-Crimp®



799-011

EMI Banding Backshell, Micro-Crimp®

- Solid, Elliptical Entry
- Band-Master® Shield Termination
- Top and Side Entry




T Top Entry

799-011


This accessory fits Series 790 connectors:
790-024 and 790-025

EMI, banding elliptical entry. 799-011 backshell fits Series 790 connectors **790-024** and **790-025**. Terminate cable shield to backshell with BandMaster ATS band strap. Connector flange sits inside backshell. Optional Qwik-Ty strain relief arm. Aluminum or stainless steel with stainless steel screwlocks and retainer clips.


TABLE 1
SCREWLOCK OPTIONS





PART NUMBER													
Sample PN→				799-011T	M	H	01	H	N	T	08		
Base P/N		799-011T	T	Top Entry									
		799-011S	S	Side Entry									
Material / Finish		TZ	Alum / Tin-Zinc										
		M	Alum / Electroless Nickel										
		MT	Alum / Nickel-PTFE										
		ZR	Alum / Black Zinc-Nickel										
		ZI	SST / Passivated										
Shell Size		A	B	C	D	E	F	G	H	J	K	L	M
Entry Size		Entry Size	E		Shell Size								
		01	.300 (7.6)		A thru M								
		02	.450 (11.4)		B thru M								
		03	.600 (15.2)		C thru M								
		04	.700 (17.8)		D thru M								
		05	.850 (21.6)		E thru M								
		06	.965 (24.5)		F thru M								
		07	1.155 (29.3)		H thru M								
		08	1.345 (34.2)		H thru M								
		09	1.460 (37.1)		K thru M								
		10	1.580 (40.1)		K thru M								
		11	1.760 (44.7)		K								
		12	1.645 (41.8)		K and M								
Screwlocks (Table 1)		B	Fillister Head Male										
		E	Extended Male										
		F	Female Jackpost										
		H	Socket Head Male										
Band		N	No Band				M Micro Band Included						
		B	Standard Band Included				J Micro Slim Band Included						
		S	Slim Standard Band Included				L Micro-Max Band Included						
Qwik-Ty®		T	Qwik-Ty Strain Relief Arm Included										
		N	No Qwik-Ty										
Height Code		Height Code	Height	Available Profiles									
		06	.750 (19.1)	T									
		07	.875 (22.2)	T									
		08	1.000 (25.4)	T S									
		09	1.125 (28.6)	T S									
		10	1.250 (31.8)	T S									



ENTRY SIZE



HEIGHT





Series 79 Micro-Crimp®



799-011

EMI Banding Backshell, Micro-Crimp

- Solid with Elliptical Entry
- Band-Master® Shield Termination
- Top and Side Entry



Shell Size	A Max		B Max		C		D		Available Entries	Entry Size	E		Available Sizes
	in	mm	in	mm	in	mm	in	mm			in	mm	
A	.935	23.7	.450	11.4	.565	14.4	.300	.76	01	01	.300	.76	A thru M
B	1.085	27.6	.450	11.4	.715	18.2	.300	.76	01 thru 02	02	.450	11.4	B thru M
C	1.235	31.4	.450	11.4	.865	22.0	.300	.76	01 thru 03	03	.600	15.2	C thru M
D	1.335	33.9	.450	11.4	.965	24.5	.300	.76	01 thru 04	04	.700	17.8	D thru M
E	1.485	37.7	.450	11.4	1.115	28.3	.300	.76	01 thru 05	05	.850	21.6	E thru M
F	1.635	41.5	.450	11.4	1.265	32.1	.300	.76	01 thru 06	06	.965	24.5	F thru M
G	1.585	40.3	.533	13.5	1.215	30.9	.383	.97	01 thru 06	07	1.155	29.3	H thru M
H	2.320	58.9	.560	14.2	1.800	45.7	.410	10.4	01 thru 08	08	1.345	34.2	H thru M
J	1.990	50.5	.450	11.4	1.615	41.0	.300	.76	01 thru 08	09	1.460	37.1	K thru M
K	2.385	60.6	.450	11.4	2.015	51.2	.300	.76	01 thru 12	10	1.580	40.1	K thru M
L	2.556	64.9	.560	14.2	2.036	51.7	.410	10.4	01 thru 10	11	1.760	44.7	K
M	2.720	69.1	.620	15.7	2.200	55.9	.470	11.9	01 thru 10, 12	12	1.645	41.8	K and M

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.


Band Type and Width	Hand Tool	Pneumatic
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

SCREWLOCKS

CLIP
Clip has circular hole and square hole.

ASSEMBLY

INSTALL CLIP WITH SQUARE HOLE ON TOP.
Screw is floating. Mate connectors first, then fasten screwlocks.




Series 79 Micro-Crimp®



799-015

Piggyback EMI Banding Backshell



- Piggyback 2 Piece, Elliptical Entry
- Band-Master® Shield Termination
- Top and Side Entry



799-015

This accessory fits Series 790 and 791 connectors:
790-024, 790-025, 791-001, 791-003

EMI, lightweight, split. 799-015 piggyback backshell fits Series 790 and 791 connectors with rear groove on shell. Terminate cable shield to backshell with BandMaster ATS band strap. Aluminum or stainless steel with stainless steel screws. Non-environmental.



PART NUMBER

Sample PN →


799-015T MT M 09 N -01

Base P/N 799-015T **T** Top Entry
799-015S **S** Side Entry

Material / Finish
TZ Alum / Tin-Zinc
M Alum / Electroless Nickel
MT Alum / Nickel-PTFE
ZR Alum / Black Zinc-Nickel
ZI SST / Passivated


Shell Size **A B C D E F G H J K L M N**

Entry Size
01 .140 (3.6) A thru N
02 .290 (7.4) B thru N
03 .440 (11.2) C thru N
04 .540 (13.7) D thru N
05 .690 (17.5) E thru N
06 .810 (20.6) F thru N
07 1.000 (25.4) H thru N
08 1.190 (30.2) H thru N
09 1.305 (33.1) K thru N
10 1.420 (36.1) K thru N
11 1.600 (40.6) K and N
12 1.500 (38.1) K thru N
13 1.750 (44.5) N
14 1.875 (47.6) N



Band
N No Band
M Micro Band Included
J Micro Slim Band Included
L Micro-Max Band Included

Height Code
-01 .810 (20.6)
-02 .940 (23.9)
-04 1.190 (30.2)
-06 1.440 (36.6)
-08 1.690 (42.9)



BAND OPTIONS

Shell Size	A Max		B		C Max		Available Entries
	in	mm	in	mm	in	mm	
A	.385	9.8	.270	6.9	.485	12.3	01
B	.385	9.8	.270	6.9	.635	16.1	01 thru 02
C	.385	9.8	.270	6.9	.785	19.9	01 thru 03
D	.385	9.8	.270	6.9	.885	22.5	01 thru 04
E	.385	9.8	.270	6.9	1.035	26.3	01 thru 05
F	.385	9.8	.270	6.9	1.185	30.1	01 thru 06
G	.465	11.8	.350	8.9	1.145	29.1	01 thru 06
H	.495	12.6	.380	9.7	1.525	38.7	01 thru 08
J	.385	9.8	.270	6.9	1.545	39.2	01 thru 08
K	.385	9.8	.270	6.9	1.945	49.4	01 thru 12
L	.495	12.6	.380	9.7	1.765	44.8	01 thru 10
M	.555	14.1	.440	11.2	1.830	46.5	01 thru 10, 12
N	.650	16.5	.535	13.6	2.200	55.9	01 thru 14

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.



Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118


Series 79 Micro-Crimp®



799-016

Piggyback EMI Banding Backshell, Panel Mount

- Solid, Elliptical Entry
- Band-Master® Shield Termination
- Top, Side and 45° Entry



799-016

This accessory fits Series 790 and 791 panel mount connectors:
790-026, 790-027, 790-049, 790-050, 791-017, 791-018, 791-019, 791-020

EMI, lightweight. 799-016 piggyback backshell fits panel mount Series 790 and 791 connectors. Terminate cable shield to backshell with BandMaster ATS band strap. Aluminum or stainless steel with stainless steel screws. Non-environmental.

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.



Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

PART NUMBER

Sample PN→

799-016T MT L 07 N 12

Base P/N

799-016T **T** Top Entry
799-016S **S** Side Entry
799-016E **E** 45° Entry

Material / Finish


TZ Alum / Tin-Zinc
M Alum / Electroless Nickel
MT Alum / Nickel-PTFE
ZR Alum / Black Zinc-Nickel
ZI SST / Passivated

Shell Size

A B C D E F G H J K L M N

Entry Size

Entry Size	E	Shell Size
01	.255 (6.5)	A thru N
02	.405 (10.3)	B thru N
03	.555 (14.1)	C thru N
04	.655 (16.6)	D thru N
05	.805 (20.4)	E thru N
06	.920 (23.4)	F thru N
07	1.110 (28.2)	H thru N
08	1.300 (33.0)	H thru N
09	1.415 (35.9)	K thru N
10	1.535 (39.0)	K thru N
11	1.705 (43.3)	K and N
12	1.600 (40.6)	K, M, N
13	2.000 (50.8)	N






ENTRY SIZE

Band

N No Band
M Micro Band Included
J Micro Slim Band Included
L Micro-Max Band Included

Height Code

Code	Height	Shell Size		
		T Top	E 45°	S Side
05	.313 (8.0)	—	—	A-F, J, K
08	.500 (12.7)	—	—	A thru M
10	.625 (15.9)	A thru L	—	A thru N
12	.750 (19.1)	A thru N	A-F, J, K	A thru N
14	.875 (22.2)	A thru N	A thru M	G, H, L, M, N
16	1.000 (25.4)	A thru N	A thru N	G, H, L, M, N
18	1.125 (28.6)	A thru N	G, H, L, M, N	M, N
20	1.250 (31.8)	G, H, L, M, N	G, H, L, M, N	M, N




**T** TOP ENTRY**S** SIDE ENTRY**E** 45° ENTRY

Series 79 Micro-Crimp®

**799-016**

Piggyback EMI Banding Backshell, Panel Mount

- Solid, Elliptical Entry
- Band-Master® Shield Termination
- Top, Side and 45° Entry




Shell Size	A Max		B Max		C		D		F		Available Entries
	in	mm	in	mm	in	mm	in	mm	in	mm	
A	.760	19.3	.308	7.8	.565	14.4	.190	4.8	.59	15.0	01
B	.910	23.1	.308	7.8	.715	18.2	.190	4.8	.59	15.0	01 thru 02
C	1.060	26.9	.308	7.8	.865	22.0	.190	4.8	.59	15.0	01 thru 03
D	1.160	29.5	.308	7.8	.965	24.5	.190	4.8	.59	15.0	01 thru 04
E	1.310	33.3	.308	7.8	1.115	28.3	.190	4.8	.59	15.0	01 thru 05
F	1.460	37.1	.308	7.8	1.265	32.1	.190	4.8	.59	15.0	01 thru 06
G	1.410	35.8	.395	10.0	1.215	30.9	.275	7.0	.68	17.3	01 thru 06
H	2.045	51.9	.410	10.4	1.800	45.7	.300	7.6	.70	17.8	01 thru 08
J	1.810	46.0	.308	7.8	1.615	41.0	.190	4.8	.59	15.0	01 thru 08
K	2.210	56.1	.308	7.8	2.015	51.2	.190	4.8	.59	15.0	01 thru 12
L	2.281	57.9	.410	10.4	2.036	51.7	.300	7.6	.70	17.8	01 thru 10
M	2.445	62.1	.470	11.9	2.200	55.9	.360	9.1	.76	19.3	01 thru 10, 12
N	2.645	67.2	.534	13.6	2.350	59.7	.425	10.8	.83	21.1	01 thru 13

Entry Size	E		Available Sizes
	in	mm	
01	.255	6.5	A thru N
02	.405	10.3	B thru N
03	.555	14.1	C thru N
04	.655	16.6	D thru N
05	.805	20.4	E thru N
06	.920	23.4	F thru N
07	1.110	28.2	H thru N
08	1.300	33.0	H thru N
09	1.415	35.9	K thru N
10	1.535	39.0	K thru N
11	1.705	43.3	K and N
12	1.600	40.6	K, M, N
13	2.000	50.8	N

799-131

Piggyback EMI Banding Backshell, Dual Port



- Piggyback Dual Round Entry
- Band-Master® Shield Termination
- Top and Side Entry



799-131

This accessory fits Series 790 and 791 connectors:
790-024, 790-025, 791-001, 791-003

EMI, lightweight, split. 799-131 piggyback backshell fits Series 790 and 791 connectors with rear groove on shell. Dual port banding. Terminate cable shield to backshell with BandMaster ATS band strap. Aluminum with stainless steel screws. Non-environmental.



PART NUMBER

Sample PN→


799-131T M H 09 N -01

Base P/N **799-131T** **T** Top Entry
799-131S **S** Side Entry

Material / Finish **TZ** Alum / Tin-Zinc
M Alum / Electroless Nickel
MT Alum / Nickel-PTFE
ZR Alum / Black Zinc-Nickel
ZI SST / Passivated


Shell Size **C D E F G H J K L M**

Entry Size	C	Shell Size
35	.109 (2.8)	C thru M
04	.125 (3.2)	D thru M
05	.156 (4.0)	D thru M
06	.188 (4.8)	E thru M
07	.219 (5.6)	E thru M
08	.250 (6.4)	F thru M
09	.281 (7.1)	F thru M
10	.312 (7.9)	F, H thru M
11	.344 (8.7)	H, L, M
12	.375 (9.5)	H, L, M
13	.406 (10.3)	H, L, M
14	.438 (11.1)	M
15	.469 (11.9)	M



Band **N** No Band
M Micro Band Included
J Micro Slim Band Included
L Micro-Max Band Included

Height Code	D
-01	.810 (20.6)
-02	.940 (23.9)
-04	1.190 (30.2)
-06	1.440 (36.6)
-08	1.690 (42.9)



Shell Size	A Max in mm	B Max in mm	Available Entries
C	.385 9.8	.785 19.9	35
D	.385 9.8	.885 22.5	35, 04, 05
E	.385 9.8	1.035 26.3	35, 04 thru 07
F	.385 9.8	1.185 30.1	35, 04 thru 10
G	.465 11.8	1.145 29.1	35, 04 thru 09
H	.495 12.6	1.525 38.7	35, 04 thru 10
J	.385 9.8	1.545 39.2	35, 04 thru 10
K	.385 9.8	1.945 49.4	35, 04 thru 10
L	.495 12.6	1.765 44.8	35, 04 thru 13
M	.555 14.1	1.830 46.5	35, 04 thru 15

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.

Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118


Series 79 Micro-Crimp®



799-164

Piggyback EMI Banding Backshell, Series 792

- Split Piggyback for Series 792
- Band-Master® Shield Termination
- For High-Speed Data Cables




799-164

This accessory fits Series 792 connectors with twinax, quadrax or El Ochito contacts:
792-001, 792-002

EMI, piggyback, split. 799-164 piggyback backshell fits Series 792 connectors with rear groove on shell. Backshell has internal fluorosilicone wire strain relief grommet. Grommet has three hole sizes to accommodate twinax, quadrax or octaxial high speed cables. Available with Qwik-Ty strain relief arm or slots for lacing tape. Terminate cable shield to backshell with BandMaster ATS band strap. Aluminum with stainless steel screws. Non-environmental.

799-164 INTERNAL VIEW




Shell Size	A Max		B Max		Height	
	in	mm	in	mm		
A	.575	14.6	.810	20.6	2.380	60.5
B	.575	14.6	1.185	30.1	2.500	63.5
C	.575	14.6	1.560	39.6	2.940	74.7
D	.575	14.6	1.935	49.1	3.120	79.2
E	.575	14.6	2.310	58.7	3.310	84.1
F	.950	24.1	2.310	58.7	3.380	85.9

PART NUMBER

Sample PN→

799-164 M D N N N 2

Base P/N	799-164
Material / Finish	TZ Alum / Tin-Zinc M Alum / Electroless Nickel MT Alum / Nickel-PTFE ZR Alum / Black Zinc-Nickel
Shell Size	A B C D E F
Band	N No Band B Standard Band Incl. S Slim Std. Band Incl. M Micro Band Included J Micro Slim Band Included L Micro-Max Band Included
Qwik-Ty	T Qwik-Ty Strain Relief Arm N No Qwik-Ty
Lace-Tie Option	H Holes for Lace-Tie S Slots for Lace-Tie N No Lace-Tie Provision
Cable Size	1 .188 (4.8) Max. Individual Cable Diameter 2 .250 (6.4) Max. Individual Cable Diameter 3 .313 (8.0) Max. Individual Cable Diameter



ENTRY SIZE 1

Shell Size	in	C mm	in	D mm
A	.200	5.1	.300	7.6
B	.250	6.4	.390	9.9
C	.400	10.2	.440	11.2
D	.400	10.2	.520	13.2
E	.400	10.2	.690	17.5
F	.700	17.8	.700	17.8

ENTRY SIZE 2

Shell Size	in	C mm	in	D mm
A	.260	6.6	.360	9.1
B	.340	8.6	.510	13.0
C	.400	10.2	.740	18.8
D	.400	10.2	.960	24.4
E	.400	10.2	1.170	29.7
F	.775	19.7	.775	19.7

ENTRY SIZE 3

Shell Size	in	C mm	in	D mm
A	.320	8.1	.420	10.7
B	.380	9.7	.630	16.0
C	.400	10.2	.940	23.9
D	.400	10.2	1.250	31.8
E	.400	10.2	1.550	39.4
F	.775	19.7	1.650	41.9

Band Type and Width	Hand Tool	Pneumatic
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

AVIATION-GRADE
ARINC 600
STRAIN-RELIEF
AND EMI BANDING
BACKSHELLS




ARINC 600 and M83527
Backshells for Industry-
Standard Modular Rack-and-
Panel Connectors



Glenair makes EMI/RFI filtered connector versions of the ARINC 600 series

ARINC 600 connectors, prevalent in commercial aviation, are modular, high-density interconnects designed for rack-and-panel avionic applications. These connectors feature a modular rectangular design with a highly-ruggedized shell, ensuring life-of-system durability and resistance to shock and vibration. ARINC 600 connectors support standard data bus as well as high-speed data, with insert modules for signal, power, and Ethernet within a single unit. Their modular design allows for easy installation and maintenance, making them a popular choice for avionics systems, communication equipment, and other aerospace applications.

Glenair Signature
ARINC 600 Backshells



527-126

This strain-relief backshell fits ARINC 600 Size 3 connectors.


The 527-126 is a heavy-duty strain relief device designed to protect the large volume of wire terminations servicing a typical ARINC 600 size 3 connector.

ARINC 600/ M83527 Backshell Selection Guide


ARINC 600 Size 1 Backshells



Strain Relief + Braid Sock
527-257
Page D-3



EMI Cone-and-Ring
527-056
Page D-5



EMI Banding Composite
527-475
Page D-6

ARINC 600 Size 2 Backshells



Strain Relief
527-149
Page D-7



EMI Cone-and-Ring
527-025
Page D-8



EMI TAG Ring®
527-071
Page D-9



EMI Banding Composite
527-464
Page D-10

ARINC 600 Size 3 Backshells



Strain Relief
527-126
Page D-11



EMI TAG Ring®
527-199
Page D-12



EMI Banding
527-216
Page D-13

MIL-DTL-83527 Backshells



M25, M28 Threads
527-114
Page D-14




EMI Banding
527-543
Page D-15

Band-Master ATS®
Shield Termination Bands and Tools

Band-Master ATS®

Terminate cable braid shield to adapter with stainless steel **Band-Master ATS®** bands. Install band with hand tool or bench-mounted pneumatic tool. Bands are available in *Standard* (.24 inch) and *Micro* (.12 inch) widths. *Slim Standard* and *Micro Slim* bands have reduced thickness for weight reduction. Hardened steel *Micro-Max* bands have 60% more tensile strength than standard Micro bands. Available pre-coiled, bands are 304 series stainless steel, passivated.



For more information on the Band-Master ATS EMI shield termination system, including instruction manuals and calibration details:

<https://www.glenair.com/bandmaster/>

Band and Band Tool Part Numbers

Size		A Length in mm	Fits up to Dia. in mm	B Width in mm	C Thickness in mm	Part Number Pre-coiled	Hand Tool Part Number
Standard		9 228	1.00 25.4	.24 6.1	.02 0.5	601-006	601-100
		14 355	1.80 45.7	.24 6.1	.02 0.5	601-041	
		18 457	2.50 63.5	.24 6.1	.02 0.5	601-050	
Slim Standard		9 228	.94 23.9	.24 6.1	.01 0.3	601-571	601-109
		14 355	1.80 45.7	.24 6.1	.01 0.3	601-573	
Micro		5 127	.50 12.7	.12 3.0	.015 0.4	601-025	601-101
		8 203	.88 22.4	.12 3.0	.015 0.4	601-061	
		14 356	1.88 47.7	.12 3.0	.015 0.4	601-065	
Micro Slim		8 203	.88 22.4	.12 3.0	.01 0.3	601-601	601-122
		14 356	1.88 47.7	.12 3.0	.01 0.3	601-603	
Micro-Max		8 203	.88 22.4	.12 3.0	.015 0.4	601-701	601-129
		14 356	1.88 47.7	.12 3.0	.015 0.4	601-703	

527-257

ARINC 600 Size 1 Backshell, Strain Relief

- Self-Locking Saddle Clamp
- EMI Braidsock Option



527-257

This strain-relief backshell fits ARINC 600 Size 1 connectors.

Two clamp types: saddle clamp for unshielded wire bundles or saddle clamp with nickel-plated copper braid sock for shielding applications. Backshell ports feature Adapter Code H (D38999 Series III/IV) interface. Composite clamps are flight-grade self-locking style with full-radius saddles.

TABLE 1
CONNECTOR CODE

Application Note

Connector Codes **P, P1**: backshell replaces connector retainer plate. Attach backshell with connector retainer plate screws. *Backshell does not include screws.*

Connector Codes **P2, P6**: backshell attaches to retainer plate. Replace connector screws with screws and lockwashers included with backshell.

P All Manufacturers plug and receptacle shells except for those listed below.
Prior to ordering, consult factory with connector part numbers not listed below to ensure a proper fit.

P1 ITT Cannon BKAD*, BKAF*, BKAX*, non-environmental series, plug

Environmental plugs:


P2 Radiall NSXE*, NSXH*, NSXC

Amphenol AE*, AC*, AS*

Souriau S60*, S62*, SB62*, SB63*, SB6A*

P6 ITT Cannon BKAC & BKAE* Envir. Plug

PORT LOCATIONS



PART NUMBER

Sample PN → **527-257 M P1 A1 5 B1 4 C1 3**

Base P/N **527-257**

Finish
M Electroless Nickel
MT Nickel-PTFE
TZ Tin-Zinc
NF Olive Drab Cadmium

Connector Code **P P1 P2 P6** See Table 1

Port A
Clamp Type
A1 Saddle Clamp
A2 Saddle Clamp with EMI Braid Sock
A- Accessory Thread (no clamp)

Size **1 2 3 4 5 6 7** See Table 2


Port B
Clamp Type
B1 Saddle Clamp
B2 Saddle Clamp with EMI Braid Sock
B- Accessory Thread (no clamp)

Size **1 2 3 4 5 6 7** See Table 2

Port C
Clamp Type
C1 Saddle Clamp
C2 Saddle Clamp with EMI Braid Sock
C- Accessory Thread (no clamp)

Size **1 2 3 4 5 6 7** See Table 2

CLAMP STYLE A1, B1 (620HS042)



CLAMP STYLE A2, B2 (447HS557)





TABLE 2
CLAMP SIZE

Size Code	A Thread	B Max	C	D Min	E
	X1.0	in mm	± .031(0.8) in mm	in mm	± .031(0.8) in mm
1	M12	.98 24.9	.265 6.7	.22 5.6	.219 5.6
2	M15	1.05 26.7	.310 7.9	.27 6.9	.264 6.7
3	M18	1.20 30.5	.390 9.9	.35 8.9	.344 8.7
4	M22	1.30 33.0	.506 12.9	.47 11.9	.460 11.7
5	M25	1.44 36.6	.591 15.0	.55 14.0	.545 13.8
6	M28	1.56 39.6	.661 16.8	.62 15.7	.615 15.6
7	M31	1.69 42.9	.744 18.9	.70 17.8	.698 17.7

527-257

ARINC 600 Size 1 Backshell, Strain Relief

- Self-Locking Saddle Clamp
- EMI Braidsock




MATERIAL/ FINISH

Shell, lid, ports: aluminum
 Style 1 Clamp: polyetherimide (PEI), natural tan color
 Style 2 Clamp: polyetherimide (PEI). Body is natural tan color, coupling nut and saddles are black. EMI adapter: brass, plated per finish code. Crimp ring: copper/tin. Braid: 34 AWG nickel-coated copper, type AA59569R34N
 Screws, washers: stainless steel/passivated
 Clinch nuts: stainless steel/silver
 Anti-decoupling spring: thermoplastic

527-056

ARINC 600 Size 1 Backshell, EMI

- Cone-and-Ring Shield Termination
- Saddle Clamp Strain Relief



527-056

This EMI backshell fits ARINC 600 Size 1 connectors.

Backshell ports feature saddle clamp strain reliefs with cone-and-ring cable shield termination. Backshell attaches to connector insert retainer plate threaded holes. Stainless steel hardware.

CONE-AND-RING




TABLE 1
CONNECTOR CODE

Application Note

Connector Codes P, P1: backshell replaces connector retainer plate. Attach backshell with connector retainer plate screws. *Backshell does not include screws.*

Connector Codes P2, P6: backshell attaches to retainer plate. Replace connector screws with screws and lockwashers included with backshell.

P All Manufacturers plug and receptacle shells except for those listed below. Prior to ordering, consult factory with connector part numbers not listed below to ensure a proper fit.

P1 ITT Cannon BKAD*, BKAF*, BKAX*, non-environmental series, plug

Environmental plugs:

P2 Radiall NSXE*, NSXH*, NSXC
Amphenol AE*, AC*, AS*
Souriau S60*, S62*, SB62*, SB63*, SB6A*

P6 ITT Cannon BKAC & BKAE* Envir. Plug

PART NUMBER

Sample PN→

527-056

M

P1

03

04

03

A

Base P/N 527-056

Finish

M Electroless Nickel
MT Nickel-PTFE
TZ Tin-Zinc
NF Olive Drab Cadmium

Connector Code **P P1 P2 P6** See Table 1

Port 1 Entry Size **00** Port 1 Deleted
01 02 03 04 05 See Table 2

Port 2 Entry Size **00** Port 2 Deleted
01 02 03 04 05 See Table 2

Port 3 Entry Size **00** Port 3 Deleted
01 02 03 04 05 See Table 2

Height **A** 1.00 (25.4)
B 1.25 (31.8)




TABLE 2 ENTRY SIZE

Entry Size	Cable Range				M	
	in	mm	in	mm	in	mm
01	.062	1.6	.125	3.2	.781	19.8
02	.125	3.2	.250	6.4	.968	24.6
03	.250	6.4	.375	9.5	1.046	26.6
04	.312	7.9	.500	12.7	1.156	29.4
05	.375	9.5	.625	15.9	1.218	30.9

△ DIMENSIONS APPLY TO CONNECTOR DESIGNATOR "P"


ARINC 600 / M83527



527-475

ARINC 600 Size 1 Backshell, EMI Banding Composite

- Lightweight Composite
- Banding Shield Termination
- Qwik-Ty Strain Relief



527-475

This composite EMI backshell fits ARINC 600 Size 1 connectors.

Terminate cable braid shields to backshell with Band-Master ATS banding straps. Backshell attaches to connector insert retainer plate threaded holes (see Connector Compatibility note). Thermoplastic with stainless steel hardware.

CONNECTOR COMPATIBILITY

Connector Designator P6

Remove insert retainer plate from connector. Attach backshell to connector plate threaded holes.

TABLE 1 ENTRY SIZE

Entry Size	Entry Diameter		L		M Max	
	in	mm	in	mm	in	mm
2	.25	6.4	.22	5.6	.475	12.1
3	.38	9.7	.28	7.1	.605	15.4
4	.50	12.7	.33	8.4	.725	18.4
5	.63	16.0	.42	10.7	.855	21.7
6	.75	19.1	.50	12.7	.975	24.8
7	.87	22.1	.60	15.2	1.095	27.8

BAND OPTIONS


Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

PART NUMBER

Sample PN→	527-475	XM	A5	B4	C3	S	J
Base P/N	527-475						
Finish	XM	Electroless Nickel					
	XW	Olive Drab Cadmium					
Connector Code	Omit	All Connectors except:					
	P6	ITT Cannon BKAC & BKAE Envir. Plug					
Port A Entry Size	A2 A3 A4 A5 A6 A7	See Table 1					
Port B Entry Size	B2 B3 B4 B5 B6 B7	See Table 1					
Port C Entry Size	C2 C3 C4 C5 C6 C7	See Table 1					
Slots	Omit	No Slots					
	S	Slots					
EMI Gasket	Omit	No Gasket					
	1	Gasket Included (Qty 2)					
Qwik-Ty	Omit	Qwik-Ty Strain Relief Arm Included					
	L	Less Qwik-Ty Arm					
Band	Omit	No Band					
	B	Standard Bands Included					
	J	Slim Standard Bands Included					



ARINC 600 / M83527 ACCESSORIES

527-149

ARINC 600 Size 2 Backshell, Strain Relief

- Saddle Clamp Strain Relief
- For Unshielded Cables


TABLE 1
CONNECTOR CODE
Application Note

Connector Codes P, P1: backshell replaces connector retainer plate. Attach backshell with connector retainer plate screws. *Backshell does not include screws.*

Connector Codes P2, P6: backshell attaches to retainer plate. Replace connector screws with screws and lockwashers included with backshell.

P All Manufacturers plug and receptacle shells except for those listed below. Prior to ordering, consult factory with connector part numbers not listed below to ensure a proper fit.

P1 ITT Cannon BKAD*, BKAF*, BKAX*, non-environmental series, plug

Environmental plugs:

P2 Radiall NSXE*, NSXH*, NSXC
Amphenol AE*, AC*, AS*
Souriau S60*, S62*, SB62*, SB63*, SB6A*

P6 ITT Cannon BKAC & BKAE* Envir. Plug

TABLE 2
ENTRY SIZE

Entry Size	Thread Size	Cable Range					
		A	Min	Max	Min	Max	
	X1.0	In	mm	In	mm	In	mm
1	M12	.800	20.3	.098	2.5	.234	5.9
2	M15	.820	20.8	.153	3.9	.234	5.9
3	M18	.870	22.1	.190	4.8	.328	8.3
4	M22	.840	21.3	.260	6.6	.457	11.6
5	M25	.910	23.1	.283	7.2	.614	15.6
6	M28	1.000	25.4	.325	8.3	.634	16.1
7	M31	1.030	26.2	.343	8.7	.698	17.7
8	M34	1.160	29.5	.381	9.7	.823	20.9
9	M37	1.190	30.2	.418	10.6	.853	21.7


527-149

This strain-relief backshell fits ARINC 600 Size 2 connectors.

ARINC 600 size 2 backshell has saddle clamp strain reliefs. Adapter code H metric thread interface (ref. 620HS011). Stainless steel hardware.

PART NUMBER

Sample PN→		527-149	M	P	A4	B7	C05	E
Base P/N		527-149						
Finish	M	Electroless Nickel						
	MT	Nickel-PTFE						
	TZ	Tin-Zinc						
	NF	Olive Drab Cadmium						
Connector Code		P P1 P2 P6	See Table 1					
Port A Entry Size		Omit Port A Deleted A1 A2 A3 A4 A5 A6 A7 A8 A9 See Table 1 For threaded port (no clamp), add "L" prefix (E.g:"LA4")						
Port B Entry Size		Omit Port B Deleted B1 B2 B3 B4 B5 B6 B7 B8 B9 See Table 1 For threaded port (no clamp), add "L" prefix (E.g:"LB6")						
Port C Entry Size		Omit Port C Deleted C1 C2 C3 C4 C5 C6 C7 C8 C9 See Table 1 For threaded port (no clamp), add "L" prefix (E.g:"LC8")						
Height	Omit	1.50 (38.1)						
	E	2.00 (50.8)						
	F	2.50 (63.5)						





527-025

ARINC 600 Size 2 Backshell, EMI

- Cone-and-Ring Shield Termination
- Saddle Clamp Strain Relief
- For Shielded Cables



527-025

This EMI backshell fits ARINC 600 Size 2 connectors.

Cone-and-Ring shield termination backshell attaches to connector insert retainer plate threaded holes. Stainless steel hardware.

TABLE 1
CONNECTOR CODE

Application Note

Connector Codes **P, P1**: backshell replaces connector retainer plate. Attach backshell with connector retainer plate screws. *Backshell does not include screws.*

Connector Codes **P2, P6**: backshell attaches to retainer plate. Replace connector screws with screws and lockwashers included with backshell.

P All Manufacturers plug and receptacle shells except for those listed below.
Prior to ordering, consult factory with connector part numbers not listed below to ensure a proper fit.

P1 ITT Cannon BKAD*, BKAF*, BKAX*, non-environmental series, plug

P2 Environmental plugs:
Radiall NSXE*, NSXH*, NSXC
Amphenol AE*, AC*, AS*
Souriau S60*, S62*, SB62*, SB63*, SB6A*


P6 ITT Cannon BKAC & BKAE* Envir. Plug

TABLE 2
ENTRY SIZE

Entry Size	Cable Range		A Max	B Max
	Min	Max		
03	.157 (4.0)	.250 (6.4)	.760 (19.3)	.844 (21.4)
04	.187 (4.7)	.312 (7.9)	.760 (19.3)	.906 (23.0)
06	.281 (7.1)	.437 (11.1)	.760 (19.3)	1.093 (27.8)
08	.344 (8.7)	.562 (14.3)	.760 (19.3)	1.187 (30.1)
10	.375 (9.5)	.625 (15.9)	.760 (19.3)	1.281 (32.5)
12	.438 (11.1)	.750 (19.1)	.760 (19.3)	1.500 (38.1)
16	.562 (14.3)	.938 (23.8)	1.073 (27.3)	1.719 (43.7)

PART NUMBER

Sample PN→		527-025	M	P1	H06	J04	K06	D	S				
Base P/N		527-025											
Finish	M	Electroless Nickel											
	MT	Nickel-PTFE											
	TZ	Tin-Zinc											
	NF	Olive Drab Cadmium											
Connector Code		P	P1	P2	P6	See Table 1							
Port 1	Location	A	B	C	D	E	F	G	H	J	K	L	See Drawing
	Entry Size	03	04	06	08	10	12	16	See Table 2				
Port 2	Location	A	B	C	D	E	F	G	H	J	K	L	See Drawing
	Entry Size	03	04	06	08	10	12	16	See Table 2				
Port 3	Location	A	B	C	D	E	F	G	H	J	K	L	See Drawing
	Entry Size	03	04	06	08	10	12	16	See Table 2				
Termination Style		D	Two Ground Rings in Saddle Clamps										
		MT	Three Ground Rings in Saddle Clamps										
Safety Wire Holes		Omit	No Safety Wire Holes in Hex Nuts										
		S	Hex Nuts with Safety Wire Holes										



527-071

ARINC 600 Size 2 Backshell, EMI, TAG Ring®

■ TAG Ring for Individual Braid Shields

**-01**

Single Port Module for Cavity C


**-02**

2 Port Module for Cavities A and B

527-071

This EMI backshell fits ARINC 600
Size 2 connectors.

Backshell consists of two modules ordered separately: single port module for cavity C, and dual port module for cavities A and B. TAG® ring has fingers for individual braid shields. Optional RFI gasket. Aluminum shell, nut and clamp. PTFE friction washer, gold plated beryllium copper ground spring, stainless steel screws and washers. Optional RFI gasket is aluminum mesh in neoprene.

TAG® RING**PART NUMBER**




Sample PN→

527-071**-02****R****L**Base P/N **527-071**


Module **-01** Single Port Module for Cavity C
-02 Dual Port Module for Cavities A and B

RFI Gasket **Omit** No Gasket
R RFI Gasket included



Strain Relief **Omit** Nut (requires shrink boot for strain relief)
L Saddle Clamp

**-01**

SINGLE PORT MODULE FOR CAVITY C

**-02**

DUAL PORT MODULE FOR CAVITIES A AND B


STYLE L
SADDLE CLAMP

VIEW A-A

527-464

ARINC 600 Size 2 Backshell, EMI Banding

- Composite or Aluminum
- Band-Master ATS® Shield Termination



527-464

This EMI backshell fits ARINC 600 Size 2 connectors.

Backshell attaches to connector retainer plate holes using 4-40 screws supplied with backshell (remove and discard retainer plate). Cable shield attaches to backshell with .24 inch (6.1 mm) wide Band-Master ATS® banding strap. Options include slots in banding area, Qwik-Ty® strain relief arm and EMI gasket.



CONNECTOR COMPATIBILITY

Remove insert retainer plate from connector and discard.

TABLE 1
CONNECTOR CODE

P All Manufacturers (unless listed below)
Due to non-standard connector modifications this backshell may require design alterations to fit properly. Consult factory to ensure a proper fit.

P1 ITT Cannon BKAD/F/X Non-Environ. Plug

Radiall NSXE/H/C Environmental Plug

P2 Amphenol AE*/AC*/AS* Environ. Plug
Souriau S60*/S62*/SB62*/SB63/SB6A Plug

P4 TE 2157236 Non-Environmental Plug

P6 ITT Cannon BKAC & BKAE Environ. Plug

TABLE 2
ENTRY SIZE

Entry Size	Entry Diameter	K	ø L
	in mm	in mm	in mm
4	.50 12.7	.38 9.7	.72 18.3
5	.63 16.0	.47 11.9	.85 21.6
6	.75 19.1	.56 14.2	.97 24.6
8	1.00 25.4	.69 17.5	1.22 31.0
9	1.12 28.4	.78 19.8	1.34 34.0

PART NUMBER

Sample PN →

527-464 XM P1 A8 B6 C5 S -1 L J

Base P/N 527-464

Material / Finish	M	Aluminum / Electroless Nickel
	TZ	Aluminum / Tin-Zinc
	NF	Aluminum / Olive Drab Cadmium
	XM	Composite / Electroless Nickel
	XW	Composite / Olive Drab Cadmium

Connector Code **P P1 P2 P4 P6** See Table 1

Port A Entry Size **Omit** Port A Deleted
A4 A5 A6 A8 A9 See Table 2

Port B Entry Size **Omit** Port B Deleted
B4 B5 B6 B8 B9 See Table 2


Port C Entry Size **Omit** Port C Deleted
C4 C5 C6 C8 C9 See Table 2

Slots **Omit** No Slots
S Slots Included

EMI Gasket **Omit** No Gasket
-1 Gasket Included (Qty 2)

Qwik-Ty **Omit** Qwik-Ty Strain Relief Arms Included
L Qwik-Ty Arms Deleted

Band **Omit** No Band
B Standard Bands Included
J Slim Standard Bands Included



BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.

Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

527-126

ARINC 600 Size 3 Backshell, Strain Relief

- Saddle Clamp Strain Relief
- For Unshielded Cables



527-126

This strain-relief backshell fits ARINC 600 Size 3 connectors.

Saddle clamps have adapter code H metric thread interface (ref. 620HS011). Backshell attaches to connector insert retainer plate holes. Aluminum with stainless steel hardware.

TABLE 1
CONNECTOR CODE

Application Note

Connector Codes **P, P1**: backshell replaces connector retainer plate. Attach backshell with connector retainer plate screws. *Backshell does not include screws.*

Connector Codes **P2, P6**: backshell attaches to retainer plate. Replace connector screws with screws and lockwashers included with backshell.

P All Manufacturers plug and receptacle shells except for those listed below. Prior to ordering, consult factory with connector part numbers not listed below to ensure a proper fit.

P1 ITT Cannon BKAD*, BKAF*, BKAX*, non-environmental series, plug

P2 Environmental plugs:
Radiall NSXE*, NSXH*, NSXC
Amphenol AE*, AC*, AS*
Souriau S60*, S62*, SB62*, SB63*, SB6A*

P6 ITT Cannon BKAC & BKAE* Envir. Plug

TABLE 2 ENTRY SIZE

Entry Size	Thread Size	A		Cable Range			
		In	mm	Min	Max	In	mm
3	M18	.790	20.0	.190	4.8	.328	8.3
4	M22	.790	20.0	.260	6.6	.457	11.6
5	M25	.915	23.2	.283	7.2	.614	15.6
6	M28	1.165	29.6	.325	8.3	.634	16.1

PART NUMBER

Sample PN→

527-126 M P1 A3 B3 C4 D4 E6 F6

Base P/N 527-126

Finish **M** Electroless Nickel
TZ Tin-Zinc
NF Olive Drab Cadmium

Connector Code **P P1 P2 P6** See Table 1

Port A Entry Size *Omit* Port A Deleted
A3 A4 A5 A6 See Table 2


Port B Entry Size *Omit* Port B Deleted
B3 B4 B5 B6 See Table 2

Port C Entry Size *Omit* Port C Deleted
C3 C4 C5 C6 See Table 2

Port D Entry Size *Omit* Port D Deleted
D3 D4 D5 D6 See Table 2

Port E Entry Size *Omit* Port E Deleted
E3 E4 E5 E6 See Table 2

Port F Entry Size *Omit* Port F Deleted
F3 F4 F5 F6 See Table 2



THREADED PORT, NO CLAMP

Add "L" to port entry size to delete cable clamp and retain threaded port. (I.e., "LB4" = less cable clamp with M22 threaded port at port B. Threaded port conforms to Adapter Code H interface (D38999 Series III/IV).

527-199

ARINC 600 Size 3 Backshell, EMI TAG Ring®

■ TAG Ring® Shield Termination



527-199

This EMI TAG Ring® backshell fits ARINC 600 Size 3 connectors.

Designed for individual wire shields termination. Aluminum shell, nut and clamp. PTFE friction washer, gold plated beryllium copper ground spring, SS hardware.

TABLE 1
CONNECTOR CODE

Application Note

Connector Codes **P, P1**: backshell replaces connector retainer plate. Attach backshell with connector retainer plate screws. *Backshell does not include screws.*

Connector Codes **P2, P6**: backshell attaches to retainer plate. Replace connector screws with screws and lockwashers included with backshell.

P All Manufacturers plug and receptacle shells except for those listed below.
Prior to ordering, consult factory with connector part numbers not listed below to ensure a proper fit.

P1 ITT Cannon BKAD*, BKAF*, BKAX*, non-environmental series, plug

P2 Environmental plugs:
Radiall NSXE*, NSXH*, NSXC
Amphenol AE*, AC*, AS*
Souriau S60*, S62*, SB62*, SB63*, SB6A*


P6 ITT Cannon BKAC & BKAE* Envir. Plug

TABLE 2 ENTRY SIZE

Entry Size	Cable Entry				B Max		C Max	
	Min	Max	Min	Max	In	mm	In	mm
2	.125	.250	.32	.64	.968	24.6	.545	13.8
3	.250	.375	.64	.95	1.046	26.6	.670	17.0
4	.250	.500	.64	1.27	1.156	29.4	.795	20.2
5	.375	.625	.95	1.59	1.218	30.9	.920	23.4
6	.500	.750	1.27	1.91	1.343	34.1	1.045	26.5
7	.625	.875	1.59	2.22	1.468	37.3	1.170	29.7
8	.750	1.000	1.91	2.54	1.593	40.5	1.295	32.9

PART NUMBER

Sample PN→		527-199	M	P1	A3	B3	C4	D4	E6	F6	L
Base P/N		527-199									
Finish	M	Electroless Nickel									
	TZ	Tin-Zinc									
	NF	Olive Drab Cadmium									
Connector Code	P	P1	P2	P6	See Table 1						
Port A Entry Size	Omit	Port A Deleted									
	A2	A3	A4	A5	A6	A7	A8	See Table 2			
Port B Entry Size	Omit	Port B Deleted									
	B2	B3	B4	B5	B6	B7	B8	See Table 2			
Port C Entry Size	Omit	Port C Deleted									
	C2	C3	C4	C5	C6	C7	C8	See Table 2			
Port D Entry Size	Omit	Port D Deleted									
	D2	D3	D4	D5	D6	D7	D8	See Table 2			
Port E Entry Size	Omit	Port E Deleted									
	E2	E3	E4	E5	E6	E7	E8	See Table 2			
Port F Entry Size	Omit	Port F Deleted									
	F2	F3	F4	F5	F6	F7	F8	See Table 2			
Strain Relief	L	Saddle Clamp									
	G	Nut									



4-40 X .312 (7.9) FILLISTER HEAD SCREWS AND LOCK WASHER, 17 PLACES

527-216

ARINC 600 Size 3 Backshell, EMI Banding

- Band-Master ATS Shield Termination
- Qwik-Ty Strain Relief



527-216

This EMI banding backshell fits ARINC 600 Size 3 connectors.

Attach cable shields with Band-Master ATS banding straps. Backshell attaches to connector insert retainer plate holes. Aluminum shell, stainless steel screws and washers.

TABLE 1
CONNECTOR CODE

Application Note

Connector Codes **P, P1**: backshell replaces connector retainer plate. Attach backshell with connector retainer plate screws. *Backshell does not include screws.*

Connector Codes **P2, P6**: backshell attaches to retainer plate. Replace connector screws with screws and lockwashers included with backshell.

P All Manufacturers plug and receptacle shells except for those listed below. Prior to ordering, consult factory with connector part numbers not listed below to ensure a proper fit.

P1 ITT Cannon BKAD*, BKAF*, BKAX*, non-environmental series, plug

P2 Environmental plugs:
Radiall NSXE*, NSXH*, NSXC
Amphenol AE*, AC*, AS*
Souriau S60*, S62*, SB62*, SB63*, SB6A*

P6 ITT Cannon BKAC & BKAE* Envir. Plug

TABLE 2 ENTRY SIZE


Entry Size	Entry Diameter		J		L	
	in	mm	in	mm	in	mm
2	.25	6.4	.38	9.7	.22	5.6
3	.38	9.7	.50	12.7	.28	7.1
4	.50	12.7	.63	16.0	.33	8.4
5	.63	16.0	.75	19.1	.38	9.7
6	.75	19.1	.88	22.4	.38	9.7
7	.87	22.1	1.00	25.4	.38	9.7
8	1.00	25.4	1.12	28.4	.38	9.7
9	1.12	28.4	1.25	31.8	.38	9.7

PART NUMBER

Sample PN→

527-216 M P1 A3 B3 C4 D4 E6 F6 S -1 T M

Base P/N	527-216
Finish	M Electroless Nickel TZ Tin-Zinc NF Olive Drab Cadmium
Connector Code	See Table 1 P P1 P2 P6
Port A Entry Size	<i>Omit</i> Port A Deleted A2 A3 A4 A5 A6 A7 A8 A9
Port B Entry Size	<i>Omit</i> Port B Deleted B2 B3 B4 B5 B6 B7 B8 B9
Port C Entry Size	<i>Omit</i> Port C Deleted C2 C3 C4 C5 C6 C7 C8 C9
Port D Entry Size	<i>Omit</i> Port D Deleted D2 D3 D4 D5 D6 D7 D8 D9
Port E Entry Size	<i>Omit</i> Port E Deleted E2 E3 E4 E5 E6 E7 E8 E9
Port F Entry Size	<i>Omit</i> Port F Deleted F2 F3 F4 F5 F6 F7 F8 F9
Slots	<i>Omit</i> No Slots S Slots Included
EMI Gasket	<i>Omit</i> No Gasket -1 Gasket Included (<i>Qty</i> 3)
Qwik-Ty	<i>Omit</i> Less Qwik-Ty Arm T Qwik-Ty Strain Relief Arms Included
Mounting Screws	<i>Omit</i> Delete Mounting Screws M Mounting Screws (<i>qty</i> 17) and lock washers (34) Included
Band	<i>Omit</i> No Band K Standard Bands Included J Slim Standard Bands Included



BAND OPTIONS


Terminate braid to backshell with band strap and banding tool. Pre-coiled bands are passivated SST. Slim Standard bands have reduced thickness for weight reduction.

Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

527-114

M83527 Backshell, M25 and M28 Thread

■ Adapter Code H (D38999) Entry




527-114

This M25 and M28 thread backshell adapter fits M83527 connectors

Backshell attaches to connector insert retainer plate holes. Two module sizes to fit both sizes of inserts. Backshell has metric threads and teeth conforming to MIL-DTL-38999 Series III/IV interface standard (Adapter Code H). Add strain relief clamp or EMI adapter, sold separately.
Aluminum shell, stainless steel screws and washers.

PART NUMBER					
Sample PN→		527-114	NF	01	17
Base P/N		527-114			
Finish	M	Electroless Nickel			
	TZ	Tin-Zinc			
	NF	Olive Drab Cadmium			
Module Size	01	Large- for Cavities A, C, E			
	02	Small- for Cavities B, D, F			
Entry Size	17	M25 Thread, .828 (21.0) I.D.			
	19	M28 Thread, .910 (23.1) I.D.			



Module Size	A		B		C		D		E		F	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
01	1.97	50.0	1.770	45.0	1.187	30.1	1.39	35.3	1.125	28.6	1.615	41.0
02	1.53	38.9	1.329	33.8	1.187	30.1	1.39	35.3	1.125	28.6	1.175	29.8

ENTRY SIZE

Entry Size	G Thread	ø H	
		in	mm
17	M25 X 1.0-6g	.828	21.0
19	M28 X 1.0-6g	.910	23.1

527-543

M83527 Backshell, EMI Banding

■ Band-Master ATS Shield Termination



527-543

This EMI banding backshell fits M83527 connectors

Attach cable shield to backshell with Band-Master ATS banding strap. Backshell attaches to connector insert retainer plate holes. Two module sizes to fit both sizes of inserts. Backshell has groove for optional lipped shrink boot.

Aluminum shell, stainless steel screws and washers. EMI gasket: monel mesh embedded in neoprene.

PART NUMBER

Sample PN→


527-543 NF 01 05 T J

Base P/N 527-543

Finish **M** Electroless Nickel
TZ Tin-Zinc
NF Olive Drab Cadmium

Module Size **01** Large- for Cavities A, C, E
02 Small- for Cavities B, D, F

Entry Size ϕK
03 .375 (9.5)
04 .500 (12.7)
05 .625 (15.9)
06 .750 (19.1)
07 .875 (22.2)



ENTRY SIZE

Shrink Boot Option **Omit** None
T Standard Heatshrink Boot
TI Standard Heatshrink Boot w/ Hot Melt Adhesive
H Zero Halogen Heatshrink Boot
HI Zero Halogen Heatshrink Boot w/ Hot Melt Adhesive

Band **Omit** No Band
K Standard Band Included
J Slim Standard Band Included

ENTRY SIZE



Entry Size	ϕK in	ϕK mm	ϕL in	ϕL mm	ϕM in	ϕM mm
03	.375	9.5	.500	12.7	.562	14.3
04	.500	12.7	.625	15.9	.688	17.5
05	.625	15.9	.750	19.1	.812	20.6
06	.750	19.1	.875	22.2	.938	23.8
07	.875	22.2	1.000	25.4	1.062	27.0

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110



Module Size	A	B	C	D	E	F
	in	mm	in	mm	in	mm
01	1.97	50.0	1.770	45.0	1.187	30.1
02	1.53	38.9	1.329	33.8	1.187	30.1

SHRINK BOOT



Optional heatshrink boot provides cable strain relief and environmental protection. Standard boot is high performance semi-rigid elastomer. Zero halogen boot is semi-rigid polyolefin. Available with W1 hot melt adhesive pre-coat. Add "W1" to part number to specify hot melt adhesive pre-coat.

Entry Size	Standard Boot	Zero Halogen Boot
03	770-001S103	770-001S203
04	770-001S104	770-001S204
05	770-001S104	770-001S204
06	770-001S105	770-001S205
07	770-001S105	770-001S205

EPXB TYPE
AVIATION
INDUSTRY MODULAR
CONNECTOR SERIES




Modular EPXB, BACC65,
EN4165, and SIM EMI/RFI
and Strain Relief Backshells



EPXB type modular connectors are widely employed in aviation for their versatility and reliability. EPXB type connectors offer a modular construction, enabling easy customization and flexibility in configuring complex avionics systems. These connectors feature a ruggedized design, capable of withstanding harsh environmental conditions such as extreme temperatures, vibrations, and electromagnetic interference commonly encountered in aircraft operations. EPXB type connectors support high-speed data transmission, power distribution, and signal connections, making them integral components in avionic systems, communication equipment, and IFE systems.

Glenair Signature
Modular Rectangular Backshells



527-410

*This EMI banding backshell fits
BACC65AA/AB and EPXB2 connectors*

The 527-410 is a split-shell EMI banding backshell with a low-profile 1" (25.4) can height. Elliptical cable entries accommodate large wire bundles. Cable shields attach with Standard or Slim Standard Band-Master ATS® band straps.

Modular Rectangular Backshell Selection Guide

BACC65AA/AB

EPXB2 Backshells



EMI Banding Backshell
2" (50.8) Can Height
BACC65AA/AB, EPXB2
527-260
Page E-2



EMI Banding Backshell
2" Can (50.8) Height
BACC65AA/AB, EPXB2,
Radial 617610100
527-265
Page E-3



EMI Banding Backshell
1.5" (38.1) Can Height
BACC65AA/AB, EPXB2
527-281
Page E-4




EMI Banding Backshell
1.0" (38.1) Can Height
BACC65AA/AB, EPXB2
527-410
Page E-5



EMI Banding Backshell
with Saddle Clamps
BACC65AA/AB, EPXB2
527-254
Page E-6




EMI Banding Backshell
1.56" (39.6) Can Height
EPXB2
527-268
Page E-7



EMI Banding Backshell
End Entry
EPXB2
527-531
Page E-8

EN4165

SIM Backshells



EMI Banding Backshell
SIM AD 6 4 Module
527-495
Page E-9



EMI Banding Backshell
Snap-Together Composite
SIM AD 6 Four Module
527-542
Page E-10



EMI Banding Backshell
Snap-Together Composite
SIM AD 6 Two Module
527-586
Page E-11

BACC65BU/CA

EN4165 Clampshells



Clampshell, Single Module
EN4165, BACC65BU/CA
527-407
Page E-12



Clampshell, Single
Extended Length Module
EN4165, BACC65BU/CA
527-493
Page E-13

MODULAR RECTANGULAR BACKSHELLS

527-260

EMI Backshell, BACC65AA/AB, EPXB2

- Elliptical Entry
- Band-Master ATS Shield Termination
- Qwik-Ty Strain Relief




527-260

*This EMI banding backshell fits
BACC65AA/AB and EPXB2 connectors*

Split diecast EMI banding backshell. Elliptical cable entries accommodate large wire bundles. Backshell attaches to connector with hex drive M8 center screw. Cable shields attach to backshell with .24 inch (6.1 mm) wide Band-Master ATS® banding strap. Aluminum with passivated stainless steel hardware.

PART NUMBER

		Sample PN→		527-260	ME	S	S	B
Base P/N		527-260						
Finish		ME Electroless Nickel						
Port X	Qwik-Ty Style	S	Straight					
Port Y	Qwik-Ty Style	S	Straight					
Band		<i>Omit</i> No band B Micro Bands Included (qty. 2) K Standard Bands Included (qty. 2) J Slim Standard Bands Included (qty. 2)						



BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.

Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

527-265

EMI Backshell, Radiall 617610100, EPXB2, BACC65AA/AB

- Elliptical Entry
- Band-Master ATS Shield Termination
- Qwik-Ty Strain Relief



PART NUMBER

Sample PN→ **527A265**

Sample PN→		527A265	M	K
Base P/N	527A265	#6-32 Mounting Screw (Radial P/N 617610100)		
	527B265	M8 Mounting Screw (EPXB2, BACC65AA/AB)		
Finish	M	Electroless Nickel		
Bands	Omit	No Band		
	K	Standard Bands Included (qty. 2)		
	J	Slim Standard Bands Included (qty. 2)		

527-265

This EMI banding backshell fits Radial 617610100, EPXB2, and BACC65AA/AB connectors


Split diecast EMI banding backshell. Elliptical cable entries accommodate large wire bundles. Backshell attaches to connector with hex drive center mounting screw. Cable shields attach to backshell with .24 inch (6.1 mm) wide Band-Master ATS® banding strap. Aluminum with passivated stainless steel hardware.

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110



527-281

EMI Banding Backshell, EPXB2, BACC65AA/AB

- Solid, 1.5" Can Height
- Band-Master ATS Shield Termination
- Qwik-Ty Strain Relief



527-281

This EMI banding backshell fits EPXB2 and BACC65AA/AB connectors

Low-profile. 1.5 inch (38.1mm) can height. Backshell attaches to connector with slotted drive center mounting screw. Cable shields attach to backshell with .24 inch (6.1 mm) wide Band-Master ATS® banding strap. Aluminum with passivated stainless steel hardware.

BAND OPTIONS


Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

PART NUMBER

Sample PN→		527-281	M	K
Base P/N		527-281		
Finish	M	Electroless Nickel		
Band	Omit	No Band		
	K	Standard Bands Included (qty. 2)		
	J	Slim Standard Bands Included (qty. 2)		
Qwik-Ty	Omit	Qwik-Ty Arms Included		
	L	Less Qwik-Ty Arms		



Modular Rectangular (EPXB, BACC65, EN4165, SIM)



527-410

EMI Backshell, BACC65AA/AB, EPXB2

- Low Profile 1" Can Height
- Band-Master ATS Shield Termination
- Qwik-Ty Strain Relief



527-410

This EMI banding backshell fits
BACC65AA/AB and EPXB2 connectors

Split diecast EMI banding backshell. Low profile 1" (25.4) can height. Elliptical cable entries accommodate large wire bundles. Backshell attaches to connector with hex drive M8 center screw. Cable shields attach to backshell with .24 inch (6.1 mm) wide Band-Master ATS® banding strap. Nickel-plated aluminum with passivated stainless steel hardware.

PART NUMBER

Sample PN→

527-410

ME

S

S

B


Base P/N 527-410

Finish ME Electroless Nickel

Port **X** Qwik-Ty Style **S** Straight

Port **Y** Qwik-Ty Style **S** Straight

Band **Omit** No band
B Micro Bands Included (qty. 2)
K Standard Bands Included (qty. 2)
J Slim Standard Bands Included (qty. 2)



BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.

Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

527-254

EMI Backshell, BACC65AA/AB, EPXB2

- Low Profile
- Band-Master ATS Shield Termination
- Saddle Clamp Strain Relief



527-254

*This EMI banding backshell fits
BACC65AA/AB and EPXB2 connectors*

Backshell attaches to connector with slot drive M8 center screw. Cable shields attach to backshell with .24 inch (6.1 mm) wide Band-Master ATS® banding strap. Saddle clamps have full-radius bars and self-locking silver plated stainless steel clinch nuts. Aluminum with passivated stainless steel screws.

BAND OPTIONS


Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

PART NUMBER

		Sample PN→	527-254	M	S	S	B
Base P/N		527-254					
Finish	M	Electroless Nickel					
	TZ	Tin-Zinc					
	NF	Olive Drab Cadmium					
Port X	S	Straight					
Port Y	S	Straight					
Band	Omit	No Band					
	B	Standard Bands Included (qty. 2)					
	J	Slim Standard Bands Included (qty. 2)					



Modular Rectangular (EPXB, BACC65, EN4165, SIM)



527-268

EMI Backshell, EPXB2, Banding

- Top and End Entry
- Band-Master ATS Shield Termination
- Qwik-Ty Strain Relief



527-268

This split EMI banding backshell fits
EPXB2 connectors

Backshell attaches to connector with M8 hex drive center mounting screw. Cable shields attach to backshell with .24 inch (6.1 mm) wide **Band-Master ATS®** banding strap. Aluminum with passivated stainless steel hardware.

TABLE 1 ENTRY SIZE

Entry Size	A in	A mm	B in	B mm	No. of Braid Slots
02	.250	6.4	.190	4.8	2
03	.312	7.9	.250	6.4	2
04	.375	9.5	.281	7.1	2
05	.438	11.1	.312	7.9	2

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

PART NUMBER

Sample PN→

527-268 M A03 B02 C04 T B

Base P/N 527-268

Finish
M Electroless Nickel
TZ Tin-Zinc
NF Olive Drab Cadmium


Port A Entry Size
Omit Port A Deleted
A02 A03 A04 A05 See Table 1

Port B Entry Size
Omit Port B Deleted
B02 B03 B04 B05 See Table 1

Port C Entry Size
Omit Port C Deleted
C02 C03 C04 C05 See Table 1

Qwik-Ty
Omit No Qwik-Ty
T Qwik-Ty Strain Relief Arms Included

Bands
Omit No Band
B Standard Band Included (one per port)
J Slim Standard Band Included (one per port)




Modular Rectangular (EPXB, BACC65, EN4165, SIM)

**527-531**


EMI Banding Backshell, EPXB2

- Band-Master ATS Shield Termination
- Qwik-Ty Strain Relief




**527-531**

This split EMI banding backshell fits EPXB2 connectors

Elliptical cable entries accommodate large wire bundles. Backshell attaches to connector with M8 mounting screw. Cable shields attach to backshell with .12 inch (3.0 mm) wide **Band-Master ATS**® Micro band strap. Aluminum with passivated stainless steel hardware.



4-40 UNC 2A PAN HEAD, CROSS RECESSED CAPTIVE SCREW & LOCKWASHER, 1/2 INCH LONG WITH VIBRATITE (2 PLACES)

**BAND OPTIONS**

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction. Micro-Max bands are high-tension for lower-resistivity termination.

Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123
Micro-Max: .12 (3.0)	601-129	601-118

PART NUMBER

Sample PN→

527-531**M****B****T**Base P/N **527-531**

Finish **M** Electroless Nickel
MT Nickel-PTFE

Bands **Omit** No Band
K Micro Band Included (qty. 2)
J Micro Slim Band Included (qty. 2)
L Micro-Max Band Included (qty. 2)

Shrink Boots **Omit** Boots Not Included
T Boots Included (qty 2)


Modular Rectangular (EPXB, BACC65, EN4165, SIM)



527-495

EMI Backshell, SIM AD 6

- Lightweight Composite
- Band-Master ATS Shield Termination
- Qwik-Ty Strain Relief



527-495



This split EMI banding backshell fits
SIM AD 6 four-module connectors

Snap-together with elliptical cable entries to accommodate large wire bundles. Backshell attaches to connector with captivation clip and screw. Cable shields attach to backshell with .12 inch (3.0 mm) wide **Band-Master ATS**® banding strap. Composite thermoplastic with passivated stainless steel hardware and aluminum clip.

PART NUMBER

Sample PN → 527-495 XM B


Base P/N	527-495
Finish	XM Electroless Nickel XW Olive Drab Cadmium
Bands	Omit No Band B Micro Band Included (qty. 2) J Micro Slim Band Included (qty. 2)
Hex Jackpost	Omit 3mm Hex Jackpost and Socket P 7/64 (2.78) Hex Jackpost and Socket L Omit Hex Jackpost and Socket
Qwik-Ty	Omit Qwik-Ty Arms Are Included L Less Qwik-Ty Arms



BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction.

Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123



- △ STANDARD JACKPOST HAS .120 (3.00) HEX SOCKET, "P" JACKPOST HAS .109 (2.78) HEX SOCKET
- △ JACKPOST TO MEET EN4165 REQUIREMENTS




Modular Rectangular (EPXB, BACC65, EN4165, SIM)

527-542

EMI Backshell, SIM AD 6 (Four Modules)

- Band-Master ATS Shield Termination
- Qwik-Ty Strain Relief



527-542

This split EMI banding backshell fits SIM AD 6 four-module connectors




Split, snap-together backshell attaches to connector with spring clip. Cable shields attach to backshell with .12 inch (3.0 mm) wide **Band-Master ATS®** Micro band strap. Composite thermoplastic with passivated stainless steel hardware and beryllium copper spring clip.

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction.

Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123

PART NUMBER				
Sample PN→		527-542	XM	B
Base P/N		527-542		
Finish	XM	Electroless Nickel		
	XW	Olive Drab Cadmium		
Bands	Omit	No Band		
	B	Micro Band Included (qty. 4)		
	J	Micro Slim Band Included (qty. 4)		



527-586

EMI Backshell, SIM AD 6 (Two Modules)

- Band-Master ATS Shield Termination
- Qwik-Ty Strain Relief



527-586

This split EMI banding backshell fits SIM AD 6 two-module connectors

Split, snap-together backshell attaches to connector with spring clip. Cable shields attach to backshell with .12 inch (3.0 mm) wide **Band-Master ATS®** Micro band strap. Composite thermoplastic with passivated stainless steel hardware and beryllium copper spring clip.

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Micro Slim bands have reduced thickness for weight reduction.






Band Type and Width	Hand Tool	Pneumatic Tool
Micro: .12 (3.0)	601-101	601-107
Micro Slim: .12 (3.0)	601-122	601-123

PART NUMBER

Sample PN → **527-586 XM B**


Base P/N	527-586
Finish	XM Electroless Nickel XW Olive Drab Cadmium
Bands	Omit No Band B Micro Band Included (qty. 2) J Micro Slim Band Included (qty. 2)



527-407

Clampshell, EN4165, BACC65BU/CA

■ Nickel-Plated Composite




527-407


*This clampshell fits EN4165 and
BACC65BU/CA single-module connectors*

Available in straight, 45° and 90° versions. Compression-type strain relief features anti-rotation detents. Nickel-plated composite thermoplastic with stainless steel screws.


527A407XM (90° ENTRY)




527C407XM (90° ENTRY)



527B407XM (45° ENTRY)




527D407XM (45° ENTRY)




PART NUMBER

Entry Style	Entry Location	Part No.
Straight	N/A	527S407XM
90°	Left or Right	527A407XM
	Top or Bottom	527C407XM
45°	Left or Right	527B407XM
	Top or Bottom	527D407XM



527S407XM (STRAIGHT ENTRY)



Modular Rectangular (EPXB, BACC65, EN4165, SIM)

**527-493**

Clampshell, EN4165, Extended Length

- Nickel-Plated Composite
- For EN4165 Fiber Optic Modules







**527-493**

Extended-length clampshell fits EN4165 single-module fiber optic connectors

Available in straight, 45° and 90° versions. Compression-type strain relief features anti-rotation detents. Nickel-plated composite thermoplastic with stainless steel screws.

PART NUMBER

Entry Style	Entry Location	Part No.
Straight	N/A	527S493XM
90°	Left or Right	527A493XM
	Top or Bottom	527C493XM
45°	Left or Right	527B493XM
	Top or Bottom	527D493XM

**527S493XM (STRAIGHT ENTRY)****527A493XM (90° ENTRY)****527C493XM (90° ENTRY)****527B493XM (45° ENTRY)****527D493XM (45° ENTRY)**

DPX / AS81659
BACKSHELLS
FOR ARINC 404
RACK-AND-PANEL
CONNECTORS



Complete DPX / AS81659 backshell capability: solid, split-shell, environmental, non-environmental, EMI/RFI, strain relief and more.



AS 81659 split-shell EMI backshell with Qwik-Ty strain relief

Line Replaceable Units (LRUs) are incorporated into avionic racks in commercial and military aircraft. Installation and maintenance of avionic equipment is facilitated through the use of rack-and-panel connectors which mate and demate without the use of mechanical coupling. On the cable side, these rack-and-panel connectors are equipped with backshell accessories to address common environmental, electrical, and mechanical stress problems which can damage cables and cable-to-connector terminations. Glenair supplies the complete range of DPX / AS81659 (ARINC 404) connector accessories and backshells for cable strain relief, environmental sealing, and EMI/RFI shield termination.

**Glenair Signature Series
AS81659 / DPX Backshells**



Glenair signature DPX backshell with integrated EMI/RFI band porch


Glenair signature DPX strain-relief backshell with split-shell construction




AS81659 / DPX Backshell Selection Guide

AS81659
Strain Reliefs

AS81659 Saddle
Clamp Backshell
507-001
Page F-2



AS81659 Qwik-Ty
Strain Relief
507-002
Page F-3



AS81659 Saddle Clamp
Strain Relief
507-249
Page F-4

AS81659
EMI Backshells

AS81659 EMI Banding
Backshell
507-011
Page F-5



AS81659 EMI TAG Ring
Backshell
507-059
Page F-6




AS81659 EMI M25
Backshell
507-117
Page F-7




AS81659 EMI Cone-
and-Ring Backshell
527-083
Page F-8



AS81659 EMI Banding
Split Composite
Backshell
527-476
Page F-9

DPX
EMI
Backshells

DPX2 EMI TAG Ring
Backshell
527-070
Page F-10



DPX4 EMI TAG Ring
Backshell
527-142
Page F-11

507-001

Backshell, AS81659, Split, Saddle Clamp

■ For unshielded wire bundles




507-001

This split, saddle-clamp backshell fits AS81659 connectors


Saddle clamp strain relief. Aluminum with stainless steel hardware.

PART NUMBER			
Sample PN→		507-001	-M -H
Base P/N	507-001		
Finish	-M Electroless Nickel -TZ Zin-Zinc -NF Olive Drab Cadmium		
Mounting Hardware	Omit No Hardware -H Hardware Included (4) #2-56 screws and (4) lockwashers		



507-002


Qwik-Ty, AS81659



507-002

This Qwik-Ty strain relief fits AS81659 connectors

Black anodized aluminum with stainless steel hardware.



PART NUMBER

Sample PN → **507-002** **L** **H**Base P/N **507-002**

Mounting


- A** Angle Mount Right
- B** Back Mount
- C** Angle Mount Left
- D** 90° Back Mount
- L** Left Mount
- R** Right Mount

Mounting Hardware

- Omit** No Hardware
- H** Hardware Included (4) #2-56 screws and (4) lockwashers


507-002A

ANGLE MOUNT RIGHT




507-002C

ANGLE MOUNT LEFT




507-002D

90° BACK MOUNT




507-002B

BACK MOUNT




507-002L

LEFT MOUNT



507-002R


RIGHT MOUNT



DPX / AS81659

507-249

Saddle Clamp Strain Relief, AS81659



507-249

Saddle-clamp backshell fits AS81659 connectors

Available in three mounting styles. Aluminum with stainless steel screws and washers. Captivated nut is silver-plated SST.

PART NUMBER

Sample PN→

507-249

M

B

H

Base P/N 507-249

Finish

M Electroless Nickel
JF Cadmium with Yellow Chromate
TZ Tin-Zinc
NF Olive Drab Cadmium


Mounting

A Angle Mount Left
B Back Mount
C Angle Mount Right


Mounting Hardware

Omit No Hardware
H Hardware Included (4) #2-56 screws and (4) lockwashers


507-249*B BACK MOUNT



507-249*A AND C ANGLE MOUNT LEFT AND RIGHT



MOUNTING HARDWARE "H" OPTION



507-011

Backshell, EMI Banding, AS81659



507-011

EMI banding backshell fits AS81659 connectors

Available with one or two ports. Terminate cable braid shield to backshell with **Band-Master ATS®** banding strap. Backshell includes RFI gasket and four #2-56 mounting screws and lockwashers.

Aluminum with stainless steel hardware and aluminum mesh/neoprene gasket.

TABLE 1 ENTRY SIZE

Entry Size	ø A Min		ø B		ø C Max	
	in	mm	in	mm	in	mm
01	.250	6.4	.375	9.5	.425	10.8
02	.375	9.5	.500	12.7	.550	14.0
03	.500	12.7	.625	15.9	.675	17.1
04 ⁽¹⁾	.625	15.9	.750	19.1	.800	20.3
05 ⁽¹⁾	.750	19.1	.875	22.2	.925	23.5

(1) Entry Sizes 04 and 05 not available for entry locations L and R

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

PART NUMBER

Sample PN →

507-011

M

04T

03B

J

Base P/N 507-011

Finish **M** Electroless Nickel
TZ Tin-Zinc
NF Olive Drab Cadmium

Port Entry Size 01 02 03 04 05 See Table 1

1


Entry Location B F L R T See Drawing

Port Entry Size Omit Port 2 Deleted 01 02 03 04 05 See Table 1

2

Entry Location Omit Port 2 Deleted B F L R T See Drawing

Band **Omit** No Band
K Standard Band Included (one per port)
J Slim Standard Band Included (one per port)



DPX / AS81659

507-059

Backshell, EMI TAG Ring®, AS81659




507-059

EMI TAG Ring® backshell fits AS81659 connectors

Backshell has slotted ring, gold-plated ground spring and PTFE friction washer for terminating individual wire shields. Two strain relief options: saddle clamp or nut. Nut requires shrink boot for cable strain relief.

Aluminum with stainless steel hardware. Gold-plated beryllium copper ground spring, Teflon friction washer.


TAG® RING



PART NUMBER									
Sample PN→					507-059		NF	04	L
Base P/N		507-059							
Finish	M	Electroless Nickel							
	TZ	Tin-Zinc							
	NF	Olive Drab Cadmium							
Entry Size		02 03 04 05 06 See Table 1							
Strain Relief	L	Saddle Clamp							
	G	Nut							
Entry Location	Omit	Top Entry							
	L	Left Side							
	R	Right Side							


TABLE 1 ENTRY SIZE

Entry Size	ø E		ø F Max		ø G Max		J Max		Cable Range			
	in	mm	in	mm	in	mm	in	mm	Min	mm	Max	mm
02	.25	6.4	.55	14.0	.69	17.5	.97	24.6	.125	3.2	.250	6.4
03	.37	9.4	.67	17.0	.79	20.1	1.05	26.7	.250	6.4	.375	9.5
04	.50	12.7	.80	20.3	.92	23.4	1.16	29.5	.250	6.4	.500	12.7
05	.62	15.7	.92	23.4	1.04	26.4	1.22	31.0	.375	9.5	.625	15.9
06	.75	19.1	1.05	26.7	1.17	29.7	1.34	34.0	.500	12.7	.750	19.1



507-117

Backshell, EMI, AS81659, M25 Thread



507-117

EMI backshell with M25 thread fits
AS81659 connectors

Backshell has M25 thread and interface teeth compatible with Adapter Code H (D38999 Series III/IV) size 17 fittings.

Aluminum with stainless steel hardware.


PART NUMBER

Sample PN → 507-117

NF

Base P/N 507-117

Finish	M	Electroless Nickel
	JF	Cadmium with Yellow Chromate
	TZ	Tin-Zinc
	NF	Olive Drab Cadmium




DPX / AS81659 BACKSHELLS

DPX / AS81659

527-083

Backshell, EMI Cone-and-Ring, AS81659



527-083

EMI Cone-and-Ring split backshell fits AS81659 connectors

Cone-and-ring shield termination.
Aluminum with stainless steel hardware, gasket is aluminum mesh embedded in neoprene.

CONE-AND-RING





TABLE 1 ENTRY SIZE

Entry Size	A Max		Cable Range			
	in	mm	Min	Max	Min	Max
-02	.968	24.6	.125	3.2	.250	6.4
-03	1.046	26.6	.250	6.4	.375	9.5
-04	1.156	29.4	.312	7.9	.500	12.7
-05	1.218	30.9	.438	11.1	.625	15.9
-06	1.343	34.1	.562	14.3	.750	19.1
-07	1.468	37.3	.687	17.4	.875	22.2
-08	1.593	40.5	.812	20.6	1.000	25.4

PART NUMBER						
Sample PN→						
527-083 -05 NF R S A						
Base P/N	527-083					
Entry Size	-02 -03 -04 -05 -06 -07 -08 See Table 1					
Finish	M Electroless Nickel JF Cadmium with Yellow Chromate TZ Tin-Zinc NF Olive Drab Cadmium					
EMI Gasket	Omit None R EMI Gasket Included					
Shield Type	Omit Overall Braid Shield S Individual Braid Shields					
Mounting Screws	Omit None A Socket Head Screws H Fillister Head Screws CA Captivated Socket Head Screws CH Captivated Fillister Head Screws					



527-476

Backshell, EMI Banding, AS81659/ DPXB

- Composite Split
- Band-Master ATS Shield Termination




527-476

Split EMI backshell fits AS81659 connectors

Lightweight composite material. Terminate cable braid shield to backshell with **Band-Master ATS®** banding strap. Options include slots for individual wire shields and Qwik-Ty arm.

Thermoplastic with stainless steel hardware and aluminum mesh/neoprene gasket.

FIGURE 1
POLYSULFIDE OPTION



BAND OPTIONS


Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

PART NUMBER


Sample PN →		527-476	XM		S	T	K		G
Base P/N	527-476								
Finish	XM	Electroless Nickel							
	XW	Olive Drab Cadmium							
Connector Code	Omit	All AS81659 Connectors except for Connector Code P1. Backshell Replaces Insert Retainer Plates.							
	P1	DPX**E and Class E Environmental Connectors with Interfacial and Grommet Seal. Backshell Installs on Insert Retainer Plates.							
Slot Option	Omit	None							
	S	Slots Included							
Qwik-Ty Option	Omit	None							
	T	Qwik-Ty Strain Relief Arm Included							
Band Option	Omit	No Band							
	K	Standard Band Included							
	J	Slim Standard Band Included							
Polysulfide Option	Omit	None							
	P	Polysulfide Stripes (Finish Code XW Only, fig. 1)							
EMI Gasket	Omit	None							
	G	EMI Gasket Included							



DPX / AS81659

527-070

Backshell, EMI TAG Ring, DPX2




527-070

EMI TAG Ring® backshell fits DPX2 connectors

Fits ITT Cannon DPX2 connectors. Backshell has slotted ring, gold-plated ground spring and Teflon friction washer for terminating individual wire shields. Two strain relief options: saddle clamp or nut (*nut requires shrink boot for cable strain relief*).

Aluminum with stainless steel hardware. Gold-plated beryllium copper ground spring, Teflon friction washer.

TAG® RING



SHRINK BOOT


Optional lipped heatshrink boot fits .135 (3.4) wide boot groove. Type 1 high-performance semi-rigid elastomer resists fuels and oils and withstands temperature extremes. Operating temperature range -75 to +150 °C.



Part Number 770-001S108


PART NUMBER

Sample PN→		527-070	M	L	S	T
Base P/N		527-070				
Finish	M	Electroless Nickel				
	JF	Cadmium with Yellow Chromate				
	TZ	Tin-Zinc				
	NF	Olive Drab Cadmium				
Strain Relief	Omit	Nut				
	L	Saddle Clamp				
Entry Location	Omit	Top Entry				
	S	Side Entry				
Shrink Boot	Omit	None				
	T	Shrink Boot Included (770-001S108)				



527-142

Backshell, EMI TAG Ring, DPX4




527-142

EMI TAG Ring® backshell fits DPX4 connectors

Fits ITT Cannon DPX4 connectors. Backshell has slotted ring, gold-plated ground spring and PTFE friction washer for terminating individual wire shields. Two strain relief options: saddle clamp or nut (nut requires shrink boot for cable strain relief).

Aluminum with stainless steel hardware. Gold-plated beryllium copper ground spring, PTFE friction washer.

TAG® RING



SHRINK BOOT





Optional lipped heatshrink boot fits .135 (3.4) wide boot groove. Type 1 high-performance semi-rigid elastomer resists fuels and oils and withstands temperature extremes. Operating temperature range -75 to +150 °C.



Part Number 770-001S108

PART NUMBER

Sample PN →		527-142	M	L	S
Base P/N		527-142			
Finish	M	Electroless Nickel			
	JF	Cadmium with Yellow Chromate			
	TZ	Tin-Zinc			
	NF	Olive Drab Cadmium			
Strain Relief	Omit	Nut			
	L	Saddle Clamp			
Entry Location	Omit	Top Entry			
	S	Side Entry			
Shrink Boot	Omit	None			
	S	Shrink Boot Included (770-001S108)			



△ BACKSHELL HEIGHT TOP ENTRY IS 2.00 (50.8), SIDE ENTRY IS 2.50 (63.8)

DPX / AS81659 BACKSHELLS

M83733/DPK TYPE
BACKSHELLS,
STRAIN RELIEFS
AND ACCESSORIES




Cable strain relief and
EMI/RFI shield termination
backshells for M83733 / DPK
connectors



MIL-C-83733 connectors are utilized in military aircraft applications and are subject to severe electrical, environmental, and mechanical stress. The cable side of these rack-and-panel connectors must be equipped with strain relief or cable shield termination backshells in accordance with DLA specifications. Glenair's split-shell backshells for MIL-C-83733 connectors are available in three designs which offer either a standard cable clamp, saddle-bar style strain-relief, or an EMI shield banding platform. Tongue-and-groove joints in the split-shell designs provide optimal electromagnetic compatibility. Backshells may be ordered with up to six cable entry locations for complete flexibility in wire and cable routing.

**Glenair Signature Series
M83733 Backshells**



Glenair designs available with six cable entry locations



Light and medium-duty cable strain relief

M83733 / DPK Backshell Selection Guide

M83733 Strain Relief




Straight Clamp
Strain Relief
507-013
Page G-2


M83733 EMI Backshells




Cone-and-Ring
Backshell
501-001
Page G-3



M83733 EMI Banding
Backshell
507-078
Page G-4



M83733 EMI Elliptical
Banding Backshell
507-158
Page G-5



M83733 EMI Elliptical
Banding Backshell
527-466
Page G-6

M83733 / DPK Backshells



507-013

Strain Relief, Straight Clamp, M83733



507-013

Straight clamp strain relief fits M83733 connectors

Fits ITT Cannon DPK and MIL-DTL-83733 connectors. Saddle bars have cushions to prevent damage to wire insulation.

Aluminum with stainless steel hardware, fluorosilicone cushions.

PART NUMBER


Sample PN → **507-013** **B** **M**

Base P/N **507-013**

Shell Size **A**
B

Finish **Omit** Olive Drab Cadmium
TZ Tin-Zinc
M Electroless Nickel

Shell Size	Connector Series	A		C	
		± .062 (1.57) in	mm	± .005 (0.13) in	mm
A	DPKA	2.437	61.9	1.895	48.1
B	DPKB / DPJM	3.750	95.3	3.195	81.2



M83733 / DPK Backshells

501-001

Backshell, EMI Cone-and-Ring, M83733



501-001

EMI Cone-and-Ring backshell fits M83733 connectors

Fits ITT Cannon DPK and MIL-DTL-83733 connectors. Available with 1-3 ports located on top, ends or sides. Cone-and-ring shield termination.

Aluminum with stainless steel hardware.

CONE-AND-RING





TABLE 1 ENTRY SIZE


Entry Size	Cable Range				M Max	
	in	Min	Max	mm	in	mm
01	.062	1.6	.125	3.2	.781	19.8
02	.125	3.2	.250	6.4	.968	24.6
03	.250	6.4	.375	9.5	1.046	26.6
04	.312	7.9	.500	12.7	1.156	29.4
05	.437	11.1	.625	15.9	1.218	30.9
06	.562	14.3	.750	19.1	1.343	34.1
07	.687	17.4	.875	22.2	1.468	37.3



PART NUMBER

Sample PN→		501-001	NF	B	A06	B03	E03	
Base P/N		501-001						
Finish	M	Electroless Nickel						
	TZ	Tin-Zinc						
	NF	Olive Drab Cadmium						
Shell Size		A B						
Port 1	Location	A B C D E F						See Drawing
	Entry Size	01 02 03 04 05 06 07						See Table 1
Omit Ports 2-3 for single entry location. When Location "C" and/or "D" are selected, Location "B" cannot be selected. When "C" and "D" are both selected, the maximum entry size is "02".								
Port 2	Location	A B C D E F	See Drawing					
	Entry Size	01 02 03 04 05 06 07	See Table 1					
Port 3	Location	A B C D E F	See Drawing					
	Entry Size	01 02 03 04 05 06 07	See Table 1					

Shell Size	A		B		C	
	in	mm	in	mm	±.005 (0.13)	mm
A	2.095	53.2	1.000	25.4	1.895	48.1
B	3.395	86.2	1.000	25.4	3.195	81.1




M83733 / DPK Backshells



507-078

Backshell, EMI Banding, M83733



507-078

EMI banding backshell fits M83733 connectors

Fits ITT Cannon DPK and MIL-DTL-83733 connectors. Available with 1-3 ports located on top, end or side. Attach cable braid to backshell with **Band-Master ATS®** banding strap. Backshell is supplied with three EMI gaskets: entry gasket, backshell/connector interface and connector/panel interface.

Aluminum with stainless steel hardware.
Backshell gaskets: metalastic.
Connector interface gasket: monel mesh.

TABLE 1 ENTRY SIZE

Entry Size	in	mm	in	mm	in	mm
02	.250	6.4	.375	9.5	.438	11.1
03	.375	9.5	.500	12.7	.562	14.3
04	.500	12.7	.625	15.9	.688	17.5
05	.625	15.9	.750	19.1	.812	20.6
06	.750	19.1	.875	22.2	.938	23.8
07*	.875	22.2	1.000	25.4	1.062	27.0

* Entry 07 available on entry location "F" only

BAND OPTIONS


Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

PART NUMBER

Sample PN→		507-078	NF	A	A05	B04	E03	K
Base P/N		507-078						
Finish	M	Electroless Nickel						
	TZ	Tin-Zinc						
	NF	Olive Drab Cadmium						
Shell Size	A							
	B							
Port 1	Location	A B C D E F	See Drawing					
	Entry Size	02 03 04 05 06 07	See Table 1					
Omit Ports 2-3 for single entry location. When Location "C" and/or "D" are selected, Location "B" cannot be selected.								
Port 2	Location	A B C D E F	See Drawing					
	Entry Size	02 03 04 05 06 07	See Table 1					
Port 3	Location	A B C D E F	See Drawing					
	Entry Size	02 03 04 05 06 07	See Table 1					
Band Option	Omit	No Band						
	K	Standard Band Included (1 per port)						
	J	Slim Standard Band Included (1 per port)						




M83733 / DPK Backshells



507-158

Backshell, EMI Banding, Top Entry, M83733

- Elliptical Top Entry
- Band-Master ATS Shield Termination



507-158

EMI banding backshell fits M83733 connectors

Fits ITT Cannon DPK and MIL-DTL-83733 connectors. Elliptical top entry accepts large wire bundles. Attach cable braid to backshell with **Band-Master ATS®** banding strap. Attach cable tie (not supplied) to optional Qwik-Ty arm for cable strain relief. Backshell is supplied with three EMI gaskets: entry gasket, backshell/connector interface and connector/panel interface.

Aluminum with stainless steel hardware.
Backshell gaskets: metalastic.
Connector interface gasket: monel mesh.

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.




Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

PART NUMBER

Sample PN → 507-158 NF -B J

Base P/N	507-158
Finish	M Electroless Nickel TZ Tin-Zinc NF Olive Drab Cadmium
Shell Size	-A -B
Qwik-Ty Option	Omit None T Qwik-Ty Included
Band	Omit No Band K Standard Band Included J Slim Standard Band Included




Shell Size	A		B		C		ø E	
	in	mm	in	mm	± .005 (0.13) in	mm	in	mm
A	2.095	53.2	1.000	25.4	1.895	48.1	1.125	28.6
B	3.395	86.2	1.000	25.4	3.195	81.1	1.375	34.9

M83733 / DPK Backshells

527-466

Backshell, EMI Banding, End Entry, DPKB

- Elliptical End Entry
- Band-Master ATS Shield Termination



527-466

EMI banding backshell fits DPKB connectors

Fits ITT Cannon DPKB and MIL-DTL-83733 shell size B connectors. Elliptical end entry accepts large wire bundles. Attach cable braid to backshell with **Band-Master ATS®** banding strap. Attach cable tie (not supplied) to optional Qwik-Ty arm for cable strain relief.

Aluminum with stainless steel hardware.

BAND OPTIONS

Terminate cable braid to backshell with optional band strap and banding tool. Pre-coiled bands are passivated stainless steel. Slim Standard bands have reduced thickness for weight reduction.



Band Type and Width	Hand Tool	Pneumatic Tool
Standard: .24 (6.1)	601-100	601-106
Slim Standard: .24 (6.1)	601-109	601-110

PART NUMBER

Sample PN→

527-466

NF

B

T

K

S

Base P/N 527-466



Finish
M Electroless Nickel
TZ Tin-Zinc
NF Olive Drab Cadmium

Shell Size **B**

Qwik-Ty Option
Omit None
T Qwik-Ty Included

Band Option
Omit No Band
K Standard Band Included
J Slim Standard Band Included

Hardware Option
Omit None
S #4-40 Mounting Screws and Lockwashers Included



Index

000-01-51-172..... B-10	500-012..... B-42	527-265..... E-3	687-316..... A-21
000-01-51-173..... B-10	500-015..... B-19	527-268..... E-7	687-345..... A-17
000-01-XX-132..... B-20	500-016..... B-23	527-281..... E-4	687-418..... A-19
000-01-XX-162..... B-10	500-017..... B-5	527-407..... E-12	687-439..... B-19
000-01-XX-163..... B-10	500-024..... A-23	527-410..... E-5	687-626..... A-19
000-01-XX-164..... B-10	500-037..... B-9	527-464..... D-10	687-695..... B-19
000-01-XX-165..... B-10	500-047..... B-32	527-466..... G-6	780-518..... A-7
080-00-00-100..... B-16	500-068..... A-23	527-475..... D-6	780-555..... B-10
080-00-00-101..... B-16	500-069..... B-16	527-476..... F-9	799-011..... C-13
080-00-00-502..... B-14	500-107..... B-7	527-493..... E-13	799-013..... C-3
080-00-00-503..... B-14	500-147..... B-12	527-495..... E-9	799-015..... C-15
080-00-00-505..... B-14	501-001..... G-3	527-531..... E-8	799-016..... C-16
080-00-00-506..... B-14	507-001..... F-2	527-542..... E-10	799-018..... C-5
080-00-00-512..... B-14	507-002..... F-3	527-543..... D-15	799-019..... C-5
080-00-00-513..... B-14	507-011..... F-5	527-586..... E-11	799-038..... C-7
080-00-00-515..... B-14	507-013..... G-2	550-004..... A-24	799-039..... C-7
080-00-00-516..... B-14	507-035..... B-22	550-005..... A-26	799-064..... C-4
177-504..... B-17	507-059..... F-6	550-009..... A-28	799-065..... C-4
177-505..... B-18	507-078..... G-4	550-039..... A-30	799-067..... C-9
179-013-1H..... B-15	507-088..... B-29	550-041..... A-32	799-117..... C-10
179-013-1S..... B-15	507-117..... F-7	550-100..... A-34	799-131..... C-18
179-013-2H..... B-15	507-142..... B-31	550-102..... A-36	799-164..... C-19
179-013-2S..... B-15	507-145..... B-39	550-186..... A-38	799-172..... C-12
179-135..... B-21	507-146..... B-44	550-200..... A-11	799-176..... C-10
179-162-1H..... B-15	507-158..... G-5	557-071..... A-43	M83513/05-02..... B-14
179-162-1S..... B-15	507-175..... B-33	557-107..... A-56	M83513/05-03..... B-14
179-162-2H..... B-15	507-178..... B-40	557-110..... A-45	M83513/05-05..... B-14
179-162-2S..... B-15	507-198..... B-45	557-246..... A-47	M83513/05-06..... B-14
179-221..... B-17	507-249..... F-4	557-281..... A-58	M83513/05-07..... B-16
289-003..... A-4	507-296..... B-35	557-316..... A-49	M83513/05-12..... B-14
289-004..... A-4	507-297..... B-37	557-319..... A-60	M83513/05-13..... B-14
289-005..... A-64	507-299..... B-46	557-432..... A-51	M83513/05-15..... B-14
289-007..... A-66	527-025..... D-8	557-467..... A-53	M83513/05-16..... B-14
289-008..... A-68	527-056..... D-5	557-493..... A-13	M83513/05-17..... B-16
289-015..... A-15	527-070..... F-10	557-538..... A-40	
289-016..... A-15	527-071..... D-9	557-553..... A-54	
289-019..... A-4	527-083..... F-8	557-561..... A-62	
289-052..... A-8	527-114..... D-14	557-609..... A-42	
289-062..... A-16	527-126..... D-11	557-666..... A-9	
289-064..... A-14	527-142..... F-11	559-001..... A-15	
289-085..... A-70	527-149..... D-7	559-002..... A-22	
289-087..... A-71	527-199..... D-12	601-***..... Intro-1	
289-181..... A-10	527-216..... D-13	687-092..... A-17	
500-008..... A-5	527-254..... E-6	687-152..... B-19	
500-010..... B-25	527-257..... D-3	687-172..... A-19	
500-011..... B-27	527-260..... E-2	687-236..... A-19	



MISSION-CRITICAL INTERCONNECT SOLUTIONS

Glenair, Inc.

1211 Air Way • Glendale, California • 91201-2497

Telephone: 818-247-6000 • Fax: 818-500-9912 • sales@glenair.com

www.glenair.com

Glenair East

20 Sterling Drive
Wallingford, CT
06492

Telephone:
203-741-1115
Facsimile:
203-741-0053
sales@glenair.com

Glenair UK Ltd

40 Lower Oakham Way
Oakham Business Park
Mansfield, Notts
NG18 5BY England

Telephone:
+44-1623-638100
Facsimile:
+44-1623-638111
sales@glenair.co.uk

Glenair Microway Systems

7000 North Lawndale Avenue
Lincolnwood, IL
60712

Telephone:
847-679-8833
Facsimile:
847-679-8849

Glenair Nordic AB

Gustav III:s Boulevard 42
SE-169 27 Solna
Sweden

Telephone:
+46-8-50550000
sales@glenair.se

Glenair GmbH

Schaberweg 28
61348 Bad Homburg
Germany

Telephone:
06172 / 68 16 0
Facsimile:
06172 / 68 16 90
info@glenair.de

Glenair Iberica S.L.

Av. De Manoteras, 24 – 2º
28050 Madrid
Spain

Telephone:
+34 915 562 687
sales@glenair.es

Glenair Italia S.p.A.

Via Del Lavoro, 7
40057 Quarto Inferiore –
Granarolo dell'Emilia
Bologna, Italy

Telephone:
+39-051-782811
Facsimile:
+39-051-782259
info@glenair.it

Glenair France SARL

7, Avenue Parmentier
Immeuble Central Parc #2
31200 Toulouse
France

Telephone:
+33-5-34-40-97-40
Facsimile:
+33-5-61-47-86-10
sales@glenair.fr

Glenair Korea

6-21Tapsil-ro 58beon-gil
Giheung-gu, Yongin-si
Gyeonggi-do
Republic of Korea

Telephone:
+82-07-5067-2437
Facsimile:
+82-504-375-4549
sales@glenair.kr

Glenair Japan

40F, Nagoya Lucent Tower,
6-1, Ushijima-cho,
Nishi-ku, Nagoya, 451-6040
Japan

Telephone:
+81-52-569-2521
Facsimile:
+81-52-569-2523
sales@glenair.jp