


SF2238E

**2560 MHz
SAW Filter**



SM3030-6

- **Low-loss RF SAW Filter**
- **Surface-mount 3.0 x 3.0 x 1.3 mm Package**
- **Complies with Directive 2002/95/EC (RoHS)**
- **Moisture Sensitivity Level: 1**

Absolute Maximum Ratings

| Rating | Value | Units |
|---|------------|-------|
| Input Power Level | 10 | dBm |
| DC Voltage on any Non-ground Terminal | 3 | V |
| Operating Temperature Range | -30 to +85 | °C |
| Storage Temperature Range | -40 to +95 | °C |
| Solder Reflow Temperature, 10 seconds, 5 cycles maximum | 260 | °C |

Electrical Characteristics

| Characteristic | Sym | Notes | Min | Typ | Max | Units |
|--|---|-------|-----|-------|-------|-------------------|
| Center Frequency | F_C | | | 2560 | | MHz |
| Maximum Insertion Loss, 2545 to 2575 MHz | IL | | | 2.4 | 4.0 | dB |
| Amplitude Ripple, 2545 to 2575MHz | | | | 0.8 | 2.0 | dB _{p-p} |
| VSWR, 2545 to 2575 MHz | | | | 1.3:1 | 2.3:1 | |
| Attenuation Referenced to 0 dB: | | | | | | |
| DC to 1100 MHz | | | 37 | 42.5 | | dB |
| 1100 to 1880 MHz | | | 31 | 42.5 | | |
| 1880 to 2280 MHz | | | 43 | 46 | | |
| 2280 to 2420 MHz | | | 40 | 43.5 | | |
| 2420 to 2460 MHz | | | 30 | 43 | | |
| 2460 to 2490 MHz | | | 10 | 23 | | |
| 2635 to 2655 MHz | | | 20 | 45 | | |
| 2655 to 3100 MHz | | | 41 | 45 | | |
| 3100 to 4000 MHz | | | 29 | 37 | | |
| Source Impedance | Z_S | | | 50 | | Ω |
| Load Impedance | Z_L | | | 50 | | |
| Case Style | SM3030-6 3.0 x 3.0 mm Nominal Footprint | | | | | |
| Lid Symbolization (Y=year, WW=week, S=shift) dot=pin 1 indicator | 972, <u>YWW</u> S | | | | | |
| Standard Reel Quantity | Reel Size 7 Inch | | | | | 500 Pieces/Reel |
| | Reel Size 13 Inch | | | | | 3000 Pieces/Reel |






CAUTION: Electrostatic Sensitive Device. Observe precautions for handling.

NOTES:



1. The design, manufacturing process, and specifications of this device are subject to change.
2. US or International patents may apply.
3. RoHS compliant from the first date of manufacture.

Filter Response Plots






Input/Output VSWR Plots





Filter Test Circuit



| Connection | Terminals |
|------------|------------|
| Input | 2 |
| Output | 5 |
| Ground | All Others |

SM3030-6 Case

6-Terminal Ceramic Surface-Mount Case 3.0 X 3.0 mm Nominal Footprint



PCB Footprint Top View


Case and PCB Footprint Dimensions

| Dimension | mm | | | Inches | | |
|-----------|------|------|------|--------|-------|-------|
| | Min | Nom | Max | Min | Nom | Max |
| A | 2.87 | 3.00 | 3.13 | 0.113 | 0.118 | 0.123 |
| B | 2.87 | 3.00 | 3.13 | 0.113 | 0.118 | 0.123 |
| C | 1.12 | 1.25 | 1.38 | 0.044 | 0.049 | 0.054 |
| D | 0.77 | 0.90 | 1.03 | 0.030 | 0.035 | 0.040 |
| E | 2.67 | 2.80 | 2.93 | 0.105 | 0.110 | 0.115 |
| F | 1.47 | 1.60 | 1.73 | 0.058 | 0.063 | 0.068 |
| G | 0.72 | 0.85 | 0.98 | 0.028 | 0.033 | 0.038 |
| H | 1.37 | 1.50 | 1.63 | 0.054 | 0.059 | 0.064 |
| I | 0.47 | 0.60 | 0.73 | 0.019 | 0.024 | 0.029 |
| J | 1.17 | 1.30 | 1.43 | 0.046 | 0.051 | 0.056 |
| K | | 3.20 | | | 0.126 | |
| L | | 1.70 | | | 0.067 | |
| M | | 1.05 | | | 0.041 | |
| N | | 0.81 | | | 0.032 | |
| O | | 0.38 | | | 0.015 | |



Case Materials

| Materials | |
|--------------------|--|
| Solder Pad Plating | 0.3 to 1.0 μm Gold over 1.27 to 8.89 μm Nickel |
| Lid Plating | 2.0 to 3.0 μm Nickel |
| Body | Al_2O_3 Ceramic |

TOP VIEW




BOTTOM VIEW




Tape and Reel Specifications

Tape and Reel Standard per ANSI/EIA-481




| "B" | | Quantity Per Reel |
|--------|-------------|-------------------|
| Inches | millimeters | |
| 7 | 178 | 500 |
| 13 | 330 | 3000 |



COMPONENT ORIENTATION and DIMENSIONS

| Carrier Tape Dimensions | |
|-------------------------|---------|
| Ao | 3.35 mm |
| Bo | 3.35 mm |
| Ko | 1.40 mm |
| Pitch | 8.0 mm |
| W | 12.0 mm |



Recommended Reflow Profile

1. Preheating shall be fixed at 150~180°C for 60~90 seconds.
2. Ascending time to preheating temperature 150°C shall be 30 seconds min.
3. Heating shall be fixed at 220°C for 50~80 seconds and at 260°C +0/-5°C peak (10 seconds).
4. Time: 5 times maximum.

