

## Uni-Dicht-Verschraubung Pg29, 14-18mm



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 00 000 5094                                                                |
| Specification      | Uni-Dicht-Verschraubung Pg29,<br>14-18mm                                      |
| HARTING eCatalogue | <a href="https://harting.com/09000005094">https://harting.com/09000005094</a> |

### Identification

|                   |             |
|-------------------|-------------|
| Category          | Accessories |
| Type of accessory | Cable gland |

### Technical characteristics

|                                        |                                                          |
|----------------------------------------|----------------------------------------------------------|
| Tightening torque                      | ≤20 Nm (depending on the cable and the seal insert used) |
| Wrench size                            | 40                                                       |
| Limiting temperature                   | -40 ... +130 °C                                          |
| Degree of protection acc. to IEC 60529 | IP68                                                     |
| Size                                   | Pg 29                                                    |
| Clamping range                         | 14 ... 18 mm                                             |

### Material properties

|                             |                                                                                     |
|-----------------------------|-------------------------------------------------------------------------------------|
| Material (cable glands)     | Metal                                                                               |
| RoHS                        | compliant with exemption                                                            |
| RoHS exemptions             | 6(c): Copper alloy containing up to 4 % lead by weight                              |
| ELV status                  | compliant with exemption                                                            |
| China RoHS                  | 50                                                                                  |
| REACH Annex XVII substances | Not contained                                                                       |
| REACH ANNEX XIV substances  | Not contained                                                                       |
| REACH SVHC substances       | Yes                                                                                 |
| REACH SVHC substances       | Lead<br>2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326) |
| ECHA SCIP number            | 6fb545c1-f438-46c2-b07a-8552e7e5a3d7                                                |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |        |
|--------------------------------------|--------|
| California Proposition 65 substances | Yes    |
| California Proposition 65 substances | Lead   |
|                                      | Nickel |

## Commercial data

|                                |                                           |
|--------------------------------|-------------------------------------------|
| Packaging size                 | 10                                        |
| Net weight                     | 120.115 g                                 |
| Country of origin              | Germany                                   |
| European customs tariff number | 74122000                                  |
| GTIN                           | 5713140001756                             |
| eCl@ss                         | 27140801 Screwed cable gland (electrical) |
| ETIM                           | EC000441                                  |
| UNSPSC 24.0                    | 39121431                                  |