

DIN-Power E048-B pcb 2,8 w locking lever



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series	DIN 41612
Type of accessory	Pin shroud
Description of the accessory	for type E with press-in pins With locking levers

Version

Fixing	Press-in fixing
--------	-----------------

Technical characteristics

Isolation group	IIIa (175 ≤ CTI < 400)
PCB thickness	2.8 mm +0.2 2.8 mm -0.3

Material properties

Material (accessories)	Thermoplastic
Colour (accessories)	RAL 7032 (pebble grey) Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Material properties

REACH SVHC substances	Not contained
-----------------------	---------------

Specifications and approvals

Railway classification	F1/I2 acc. to NFF 16-101/102
------------------------	------------------------------

Commercial data

Packaging size	56
Net weight	7.2 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140008786
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400