

## Han 1A-3+PE-C-f shielded, latch



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Inserts
Series	Han® 1A

### Version

Termination method	Crimp termination
Gender	Female
Size	1 A
Shielding	With cable tie
Number of contacts	3
Further contacts	+ shielding
PE contact	Yes
Locking type	Snap-in latches
Details	<p>Please order crimp contacts separately. Order separately the hoods/housings for an IP65 performance.</p>

A Han® 1A configuration that only consists of inserts (with or without strain relief, 09 10 000 5300) is an unenclosed connector according to IEC 61984. In this case protection against electric shock must be provided by the installation methods of the user.

Details	<p>The Han® 1A insert has no conductive connection between PE-contact and shielding element. Protection against electric shock must be provided by connecting the cable shielding to a protective earth (PE).</p> <p>Contact inserts must not be coupled or decoupled under electrical load.</p> <p>Contact inserts must not be powered-up in the un-mated condition.</p>
Pack contents	Shielding element is included within the delivery

## Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm <sup>2</sup>
Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated current acc. to UL	15 A AWG 14
Rated voltage acc. to UL	600 V
Insulation resistance	>10 <sup>8</sup> Ω
Limiting temperature	-30 ... +90 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP20

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	EN 45545-2 Fire protection on railway vehicles IEC 61373 Category 1 Class B IEC 60664-1 IEC 61984
----------------	--

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 Please contact your local HARTING subsidiary for further information.
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	15.8 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140185500
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522