






PART NUMBER		SML-LX0404SIUPGUSB	REV	D
REV	E.C.N. NUMBER AND REVISION COMMENTS			DATE
A	E.C.N. #11941			05.11.15
B	E.C.N. #11956			06.03.15
C	ECN-Lumex201700046			08.10.17
D	ECN-Lumex202300094			08.10.23



RECOMMENDED SOLDER PAD LAYOUT



ELECTRO-OPTICAL CHARACTERISTIC TA=25°C

PARAMETER		MIN	TYP	MAX	UNITS	TEST COND
PEAK WAVELENGTH	R	-	632	-	nm	If=2mA
	G	-	518	-		
	B	-	468	-		
DOMINANT WAVELENGTH	R	622	-	632	nm	If=2mA
	G	524	-	538		
	B	465	-	475		
FORWARD VOLTAGE	R	1.75	-	2.15	Vf	If=2mA
	G	2.60	-	2.95		
	B	2.60	-	2.85		
REVERSE CURRENT	R	-	-	10	uA	VR=5V
	G	-	-	50		
	B	-	-	50		
LUMINOUS INTENSITY	R	25	-	45	mcd	If=2mA
	G	35	-	65		
	B	16	-	24		
VIEWING ANGLE		-	120	-	2x theta1/2	-
EMITTED COLOR	RED / GREEN / BLUE					
EPOXY LENS FINISH	WATER CLEAR					

ABSOLUTE MAXIMUM RATINGS TA=25°C

PARAMETER	MAX	UNITS
PEAK FORWARD CURRENT(R/G/B)*	60 / 100 / 20	mA
FORWARD CURRENT(R/G/B)	25 / 25 / 10	mA
POWER DISSIPATION(R/G/B)	60 / 95 / 30	mW
STORAGE TEMPERATURE	-40 TO +90	°C
OPERATING TEMPERATURE	-40 TO +85	°C

*t<10us

MOISTURE SENSITIVE DEVICE
PER JEDEC LEVEL 2 STANDARDS

NOTE:
1.THE PRODUCT ITSELF WILL REMAIN WITHIN RoHS COMPLIANT VERSION.

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= ^{+DECIMAL PRECISION}/_{-0.00} MAX= ^{+0.00}/_{-DECIMAL PRECISION}



425 N. GARY AVE.
CAROL STREAM, IL 60188
PHONE : 800-278-5666
FAX : 630-315-2150
WEB : WWW.LUMEX.COM

1(L)*1(W)*0.25(H)mm, SURFACE MOUNT TOP VIEW LED,AlGaInP RED / InGaN GREEN / InGaN BLUE, WATER CLEAR LENS, TAPE & REEL.

THE SPECIFICATIONS MAY CHANGE AT ANY TIME WITHOUT NOTICE.

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

DATE : 2017.08.11

DRAWN BY : E.C

PAGE : 1 OF 2

CHKD BY : T.S.


SCALE : NTF

APRVD BY : G.Y


UNIT : mm [INCH]



SOLDERING PROFILE



CARRIER TAPE DIMENSION



*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= ^{+DECIMAL PRECISION}_{-0.00} MAX.= ^{+0.00}_{-DECIMAL PRECISION}



425 N. GARY AVE.
CAROL STREAM, IL 60188
PHONE : 800-278-5666
FAX : 630-315-2150
WEB : WWW.LUMEX.COM

1(L)*1(W)*0.25(H)mm, SURFACE MOUNT TOP VIEW LED,AlGaInP RED / InGaIn GREEN / InGaIn BLUE, WATER CLEAR LENS, TAPE & REEL.

THE SPECIFICATIONS MAY CHANGE AT ANY TIME WITHOUT NOTICE DUE.

CONFIDENTIAL INFORMATION

THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

DATE : 2017.08.11

DRAWN BY : E.C

PAGE : 2 OF 2

CHKD BY : T.S.

SCALE : NTF

APRVD BY : G.Y

UNIT : mm [INCH]

Ⓢ