

W48- X - XX - X - X - X - X

SWITCH FUNCTION CODE	SWITCH FUNCTION DESCRIPTION
E	MOMENTARY SOLDER TERMINAL
F	MAINTAINE SOLDER TERMINAL
G	MOMENTARY P.C. TERMINAL
H	MAINTAINE P.C. TERMINAL

BEZEL CODE	BEZEL DESCRIPTION
RB	ROUND, BLACK
SB	SQUARE, BLACK (ONLY FOR BUSHING MOUNTING)


ILLUMINATION CODE	LED COLOR DESCRIPTION
R	RED
A	AMBER
Y	YELLOW
G	GREEN
B	BLUE
W	WHITE
RG	RED/BLUE
RB	RED/GREEN

BUTTON CODE	BUTTON COLOR DESCRIPTION
BK	BLACK
RD	RED
GR	GREEN
BL	BLUE
YL	YELLOW
OR	ORANGE
WH	WHITE
PK	POWER/STANDBY BLACK (ONLY FOR ROUND BEZEL & BUSHING MOUNT)



MOUNTING CODE	MOUNTING STYLE DESCRIPTION
B	BUSHING
F	SNAP FIT (ONLY FOR ROUND BEZEL)

LED VOLTAGE CODE	LED VOLTAGE DESCRIPTION
IF BLANK	SEE LED SPEC.
05	5V (SEE NOTE3)

MECHANICAL CHARACTERISTICS:
SWITCH CIRCUITRY: SPST-NO-DB
SWITCH ACTION: MOMENTARY AND MAINTAINED (PER CHART)
BUTTON TRAVEL: 2.3mm NOMINAL
OPERATING FORCE: 3N [306g] NOMINAL
PANEL THICKNESS:
BUSHING MOUNT: 0.5 - 3.0mm
SNAP MOUNT: 1mm/2mm/3mm ± 0.05
CONTACTS: GOLD PLATED
NUT TORQUE FORCE: MAX 6 kgf-cm[5.2 LB-in]
ENVIRONMENTAL SPECIFICATIONS:
ACTUATOR INGRESS PROTECTION: IP67

LED SPECIFICATION					
LED CODE	LED SINGLE COLOR		Vf(VDC)	If (mA)	
			TYP.		
R	RED		2.0	20	
A	AMBER		2.0	20	
Y	YELLOW		2.0	20	
G	GREEN		3.0	20	
B	BLUE		3.1	20	
W	WHITE		3.3	20	
LED CODE	BICOLOR LED		Vf(VDC)	If (mA)	CIRCUITRY
	COLOR1	COLOR2	TYP.		
RB	RED	BLUE	2.0(RED) 3.3(BLUE)	20	
RG	RED	GREEN	2.0(RED) 3.4(GREEN)	20	






NOTE:
Hand Soldering Temperature (4mm above from Body) : 320°C for 3 seconds



NOTE




- 1.CURRENT LIMITING RESISTOR IS REQUIRED TO LIMIT LED FORWARD CURRENT TO 20mA
2. SUPPLY HEX NUT AND SEALING WASHER BULK PACKED.
- 3.INNER RESISTOR ONLY FOR LED :RED / BLUE / GREEN / WHITE.

DWG TYPE SALES DRAWING	DRAWN <i>K.Y.</i>	TOLERANCES: UNLESS OTHERWISE NOTED X.X ± 0.5 X.XX ± 0.25 ANGULAR ± 5°	DWG TITLE W48-MECHANICAL MOMENTARY/MAINTAINED, CENTER SPOT/POWER-STANDBY ILLUMINATION					
STATUS RELEASE	REVIEW		DWG NO. W48-E,F,G,H					
This document is the intellectual property of ITW Electronic Business Asia Co., Limited and may contain confidential, proprietary, privileged information protected by law. Neither this document nor any information it contains can be reproduced, transformed to any other format, or distributed, without written permission by ITW Electronic Business Asia Co., Limited. 本文為安天德百電股份有限公司之智慧財產，非經許可不得複製、複製、轉變成其他形式使用或散佈	APPROVED <i>v.w.</i>	THIRD ANGLE PROJECTION 	■ 管制文件 □ 非管制文件 Unit mm SCALE REV 1				RoHS Compliant	SHEET 1 OF 3
	DATE 2010/3/11	REF: ---						



RECOMMENDED P.C. BOARD HOLE PATTERN
(FOR PC TERMINAL)
COMPONENT SIDE




DETAIL OF TERMINAL POSITION



REFERENCE

PANEL CUT-OUT

PANEL THICKNESS: 0.5-3mm



RECOMMENDED PANEL CUT-OUT

PANEL THICKNESS: 1.0mm , 2.0mm , 3.0mm ± 0.5

SWITCH ACTION	BUTTON TYPE	FP(mm)
MOMENTARY	ILLUMINATION LIGHT PIPE BUTTON	7.6±0.5
MAINTAINED	ILLUMINATION LIGHT PIPE BUTTON	6.0±0.5

DWG TYPE SALES DRAWING	DRAWN K.Y.	TOLERANCES: UNLESS OTHERWISE NOTED X.X ± 0.5		DWG TITLE W48-MECHANICAL MOMENTARY/MAINTAINED, CENTER SPOT/POWER-STANDBY ILLUMINATION				ITW SWITCH LUMEX			
STATUS RELEASE	REVIEW	X.XX ± 0.25 ANGULAR ± 5°		DWG NO. W48-E,F,G,H							
This document is the intellectual property of ITW Electronic Business Asia Co., Limited and may contain confidential, proprietary, privileged information protected by law. Neither this document nor any information it contains can be reproduced, transformed to any other format, or distributed, without written permission by ITW Electronic Business Asia Co., Limited. 本文件為安天德百電股份有限公司之智慧財產，非經許可不得擷取、複製、轉變成其他形式使用或散佈	APPROVED v.w.	THIRD ANGLE PROJECTION 						■ 管制文件 □ 非管制文件 Unit mm SCALE REV 1			
	DATE 2010/3/11	REF: ---									