

## Han Q12-M-QL 1,5mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 012 3004
Specification	Han Q12-M-QL 1,5mm <sup>2</sup>
HARTING eCatalogue	<a href="https://harting.com/09120123004">https://harting.com/09120123004</a>

### Identification

Category	Inserts
Series	Han® Q
Identification	12/0
Specification	With Han-Quick Lock® PE contact

### Version

Termination method	Crimp termination
Gender	Male
Size	3 A
Number of contacts	12
PE contact	Yes
Details	Black slide (PE: 0.25 ... 1.5 mm <sup>2</sup> ) Please order crimp contacts separately.
Details	for stranded wire according to IEC 60228 Class 5

### Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm <sup>2</sup>
Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C

## Technical characteristics

Mating cycles	≥500
---------------	------

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	10
Net weight	10.72 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140018037

## Commercial data

eCl@ss 27440205 Contact insert for industrial connectors

ETIM EC000438

UNSPSC 24.0 39121522