

Series 44 Banding Backshells

for MIL-DTL-38999 Series III and IV Connectors

440H*069 Banding Backshell, Shrink Boot, Self-Locking



Self-Locking

Adapter Code H

This accessory fits these connectors:
MIL-DTL-38999 Series III and Series IV

PROFILE SELECTION GUIDE

S Straight 	C 90° Low Profile Split
D 90° Split	F 45° Split
H 45° Cut and Weld	J 90° Cut and Weld
M 45° Full Radius	N 90° Full Radius


PART NUMBER

		440HS069	ZI	17	06-	4	K	P	T	
Base P/N	Base Part No.	Profile								
	440HS069	S	Straight							
	440HC069	C	90° Split Low Prof.							
	440HD069	D	90° Split							
	440HF069	F	45° Split							
	440HH069	H	45° Cut/Weld							
	440HJ069	J	90° Cut/Weld							
	440HM069	M	45° Full Radius							
440HN069	N	90° Full Radius								
Material/Finish	M	Alum/ Electroless Nickel								
	MT	Alum/ Nickel-PTFE								
	NF	Alum/ Olive Drab Cadmium								
	ZR	Alum/ Black Zinc-Nickel								
	TZ	Alum/ Tin-Zinc								
	ZI	SST/ Passivated (Profiles H, J, M, N, S only)								
Shell Size	Shell Size	9	11	13	15	17	19	21	23	25
	Size Code	A	B	C	D	E	F	G	H	J
		09	11	13	15	17	19	21	23	25
Entry Size	Size	Inside Dia.	Shell Sizes*	Size	Inside Dia.	Shell Sizes*				
	01	.125 (3.2)	09-25	07	.875 (22.2)	19-25				
	31	.188 (4.8)	09-25	37	.938 (23.8)	21-25				
	02	.250 (6.4)	09-25	08	1.000 (25.4)	21-25				
	32	.312 (7.9)	11-25	38	1.062 (27.0)	23-25				
	03	.375 (9.5)	11-25	09	1.125 (28.6)	23-25				
	33	.438 (11.1)	13-25	10	1.250 (31.8)	25				
	04	.500 (12.7)	13-25	11	1.375 (34.9)	-				
	34	.562 (14.3)	15-25	12	1.500 (38.1)	-				
	05	.625 (15.9)	15-25	13	1.625 (41.3)	-				
	35	.688 (17.5)	17-25	14	1.750 (44.5)	-				
	06	.750 (19.1)	17-25	15	1.875 (47.6)	-				
	36	.812 (20.6)	19-25	16	2.000 (50.8)	-				
	* If selected entry size exceeds shell size range, a Style 2 transition adapter will be included. See Maximum Entry Size for details. ⚠ Profile G entry size cannot exceed shell size range listed in table.									
Length	3	1.5 inches	Applies to Profile S only.							
	4	2.0 inches	If Entry Size is greater than "Maximum Entry Size" (see table), then 2 inch							
	5	2.5 inches	minimum applies.							
	6	3.0 inches								
Band	Omit if not required									
	K	Pre-Coiled Band Included With Backshell								
Polysulfide	Omit if not required. Applies to Plating Codes NF, ZR, TZ only.									
	P	Nickel Plated Shield Termination Area with Polysulfide Barrier								
Shrink Boot	Omit if not required									
	T	Shrink Boot Included With Backshell								
	TI	Adhesive-lined Shrink Boot Included With Backshell								

Series 44 Banding Backshells

for MIL-DTL-38999 Series III and IV Connectors

440H*069 Banding Backshell, Shrink Boot, Self-Locking



Shell Size	A Thread	$\varnothing B$ Max		C Max.		D Max.		G Max.		H Max.		N Max.		P Max.		R Max.		S Max.	
		in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
9 (A)	M12X1.0-6H	.94	24.8	.806	20.5	1.038	26.4	.906	23.0	1.146	29.1	.968	24.6	1.017	25.8	1.281	32.5	1.335	33.9
11 (B)	M15X1.0-6H	1.06	26.9	.832	21.1	1.064	27.0	.966	24.5	1.210	30.7	1.031	26.2	1.071	27.2	1.406	35.7	1.460	37.1
13 (C)	M18X1.0-6H	1.17	29.7	.856	21.7	1.088	27.6	1.026	26.0	1.268	32.2	1.094	27.8	1.121	28.5	1.531	38.9	1.585	40.3
15 (D)	M22X1.0-6H	1.29	32.7	.882	22.4	1.114	28.3	1.076	27.3	1.330	33.8	1.156	29.4	1.175	29.8	1.656	42.1	1.710	43.4
17 (E)	M25X1.0-6H	1.42	36.1	.908	23.1	1.150	29.2	1.136	28.8	1.392	35.4	1.218	30.9	1.224	31.1	1.781	45.2	1.835	46.6
19 (F)	M28X1.0-6H	1.54	39.1	.927	23.5	1.190	30.2	1.176	29.9	1.438	36.5	1.250	31.8	1.274	32.4	1.906	48.4	1.960	49.8
21 (G)	M31X1.0-6H	1.67	42.4	.953	24.2	1.250	31.8	1.236	31.4	1.500	38.1	1.312	33.3	1.328	33.7	2.031	51.6	2.085	53.0
23 (H)	M34X1.0-6H	2.01	51.1	.979	24.9	1.320	33.5	1.296	32.9	1.562	39.7	1.344	34.1	1.382	35.1	2.156	54.8	2.210	56.1
25 (J)	M37X1.0-6H	2.12	53.8	1.004	25.5	1.380	35.1	1.356	34.4	1.625	41.3	1.406	35.7	1.431	36.3	2.281	57.9	2.335	59.3


Shell Size	T Max.	U Max.	V Max.	W Max.	X Max.	Y Max.	Z Max.	Profile C	
	in	mm	in	mm	in	mm	in	mm	Max. Wire Bundle
9 (A)	.596	15.1	1.635	41.5	.836	21.2	1.575	40.0	.496
11 (B)	.656	16.7	1.695	43.1	.906	23.0	1.635	41.5	.426
13 (C)	.716	18.2	1.765	44.8	.966	24.5	1.705	43.3	.426
15 (D)	.776	19.7	1.795	45.6	1.026	26.1	1.735	44.1	.436
17 (E)	.836	21.2	1.895	48.1	1.086	27.6	1.835	46.6	.576
19 (F)	.906	23.0	1.955	49.7	1.156	29.4	1.895	48.1	.796
21 (G)	.976	24.8	2.015	51.2	1.216	30.9	1.955	49.7	.796
23 (H)	1.036	26.3	2.075	52.7	1.276	32.4	2.015	51.2	.696
25 (J)	1.096	27.8	2.135	54.2	1.336	33.9	2.075	52.7	.696

Series 44 Banding Backshells

for MIL-DTL-38999 Series III and IV Connectors

440H*069 Banding Backshell, Shrink Boot, Self-Locking

ENTRY SIZE



Entry Size	Shell Sizes	øK ± .015 (0.4) in mm		øL ± .015 (0.4) in mm		øM ± .015 (0.4) in mm	
01	09-25	.125	3.2	.250	6.4	.312	7.9
31	09-25	.188	4.8	.312	7.9	.375	9.5
02	09-25	.250	6.4	.375	9.5	.438	11.1
32	11-25	.312	7.9	.438	11.1	.500	12.7
03	11-25	.375	9.5	.500	12.7	.562	14.3
33	13-25	.438	11.1	.562	14.3	.625	15.9
04	13-25	.500	12.7	.625	15.9	.687	17.4
34	15-25	.562	14.3	.688	17.5	.750	19.1
05	15-25	.625	15.9	.750	19.1	.812	20.6
35	17-25	.688	17.5	.812	20.6	.875	22.2
06	17-25	.750	19.1	.875	22.2	.938	23.8
36	19-25	.812	20.6	.938	23.8	1.000	25.4
07	19-25	.875	22.2	1.000	25.4	1.062	27.0
37	21-25	.938	23.8	1.062	27.0	1.125	28.6
08	21-25	1.000	25.4	1.125	28.6	1.188	30.2
38	23-25	1.062	27.0	1.188	30.2	1.250	31.8
09	23-25	1.125	28.6	1.250	31.8	1.312	33.3
10	25	1.250	31.8	1.375	34.9	1.438	36.5
11	-	1.375	34.9	1.500	38.1	1.562	39.7
12	-	1.500	38.1	1.625	41.3	1.688	42.9
13	-	1.625	41.3	1.750	44.5	1.812	46.0
14	-	1.750	44.5	1.875	47.6	1.938	49.2
15	-	1.875	47.6	2.000	50.8	2.062	52.4
16	-	2.000	50.8	2.125	54.0	2.188	55.6


MAXIMUM ENTRY SIZE

If the selected entry size exceeds the maximum size in this table, the backshell will have a front adapter. This is called a **Style 2** backshell.

△ Profile G backshells are not available with entry sizes larger than shown in table.


Shell Size	Max. Entry Size	Shell Size	Max. Entry Size
9(A)	02	19(F)	07
11(B)	03	21(G)	08
13(C)	04	23(H)	09
15(D)	05	25(J)	10
17(E)	06		

Style 2 Straight Backshell



For Style 2 straight backshells, the minimum length code increases from 3 (1 1/2 inches) to 4 (2 inches).


Style 2 45° and 90° Backshells



For Style 2 45° and 90° backshells, the length increases by one inch.

SHRINK BOOT

Optional heatshrink boot provides cable strain relief and environmental protection. Type 1 high-performance semi-rigid elastomer resists fuels and oils and withstands temperature extremes. Available with W1 hot melt adhesive pre-coat. Operating temperature range -75 to +150 °C (no adhesive), -55 to +125 °C (with W1 adhesive).



Entry Sizes	Shrink Boot P/N	Adhesive Lined Shrink Boot P/N
01-31	770-003S111	770-003S111W1
02-32	770-003S112	770-003S112W1
03	770-001S103	770-001S103W1
33-35	770-001S104	770-001S104W1
06-37	770-001S105	770-001S105W1
08-38	770-001S106	770-001S106W1
09-12	770-001S107	770-001S107W1
13-14	770-001S108	770-001S108W1
15-16	770-001S109	770-001S109W1

BAND

Optional SST band strap provides fast, cost-effective and highly reliable termination of braided metallic shielding. The **Band-Master ATS® Advanced Cable Shield Termination System** is the overwhelming favorite throughout the military aerospace and defense industries, providing excellent static loading and corrosion resistance in electrical wire interconnect systems.



Band
601-041



Banding Tool
601-100

POLYSULFIDE

Optional selective electroless nickel plating on shield termination area and polysulfide dielectric barrier prevents galvanic mismatch between nickel-coated braid shield and backshell.

△ Plating codes NF, ZR and TZ only

