

## Han 70A crimp module 1500V, female




Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 14 002 3142  |
| Specification      | Han 70A crimp module 1500V, female  |
| HARTING eCatalogue | <a href="https://harting.com/09140023142">https://harting.com/09140023142</a> |

### Identification

|                    |                  |
|--------------------|------------------|
| Category           | Modules          |
| Series             | Han-Modular®     |
| Type of module     | Han® 70 A module |
| Size of the module | Single module    |

### Version

|                    |   |
|--------------------|---|
| Termination method | Crimp termination                       |
| Gender             | Female                                  |
| Number of contacts | 2                                       |
| Details            | Please order crimp contacts separately. |

### Technical characteristics

|                         |                          |
|-------------------------|--------------------------|
| Conductor cross-section | 6 ... 25 mm <sup>2</sup> |
| Wire outer diameter     | ≤11.5 mm                 |
| Rated current           | 70 A                     |
| Rated voltage           | 1,500 V                  |
| Rated impulse voltage   | 8 kV                     |
| Pollution degree        | 3                        |
| Insulation resistance   | >10 <sup>10</sup> Ω      |
| Limiting temperature    | -40 ... +125 °C          |
| Mating cycles           | ≥500                     |

## Material properties

|   |                                     |
|---|-------------------------------------|
| Material (insert)                         | Polycarbonate (PC)                  |
| Colour (insert)                           | RAL 7032 (pebble grey)              |
| Material flammability class acc. to UL 94 | V-0                                 |
| RoHS                                      | compliant                           |
| ELV status                                | compliant                           |
| China RoHS                                | e                                   |
| REACH Annex XVII substances               | Not contained                       |
| REACH ANNEX XIV substances                | Not contained                       |
| REACH SVHC substances                     | Not contained                       |
| California Proposition 65 substances      | Not contained                       |
| Fire protection on railway vehicles       | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels        | R22 (HL 1-3)<br>R23 (HL 1-3)        |

## Specifications and approvals

|                |                          |
|----------------|--------------------------|
| Specifications | IEC 60664-1<br>IEC 61984 |
|----------------|--------------------------|

## Commercial data

|                                |   |
|--------------------------------|---|
| Packaging size                 | 2   |
| Net weight                     | 11.767 g  |
| Country of origin              | China   |
| European customs tariff number | 85389099  |
| GTIN                           | 5713140479456   |
| eCl@ss                         | 27440217 Module for industrial connectors (power/signals) |
| ETIM                           | EC000438  |
| UNSPSC 24.0                    | 39121552  |