

Han CD module, crimp male



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 14 007 3001 |
| Specification | Han CD module, crimp male |
| HARTING eCatalogue | https://harting.com/09140073001 |

Identification

| | |
|--------------------|----------------------|
| Category | Modules |
| Series | Han-Modular® |
| Type of module | Han® CD module |
| Size of the module | Single module |
| Features | Finger safe contacts |

Version

| | |
|---------------------------|---|
| Termination method | Crimp termination |
| Gender | Male |
| Number of contacts | 7 |
| Number of signal contacts | 4 |
| Number of power contacts | 3 |
| Details | Please order crimp contacts separately. |

Technical characteristics

| | |
|-------------------------|---|
| Conductor cross-section | 0.14 ... 6 mm ² |
| Wire outer diameter | ≤4.8 mm 4.8 ... 6.4 mm Stripping length 15 mm and restricted contact removal |
| Rated current | 40 A |
| Rated voltage | 830 V |
| Rated impulse voltage | 8 kV |
| Pollution degree | 3 |
| Rated current (signal) | 10 A |

Technical characteristics

| | |
|--------------------------------|---|
| Rated voltage (signal) | 830 V |
| Rated impulse voltage (signal) | 8 kV |
| Pollution degree (signal) | 3 |
| Rated voltage acc. to UL | 600 V |
| Insulation resistance | $>10^{10} \Omega$ |
| Limiting temperature | -40 ... +125 °C |
| Mating cycles | $\geq 10,000$ |
| Note on the mating cycles | Mating cycles with other HMC components |

Material properties

| | |
|---|-------------------------------------|
| Material (insert) | Polycarbonate (PC) |
| Colour (insert) | RAL 7032 (pebble grey) |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels | R22 (HL 1-3) R23 (HL 1-3) |

Specifications and approvals

| | |
|----------------|--------------------------|
| Specifications | IEC 60664-1 IEC 61984 |
| UL / CSA | UL 1977 ECBT2.E235076 |
| Approvals | DNV GL |

Commercial data

| | |
|-------------------|---------|
| Packaging size | 2 |
| Net weight | 13.5 g |
| Country of origin | Germany |

Commercial data

| | |
|--------------------------------|---|
| European customs tariff number | 85389099 |
| GTIN | 5713140020566 |
| eCl@ss | 27440217 Module for industrial connectors (power/signals) |
| ETIM | EC000438 |
| UNSPSC 24.0 | 39121552 |