



THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS DE TERUGZENDING VERPLICHT.

REV.	DATE	DESCRIPTION	BY	C'K'D'
01	6-2-91	BEC 9.3036 :DIM 30.3 WAS 38.2	M B	
02	03-09-92	CAV. DIA. ENLARGED	Y.D.	
03	10-03-99	CONVERSION ME10	K.N.	
04	10-03-99	TEMPERATURE RANGE -55C INSTEAD OF -25C	K.N.	




MALE POWER CONTACTS (7*): SEE NOTE 1
MOULDED-IN TRILOK RING



SIGNAL CAVITY (2*)
POWER CAVITIES (6*)
GROUNDING CAVITY (1*): FM/LB POS.

SECTION CC



PERFORMANCE CHARACTERISTICS

- OPERATING TEMPERATURE : -55 °C TO +125 °C.
- INSULATION RESISTANCE : 5000 MΩ MIN.
- TEST POTENTIAL : 2000 V EFF.
- CONNECTOR AS PER VDE 0110 GROUPE 660V


MATERIAL

- BODY : GLASS-FILLED POLYESTER UL94-V0
COLOUR : BLACK.
- TRILOK RING: HIGH STRENGTH CUZN ALLOY, NI PLATED

NOTES

1. CONTACTS TO BE ORDERED SEPARATELY
2. FOR ADDITIONAL INFORMATION REFER TO TRIM-TRIO CATALOG.
3. CONNECTOR TO BE MATED WITH UTG6247SN

GEN. ST.	01		02		03		04		05		06		07		08		0D		50		60		70		80		90				
INT. ST.	10	11	12	13	14	18	20	31	32	33	34	38	39	40	42	43	44	45	46	48	56	70	72	73	75	76	81	82	83	84	88

1DEC ±0,2 1DEC 2DEC ±0,1 2DEC ANGLES ±1° HOEKEN	APPR.	DATE	SIGN.	MALE RECEPTACLE	
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.	DRAFT	26-9-90	M BUEDS	CAT. No. UTG0247P	
	CHECKED			 SOURIAU Connection Technology	SOURIAU Route Nationale 23 72470 CHAMPAGNE
	PROD. MGR.				
ALL DIMENSIONS IN MM	PR.ENG. MGR.			SCALE	
	PR.MGT. MGR.			BS, A , 201178 , 004	
	REFERENCES / REFERENTIES			NOT EXPORT CONTROLLED	
				DRAWING NR.	CUSTOMER DRAWING
ALLE AFMETINGEN IN MM				REV	STON