

## Han-Mod RJ45 IDC cable jack 8P AWG 24-22



Image is for illustration purposes only. Please refer to product description.

### Identification

|               |                      |
|---------------|----------------------|
| Category      | Inserts              |
| Element       | Data connectors      |
| Specification | Han® RJ45 cable jack |

### Version

|                    |   |
|--------------------|---|
| Termination method | IDC insulation displacement termination |
| Gender             | Female                                  |
| Number of contacts | 8                                       |

### Technical characteristics

|                               |                                |
|-------------------------------|--------------------------------|
| Conductor cross-section [AWG] | AWG 24 ... AWG 22              |
| Wire outer diameter           | 1.7 mm                         |
| Transmission characteristics  | Cat. 6A Class EA up to 500 MHz |
| Data rate                     | 10 Mbit/s                      |
|                               | 100 Mbit/s                     |
|                               | 1 Gbit/s                       |
|                               | 2.5 Gbit/s                     |
|                               | 5 Gbit/s                       |
|                               | 10 Gbit/s                      |
| Limiting temperature          | -40 ... +70 °C                 |
| Mating cycles                 | ≥500                           |
| Cable diameter                | 5 ... 9 mm                     |

### Material properties

|                   |                |
|-------------------|----------------|
| Material (insert) | Polyamide (PA) |
|-------------------|----------------|

## Material properties

|   |                              |
|---|------------------------------|
| Material (shielding)                      | Zinc die-cast, nickel-plated |
| Material flammability class acc. to UL 94 | V-0                          |
| RoHS                                      | compliant                    |
| ELV status                                | compliant                    |
| China RoHS                                | e                            |
| REACH Annex XVII substances               | Not contained                |
| REACH ANNEX XIV substances                | Not contained                |
| REACH SVHC substances                     | Not contained                |

## Specifications and approvals

|                |                          |
|----------------|--------------------------|
| Specifications | IEC 60664-1<br>IEC 61984 |
| Approvals      | DNV GL                   |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 20 g   |
| Country of origin              | Latvia   |
| European customs tariff number | 85389099   |
| GTIN                           | 5713140021587                                    |
| eCl@ss                         | 27440218 Module for industrial connectors (data) |
| ETIM                           | EC000438   |
| UNSPSC 24.0                    | 39121552   |