

Han 3 Quintax-M-c




Image is for illustration purposes only. Please refer to product description.

Part number	09 15 003 3001
Specification	Han 3 Quintax-M-c
HARTING eCatalogue	https://harting.com/09150033001

Identification

Category	Inserts
Series	Han-Brid®
Identification	Han-Brid® Quintax 3 A

Version

Termination method	Crimp termination			
Gender	Male			
Size	3 A			
Number of contacts	<table><tr><td>1</td></tr><tr><td>4</td></tr><tr><td>8</td></tr></table>	1	4	8
1				
4				
8				
further contacts	+ shielding + 2 power contacts			
Details	Please order crimp contacts separately.			

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	13 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140022560
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522