

M23 06 Male - solder (termination)



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 106 2602
Specification	M23 06 Male - solder (termination)
HARTING eCatalogue	https://harting.com/09151062602

Identification

Category	Inserts
Series	Circular connectors M23
Identification	Signal
Element	Inserts

Version

Termination method	Solder termination
Gender	Male
Number of contacts	6

Technical characteristics

Conductor cross-section	2.5 mm ² max.
Rated current	20 A
Rated voltage	300 V
Rated impulse voltage	2.5 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	White

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	052d6da0-30ef-44e8-bbe4-e75780521d22
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	6.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140162990
eCl@ss	27440223 Contact insert for circular connectors
ETIM	EC003557
UNSPSC 24.0	39121421