

## M23 P male-c 1mm (0,14–1mm<sup>2</sup>) Au

	Part number 09 15 600 6101
Specification M23 P male-c 1mm (0,14–1mm <sup>2</sup> ) Au	
HARTING eCatalogue <a href="https://harting.com/09156006101">https://harting.com/09156006101</a>	

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Contacts
Series	Circular connectors M23
Identification	Power
Type of contact	Crimp contact
Description of the contact	1 mm

### Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.14 ... 1 mm <sup>2</sup>
Rated current	≤10 A
Contact resistance	≤3 mΩ
Stripping length	7 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption

## Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	100
Net weight	0.37 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140189003
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522