

## M23 P fem.-c 0,6mm (0,08–0,34mm<sup>2</sup>) Au

	Part number 09 15 600 6291
Specification M23 P fem.-c 0,6mm (0,08–0,34mm <sup>2</sup> ) Au	
HARTING eCatalogue <a href="https://harting.com/09156006291">https://harting.com/09156006291</a>	

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Contacts
Series	Circular connectors M23
Identification	Power
Type of contact	Crimp contact
Description of the contact	0.6 mm

### Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.08 ... 0.34 mm <sup>2</sup>
Rated current	≤2 A
Contact resistance	≤3 mΩ
Stripping length	4 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption

## Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	100
Net weight	0.193 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140189041
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522