

Han Q5/0_I_F_PIT_0.5-2.5mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 005 5101
Specification	Han Q5/0_I_F_PIT_0.5-2.5mm ²
HARTING eCatalogue	https://harting.com/09120055101

Identification

Category	Inserts
Series	Han® Q
Identification	5/0

Version

Termination method	Push-In
Gender	Female
Size	3 A
Number of contacts	5
PE contact	Yes

Technical characteristics

Conductor cross-section	0.5 ... 2.5 mm ²
Rated current	16 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	10
Net weight	21 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140447905
eCl@ss	27440205 Contact insert for industrial connectors
UNSPSC 24.0	39121522