

Pneum.contact metal ID 10mm,female+valve



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	With shut-off Straight

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-40 ... +85 °C
Operating pressure	≤10 bar
Mating cycles	≥10,000
Tube inner diameter	10 mm

Material properties

Material (contacts)	Brass
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Material properties

REACH SVHC substances	Not contained
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Not contained

Commercial data

Packaging size	10
Net weight	31.3 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140189379
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522

