

## Adapter module for D-Sub, male - 1 cable




Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 14 000 9930                                                                |
| Specification      | Adapter module for D-Sub, male - 1 cable                                      |
| HARTING eCatalogue | <a href="https://harting.com/09140009930">https://harting.com/09140009930</a> |

### Identification

|                           |                       |
|---------------------------|-----------------------|
| Category                  | Modules               |
| Series                    | Han-Modular®          |
| Type of module            | Adapter module        |
| Size of the module        | Single module         |
| Description of the module | for D-Sub 1 (9 poles) |

### Version

|         |               |
|---------|---------------|
| Gender  | Male          |
| Details | for one cable |

### Technical characteristics

|                       |                   |
|-----------------------|-------------------|
| Insulation resistance | $>10^{10} \Omega$ |
| Limiting temperature  | -40 ... +125 °C   |
| Mating cycles         | $\geq 500$        |

### Material properties

|                                           |                                     |
|-------------------------------------------|-------------------------------------|
| Material (insert)                         | Polycarbonate (PC)<br>Zinc die-cast |
| Colour (insert)                           | RAL 7032 (pebble grey)              |
| Material flammability class acc. to UL 94 | V-0                                 |
| RoHS                                      | compliant                           |
| ELV status                                | compliant                           |
| China RoHS                                | e                                   |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| REACH Annex XVII substances          | Not contained                       |
| REACH ANNEX XIV substances           | Not contained                       |
| REACH SVHC substances                | Not contained                       |
| California Proposition 65 substances | Yes                                 |
| California Proposition 65 substances | Lead<br>Nickel                      |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels   | R22 (HL 1-3)<br>R23 (HL 1-3)        |

## Specifications and approvals

|                |                          |
|----------------|--------------------------|
| Specifications | IEC 60664-1<br>IEC 61984 |
| Approvals      | DNV GL                   |

## Commercial data

|                                |                                                  |
|--------------------------------|--------------------------------------------------|
| Packaging size                 | 1                                                |
| Net weight                     | 18 g                                             |
| Country of origin              | Germany                                          |
| European customs tariff number | 85389099                                         |
| GTIN                           | 5713140018655                                    |
| eCl@ss                         | 27440218 Module for industrial connectors (data) |
| ETIM                           | EC000438                                         |
| UNSPSC 24.0                    | 39121552                                         |