

## Han-Modular ECO base panel (with PE mark)



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 0321
Specification	Han-Modular ECO base panel (with PE mark)
HARTING eCatalogue	<a href="https://harting.com/09140010321">https://harting.com/09140010321</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Modular® ECO
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With PE identification (pin 1 = PE)

### Version

Size	Modular ECO
Locking type	Snap-in latches

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE

## Commercial data

Packaging size	2
Net weight	14.26 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019010
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466