

## Han module adapter, female



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 3111
Specification	Han module adapter, female
HARTING eCatalogue	<a href="https://harting.com/09140013111">https://harting.com/09140013111</a>

### Identification

Category	Modules
Series	Han-Modular®
Type of module	<ul style="list-style-type: none"><li>Han® Gigabit module</li><li>Han® Gigabit HMC module</li><li>Han® Megabit module</li><li>Han® Megabit HMC module</li><li>Han® Shielded module</li></ul>
Size of the module	Single module
Description of the module	Adapter module

### Version

Gender	Female
--------	--------

### Technical characteristics

Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +85 °C

### Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984 IEC 61373 Category 2
UL / CSA	UL 1977 ECBT2.E235076
Approvals	DNV GL

## Commercial data

Packaging size	2
Net weight	4 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019379
eCl@ss	27440207 Adapter for industrial connectors (module/contact insert)
ETIM	EC002312
UNSPSC 24.0	39121469