

Han 40A PCB module, male




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 002 2603
Specification	Han 40A PCB module, male
HARTING eCatalogue	https://harting.com/09140022603

Identification

Category	Accessories
Type of accessory	PCB adapter
Description of the accessory	In the Han® 40 A Axial module

Version

Gender	Male
--------	------

Technical characteristics

Rated current	40 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Limiting temperature	-40 ... +125 °C

Material properties

Material (insert)	Polycarbonate (PC)
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes

Material properties

REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61373 Category 1 Class B
----------------	------------------------------

Commercial data

Packaging size	2
Net weight	24.1 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019607
eCl@ss	27440217 Module for industrial connectors (power/signals)
ETIM	EC000438
UNSPSC 24.0	39121552