

Han shielded module basic plus, female



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Shielded module basic plus
Size of the module	Single module
Description of the module	With 360° shielding element

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	27
further contacts	+ shielding
Details	With additional shield connection to the hinged frame Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.09 ... 0.52 mm²
Wire outer diameter	≤2.3 mm
Rated current	4 A
Rated voltage	32 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C

Technical characteristics

Mating cycles	≥500
---------------	------

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984 IEC 61373 Category 1 Class B
----------------	----------------------------------------------------------

Commercial data

Packaging size	1
Net weight	13.645 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140185012
eCl@ss	27440218 Module for industrial connectors (data)
ETIM	EC000438
UNSPSC 24.0	39121552