

PP-V14-CC-IDC-RJ45-4P-P-M-STR-SHLD



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 229 0401
Specification	PP-V14-CC-IDC-RJ45-4P-P-M-STR-SHLD
HARTING eCatalogue	https://harting.com/09352290401

Identification

Category	Connectors
Series	Han® PushPull (V14) RJ45
Element	Connector
Specification	AIDA compliant PROFINET Multi Feature RJ45 Straight
Features	Suitable for all PoE versions

Version

Termination method	IDC insulation displacement termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	4
Coding	RJ45
Details	When installing a PROFINET system, observe the PROFINET installation guideline.

Technical characteristics

Conductor cross-section	0.12 ... 0.32 mm² Stranded 0.12 ... 0.32 mm² Solid
Conductor cross-section [AWG]	AWG 26/7 ... AWG 22/7 Stranded AWG 24/1 ... AWG 22/1 Solid
Wire outer diameter	0.8 ... 1.6 mm
Transmission characteristics	Cat. 5 Class D up to 100 MHz

Technical characteristics

Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +85 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	5 ... 8 mm
Vibration resistance	10-500 Hz, 0.35 mm / 50 m/s ² , 2h/axis 5.72 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	50 g / 30 ms, 3 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Surface (contacts)	Au over Ni Mating side Sn over Ni Termination side
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60603-7 Mating face ISO/IEC 11801 EN 50173-1 IEC 61076-3-117 Variant 14
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
----------------	---

Commercial data

Net weight	94.5 g
Country of origin	Latvia
European customs tariff number	85366990
GTIN	5713140224292
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408