

## M23 09 Male -C



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Inserts
Series	Circular connectors M23
Identification	Signal
Element	Inserts

### Version

Termination method	Crimp termination
Gender	Male
Number of contacts	9
Number of signal contacts	8
Number of special contacts	1x Auxiliary contact
Details	<p>Please order crimp contacts separately.</p> <p>8x 1 mm</p> <p>1x 2 mm</p>

### Technical characteristics

Conductor cross-section	0.08 ... 1.5 mm <sup>2</sup>
Rated current (signal)	8 A
Rated voltage (signal)	200 V
Rated impulse voltage (signal)	2.5 kV
Pollution degree (signal)	3
Rated current (special contact)	20 A
Rated voltage (special contact)	200 V
Rated impulse voltage (special contact)	2.5 kV

## Technical characteristics

Pollution degree (special contact)	3
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	$\geq 500$

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	White
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	be45dcda-0f90-459a-a8bc-78fb7986a295
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

## Commercial data

Packaging size	5
Net weight	2.8 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140187061
eCl@ss	27440223 Contact insert for circular connectors
ETIM	EC003557
UNSPSC 24.0	39121421