

## Han K 32-24-F-C



Image is for illustration purposes only. Please refer to product description.

Part number	09 38 056 3101
Specification	Han K 32-24-F-C
HARTING eCatalogue	<a href="https://harting.com/09380563101">https://harting.com/09380563101</a>

### Identification

Category	Inserts
Series	Han-Com®
Identification	Han® K 32/24

### Version

Termination method	Crimp termination
Gender	Female
Size	16 B
Number of contacts	56
Number of signal contacts	24
Number of power contacts	32
PE contact	Yes
Details	<p>Please order crimp contacts separately.</p> <p>32x Han E®</p> <p>24x Han D®</p>

### Technical characteristics

Conductor cross-section	0.14 ... 4 mm <sup>2</sup> Power 0.14 ... 2.5 mm <sup>2</sup> Signal
Rated current (signal)	10 A
Rated voltage (signal)	250 V
Rated impulse voltage (signal)	4 kV
Pollution degree (signal)	3

## Technical characteristics

Rated current (power)	16 A
Rated voltage (power)	500 V
Rated impulse voltage (power)	6 kV
Pollution degree (power)	3
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	75.8 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140186484
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438

Commercial data

UNSPSC 24.0

39121522

---