

Han F+B Hybrid Male



Image is for illustration purposes only. Please refer to product description.

Part number 09 15 512 3001

Specification Han F+B Hybrid Male

Identification

Category	Inserts
Series	Han® F+B

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	12
Number of data contacts	4
Number of signal contacts	4
Number of power contacts	4
PE contact	Yes
Details	<p>Please order crimp contacts separately.</p> <p>4x Han E®</p> <p>4x Han D®</p> <p>4x M12 for data element</p>

Technical characteristics

Conductor cross-section	0.14 ... 4 mm ²
Rated current (signal)	10 A
Rated voltage (signal)	250 V
Rated impulse voltage (signal)	4 kV
Pollution degree (signal)	3
Rated current (power)	20 A
Rated voltage (power)	400 V

Technical characteristics

Rated impulse voltage (power)	6 kV
Pollution degree (power)	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥3,000
Note on the mating cycles	Mating cycles with other HMC components

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0

Commercial data

Packaging size	1
Net weight	15.75 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140930124
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522