

Han3A RJ45 Hybrid 10G Cat6 plug 8+4p IDC



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 125 1760
Specification	Han3A RJ45 Hybrid 10G Cat6 plug 8+4p IDC
HARTING eCatalogue	https://harting.com/09451251760

Identification

Category	Connectors
Series	RJ45
Identification	Hybrid
Series of hoods/housings	Han A [®]
Element	Cable connector
Type of hood/housing	Hood
Description of hood/housing	Straight
Features	Suitable for all PoE versions

Version

Termination method	IDC insulation displacement termination
Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	12
Number of data contacts	8
Number of power contacts	4

Technical characteristics

Conductor cross-section	0.1 ... 0.32 mm ² Data 1.5 mm ² Power
Conductor cross-section [AWG]	AWG 27/7 ... AWG 22/7 Stranded (Data) AWG 27/1 ... AWG 22/1 Solid (Data) AWG 16 Power



Pushing Performance
 Since 1945

Technical characteristics

Wire outer diameter	≤1.6 mm (Data) ≤2.75 mm (Power)
Rated current (data)	1.76 A
Rated voltage (data)	50 V AC 60 V DC
Rated current (power)	16 A
Rated voltage (power)	48 V DC
Transmission characteristics	Cat. 6 Class E _A up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s
Limiting temperature	-40 ... +70 °C
Storage temperature	+5 ... +50 °C
Mating cycles	≥500
Cable diameter	6 ... 12 mm
Vibration resistance	10-500 Hz, 5 g, 0.35 mm, 2h/axis 7.9 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one
ECHA SCIP number	d361ed36-dee0-4df8-9f2e-b62dd7563c1a
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Lead Nickel
--------------------------------------	----------------

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	10
Net weight	35.55 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140058927
eCl@ss	27440113 Rectangular connectors (set)
ETIM	EC002636
UNSPSC 24.0	39121408