

## RJI RJ45 plug Cat5, 4p IDC AWG26




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 151 1109
Specification	RJI RJ45 plug Cat5, 4p IDC AWG26
HARTING eCatalogue	<a href="https://harting.com/09451511109">https://harting.com/09451511109</a>

### Identification

Category	Connectors
Series	HARTING RJ Industrial® RJ45
Element	Cable connector
Specification	Straight

### Version

Termination method	IDC insulation displacement termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	4
Pack contents	Hood with shielding Splicing element Cable gland Assembly instructions

### Technical characteristics

Conductor cross-section	0.12 mm <sup>2</sup> Stranded
Conductor cross-section [AWG]	AWG 26 Stranded
Wire outer diameter	1.6 mm
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +70 °C +5 ... +50 °C
Relative humidity	95 % Non-condensing (operation)

## Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP20
Cable diameter	4.5 ... 9 mm

## Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	EN 45545-2
Approvals	DNV GL
PROFINET	Yes

## Commercial data

Packaging size	10
Net weight	10 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140059344
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408