

## SEK-19 SV MA STD STR29 RLG 16P PL2 KINK




Image is for illustration purposes only. Please refer to product description.

Part number	09 19 516 6004
Specification	SEK-19 SV MA STD STR29 RLG 16P PL2 KINK

### Identification

Category	Connectors
Series	SEK Standard
Element	Male connector
Description of the contact	Straight Kinked

### Version

Termination method	Reflow soldering termination (THR)
Connection type	PCB to cable
Number of contacts	16
Termination length	2.9 mm
Locking type	With long levers

### Technical characteristics

Contact rows	2
Contact spacing (termination side)	2.54 mm
Rated current	1 A
Insulation resistance	$>10^9 \Omega$
Contact resistance	$\leq 20 \text{ m}\Omega$
Limiting temperature	-55 ... +125 °C (during reflow soldering max. +240 °C for 60 s)
Performance level	2 acc. to IEC 60603-13
Mating cycles	$\geq 250$



Pushing Performance  
Since 1945

## Technical characteristics

Test voltage $U_{r,m.s.}$	1 kV
Isolation group	II ( $400 \leq CTI < 600$ )
PCB thickness	1.5 mm +0.44

## Material properties

Material (insert)	Thermoplastic resin (PCT)
Colour (insert)	Beige
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 60603-13
----------------	--------------

## Commercial data

Packaging size	1
GTIN	5713140919525
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)



Pushing Performance  
Since 1945

Cross section of solder termination

