

## Ha-Vis EtherRail 4x2xAWG24/7 CAT7 100m



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 45 600 0692  |
| Specification      | Ha-Vis EtherRail 4x2xAWG24/7 CAT7 100m  |
| HARTING eCatalogue | <a href="https://harting.com/09456000692">https://harting.com/09456000692</a> |

### Identification

|                          |                          |
|--------------------------|--------------------------|
| Category                 | System cabling           |
| Element                  | Bulk cables              |
| Specification            | Not assembled            |
| Type of cable            | Copper cable (round)     |
| Description of the cable | for railway applications |

### Version

|                 |                |
|-----------------|----------------|
| Cable length    | 100 m          |
| Number of cores | 8              |
| Core structure  | 4x 2x AWG 24/7 |

### Technical characteristics

|                                       |  |
|---------------------------------------|--|
| Transmission characteristics          | Cat. 7 Class F up to 600 MHz                   |
| Data rate                             | 10 Mbit/s                                      |
|                                       | 100 Mbit/s                                     |
|                                       | 1 Gbit/s                                       |
|                                       | 2.5 Gbit/s                                     |
|                                       | 5 Gbit/s                                       |
|                                       | 10 Gbit/s                                      |
| Limiting temperature                  | -40 ... +80 °C unmoved<br>-25 ... +70 °C moved |
| Cable diameter                        | 8.1 mm ± 0.3 mm                                |
| Minimum bending radius                | 6x Cable diameter                              |
| Test voltage U <sub>r.m.s.</sub>      | 1 kV Wire / wire / shielding                   |
| Coupling attenuation @ 20 °C / 10 MHz | 5 mΩ/m   |

## Technical characteristics

Conductor resistance @ 20 °C  $\leq 84 \Omega/\text{km}$

Insulation resistance @ 20 °C  $\geq 5,000 \text{ M}\Omega \times \text{km}$

Signal run time @ 20 °C  $\leq 4.4 \text{ ns/m}$

Impedance @ 100 MHz  $100 \Omega \pm 5 \%$

## Material properties

Material (cable) Polyolefin copolymer electron beam crosslinked Comp 752

Colour (cable) Black

RoHS compliant

ELV status compliant

China RoHS e

REACH Annex XVII substances Not contained

REACH ANNEX XIV substances Not contained

REACH SVHC substances Not contained

California Proposition 65 substances Not contained

## Specifications and approvals

|                |  |
|----------------|--|
| Specifications | EN 45545-2 Fire protection on railway vehicles |
|                | EN 50264-1 Fire protection on railway vehicles |
|                | EN 50306-1 Fire protection on railway vehicles |
|                | NFPA 130 Fire protection on railway vehicles   |
|                | UN/ECE-R 118 fire protection for rolling stock |
|                | EN 50306-4 Resistance to ozone                 |
|                | EN 60811-504 High low temperature resistance   |
|                | EN 60811-404 High oil resistance               |
|                | EN 60811-404 High fuel resistance              |
|                | EN 60811-404 Alkali resistance                 |

## Commercial data

Packaging size 1

Net weight 7,000 g

Net weight 75 g/m

Country of origin Switzerland

European customs tariff number 85444290

GTIN 5713140273634

### Commercial data

|             |  |
|-------------|--|
| eCl@ss      | 27061801 Data and communication cable (copper) |
| ETIM        | EC003249                                       |
| UNSPSC 24.0 | 26121609                                       |