

## HPP V4 Power plug 250V/16A 3p



Image is for illustration purposes only. Please refer to product description.

Part number	09 46 145 3420
Specification	HPP V4 Power plug 250V/16A 3p
HARTING eCatalogue	<a href="https://harting.com/09461453420">https://harting.com/09461453420</a>

### Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	Power
Element	Connector sets

### Version

Termination method	Crimp termination
Shielding	Unshielded
Number of contacts	2
PE contact	Yes
Locking type	PushPull
Pack contents	with 3 turned male contacts, insulation body, hood and cable gland

### Technical characteristics

Conductor cross-section	1.5 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 16 ... AWG 14
Wire outer diameter	≤3.7 mm
Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Tightening torque	1.3 ... 1.5 Nm
Limiting temperature	-40 ... +70 °C

## Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	4.5 ... 10 mm
Vibration resistance	10-500 Hz, 5 g, 0.35 mm, 2h/axis 5.72 m/s <sup>2</sup> acc. to IEC 61373 Category 1 Class B
Shock resistance	25 g / 11 ms, 3 shocks / axis and direction 5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

## Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4) EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL

## Commercial data

Packaging size	1
----------------	---

## Commercial data

Net weight	10 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140223691
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408